


# FLAMAR STANDARD CABLES > FOR INDUSTRIAL AUTOMATION





# Find the Latest Innovations and Information **at molex.com**

For the most in-depth and up-to-date information on all our products, visit [molex.com](http://molex.com). It's designed to help you get more done in less time with advanced search capabilities, 3D models, product specifications, easy sample ordering and more.



## **Mobile App for Anytime, Anywhere Access to Molex Connector Solutions.**

The Molex App gives apple and android tablet and smartphone users ready-access to information on over 90 different Molex product families. Users can visually compare product ranges, access product information and view datasheets offline. App users with an internet connection can directly link to [Molex.com](http://Molex.com) for more detailed part number information and product videos. Download the free app now at the App Store and GooglePlay.



## TABLE OF CONTENTS

About Flamar .....	4
<b>Product Families</b>	
<b>Signal &amp; Control (Sensor, Actuator, Distribution Boxes) .....</b>	<b>6</b>
PVC Jacket .....	8
WSOR Jacket .....	20
PUR Jacket .....	32
TPE Jacket .....	44
<b>Servo Motor (Power, Feedback) .....</b>	<b>54</b>
PVC Jacket .....	56
WSOR Jacket .....	58
PUR Jacket .....	60
<b>Network (CC-Link, PROFIBUS, PROFINET, Ethernet) .....</b>	<b>62</b>
PVC Jacket .....	64
WSOR Jacket .....	68
PUR Jacket .....	72
<b>Hybrid .....</b>	<b>76</b>
<b>Packaging .....</b>	<b>81</b>
<b>Useful documentation and resources available .....</b>	<b>82</b>
<b>Connector Series Index .....</b>	<b>83</b>

### Certifications / Conformities



### Legend



Oil Resistant



Suitable for Drag Chain



Halogen-Free



Flame Resistant

The background of the header section is a photograph of an industrial factory floor. It features several large, yellow robotic arms (likely KUKA) in various positions, surrounded by complex machinery, pipes, and structural elements of the facility. The lighting is bright, highlighting the metallic surfaces and the vibrant yellow of the robots.

**OUR PROVEN EXPERIENCE IN  
CABLE MANUFACTURING  ASSURES EXCELLENT PERFORMANCE,  
QUALITY AND DURABILITY IN THE  
INDUSTRIAL SECTOR**

**Flamar was founded in 1975 and over the years has developed a significant know-how in the design and manufacturing of cables for Industrial Automation.**

**The company is equipped with state-of-the-art extrusion lines and back-torsion cabling machines which are essential to meet top quality expectations of key market players. The internal Reliability & Testing Laboratory performs mechanical, electrical, flame resistance, drag chain tests and validates new cable developments in compliance with many agency approvals.**



## Industrial Automation cables for machine builder application

Flamar, a Molex company since 2014, proposes a brand-new set of cables designed to cover the broadest range of applications for machine builders and system integrators:

- **Signal & Control**  
to connect sensors, actuators, valves, control cabinets and distribution boxes
- **Servo Motor**  
for power and encoder/resolver connection
- **Network**  
for I/O modules and connection to PLC
- **Hybrid**  
composite multicore cables whenever an extremely compact solution is required



## Signal & Control

Series	Environment	Installation	Halogen Free	Temperature Rating °C (flexible installation)		Voltage Rating V	Bending Radius (flex. install. at 20°C)
155210	Standard	Flexible	No	+5°C	+80°C	300V	> 15xOD
155211	Standard	Flexible	No	+5°C	+80°C	300V	> 15xOD
155220	Severe	Drag Chain	No	-25°C	+80°C	600V	> 7,5xOD
155221	Severe	Drag Chain	No	-25°C	+80°C	600V	> 7,5xOD
155230	Harsh	Drag Chain	Yes	-40°C	+80°C	1000V	> 7,5xOD
155231	Harsh	Drag Chain	Yes	-40°C	+80°C	1000V	> 7,5xOD
155240	Severe	Drag Chain	No	-40°C	+105°C	300V	> 10xOD
155241	Severe	Drag Chain	No	-40°C	+105°C	300V	> 10xOD

## Typical Applications



Sensors



Actuators, valves,  
control cabinets



Distribution Boxes

## Jacket choice criteria

- PVC: The most cost-effective solution for flexible and static installation.
- WSOR: Weld-Slag and Oil-Resistant Cable, a single-cable solution designed to withstand the severe environments found in automotive and industrial factory floors. ECOLAB compatible (resistant to detergents, disinfectants and wash down water-jet used in Food & Beverage). Suitable for drag chain applications.
- PUR (Polyurethane): Ensures top mechanical performance, withstands harsh environments, abrasion resistant. Suitable for drag chain applications
- TPE: Cables defined according to the US/Canadian market requirements (UL «PLTC»). ECOLAB compatible (resistant to detergents, disinfectants and wash down water-jet used in Food & Beverage). Suitable for drag chain applications.



# Flamar Cables for Signal & Control Applications

Jacket Material	Shielded	Approval	Flame Resistance	Oil & Lubricants Resistance	Abrasion Resistance	Page No.
PVC	No	UL AWM 2464 / CSA	Good	Limited	Limited	8
PVC	Yes	UL AWM 2464 / CSA	Good	Limited	Limited	18
WSOR	No	UL AWM 21215 / CSA	Good	Good	Medium	20
WSOR	Yes	UL AWM 21215 / CSA	Good	Good	Medium	30
PUR	No	UL AWM 21223 / CSA	Good	Excellent	Excellent	32
PUR	Yes	UL AWM 21223 / CSA	Good	Excellent	Excellent	42
TPE	No	UL Listed PLTC	Excellent	Good	Medium	44
TPE	Yes	UL Listed PLTC	Excellent	Good	Medium	52

**Selecting the right cable for your application is very important to ensure a reliable, problem-free installation. Careful consideration of mechanical abrasion, fluid/chemical exposure, flexibility (C-track, torsion), temperature resistance and flame retardancy requirements is required to select the cable that will provide performance and reliability in service.**



# Flamar Signal & Control

## 155210 Sensor Cables, PVC Jacket

Flexible Installation, Unshielded, +5°C/+80°C, 300V

**molex**

Cables with PVC jacket, suitable for flexible installation in standard environments. Typically used for sensors (position, pressure, temperature, motion...) and optical switches in combination with M8 and M12 connectors.



### Specifications

Application: Standard Environment  
 Installation: Flexible  
 Halogen Free: No  
 Temp. rating (flexible installation):  
 +5°C/+80°C  
 Voltage rating: 300V  
 Bending radius (flex. install. at 20°C):  
 > 15xOD  
 Insulation material: TPE  
 Jacket material: PVC

Shielded: No  
 Approval: UL AWM 2464 / CSA  
 Marking: acc. to UL/CSA  
 Silicone, Pb,Cd,Hg & FCKW free: Yes  
 Flame resistance:  
 Good (VW1/FT1 & IEC60332-1)  
 Key factor:  
 Cost-effective solution for less demanding environments (limited exposure to oil and lubricants)

Cross Section		No. of Circuits	Diameter in mm	Jacket Color	Packaging Size	Packaging Composition	Standard Order No	Sketch
mm <sup>2</sup>	AWG							
0,25	24	3	4,5	Black	S	3x200m	155210-0001	
					M	1x800m	155210-0002	
					L	1x1500m	155210-0003	
				Grey	S	3x200m	155210-0004	
					M	1x800m	155210-0005	
					L	1x1500m	155210-0006	
				Yellow	S	3x200m	155210-0007	
					M	1x800m	155210-0008	
					L	1x1500m	155210-0009	
				Orange	S	3x200m	155210-0010	
					M	1x800m	155210-0011	
					L	1x1500m	155210-0012	
		4	4,8	Black	S	3x200m	155210-0013	
					M	1x800m	155210-0014	
					L	1x1500m	155210-0015	
				Grey	S	3x200m	155210-0016	
					M	1x800m	155210-0017	
					L	1x1500m	155210-0018	
				Yellow	S	3x200m	155210-0019	
					M	1x800m	155210-0020	
					L	1x1500m	155210-0021	
				Orange	S	3x200m	155210-0022	
					M	1x800m	155210-0023	
					L	1x1500m	155210-0024	
5	5,3	Black	S	3x200m	155210-0025			
			M	1x800m	155210-0026			
			L	1x1500m	155210-0027			
		Grey	S	3x200m	155210-0028			
			M	1x800m	155210-0029			
			L	1x1500m	155210-0030			
		Yellow	S	3x200m	155210-0031			
			M	1x800m	155210-0032			
			L	1x1500m	155210-0033			

# Flamar Signal & Control

## 155210 Sensor Cables, PVC Jacket

Flexible Installation, Unshielded, +5°C/+80°C, 300V

**molex**



Cross Section		No. of Circuits	Diameter in mm	Jacket Color	Packaging Size	Packaging Composition	Standard Order No	Sketch
mm <sup>2</sup>	AWG							
0,25	24	8	6,4	Black	S	3x100m	155210-0034	
					M	1x500m	155210-0035	
					L	1x1000m	155210-0036	
				Grey	S	3x100m	155210-0037	
					M	1x500m	155210-0038	
					L	1x1000m	155210-0039	
		Yellow	S	3x100m	155210-0040			
			M	1x500m	155210-0041			
			L	1x1000m	155210-0042			
		12	6,9	Black	S	3x100m	155210-0043	
					M	1x500m	155210-0044	
					L	1x1000m	155210-0045	
	Grey			S	3x100m	155210-0046		
				M	1x500m	155210-0047		
				L	1x1000m	155210-0048		
	Yellow	S	3x100m	155210-0049				
		M	1x500m	155210-0050				
		L	1x1000m	155210-0051				
0,34	22	3	4,8	Black	S	3x200m	155210-0052	
					M	1x800m	155210-0053	
					L	1x1500m	155210-0054	
				Grey	S	3x200m	155210-0055	
					M	1x800m	155210-0056	
					L	1x1500m	155210-0057	
		Yellow	S	3x200m	155210-0058			
			M	1x800m	155210-0059			
			L	1x1500m	155210-0060			
		Orange	S	3x200m	155210-0061			
			M	1x800m	155210-0062			
			L	1x1500m	155210-0063			
	4	5,1	Black	S	3x200m	155210-0064		
				M	1x800m	155210-0065		
				L	1x1500m	155210-0066		
			Grey	S	3x200m	155210-0067		
				M	1x800m	155210-0068		
				L	1x1500m	155210-0069		
			Yellow	S	3x200m	155210-0070		
				M	1x800m	155210-0071		
				L	1x1500m	155210-0072		
			Orange	S	3x200m	155210-0073		
				M	1x800m	155210-0074		
				L	1x1500m	155210-0075		

# Flamar Signal & Control

## 155210 Sensor Cables, PVC Jacket

Flexible Installation, Unshielded, +5°C/+80°C, 300V

**molex**



Cross Section		No. of Circuits	Diameter in mm	Jacket Color	Packaging Size	Packaging Composition	Standard Order No	Sketch		
mm <sup>2</sup>	AWG									
0,34	22	5	5,5	Black	S	3x200m	155210-0076			
					M	1x800m	155210-0077			
					L	1x1500m	155210-0078			
				Grey	S	3x200m	155210-0079			
					M	1x800m	155210-0080			
					L	1x1500m	155210-0081			
				Yellow	S	3x200m	155210-0082			
					M	1x800m	155210-0083			
					L	1x1500m	155210-0084			
				Orange	S	3x200m	155210-0085			
					M	1x800m	155210-0086			
					L	1x1500m	155210-0087			
		5	5,5	5	5,5	Black	S	3x200m	155210-0088	
							M	1x800m	155210-0089	
							L	1x1500m	155210-0090	
						Grey	S	3x200m	155210-0091	
							M	1x800m	155210-0092	
							L	1x1500m	155210-0093	
						Yellow	S	3x200m	155210-0094	
							M	1x800m	155210-0095	
Orange	S	3x200m	155210-0097							
	M	1x800m	155210-0098							
	L	1x1500m	155210-0099							

### Related Products

#### Field Attachable Connectors



**120091** – Brad Nano-Change (M8)  
Field Attachable Connectors



**120071** – Brad Micro-Change (M12)  
Field Attachable Connector



**120085** – Brad Ultra-Lock (M12)  
Field Attachable Connectors

#### Overmolded Connectors



**120027, 120028, 120086, 120087** –  
Brad Nano-Change (M8)  
Single-Ended and Double Ended Cordsets



**120006** – Brad Micro-Change (M12)  
Single-Ended Cordsets

**120009** – Brad Micro-Change (M12)  
Cordsets with Knurled Hexnuts



**120065, 120066** – Brad Micro-Push (M12)  
Single-Ended and Double Ended Cordsets

# Flamar Signal & Control

## 155210 Control Cables, PVC Jacket

Flexible Installation, Unshielded, +5°C/+80°C, 300V

**molex**

Cables with PVC jacket, suitable for flexible installation in standard environments. The right choice for actuators (valves, slides, cylinders...) and control cabinets in combination with DIN, M16, M23 or heavy duty connectors.



### Specifications

Application: Standard environment  
 Installation: Flexible  
 Halogen Free: No  
 Temp. rating (flexible installation):  
 +5°C/+80°C  
 Voltage rating: 300V  
 Bending radius (flex. install. at 20°C):  
 > 15xOD  
 Insulation material: TPE  
 Jacket material: PVC

Shielded: No  
 Approval: UL AWM 2464 / CSA  
 Marking: acc. to UL/CSA  
 Silicone, Pb,Cd,Hg & FCKW free: Yes  
 Flame resistance:  
 Good (VW1/FT1 & IEC60332-1)  
 Key factor:  
 Cost-effective solution for less demanding environments (limited exposure to oil and lubricants)

Cross Section		No. of Circuits	Diameter in mm	Jacket Color	Packaging	Packaging Composition	Standard Order No	Sketch
mm <sup>2</sup>	AWG							
0,5	21	2	5,2	Black	S	3x200m	155210-0100	
					M	1x800m	155210-0101	
					L	1x1500m	155210-0102	
				Grey	S	3x200m	155210-0103	
					M	1x800m	155210-0104	
					L	1x1500m	155210-0105	
		3	5,6	Black	S	3x100m	155210-0106	
					M	1x500m	155210-0107	
					L	1x1000m	155210-0108	
				Grey	S	3x100m	155210-0109	
					M	1x500m	155210-0110	
					L	1x1000m	155210-0111	
		4	5,9	Orange	S	3x100m	155210-0112	
					M	1x500m	155210-0113	
					L	1x1000m	155210-0114	
				Black	S	3x100m	155210-0115	
					M	1x500m	155210-0116	
					L	1x1000m	155210-0117	
		5	6,2	Grey	S	3x100m	155210-0118	
					M	1x500m	155210-0119	
					L	1x1000m	155210-0120	
				Black	S	3x100m	155210-0121	
					M	1x500m	155210-0122	
					L	1x1000m	155210-0123	
12	8,7	Grey	S	3x100m	155210-0124			
			M	1x500m	155210-0125			
			L	1x1000m	155210-0126			
		Black	S	1x200m	155210-0127			
			M	1x500m	155210-0128			
			L	1x1000m	155210-0129			
Grey	S	1x200m	155210-0130					
	M	1x500m	155210-0131					
	L	1x1000m	155210-0132					

# Flamar Signal & Control

## 155210 Control Cables, PVC Jacket

Flexible Installation, Unshielded, +5°C/+80°C, 300V

**molex**



Cross Section		No. of Circuits	Diameter in mm	Jacket Color	Packaging	Packaging Composition	Standard Order No	Sketch
mm <sup>2</sup>	AWG							
0,75	19	2	6,0	Black	S	3x100m	155210-0133	
					M	1x500m	155210-0134	
					L	1x1000m	155210-0135	
				Grey	S	3x100m	155210-0136	
					M	1x500m	155210-0137	
					L	1x1000m	155210-0138	
		3	6,4	Black	S	3x100m	155210-0139	
					M	1x500m	155210-0140	
					L	1x1000m	155210-0141	
				Grey	S	3x100m	155210-0142	
					M	1x500m	155210-0143	
					L	1x1000m	155210-0144	
		4	7,0	Black	S	3x100m	155210-0145	
					M	1x500m	155210-0146	
					L	1x1000m	155210-0147	
				Grey	S	3x100m	155210-0148	
					M	1x500m	155210-0149	
					L	1x1000m	155210-0150	
		5	7,5	Black	S	3x100m	155210-0151	
					M	1x500m	155210-0152	
					L	1x1000m	155210-0153	
				Grey	S	3x100m	155210-0154	
					M	1x500m	155210-0155	
					L	1x1000m	155210-0156	
1,00	18	2	6,7	Black	S	3x100m	155210-0157	
					M	1x500m	155210-0158	
					L	1x1000m	155210-0159	
				Grey	S	3x100m	155210-0160	
					M	1x500m	155210-0161	
					L	1x1000m	155210-0162	
		3	7,1	Black	S	3x100m	155210-0163	
					M	1x500m	155210-0164	
					L	1x1000m	155210-0165	
				Grey	S	3x100m	155210-0166	
					M	1x500m	155210-0167	
					L	1x1000m	155210-0168	
		4	7,6	Black	S	3x100m	155210-0169	
					M	1x500m	155210-0170	
					L	1x1000m	155210-0171	
				Grey	S	3x100m	155210-0172	
					M	1x500m	155210-0173	
					L	1x1000m	155210-0174	

# Flamar Signal & Control

## 155210 Control Cables, PVC Jacket

Flexible Installation, Unshielded, +5°C/+80°C, 300V

**molex**



Cross Section		No. of Circuits	Diameter in mm	Jacket Color	Packaging	Packaging Composition	Standard Order No	Sketch
mm <sup>2</sup>	AWG							
1,0	18	5	8,3	Black	S	1x200m	155210-0175	
					M	1x500m	155210-0176	
					L	1x1000m	155210-0177	
				Grey	S	1x200m	155210-0178	
					M	1x500m	155210-0179	
					L	1x1000m	155210-0180	
		7	9,6	Black	S	1x200m	155210-0181	
					M	1x500m	155210-0182	
					L	1x1000m	155210-0183	
				Grey	S	1x200m	155210-0184	
					M	1x500m	155210-0185	
					L	1x1000m	155210-0186	
		11	11,5	Black	S	1x100m	155210-0187	
					M	1x500m	155210-0188	
					L	1x1000m	155210-0189	
				Grey	S	1x100m	155210-0190	
					M	1x500m	155210-0191	
					L	1x1000m	155210-0192	
		12	11,5	Black	S	1x100m	155210-0193	
					M	1x500m	155210-0194	
					L	1x1000m	155210-0195	
				Grey	S	1x100m	155210-0196	
					M	1x500m	155210-0197	
					L	1x1000m	155210-0198	
17	13,4	Black	S	1x100m	155210-0199			
			M	1x500m	155210-0200			
			L	1x1000m	155210-0201			
		Grey	S	1x100m	155210-0202			
			M	1x500m	155210-0203			
			L	1x1000m	155210-0204			
25	16,0	Black	S	1x100m	155210-0205			
			M	1x250m	155210-0206			
			L	1x500m	155210-0207			
		Grey	S	1x100m	155210-0208			
			M	1x250m	155210-0209			
			L	1x500m	155210-0210			

# Flamar Signal & Control

## 155210 Control Cables, PVC Jacket

Flexible Installation, Unshielded, +5°C/+80°C, 300V

**molex**



Cross Section		No. of Circuits	Diameter in mm	Jacket Color	Packaging	Packaging Composition	Standard Order No	Sketch
mm <sup>2</sup>	AWG							
1,5	16	2	7,1	Black	S	3x100m	155210-0211	
					M	1x500m	155210-0212	
					L	1x1000m	155210-0213	
				Grey	S	3x100m	155210-0214	
					M	1x500m	155210-0215	
					L	1x1000m	155210-0216	
		3	7,3	Black	S	3x100m	155210-0217	
					M	1x500m	155210-0218	
					L	1x1000m	155210-0219	
				Grey	S	3x100m	155210-0220	
					M	1x500m	155210-0221	
					L	1x1000m	155210-0222	
		4	7,9	Black	S	3x100m	155210-0223	
					M	1x500m	155210-0224	
					L	1x1000m	155210-0225	
				Grey	S	3x100m	155210-0226	
					M	1x500m	155210-0227	
					L	1x1000m	155210-0228	
		4	7,9	Black	S	3x100m	155210-0229	
					M	1x500m	155210-0230	
					L	1x1000m	155210-0231	
				Grey	S	3x100m	155210-0232	
					M	1x500m	155210-0233	
					L	1x1000m	155210-0234	
5	8,6	Black	S	1x200m	155210-0235			
			M	1x500m	155210-0236			
			L	1x1000m	155210-0237			
		Grey	S	1x200m	155210-0238			
			M	1x500m	155210-0239			
			L	1x1000m	155210-0240			
7	10,5	Black	S	1x100m	155210-0241			
			M	1x500m	155210-0242			
			L	1x1000m	155210-0243			
		Grey	S	1x100m	155210-0244			
			M	1x500m	155210-0245			
			L	1x1000m	155210-0246			
11	12,7	Black	S	1x100m	155210-0247			
			M	1x500m	155210-0248			
			L	1x1000m	155210-0249			
		Grey	S	1x100m	155210-0250			
			M	1x500m	155210-0251			
			L	1x1000m	155210-0252			
12	12,7	Black	S	1x100m	155210-0253			
			M	1x500m	155210-0254			
			L	1x1000m	155210-0255			
		Grey	S	1x100m	155210-0256			
			M	1x500m	155210-0257			
			L	1x1000m	155210-0258			

# Flamar Signal & Control

## 155210 Control Cables, PVC Jacket

Flexible Installation, Unshielded, +5°C/+80°C, 300V

**molex**



Cross Section		No. of Circuits	Diameter in mm	Jacket Color	Packaging	Packaging Composition	Standard Order No	Sketch
mm <sup>2</sup>	AWG							
1,5	16	17	14,7	Black	S	1x100m	155210-0259	
					M	1x500m	155210-0260	
					L	1x1000m	155210-0261	
				Grey	S	1x100m	155210-0262	
					M	1x500m	155210-0263	
					L	1x1000m	155210-0264	
	25	17,7	Black	S	1x100m	155210-0265		
				M	1x250m	155210-0266		
				L	1x500m	155210-0267		
			Grey	S	1x100m	155210-0268		
				M	1x250m	155210-0269		
				L	1x500m	155210-0270		
2,5	14	2	8,8	Black	S	1x200m	155210-0271	
					M	1x500m	155210-0272	
					L	1x1000m	155210-0273	
				Grey	S	1x200m	155210-0274	
					M	1x500m	155210-0275	
					L	1x1000m	155210-0276	
	3	9,3	Black	S	1x200m	155210-0277		
				M	1x500m	155210-0278		
				L	1x1000m	155210-0279		
			Grey	S	1x200m	155210-0280		
				M	1x500m	155210-0281		
				L	1x1000m	155210-0282		
	4	10,1	Black	S	1x100m	155210-0283		
				M	1x500m	155210-0284		
				L	1x1000m	155210-0285		
			Grey	S	1x100m	155210-0286		
				M	1x500m	155210-0287		
				L	1x1000m	155210-0288		
	5	11,3	Black	S	1x100m	155210-0289		
				M	1x500m	155210-0290		
				L	1x1000m	155210-0291		
			Grey	S	1x100m	155210-0292		
				M	1x500m	155210-0293		
				L	1x1000m	155210-0294		

# Flamar Signal & Control

## 155210 Control Cables, PVC Jacket

Flexible Installation, Unshielded, +5°C/+80°C, 300V

**molex**



Cross Section		No. of Circuits	Diameter in mm	Jacket Color	Packaging	Packaging Composition	Standard Order No	Sketch
mm <sup>2</sup>	AWG							
2,5	14	7	13,3	Black	S	1x100m	155210-0295	
					M	1x500m	155210-0296	
					L	1x1000m	155210-0297	
				Grey	S	1x100m	155210-0298	
					M	1x500m	155210-0299	
					L	1x1000m	155210-0300	
		11	15,7	Black	S	1x100m	155210-0301	
					M	1x250m	155210-0302	
					L	1x500m	155210-0303	
				Grey	S	1x100m	155210-0304	
					M	1x250m	155210-0305	
					L	1x500m	155210-0306	
		12	15,9	Black	S	1x100m	155210-0307	
					M	1x250m	155210-0308	
					L	1x500m	155210-0309	
				Grey	S	1x100m	155210-0310	
					M	1x250m	155210-0311	
					L	1x500m	155210-0312	
		17	18,5	Black	S	1x100m	155210-0313	
					M	1x250m	155210-0314	
L	1x500m				155210-0315			
Grey	S			1x100m	155210-0316			
	M			1x250m	155210-0317			
	L			1x500m	155210-0318			
25	22,3	Black	S	1x350m	155210-0319			
			Grey	S	1x350m		155210-0322	

### Related Products

#### Field Attachable Connectors



**121201, 121207** – Brad mPm DIN Valve Connectors, Form A, External Thread

**121202, 121208** – Brad mPm DIN Valve Connector, Form B - Industrial, External Thread

**121205, 121211** – Brad mPm DIN Valve Connector, Form C - Industrial, External Thread



**120071** – Brad Micro-Change (M12) Field Attachable Connectors

#### Field Attachable Connectors



**120085** – Brad Ultra-Lock (M12) Field Attachable Connectors

**93601** - GWconnect Heavy Duty Connectors

#### Overmolded Connectors



**120094** – Brad M23 Single-Ended Cordsets

# Flamar Signal & Control

## 155210 Distribution Boxes, PVC Jacket

Flexible Installation, Unshielded, +5°C/+80°C, 300V

**molex**

Cables with PVC jacket, suitable for flexible installation in standard environments. Select this cable for distribution boxes ("MPIS") and safety barriers in combination with M23 signal connectors.



### Specifications


Application: Standard environment  
 Installation: Flexible  
 Halogen Free: No  
 Temp. rating (flexible installation): +5°C/+80°C  
 Voltage rating: 300V  
 Bending radius (flex. install. at 20°C): > 15xOD  
 Insulation material: TPE  
 Jacket material: PVC

Shielded: No  
 Approval: UL AWM 2464 / CSA  
 Marking: acc. to UL/CSA  
 Silicone, Pb,Cd,Hg & FCKW free: Yes  
 Flame resistance: Good (VW1/FT1 & IEC60332-1)  
 Key factor: Cost-effective solution for less demanding environments (limited exposure to oil and lubricants)

Cross Section		No. of Circuits	Diameter in mm	Jacket Color	Packaging	Packaging Composition	Standard Order No	Sketch
mm <sup>2</sup>	AWG							
3x0,75 + 4x0,34	3x AWG 19 + 4x AWG 22	7 (3+4)	7,8	Black	S	3x100m	155210-9001	
					M	1x500m	155210-9002	
					L	1x1000m	155210-9003	
				Grey	S	3x100m	155210-9004	
					M	1x500m	155210-9005	
					L	1x1000m	155210-9006	
3x0,75 + 6x0,34	3x AWG 19 + 6x AWG 22	9 (3+6)	8,5	Black	S	1x200m	155210-9007	
					M	1x500m	155210-9008	
					L	1x1000m	155210-9009	
				Grey	S	1x200m	155210-9010	
					M	1x500m	155210-9011	
					L	1x1000m	155210-9012	
3x0,75 + 8x0,34	3x AWG 19 + 8x AWG 22	11 (3+8)	8,5	Black	S	1x200m	155210-9013	
					M	1x500m	155210-9014	
					L	1x1000m	155210-9015	
				Grey	S	1x200m	155210-9016	
					M	1x500m	155210-9017	
					L	1x1000m	155210-9018	
3x0,75 + 16x0,34	3x AWG 19 + 16x AWG 22	19 (3+16)	10,2	Black	S	1x100m	155210-9019	
					M	1x500m	155210-9020	
					L	1x1000m	155210-9021	
				Grey	S	1x100m	155210-9022	
					M	1x500m	155210-9023	
					L	1x1000m	155210-9024	


### Related Products

**Field Attachable Connectors**



**120230** – Brad M23 Signal Connectors  
**120233** – Brad M23 Power Connectors

**Overmolded Connectors**



**120094** – Brad M23 Single-Ended Cordsets

# Flamar Signal & Control

## 155211 Sensor Cables, PVC Jacket

Flexible Installation, Shielded, +5°C/+80°C, 300V

**molex**

Cables with PVC jacket, suitable for flexible installation in standard environments. Shielded cable for sensors (position, pressure, temperature, motion...) and optical switches in combination with M8 and M12 connectors.



### Specifications

Application: Standard environment  
 Installation: Flexible  
 Halogen Free: No  
 Temp. rating (flexible installation):  
 +5°C/+80°C  
 Voltage rating: 300V  
 Bending radius (flex. install. at 20°C):  
 > 15xOD  
 Insulation material: TPE  
 Jacket material: PVC

Shielded: Yes  
 Approval: UL AWM 2464 / CSA  
 Marking: acc. to UL/CSA  
 Silicone, Pb,Cd,Hg & FCKW free: Yes  
 Flame resistance:  
 Good (VW1/FT1 & IEC60332-1)  
 Key factor:  
 Cost-effective solution for less demanding environments (limited exposure to oil and lubricants)

Cross Section		No. of Circuits	Diameter in mm	Jacket Color	Packaging	Packaging Composition	Standard Order No	Sketch
mm <sup>2</sup>	AWG							
0,34	22	3	5,4	Black	S	3x200m	155211-0001	
					M	1x800m	155211-0002	
					L	1x1500m	155211-0003	
				Grey	S	3x200m	155211-0004	
					M	1x800m	155211-0005	
					L	1x1500m	155211-0006	
				Yellow	S	3x200m	155211-0007	
					M	1x800m	155211-0008	
					L	1x1500m	155211-0009	
				Orange	S	3x200m	155211-0010	
					M	1x800m	155211-0011	
					L	1x1500m	155211-0012	
0,34	22	4	5,7	Black	S	3x100m	155211-0013	
					M	1x500m	155211-0014	
					L	1x1000m	155211-0015	
				Grey	S	3x100m	155211-0016	
					M	1x500m	155211-0017	
					L	1x1000m	155211-0018	
				Yellow	S	3x100m	155211-0019	
					M	1x500m	155211-0020	
					L	1x1000m	155211-0021	
				Orange	S	3x100m	155211-0022	
					M	1x500m	155211-0023	
					L	1x1000m	155211-0024	
0,34	22	5	6,1	Black	S	3x100m	155211-0025	
					M	1x500m	155211-0026	
					L	1x1000m	155211-0027	
				Grey	S	3x100m	155211-0028	
					M	1x500m	155211-0029	
					L	1x1000m	155211-0030	
				Yellow	S	3x100m	155211-0031	
					M	1x500m	155211-0032	
					L	1x1000m	155211-0033	
				Orange	S	3x100m	155211-0034	
					M	1x500m	155211-0035	
					L	1x1000m	155211-0036	

# Flamar Signal & Control

## 155211 Sensor Cables, PVC Jacket

Flexible Installation, Shielded, +5°C/+80°C, 300V

**molex**



Cross Section		No. of Circuits	Diameter in mm	Jacket Color	Packaging	Packaging Composition	Standard Order No	Sketch
mm <sup>2</sup>	AWG							
0,34	22	5	6,1	Black	S	3x100m	155211-0037	
					M	1x500m	155211-0038	
					L	1x1000m	155211-0039	
				Grey	S	3x100m	155211-0040	
					M	1x500m	155211-0041	
					L	1x1000m	155211-0042	
				Yellow	S	3x100m	155211-0043	
					M	1x500m	155211-0044	
					L	1x1000m	155211-0045	
				Orange	S	3x100m	155211-0046	
					M	1x500m	155211-0047	
					L	1x1000m	155211-0048	

### Related Products

#### Field Attachable Connectors

- 120091** – Brad Nano-Change (M8) Field Attachable Connectors
- 120071** – Brad Micro-Change (M12) Field Attachable Connectors
- 120085** – Brad Ultra-Lock (M12) Field Attachable Connectors

#### Overmolded Connectors

- 120027, 120028, 120086, 120087** – Brad Nano-Change (M8) Single-Ended and Double Ended Cordsets
- 120006, 120009** – Brad Micro-Change (M12) Single-Ended and Double Ended Cordsets
- 120065, 120066** – Brad Micro-Push (M12) Single-Ended and Double Ended Cordsets

# Flamar Signal & Control

## 155220 Sensor Cables, WSOR Jacket

Drag Chain Installation, Unshielded, -25°C/+80°C, 600V

**molex**

Cables with Weld-Slag and Oil-Resistant "WSOR" jacket cover the broadest range of industrial applications, allowing the reduction of inventory costs. Suitable for drag chain applications. Typically used for sensors (position, pressure, temperature, motion...) and optical switches in combination with M8 and M12 connectors.



### Specifications

Application: Severe environment  
 Installation: Drag Chain  
 Halogen Free: No  
 Temp. rating (flexible installation):  
 -25°C/+80°C  
 Voltage rating: 600V  
 Bending radius (flex. install. at 20°C):  
 > 7,5xOD  
 Insulation material: TPE  
 Jacket material: WSOR  
 Shielded: No

Approval: UL AWM 21215 / CSA  
 Marking: acc. to UL/CSA  
 Silicone, Pb,Cd,Hg & FCKW free: Yes  
 Flame resistance:  
 Good (VW1/FT1 & IEC60332-1)  
 Key factor:  
 Weld-Slag and Oil-Resistant. A single cable solution for automotive lines and industrial applications. ECOLAB compatible (for Food & Beverage environments).

Cross Section		No. of Circuits	Diameter in mm	Jacket Color	Packaging	Packaging Composition	Standard Order No	Sketch
mm²	AWG							
0,25	24	3	4,5	Black	S	3x200m	155220-0001	
					M	1x800m	155220-0002	
					L	1x1500m	155220-0003	
				Grey	S	3x200m	155220-0004	
					M	1x800m	155220-0005	
					L	1x1500m	155220-0006	
		Yellow	S	3x200m	155220-0007			
			M	1x800m	155220-0008			
			L	1x1500m	155220-0009			
			Orange	S	3x200m	155220-0010		
				M	1x800m	155220-0011		
				L	1x1500m	155220-0012		
	4	4,8	Black	S	3x200m	155220-0013		
				M	1x800m	155220-0014		
				L	1x1500m	155220-0015		
			Grey	S	3x200m	155220-0016		
				M	1x800m	155220-0017		
				L	1x1500m	155220-0018		
		Yellow	S	3x200m	155220-0019			
			M	1x800m	155220-0020			
			L	1x1500m	155220-0021			
		Orange	S	3x200m	155220-0022			
			M	1x800m	155220-0023			
			L	1x1500m	155220-0024			
Black	S		3x200m	155220-0025				
	M		1x800m	155220-0026				
	L		1x1500m	155220-0027				
Grey	S	3x200m	155220-0028					
	M	1x800m	155220-0029					
	L	1x1500m	155220-0030					
Yellow	S	3x200m	155220-0031					
	M	1x800m	155220-0032					
	L	1x1500m	155220-0033					

# Flamar Signal & Control

## 155220 Sensor Cables, WSOR Jacket

Drag Chain Installation, Unshielded, -25°C/+80°C, 600V

**molex**



Cross Section		No. of Circuits	Diameter in mm	Jacket Color	Packaging	Packaging Composition	Standard Order No	Sketch
mm <sup>2</sup>	AWG							
0,25	24	8	6,4	Black	S	3x100m	155220-0034	
					M	1x500m	155220-0035	
					L	1x1000m	155220-0036	
				Grey	S	3x100m	155220-0037	
					M	1x500m	155220-0038	
					L	1x1000m	155220-0039	
				Yellow	S	3x100m	155220-0040	
					M	1x500m	155220-0041	
					L	1x1000m	155220-0042	
		12	6,9	Black	S	3x100m	155220-0043	
					M	1x500m	155220-0044	
					L	1x1000m	155220-0045	
				Grey	S	3x100m	155220-0046	
					M	1x500m	155220-0047	
					L	1x1000m	155220-0048	
				Yellow	S	3x100m	155220-0049	
					M	1x500m	155220-0050	
					L	1x1000m	155220-0051	
0,34	22	3	4,8	Black	S	3x200m	155220-0052	
					M	1x800m	155220-0053	
					L	1x1500m	155220-0054	
				Grey	S	3x200m	155220-0055	
					M	1x800m	155220-0056	
					L	1x1500m	155220-0057	
				Yellow	S	3x200m	155220-0058	
					M	1x800m	155220-0059	
					L	1x1500m	155220-0060	
		Orange	S	3x200m	155220-0061			
			M	1x800m	155220-0062			
			L	1x1500m	155220-0063			
		4	5,1	Black	S	3x200m	155220-0064	
					M	1x800m	155220-0065	
					L	1x1500m	155220-0066	
				Grey	S	3x200m	155220-0067	
					M	1x800m	155220-0068	
					L	1x1500m	155220-0069	
Yellow	S			3x200m	155220-0070			
	M			1x800m	155220-0071			
	L			1x1500m	155220-0072			
Orange	S	3x200m	155220-0073					
	M	1x800m	155220-0074					
	L	1x1500m	155220-0075					

# Flamar Signal & Control

## 155220 Sensor Cables, WSOR Jacket

Drag Chain Installation, Unshielded, -25°C/+80°C, 600V

**molex**



Cross Section		No. of Circuits	Diameter in mm	Jacket Color	Packaging	Packaging Composition	Standard Order No	Sketch	
mm <sup>2</sup>	AWG								
0,34	22	5	5,5	Black	S	3x200m	155220-0076		
					M	1x800m	155220-0077		
					L	1x1500m	155220-0078		
				Grey	S	3x200m	155220-0079		
					M	1x800m	155220-0080		
					L	1x1500m	155220-0081		
				Yellow	S	3x200m	155220-0082		
					M	1x800m	155220-0083		
					L	1x1500m	155220-0084		
				Orange	S	3x200m	155220-0085		
					M	1x800m	155220-0086		
					L	1x1500m	155220-0087		
				Black	S	3x200m	155220-0088		
					M	1x800m	155220-0089		
					L	1x1500m	155220-0090		
					Grey	S	3x200m		155220-0091
						M	1x800m		155220-0092
						L	1x1500m		155220-0093
					Yellow	S	3x200m		155220-0094
						M	1x800m		155220-0095
						L	1x1500m		155220-0096
				Orange	S	3x200m	155220-0097		
					M	1x800m	155220-0098		
					L	1x1500m	155220-0099		

### Related Products

#### Field Attachable Connectors



**120091** – Brad Nano-Change (M8)  
Field Attachable Connectors



**120071** – Brad Micro-Change (M12)  
Field Attachable Connectors



**120085** – Brad Ultra-Lock (M12)  
Field Attachable Connectors

#### Overmolded Connectors



**120027, 120028, 120086, 120087** –  
Brad Nano-Change (M8)  
Single-Ended and Double Ended Cordsets



**120006** – Brad Micro-Change (M12)  
Single-Ended and Double Ended Cordsets

**120009** – Brad Micro-Change  
M12 Cordsets with Knurled Hexnuts



**120065, 120066** – Brad Micro-Push (M12) Single-  
Ended and Double Ended Cordsets

# Flamar Signal & Control

## 155220 Control Cables, WSOR Jacket

Drag Chain Installation, Unshielded, -25°C/+80°C, 600V

**molex**

Cables with Weld-Slag and Oil-Resistant "WSOR" jacket cover the broadest range of industrial applications, allowing the reduction of inventory costs. Suitable for drag chain applications. The right choice for actuators (valves, slides, cylinders...) and control cabinets in combination with DIN, M16, M23 or heavy duty connectors.



### Specifications

Application: Severe environment  
 Installation: Drag Chain  
 Halogen Free: No  
 Temp. rating (flexible installation):  
 -25°C/+80°C  
 Voltage rating: 600V  
 Bending radius (flex. install. at 20°C):  
 > 7,5xOD  
 Insulation material: TPE  
 Jacket material: WSOR  
 Shielded: No

Approval: UL AWM 21215 / CSA  
 Marking: acc. to UL/CSA  
 Silicone, Pb,Cd,Hg & FCKW free: Yes  
 Flame resistance:  
 Good (VW1/FT1 & IEC60332-1)  
 Key factor:  
 Weld-Slag and Oil-Resistant. A single cable solution for automotive lines and industrial applications. ECOLAB compatible (for Food & Beverage environments).

Cross Section		No. of Circuits	Diameter in mm	Jacket Color	Packaging	Packaging Composition	Standard Order No	Sketch
mm²	AWG							
0,5	21	2	5,2	Black	S	3x200m	155220-0100	
					M	1x800m	155220-0101	
					L	1x1500m	155220-0102	
				Grey	S	3x200m	155220-0103	
					M	1x800m	155220-0104	
					L	1x1500m	155220-0105	
		3	5,6	Black	S	3x100m	155220-0106	
					M	1x500m	155220-0107	
					L	1x1000m	155220-0108	
				Grey	S	3x100m	155220-0109	
					M	1x500m	155220-0110	
					L	1x1000m	155220-0111	
				Orange	S	3x100m	155220-0112	
					M	1x500m	155220-0113	
					L	1x1000m	155220-0114	
		4	5,9	Black	S	3x100m	155220-0115	
					M	1x500m	155220-0116	
					L	1x1000m	155220-0117	
				Grey	S	3x100m	155220-0118	
					M	1x500m	155220-0119	
					L	1x1000m	155220-0120	
		5	6,2	Black	S	3x100m	155220-0121	
					M	1x500m	155220-0122	
					L	1x1000m	155220-0123	
Grey	S			3x100m	155220-0124			
	M			1x500m	155220-0125			
	L			1x1000m	155220-0126			
12	8,7	Black	S	1x200m	155220-0127			
			M	1x500m	155220-0128			
			L	1x1000m	155220-0129			
		Grey	S	1x200m	155220-0130			
			M	1x500m	155220-0131			
			L	1x1000m	155220-0132			

# Flamar Signal & Control

## 155220 Control Cables, WSOR Jacket

Drag Chain Installation, Unshielded, -25°C/+80°C, 600V

**molex**



Cross Section		No. of Circuits	Diameter in mm	Jacket Color	Packaging	Packaging Composition	Standard Order No	Sketch
mm <sup>2</sup>	AWG							
0,75	19	2	6,0	Black	S	3x100m	155220-0133	
					M	1x500m	155220-0134	
					L	1x1000m	155220-0135	
				Grey	S	3x100m	155220-0136	
					M	1x500m	155220-0137	
					L	1x1000m	155220-0138	
		3	6,4	Black	S	3x100m	155220-0139	
					M	1x500m	155220-0140	
					L	1x1000m	155220-0141	
				Grey	S	3x100m	155220-0142	
					M	1x500m	155220-0143	
					L	1x1000m	155220-0144	
		4	7,0	Black	S	3x100m	155220-0145	
					M	1x500m	155220-0146	
					L	1x1000m	155220-0147	
				Grey	S	3x100m	155220-0148	
					M	1x500m	155220-0149	
					L	1x1000m	155220-0150	
		5	7,5	Black	S	3x100m	155220-0151	
					M	1x500m	155220-0152	
L	1x1000m				155220-0153			
Grey	S			3x100m	155220-0154			
	M			1x500m	155220-0155			
	L			1x1000m	155220-0156			
1,00	18	2	6,7	Black	S	3x100m	155220-0157	
					M	1x500m	155220-0158	
					L	1x1000m	155220-0159	
				Grey	S	3x100m	155220-0160	
					M	1x500m	155220-0161	
					L	1x1000m	155220-0162	
		3	7,1	Black	S	3x100m	155220-0163	
					M	1x500m	155220-0164	
					L	1x1000m	155220-0165	
				Grey	S	3x100m	155220-0166	
					M	1x500m	155220-0167	
					L	1x1000m	155220-0168	
		4	7,6	Black	S	3x100m	155220-0169	
					M	1x500m	155220-0170	
					L	1x1000m	155220-0171	
				Grey	S	3x100m	155220-0172	
					M	1x500m	155220-0173	
					L	1x1000m	155220-0174	
		5	8,3	Black	S	1x200m	155220-0175	
					M	1x500m	155220-0176	
					L	1x1000m	155220-0177	
				Grey	S	1x200m	155220-0178	
					M	1x500m	155220-0179	
					L	1x1000m	155220-0180	

# Flamar Signal & Control

## 155220 Control Cables, WSOR Jacket

Drag Chain Installation, Unshielded, -25°C/+80°C, 600V

**molex**



Cross Section		No. of Circuits	Diameter in mm	Jacket Color	Packaging	Packaging Composition	Standard Order No	Sketch
mm <sup>2</sup>	AWG							
1,00	18	7	9,6	Black	S	1x200m	155220-0181	
					M	1x500m	155220-0182	
					L	1x1000m	155220-0183	
				Grey	S	1x200m	155220-0184	
					M	1x500m	155220-0185	
					L	1x1000m	155220-0186	
		11	11,5	Black	S	1x100m	155220-0187	
					M	1x500m	155220-0188	
					L	1x1000m	155220-0189	
				Grey	S	1x100m	155220-0190	
					M	1x500m	155220-0191	
					L	1x1000m	155220-0192	
		12	11,5	Black	S	1x100m	155220-0193	
					M	1x500m	155220-0194	
					L	1x1000m	155220-0195	
				Grey	S	1x100m	155220-0196	
					M	1x500m	155220-0197	
					L	1x1000m	155220-0198	
		17	13,4	Black	S	1x100m	155220-0199	
					M	1x500m	155220-0200	
					L	1x1000m	155220-0201	
				Grey	S	1x100m	155220-0202	
					M	1x500m	155220-0203	
					L	1x1000m	155220-0204	
25	16,0	Black	S	1x100m	155220-0205			
			M	1x250m	155220-0206			
			L	1x500m	155220-0207			
		Grey	S	1x100m	155220-0208			
			M	1x250m	155220-0209			
			L	1x500m	155220-0210			
1,5	16	2	7,1	Black	S	3x100m	155220-0211	
					M	1x500m	155220-0212	
					L	1x1000m	155220-0213	
				Grey	S	3x100m	155220-0214	
					M	1x500m	155220-0215	
					L	1x1000m	155220-0216	
		3	7,3	Black	S	3x100m	155220-0217	
					M	1x500m	155220-0218	
					L	1x1000m	155220-0219	
				Grey	S	3x100m	155220-0220	
					M	1x500m	155220-0221	
					L	1x1000m	155220-0222	

# Flamar Signal & Control

## 155220 Control Cables, WSOR Jacket

Drag Chain Installation, Unshielded, -25°C/+80°C, 600V

**molex**



Cross Section		No. of Circuits	Diameter in mm	Jacket Color	Packaging	Packaging Composition	Standard Order No	Sketch
mm <sup>2</sup>	AWG							
1,5	16	4	7,9	Black	S	3x100m	155220-0223	
					M	1x500m	155220-0224	
					L	1x1000m	155220-0225	
				Grey	S	3x100m	155220-0226	
					M	1x500m	155220-0227	
					L	1x1000m	155220-0228	
		4	7,9	Black	S	3x100m	155220-0229	
					M	1x500m	155220-0230	
					L	1x1000m	155220-0231	
				Grey	S	3x100m	155220-0232	
					M	1x500m	155220-0233	
					L	1x1000m	155220-0234	
		5	8,6	Black	S	1x200m	155220-0235	
					M	1x500m	155220-0236	
					L	1x1000m	155220-0237	
				Grey	S	1x200m	155220-0238	
					M	1x500m	155220-0239	
					L	1x1000m	155220-0240	
		7	10,5	Black	S	1x100m	155220-0241	
					M	1x500m	155220-0242	
					L	1x1000m	155220-0243	
				Grey	S	1x100m	155220-0244	
					M	1x500m	155220-0245	
					L	1x1000m	155220-0246	
		11	12,7	Black	S	1x100m	155220-0247	
					M	1x500m	155220-0248	
					L	1x1000m	155220-0249	
				Grey	S	1x100m	155220-0250	
					M	1x500m	155220-0251	
					L	1x1000m	155220-0252	
		12	12,7	Black	S	1x100m	155220-0253	
					M	1x500m	155220-0254	
					L	1x1000m	155220-0255	
				Grey	S	1x100m	155220-0256	
					M	1x500m	155220-0257	
					L	1x1000m	155220-0258	
		17	14,7	Black	S	1x100m	155220-0259	
					M	1x500m	155220-0260	
					L	1x1000m	155220-0261	
				Grey	S	1x100m	155220-0262	
					M	1x500m	155220-0263	
					L	1x1000m	155220-0264	
		25	17,7	Black	S	1x100m	155220-0265	
					M	1x250m	155220-0266	
					L	1x500m	155220-0267	
				Grey	S	1x100m	155220-0268	
					M	1x250m	155220-0269	
					L	1x500m	155220-0270	

# Flamar Signal & Control

## 155220 Control Cables, WSOR Jacket

Drag Chain Installation, Unshielded, -25°C/+80°C, 600V

**molex**



Cross Section		No. of Circuits	Diameter in mm	Jacket Color	Packaging	Packaging Composition	Standard Order No	Sketch
mm <sup>2</sup>	AWG							
2,5	14	2	8,8	Black	S	1x200m	155220-0271	
					M	1x500m	155220-0272	
					L	1x1000m	155220-0273	
				Grey	S	1x200m	155220-0274	
					M	1x500m	155220-0275	
					L	1x1000m	155220-0276	
		3	9,3	Black	S	1x200m	155220-0277	
					M	1x500m	155220-0278	
					L	1x1000m	155220-0279	
				Grey	S	1x200m	155220-0280	
					M	1x500m	155220-0281	
					L	1x1000m	155220-0282	
		4	10,1	Black	S	1x100m	155220-0283	
					M	1x500m	155220-0284	
					L	1x1000m	155220-0285	
				Grey	S	1x100m	155220-0286	
					M	1x500m	155220-0287	
					L	1x1000m	155220-0288	
		5	11,3	Black	S	1x100m	155220-0289	
					M	1x500m	155220-0290	
					L	1x1000m	155220-0291	
				Grey	S	1x100m	155220-0292	
					M	1x500m	155220-0293	
					L	1x1000m	155220-0294	
		7	13,1	Black	S	1x100m	155220-0295	
					M	1x500m	155220-0296	
					L	1x1000m	155220-0297	
				Grey	S	1x100m	155220-0298	
					M	1x500m	155220-0299	
					L	1x1000m	155220-0300	
		11	15,7	Black	S	1x100m	155220-0301	
					M	1x250m	155220-0302	
L	1x500m				155220-0303			
Grey	S			1x100m	155220-0304			
	M			1x250m	155220-0305			
	L			1x500m	155220-0306			
12	15,9	Black	S	1x100m	155220-0307			
			M	1x250m	155220-0308			
			L	1x500m	155220-0309			
		Grey	S	1x100m	155220-0310			
			M	1x250m	155220-0311			
			L	1x500m	155220-0312			

# Flamar Signal & Control

## 155220 Control Cables, WSOR Jacket

Drag Chain Installation, Unshielded, -25°C/+80°C, 600V

**molex**



Cross Section		No. of Circuits	Diameter in mm	Jacket Color	Packaging	Packaging Composition	Standard Order No	Sketch
mm <sup>2</sup>	AWG							
2,5	14	17	18,5	Black	S	1x100m	155220-0313	
					M	1x250m	155220-0314	
					L	1x500m	155220-0315	
				Grey	S	1x100m	155220-0316	
					M	1x250m	155220-0317	
					L	1x500m	155220-0318	
25	22,3	25	22,3	Black	S	1x350m	155220-0319	
				Grey	S	1x350m	155220-0322	

### Related Products

#### Field Attachable Connectors



**121201, 121207** – Brad mPm DIN Valve Connectors, Form A, External Thread

**121202, 121208** – Brad mPm DIN Valve Connector, Form B - Industrial, External Thread

**121205, 121211** – Brad mPm DIN Valve Connector, Form C - Industrial, External Thread



**120071** – Brad Micro-Change (M12) Field Attachable Connectors



**120085** – Brad Ultra-Lock (M12) Field Attachable Connectors



**93601** - GWconnect Heavy Duty Connectors

#### Overmolded Connectors



**120094** – Brad M23 Single-Ended Cordsets

# Flamar Signal & Control

## 155220 Distribution Boxes, WSOR Jacket

Drag Chain Installation, Unshielded, -25°C/+80°C, 600V

**molex**

Cables with Weld-Slag and Oil-Resistant "WSOR" jacket cover the broadest range of industrial applications, allowing the reduction of inventory costs. Suitable for drag chain applications. Select this cable for distribution boxes ("MPIS") and safety barriers in combination with M23 signal connectors.



### Specifications

Application: Severe environment  
 Installation: Drag Chain  
 Halogen Free: No  
 Temp. rating (flexible installation):  
 -25°C/+80°C  
 Voltage rating: 600V  
 Bending radius (flex. install. at 20°C):  
 > 10xOD  
 Insulation material: TPE  
 Jacket material: WSOR  
 Shielded: No

Approval: UL AWM 21215 / CSA  
 Marking: acc. to UL/CSA  
 Silicone, Pb,Cd,Hg & FCKW free: Yes  
 Flame resistance:  
 Good (VW1/FT1 & IEC60332-1)  
 Key factor:  
 Weld-Slag and Oil-Resistant. A single cable solution for automotive lines and industrial applications. ECOLAB compatible (for Food & Beverage environments).

Cross Section		No. of Circuits	Diameter in mm	Jacket Color	Packaging	Packaging Composition	Standard Order No	Sketch
mm²	AWG							
3x0,75 + 4x0,34	3x AWG19 + 4x AWG22	7 (3+4)	7,8	Black	S	3x100m	155220-9001	
					M	1x500m	155220-9002	
					L	1x1000m	155220-9003	
				Grey	S	3x100m	155220-9004	
					M	1x500m	155220-9005	
					L	1x1000m	155220-9006	
3x0,75 + 6x0,34	3x AWG19 + 6x AWG22	9 (3+6)	8,5	Black	S	1x200m	155220-9007	
					M	1x500m	155220-9008	
					L	1x1000m	155220-9009	
				Grey	S	1x200m	155220-9010	
					M	1x500m	155220-9011	
					L	1x1000m	155220-9012	
3x0,75 + 8x0,34	3x AWG19 + 8x AWG22	11 (3+8)	8,5	Black	S	1x200m	155220-9013	
					M	1x500m	155220-9014	
					L	1x1000m	155220-9015	
				Grey	S	1x200m	155220-9016	
					M	1x500m	155220-9017	
					L	1x1000m	155220-9018	
3x0,75 + 16x0,34	3x AWG19 + 16x AWG22	19 (3+16)	10,2	Black	S	1x100m	155220-9019	
					M	1x500m	155220-9020	
					L	1x1000m	155220-9021	
				Grey	S	1x100m	155220-9022	
					M	1x500m	155220-9023	
					L	1x1000m	155220-9024	

### Related Products

#### Field Attachable Connectors



**120230** – Brad M23 Signal Connectors

**120233** – Brad M23 Power Connectors

#### Overmolded Connectors



**120094** – Brad M23  
Single-Ended Cordsets

# Flamar Signal & Control

## 155221 Sensor Cables, WSOR Jacket

Drag Chain Installation, Shielded, -25°C/+80°C, 600V

**molex**

Cables with Weld-Slag and Oil-Resistant "WSOR" jacket cover the broadest range of industrial applications, allowing the reduction of inventory costs. Suitable for drag chain applications. Shielded cable for sensors (position, pressure, temperature, motion...) and optical switches in combination with M8 and M12 connectors.



### Specifications

Application: Severe environment  
 Installation: Drag Chain  
 Halogen Free: No  
 Temp. rating (flexible installation):  
 -25°C/+80°C  
 Voltage rating: 600V  
 Bending radius (flex. install. at 20°C):  
 > 7,5xOD  
 Insulation material: TPE  
 Jacket material: WSOR  
 Shielded: Yes

Approval: UL AWM 21215 / CSA  
 Marking: acc. to UL/CSA  
 Silicone, Pb,Cd,Hg & FCKW free: Yes  
 Flame resistance:  
 Good (VW1/FT1 & IEC60332-1)  
 Key factor:  
 Weld-Slag and Oil-Resistant. A single cable solution for automotive lines and industrial applications. ECOLAB compatible (for Food & Beverage environments).

Cross Section		No. of Circuits	Diameter in mm	Jacket Color	Packaging	Packaging Composition	Standard Order No	Sketch		
mm <sup>2</sup>	AWG									
0,34	22	3	5,4	Black	S	3x200m	155221-0001			
					M	1x800m	155221-0002			
					L	1x1500m	155221-0003			
				Grey	S	3x200m	155221-0004			
					M	1x800m	155221-0005			
					L	1x1500m	155221-0006			
				Yellow	S	3x200m	155221-0007			
					M	1x800m	155221-0008			
					L	1x1500m	155221-0009			
				Orange	S	3x200m	155221-0010			
					M	1x800m	155221-0011			
					L	1x1500m	155221-0012			
		4	5,7	4	5,7	Black	S	3x100m	155221-0013	
							M	1x500m	155221-0014	
							L	1x1000m	155221-0015	
						Grey	S	3x100m	155221-0016	
							M	1x500m	155221-0017	
							L	1x1000m	155221-0018	
						Yellow	S	3x100m	155221-0019	
							M	1x500m	155221-0020	
							L	1x1000m	155221-0021	
						Orange	S	3x100m	155221-0022	
							M	1x500m	155221-0023	
							L	1x1000m	155221-0024	
		5	6,1	5	6,1	Black	S	3x100m	155221-0025	
							M	1x500m	155221-0026	
							L	1x1000m	155221-0027	
						Grey	S	3x100m	155221-0028	
							M	1x500m	155221-0029	
							L	1x1000m	155221-0030	
						Yellow	S	3x100m	155221-0031	
							M	1x500m	155221-0032	
							L	1x1000m	155221-0033	
						Orange	S	3x100m	155221-0034	
							M	1x500m	155221-0035	
							L	1x1000m	155221-0036	

# Flamar Signal & Control

## 155221 Sensor Cables, WSOR Jacket

Drag Chain Installation, Shielded, -25°C/+80°C, 600V




**molex**







Cross Section		No. of Circuits	Diameter in mm	Jacket Color	Packaging	Packaging Composition	Standard Order No	Sketch
mm <sup>2</sup>	AWG							
0,34	22	5	6,1	Black	S	3x100m	155221-0037	
					M	1x500m	155221-0038	
					L	1x1000m	155221-0039	
				Grey	S	3x100m	155221-0040	
					M	1x500m	155221-0041	
					L	1x1000m	155221-0042	
				Yellow	S	3x100m	155221-0043	
					M	1x500m	155221-0044	
					L	1x1000m	155221-0045	
				Orange	S	3x100m	155221-0046	
					M	1x500m	155221-0047	
					L	1x1000m	155221-0048	

### Related Products

#### Field Attachable Connectors

- 
**120091** – Brad Nano-Change (M8) Field Attachable Connectors
- 
**120071** – Brad Micro-Change (M12) Field Attachable Connectors
- 
**120085** – Brad Ultra-Lock (M12) Field Attachable Connectors

#### Overmolded Connectors

- 
**120027, 120028, 120086, 120087** – Brad Nano-Change (M8) Single-Ended and Double Ended Cordsets
- 
**120006** – Brad Micro-Change (M12) Single-Ended and Double Ended Cordsets
- 
**120009** – Brad Micro-Change (M12) Cordsets with Knurled Hexnuts
- 
**120065, 120066** – Brad Micro-Push (M12) Single-Ended and Double Ended Cordsets

# Flamar Signal & Control

## 155230 Sensor Cables, PUR Jacket

Drag Chain Installation, Unshielded, -40°C/+80°C, 1000V

**molex**

Cables with Polyurethane (PUR, TPU) jacket ensure top mechanical performance, withstand harsh environments and resist to abrasion. Suitable for drag chain applications. Typically used for sensors (position, pressure, temperature, motion...) and optical switches in combination with M8 and M12 connectors.



### Specifications

Application: Harsh environment  
 Installation: Drag Chain  
 Halogen Free: Yes  
 Temp. rating (flexible installation):  
 -40°C/+80°C  
 Voltage rating: 1000V  
 Bending radius (flex. install. at 20°C):  
 > 7,5xOD  
 Insulation material: TPE  
 Jacket material: PUR

Shielded: No  
 Approval: UL AWM 21223 / CSA  
 Marking: acc. to UL/CSA  
 Silicone, Pb,Cd,Hg & FCKW free: Yes  
 Flame resistance:  
 Good (VW1/FT1 & IEC60332-1)  
 Key factor:  
 Excellent resistance to oil and abrasion. Ensures top mechanical performances.

Cross Section		No. of Circuits	Diameter in mm	Jacket Color	Packaging	Packaging Composition	Standard Order No	Sketch	
mm <sup>2</sup>	AWG								
0,25	24	3	4,5	Black	S	3x200m	155230-0001		
					M	1x800m	155230-0002		
					L	1x1500m	155230-0003		
				Grey	S	3x200m	155230-0004		
					M	1x800m	155230-0005		
					L	1x1500m	155230-0006		
				Yellow	S	3x200m	155230-0007		
					M	1x800m	155230-0008		
					L	1x1500m	155230-0009		
				Orange	S	3x200m	155230-0010		
					M	1x800m	155230-0011		
					L	1x1500m	155230-0012		
		4	4,8	Black	S	3x200m	155230-0013		
					M	1x800m	155230-0014		
					L	1x1500m	155230-0015		
					Grey	S	3x200m		155230-0016
						M	1x800m		155230-0017
						L	1x1500m		155230-0018
				Yellow	S	3x200m	155230-0019		
					M	1x800m	155230-0020		
					L	1x1500m	155230-0021		
				Orange	S	3x200m	155230-0022		
					M	1x800m	155230-0023		
					L	1x1500m	155230-0024		
5	5,3	Black	S	3x200m	155230-0025				
			M	1x800m	155230-0026				
			L	1x1500m	155230-0027				
		Grey	S	3x200m	155230-0028				
			M	1x800m	155230-0029				
			L	1x1500m	155230-0030				
		Yellow	S	3x200m	155230-0031				
			M	1x800m	155230-0032				
			L	1x1500m	155230-0033				

# Flamar Signal & Control

## 155230 Sensor Cables, PUR Jacket

Drag Chain Installation, Unshielded, -40°C/+80°C, 1000V

**molex**



Cross Section		No. of Circuits	Diameter in mm	Jacket Color	Packaging	Packaging Composition	Standard Order No	Sketch
mm <sup>2</sup>	AWG							
0,25	24	8	6,4	Black	S	3x100m	155230-0034	
					M	1x500m	155230-0035	
					L	1x1000m	155230-0036	
				Grey	S	3x100m	155230-0037	
					M	1x500m	155230-0038	
					L	1x1000m	155230-0039	
				Yellow	S	3x100m	155230-0040	
					M	1x500m	155230-0041	
					L	1x1000m	155230-0042	
		12	6,9	Black	S	3x100m	155230-0043	
					M	1x500m	155230-0044	
					L	1x1000m	155230-0045	
				Grey	S	3x100m	155230-0046	
					M	1x500m	155230-0047	
					L	1x1000m	155230-0048	
				Yellow	S	3x100m	155230-0049	
					M	1x500m	155230-0050	
					L	1x1000m	155230-0051	
0,34	22	3	4,8	Black	S	3x200m	155230-0052	
					M	1x800m	155230-0053	
					L	1x1500m	155230-0054	
				Grey	S	3x200m	155230-0055	
					M	1x800m	155230-0056	
					L	1x1500m	155230-0057	
				Yellow	S	3x200m	155230-0058	
					M	1x800m	155230-0059	
					L	1x1500m	155230-0060	
		Orange	S	3x200m	155230-0061			
			M	1x800m	155230-0062			
			L	1x1500m	155230-0063			
		4	5,1	Black	S	3x200m	155230-0064	
					M	1x800m	155230-0065	
					L	1x1500m	155230-0066	
				Grey	S	3x200m	155230-0067	
					M	1x800m	155230-0068	
					L	1x1500m	155230-0069	
Yellow	S			3x200m	155230-0070			
	M			1x800m	155230-0071			
	L			1x1500m	155230-0072			
Orange	S	3x200m	155230-0073					
	M	1x800m	155230-0074					
	L	1x1500m	155230-0075					

# Flamar Signal & Control

## 155230 Sensor Cables, PUR Jacket

Drag Chain Installation, Unshielded, -40°C/+80°C, 1000V

**molex**



Cross Section		No. of Circuits	Diameter in mm	Jacket Color	Packaging	Packaging Composition	Standard Order No	Sketch
mm <sup>2</sup>	AWG							
0,34	22	5	5,5	Black	S	3x200m	155230-0076	
					M	1x800m	155230-0077	
					L	1x1500m	155230-0078	
				Grey	S	3x200m	155230-0079	
					M	1x800m	155230-0080	
					L	1x1500m	155230-0081	
				Yellow	S	3x200m	155230-0082	
					M	1x800m	155230-0083	
					L	1x1500m	155230-0084	
				Orange	S	3x200m	155230-0085	
					M	1x800m	155230-0086	
					L	1x1500m	155230-0087	
		5	5,5	Black	S	3x200m	155230-0088	
					M	1x800m	155230-0089	
					L	1x1500m	155230-0090	
				Grey	S	3x200m	155230-0091	
					M	1x800m	155230-0092	
					L	1x1500m	155230-0093	
				Yellow	S	3x200m	155230-0094	
					M	1x800m	155230-0095	
L	1x1500m				155230-0096			
Orange	S			3x200m	155230-0097			
	M			1x800m	155230-0098			
	L			1x1500m	155230-0099			

### Related Products

#### Field Attachable Connectors



**120091** – Brad Nano-Change (M8)  
Field Attachable Connectors



**120071** – Brad Micro-Change (M12)  
Field Attachable Connectors



**120085** – Brad Ultra-Lock (M12)  
Field Attachable Connectors

#### Overmolded Connectors



**120027, 120028, 120086, 120087** –  
Brad Nano-Change (M8) Single-Ended and Double  
Ended Cordsets



**120006** – Brad Micro-Change (M12)  
Single-Ended and Double Ended Cordsets

**120009** – Brad Micro-Change (M12)  
Cordsets with Knurled Hexnuts



**120065, 120066** – Brad Micro-Push (M12)  
Single-Ended and Double Ended Cordsets

# Flamar Signal & Control

## 155230 Control Cables, PUR Jacket

Drag Chain Installation, Unshielded, -40°C/+80°C, 1000V

**molex**

Cables with Polyurethane (PUR, TPU) jacket ensure top mechanical performance, withstand harsh environments and resist to abrasion. Suitable for drag chain applications. The right choice for actuators (valves, slides, cylinders...) and control cabinets in combination with DIN, M16, M23 or heavy duty connectors.



### Specifications

Application: Harsh environment  
 Installation: Drag Chain  
 Halogen Free: Yes  
 Temp. rating (flexible installation):  
 -40°C/+80°C  
 Voltage rating: 1000V  
 Bending radius (flex. install. at 20°C):  
 > 7,5xOD  
 Insulation material: TPE  
 Jacket material: PUR

Shielded: No  
 Approval: UL AWM 21223 / CSA  
 Marking: acc. to UL/CSA  
 Silicone, Pb,Cd,Hg & FCKW free: Yes  
 Flame resistance:  
 Good (VW1/FT1 & IEC60332-1)  
 Key factor:  
 Excellent resistance to oil and abrasion. Ensures top mechanical performances.

Cross Section		No. of Circuits	Diameter in mm	Jacket Color	Packaging	Packaging Composition	Standard Order No	Sketch
mm <sup>2</sup>	AWG							
0,5	21	2	5,2	Black	S	3x200m	155230-0100	
					M	1x800m	155230-0101	
					L	1x1500m	155230-0102	
				Grey	S	3x200m	155230-0103	
					M	1x800m	155230-0104	
					L	1x1500m	155230-0105	
		3	5,6	Black	S	3x100m	155230-0106	
					M	1x500m	155230-0107	
					L	1x1000m	155230-0108	
				Grey	S	3x100m	155230-0109	
					M	1x500m	155230-0110	
					L	1x1000m	155230-0111	
				Orange	S	3x100m	155230-0112	
					M	1x500m	155230-0113	
					L	1x1000m	155230-0114	
		4	5,9	Black	S	3x100m	155230-0115	
					M	1x500m	155230-0116	
					L	1x1000m	155230-0117	
				Grey	S	3x100m	155230-0118	
					M	1x500m	155230-0119	
					L	1x1000m	155230-0120	
		5	6,2	Black	S	3x100m	155230-0121	
					M	1x500m	155230-0122	
					L	1x1000m	155230-0123	
Grey	S			3x100m	155230-0124			
	M			1x500m	155230-0125			
	L			1x1000m	155230-0126			
12	8,7	Black	S	1x200m	155230-0127			
			M	1x500m	155230-0128			
			L	1x1000m	155230-0129			
		Grey	S	1x200m	155230-0130			
			M	1x500m	155230-0131			
			L	1x1000m	155230-0132			

# Flamar Signal & Control

## 155230 Control Cables, PUR Jacket

Drag Chain Installation, Unshielded, -40°C/+80°C, 1000V

**molex**



Cross Section		No. of Circuits	Diameter in mm	Jacket Color	Packaging	Packaging Composition	Standard Order No	Sketch
mm <sup>2</sup>	AWG							
0,75	19	2	6,0	Black	S	3x100m	155230-0133	
					M	1x500m	155230-0134	
					L	1x1000m	155230-0135	
				Grey	S	3x100m	155230-0136	
					M	1x500m	155230-0137	
					L	1x1000m	155230-0138	
		3	6,4	Black	S	3x100m	155230-0139	
					M	1x500m	155230-0140	
					L	1x1000m	155230-0141	
				Grey	S	3x100m	155230-0142	
					M	1x500m	155230-0143	
					L	1x1000m	155230-0144	
		4	7,0	Black	S	3x100m	155230-0145	
					M	1x500m	155230-0146	
					L	1x1000m	155230-0147	
				Grey	S	3x100m	155230-0148	
					M	1x500m	155230-0149	
					L	1x1000m	155230-0150	
		5	7,5	Black	S	3x100m	155230-0151	
					M	1x500m	155230-0152	
					L	1x1000m	155230-0153	
				Grey	S	3x100m	155230-0154	
					M	1x500m	155230-0155	
					L	1x1000m	155230-0156	
1,00	18	2	6,7	Black	S	3x100m	155230-0157	
					M	1x500m	155230-0158	
					L	1x1000m	155230-0159	
				Grey	S	3x100m	155230-0160	
					M	1x500m	155230-0161	
					L	1x1000m	155230-0162	
		3	7,1	Black	S	3x100m	155230-0163	
					M	1x500m	155230-0164	
					L	1x1000m	155230-0165	
				Grey	S	3x100m	155230-0166	
					M	1x500m	155230-0167	
					L	1x1000m	155230-0168	
		4	7,6	Black	S	3x100m	155230-0169	
					M	1x500m	155230-0170	
					L	1x1000m	155230-0171	
				Grey	S	3x100m	155230-0172	
					M	1x500m	155230-0173	
					L	1x1000m	155230-0174	
		5	8,3	Black	S	1x200m	155230-0175	
					M	1x500m	155230-0176	
					L	1x1000m	155230-0177	
				Grey	S	1x200m	155230-0178	
					M	1x500m	155230-0179	
					L	1x1000m	155230-0180	

# Flamar Signal & Control

## 155230 Control Cables, PUR Jacket

Drag Chain Installation, Unshielded, -40°C/+80°C, 1000V

**molex**



Cross Section		No. of Circuits	Diameter in mm	Jacket Color	Packaging	Packaging Composition	Standard Order No	Sketch
mm <sup>2</sup>	AWG							
1,00	18	7	9,6	Black	S	1x200m	155230-0181	
					M	1x500m	155230-0182	
					L	1x1000m	155230-0183	
				Grey	S	1x200m	155230-0184	
					M	1x500m	155230-0185	
					L	1x1000m	155230-0186	
		11	11,5	Black	S	1x100m	155230-0187	
					M	1x500m	155230-0188	
					L	1x1000m	155230-0189	
				Grey	S	1x100m	155230-0190	
					M	1x500m	155230-0191	
					L	1x1000m	155230-0192	
		12	11,5	Black	S	1x100m	155230-0193	
					M	1x500m	155230-0194	
					L	1x1000m	155230-0195	
				Grey	S	1x100m	155230-0196	
					M	1x500m	155230-0197	
					L	1x1000m	155230-0198	
		17	13,4	Black	S	1x100m	155230-0199	
					M	1x500m	155230-0200	
					L	1x1000m	155230-0201	
				Grey	S	1x100m	155230-0202	
					M	1x500m	155230-0203	
					L	1x1000m	155230-0204	
25	16,0	Black	S	1x100m	155230-0205			
			M	1x250m	155230-0206			
			L	1x500m	155230-0207			
		Grey	S	1x100m	155230-0208			
			M	1x250m	155230-0209			
			L	1x500m	155230-0210			

# Flamar Signal & Control

## 155230 Control Cables, PUR Jacket

Drag Chain Installation, Unshielded, -40°C/+80°C, 1000V

**molex**



Cross Section		No. of Circuits	Diameter in mm	Jacket Color	Packaging	Packaging Composition	Standard Order No	Sketch
mm <sup>2</sup>	AWG							
1,5	16	2	7,1	Black	S	3x100m	155230-0211	
					M	1x500m	155230-0212	
					L	1x1000m	155230-0213	
				Grey	S	3x100m	155230-0214	
					M	1x500m	155230-0215	
					L	1x1000m	155230-0216	
		3	7,3	Black	S	3x100m	155230-0217	
					M	1x500m	155230-0218	
					L	1x1000m	155230-0219	
				Grey	S	3x100m	155230-0220	
					M	1x500m	155230-0221	
					L	1x1000m	155230-0222	
		4	7,9	Black	S	3x100m	155230-0223	
					M	1x500m	155230-0224	
					L	1x1000m	155230-0225	
				Grey	S	3x100m	155230-0226	
					M	1x500m	155230-0227	
					L	1x1000m	155230-0228	
		4	7,9	Black	S	3x100m	155230-0229	
					M	1x500m	155230-0230	
					L	1x1000m	155230-0231	
				Grey	S	3x100m	155230-0232	
					M	1x500m	155230-0233	
					L	1x1000m	155230-0234	
		5	8,6	Black	S	1x200m	155230-0235	
					M	1x500m	155230-0236	
					L	1x1000m	155230-0237	
				Grey	S	1x200m	155230-0238	
					M	1x500m	155230-0239	
					L	1x1000m	155230-0240	
		7	10,5	Black	S	1x100m	155230-0241	
					M	1x500m	155230-0242	
					L	1x1000m	155230-0243	
				Grey	S	1x100m	155230-0244	
					M	1x500m	155230-0245	
					L	1x1000m	155230-0246	
11	12,7	Black	S	1x100m	155230-0247			
			M	1x500m	155230-0248			
			L	1x1000m	155230-0249			
		Grey	S	1x100m	155230-0250			
			M	1x500m	155230-0251			
			L	1x1000m	155230-0252			

# Flamar Signal & Control

## 155230 Control Cables, PUR Jacket

Drag Chain Installation, Unshielded, -40°C/+80°C, 1000V

**molex**



Cross Section		No. of Circuits	Diameter in mm	Jacket Color	Packaging	Packaging Composition	Standard Order No	Sketch
mm <sup>2</sup>	AWG							
1,5	16	12	12,7	Black	S	1x100m	155230-0253	
					M	1x500m	155230-0254	
					L	1x1000m	155230-0255	
				Grey	S	1x100m	155230-0256	
					M	1x500m	155230-0257	
					L	1x1000m	155230-0258	
		17	14,7	Black	S	1x100m	155230-0259	
					M	1x500m	155230-0260	
					L	1x1000m	155230-0261	
				Grey	S	1x100m	155230-0262	
					M	1x500m	155230-0263	
					L	1x1000m	155230-0264	
	25	17,7	Black	S	1x100m	155230-0265		
				M	1x250m	155230-0266		
				L	1x500m	155230-0267		
			Grey	S	1x100m	155230-0268		
				M	1x250m	155230-0269		
				L	1x500m	155230-0270		
2,5	14	2	8,8	Black	S	1x200m	155230-0271	
					M	1x500m	155230-0272	
					L	1x1000m	155230-0273	
				Grey	S	1x200m	155230-0274	
					M	1x500m	155230-0275	
					L	1x1000m	155230-0276	
		3	9,3	Black	S	1x200m	155230-0277	
					M	1x500m	155230-0278	
					L	1x1000m	155230-0279	
				Grey	S	1x200m	155230-0280	
					M	1x500m	155230-0281	
					L	1x1000m	155230-0282	
	4	10,1	Black	S	1x100m	155230-0283		
				M	1x500m	155230-0284		
				L	1x1000m	155230-0285		
			Grey	S	1x100m	155230-0286		
				M	1x500m	155230-0287		
				L	1x1000m	155230-0288		
	5	11,3	Black	S	1x100m	155230-0289		
				M	1x500m	155230-0290		
				L	1x1000m	155230-0291		
			Grey	S	1x100m	155230-0292		
				M	1x500m	155230-0293		
				L	1x1000m	155230-0294		

# Flamar Signal & Control

## 155230 Control Cables, PUR Jacket

Drag Chain Installation, Unshielded, -40°C/+80°C, 1000V

**molex**



Cross Section		No. of Circuits	Diameter in mm	Jacket Color	Packaging	Packaging Composition	Standard Order No	Sketch
mm <sup>2</sup>	AWG							
2,5	14	7	13,3	Black	S	1x100m	155230-0295	
					M	1x500m	155230-0296	
					L	1x1000m	155230-0297	
				Grey	S	1x100m	155230-0298	
					M	1x500m	155230-0299	
					L	1x1000m	155230-0300	
		11	15,7	Black	S	1x100m	155230-0301	
					M	1x250m	155230-0302	
					L	1x500m	155230-0303	
				Grey	S	1x100m	155230-0304	
					M	1x250m	155230-0305	
					L	1x500m	155230-0306	
		12	15,9	Black	S	1x100m	155230-0307	
					M	1x250m	155230-0308	
					L	1x500m	155230-0309	
				Grey	S	1x100m	155230-0310	
					M	1x250m	155230-0311	
					L	1x500m	155230-0312	
		17	18,5	Black	S	1x100m	155230-0313	
					M	1x250m	155230-0314	
L	1x500m				155230-0315			
Grey	S			1x100m	155230-0316			
	M			1x250m	155230-0317			
	L			1x500m	155230-0318			
25	22,3	Black	S	1x350m	155230-0319			
			Grey	S	1x350m		155230-0322	

### Related Products

#### Field Attachable Connectors



**121201, 121207** – Brad mPm DIN Valve Connectors, Form A, External Thread

**121202, 121208** – Brad mPm DIN Valve Connector, Form B - Industrial, External Thread

**121205, 121211** – Brad mPm DIN Valve Connector, Form C - Industrial, External Thread



**120071** – Brad Micro-Change (M12) Field Attachable Connectors

#### Field Attachable Connectors



**120085** – Brad Ultra-Lock (M12) Field Attachable Connectors

**93601** - GWconnect Heavy Duty Connectors

#### Overmolded Connectors



**120094** – Brad M23 Single-Ended Cordsets


# Flamar Signal & Control

## 155230 Distribution Boxes, PUR Jacket

Drag Chain Installation, Unshielded, -40°C/+80°C, 1000V

**molex**

Cables with Polyurethane (PUR, TPU) jacket ensure top mechanical performance, withstand harsh environments and resist to abrasion. Suitable for drag chain applications. Select this cable for distribution boxes ("MPIS") and safety barriers in combination with M23 signal connectors.



### Specifications

Application: Harsh environment  
 Installation: Drag Chain  
 Halogen Free: Yes  
 Temp. rating (flexible installation):  
 -40°C/+80°C  
 Voltage rating: 1000V  
 Bending radius (flex. install. at 20°C):  
 > 10 x OD  
 Insulation material: TPE  
 Jacket material: PUR

Shielded: No  
 Approval: UL AWM 21223 / CSA  
 Marking: acc. to UL/CSA  
 Silicone, Pb,Cd,Hg & FCKW free: Yes  
 Flame resistance:  
 Good (VW1/FT1 & IEC60332-1)  
 Key factor:  
 Excellent resistance to oil and abrasion. Ensures top mechanical performances.

### Distribution Boxes

Cross Section		No. of Circuits	Diameter in mm	Jacket Color	Packaging	Packaging Composition	Standard Order No	Sketch
mm <sup>2</sup>	AWG							
3x0,75 + 4x0,34	3x AWG19 + 4x AWG22	7 (3+4)	7,8	Black	S	3x100m	155230-9001	
					M	1x500m	155230-9002	
					L	1x1000m	155230-9003	
				Grey	S	3x100m	155230-9004	
					M	1x500m	155230-9005	
					L	1x1000m	155230-9006	
3x0,75 + 6x0,34	3x AWG19 + 6x AWG22	9 (3+6)	8,5	Black	S	1x200m	155230-9007	
					M	1x500m	155230-9008	
					L	1x1000m	155230-9009	
				Grey	S	1x200m	155230-9010	
					M	1x500m	155230-9011	
					L	1x1000m	155230-9012	
3x0,75 + 8x0,34	3x AWG19 + 8x AWG22	11 (3+8)	8,5	Black	S	1x200m	155230-9013	
					M	1x500m	155230-9014	
					L	1x1000m	155230-9015	
				Grey	S	1x200m	155230-9016	
					M	1x500m	155230-9017	
					L	1x1000m	155230-9018	
3x0,75 + 16x0,34	3x AWG19 + 16x AWG22	19 (3+16)	10,2	Black	S	1x100m	155230-9019	
					M	1x500m	155230-9020	
					L	1x1000m	155230-9021	
				Grey	S	1x100m	155230-9022	
					M	1x500m	155230-9023	
					L	1x1000m	155230-9024	

### Related Products

#### Field Attachable Connectors



**120230** – Brad M23 Signal Connectors

**120233** – Brad M23 Power Connectors

#### Overmolded Connectors



**120094** – Brad M23  
Single-Ended Cordsets

# Flamar Signal & Control

## 155231 Sensor Cables, PUR Jacket

Drag Chain Installation, Shielded, -40°C/+80°C, 1000V

**molex**

Cables with Polyurethane (PUR, TPU) jacket ensure top mechanical performance, withstand harsh environments and resist to abrasion. Suitable for drag chain applications. Shielded cable for sensors (position, pressure, temperature, motion...) and optical switches in combination with M8 and M12 connectors.



### Specifications

Application: Harsh environment  
 Installation: Drag Chain  
 Halogen Free: Yes  
 Temp. rating (flexible installation):  
 -40°C/+80°C  
 Voltage rating: 1000V  
 Bending radius (flex. install. at 20°C):  
 > 7,5xOD  
 Insulation material: TPE  
 Jacket material: PUR

Shielded: Yes  
 Approval: UL AWM 21223 / CSA  
 Marking: acc. to UL/CSA  
 Silicone, Pb,Cd,Hg & FCKW free: Yes  
 Flame resistance:  
 Good (VW1/FT1 & IEC60332-1)  
 Key factor:  
 Excellent resistance to oil and abrasion. Ensures top mechanical performances.

Cross Section		No. of Circuits	Diameter in mm	Jacket Color	Packaging	Packaging Composition	Standard Order No	Sketch
mm <sup>2</sup>	AWG							
0,34	22	3	5,4	Black	S	3x200m	155231-0001	
					M	1x800m	155231-0002	
					L	1x1500m	155231-0003	
				Grey	S	3x200m	155231-0004	
					M	1x800m	155231-0005	
					L	1x1500m	155231-0006	
		Yellow	S	3x200m	155231-0007			
			M	1x800m	155231-0008			
			L	1x1500m	155231-0009			
			Orange	S	3x200m	155231-0010		
				M	1x800m	155231-0011		
				L	1x1500m	155231-0012		
	4	5,7	Black	S	3x100m	155231-0013		
				M	1x500m	155231-0014		
				L	1x1000m	155231-0015		
			Grey	S	3x100m	155231-0016		
				M	1x500m	155231-0017		
				L	1x1000m	155231-0018		
		Yellow	S	3x100m	155231-0019			
			M	1x500m	155231-0020			
			L	1x1000m	155231-0021			
		Orange	S	3x100m	155231-0022			
			M	1x500m	155231-0023			
			L	1x1000m	155231-0024			
5	6,1		Black	S	3x100m	155231-0025		
				M	1x500m	155231-0026		
				L	1x1000m	155231-0027		
		Grey	S	3x100m	155231-0028			
			M	1x500m	155231-0029			
			L	1x1000m	155231-0030			
Yellow	S	3x100m	155231-0031					
	M	1x500m	155231-0032					
	L	1x1000m	155231-0033					
Orange	S	3x100m	155231-0034					
	M	1x500m	155231-0035					
	L	1x1000m	155231-0036					

# Flamar Signal & Control

## 155231 Sensor Cables, PUR Jacket

Drag Chain Installation, Shielded, -40°C/+80°C, 1000V




**molex**






Cross Section		No. of Circuits	Diameter in mm	Jacket Color	Packaging	Packaging Composition	Standard Order No	Sketch
mm <sup>2</sup>	AWG							
0,34	22	5	6,1	Black	S	3x100m	155231-0037	
					M	1x500m	155231-0038	
					L	1x1000m	155231-0039	
				Grey	S	3x100m	155231-0040	
					M	1x500m	155231-0041	
					L	1x1000m	155231-0042	
				Yellow	S	3x100m	155231-0043	
					M	1x500m	155231-0044	
					L	1x1000m	155231-0045	
				Orange	S	3x100m	155231-0046	
					M	1x500m	155231-0047	
					L	1x1000m	155231-0048	

### Related Products

#### Field Attachable Connectors

-  **120091** – Brad Nano-Change (M8) Field Attachable Connectors
-  **120071** – Brad Micro-Change (M12) Field Attachable Connectors
-  **120085** – Brad Ultra-Lock (M12) Field Attachable Connectors

#### Overmolded Connectors

-  **120027, 120028, 120086, 120087** – Brad Nano-Change (M8) Single-Ended and Double Ended Cordsets
-  **120006** – Brad Micro-Change (M12) Single-Ended and Double Ended Cordsets
- 120009** – Brad Micro-Change (M12) Cordsets with Knurled Hexnuts
-  **120065, 120066** – Brad Micro-Push (M12) Single-Ended and Double Ended Cordsets

# Flamar Signal & Control

## 155240 Sensor Cables, TPE Jacket

Drag Chain Installation, Unshielded, -40°C/+105°C, 300V

**molex**

**UL Listed cables with TPE (Thermoplastic Elastomer) jacket, defined according to the US/Canadian market requirements. Excellent flame resistance. Suitable for drag chain applications. Typically used for sensors (position, pressure, temperature, motion...) and optical switches in combination with M8 and M12 connectors.**



### Specifications

Application: Severe environment  
 Installation: Drag Chain  
 Halogen Free: No  
 Temp. rating (flexible installation):  
 -40°C/+105°C  
 Voltage rating: 300V  
 Bending radius (flex. install. at 20°C):  
 > 10xOD  
 Insulation material: PVC  
 Jacket material: TPE  
 Shielded: No

Approval: UL Listed PLTC  
 Marking: acc. to UL/CSA  
 Silicone, Pb,Cd,Hg & FCKW free: Yes  
 Flame resistance:  
 Excellent (FT4 & VW1/FT1 &  
 IEC60332-3A)  
 Key factor:  
 Designed in accordance with North  
 American market requirements.  
 Good resistance to oil. ECOLAB compatible  
 (for Food & Beverage environments).

Cross section		No. of Circuits	Diameter in mm	Jacket Color	Packaging	Packaging Composition	Standard Order No	Sketch
mm <sup>2</sup>	AWG							
0,34	22	3	5,1	Black	S	3x200m	155240-0001	
					M	1x800m	155240-0002	
					L	1x1500m	155240-0003	
				Grey	S	3x200m	155240-0004	
					M	1x800m	155240-0005	
					L	1x1500m	155240-0006	
				Yellow	S	3x200m	155240-0007	
					M	1x800m	155240-0008	
					L	1x1500m	155240-0009	
				Orange	S	3x200m	155240-0010	
					M	1x800m	155240-0011	
					L	1x1500m	155240-0012	
		4	5,4	Black	S	3x200m	155240-0013	
					M	1x800m	155240-0014	
					L	1x1500m	155240-0015	
				Grey	S	3x200m	155240-0016	
					M	1x800m	155240-0017	
					L	1x1500m	155240-0018	
				Yellow	S	3x200m	155240-0019	
					M	1x800m	155240-0020	
					L	1x1500m	155240-0021	
				Orange	S	3x200m	155240-0022	
					M	1x800m	155240-0023	
					L	1x1500m	155240-0024	

# Flamar Signal & Control

## 155240 Sensor Cables, TPE Jacket







Drag Chain Installation, Unshielded, -40°C/+105°C, 300V

**molex**



Cross section		No. of Circuits	Diameter in mm	Jacket Color	Packaging	Packaging Composition	Standard Order No	Sketch
mm <sup>2</sup>	AWG							
0,34	22	5	5,8	Black	S	3x100m	155240-0025	
					M	1x500m	155240-0026	
					L	1x1000m	155240-0027	
				Grey	S	3x100m	155240-0028	
					M	1x500m	155240-0029	
					L	1x1000m	155240-0030	
				Yellow	S	3x100m	155240-0031	
					M	1x500m	155240-0032	
					L	1x1000m	155240-0033	
				Orange	S	3x100m	155240-0034	
					M	1x500m	155240-0035	
					L	1x1000m	155240-0036	
		5	5,8	Black	S	3x100m	155240-0037	
					M	1x500m	155240-0038	
					L	1x1000m	155240-0039	
				Grey	S	3x100m	155240-0040	
					M	1x500m	155240-0041	
					L	1x1000m	155240-0042	
				Yellow	S	3x100m	155240-0043	
					M	1x500m	155240-0044	
Orange	L	1x1000m	155240-0045					
	S	3x100m	155240-0046					
	M	1x500m	155240-0047					
L	1x1000m	155240-0048						

### Related Products

<p><b>Field Attachable Connectors</b></p> <p> <b>120091</b> – Brad Nano-Change (M8) Field Attachable Connectors</p> <p> <b>120071</b> – Brad Micro-Change (M12) Field Attachable Connectors</p> <p> <b>120085</b> – Brad Ultra-Lock (M12) Field Attachable Connectors</p>	<p><b>Overmolded Connectors</b></p> <p> <b>120027, 120028, 120086, 120087</b> – Brad Nano-Change (M8) Single-Ended and Double Ended Cordsets</p> <p> <b>120006</b> – Brad Micro-Change (M12) Single-Ended and Double Ended Cordsets</p> <p><b>120009</b> – Brad Micro-Change M12 Cordsets with Knurled Hexnuts</p> <p> <b>120065, 120066</b> – Brad Micro-Push (M12) Single-Ended and Double Ended Cordsets</p>
--	---

# Flamar Signal & Control

## 155240 Control Cables, TPE Jacket

Drag Chain Installation, Unshielded, -40°C/+105°C, 300V

**molex**

**UL Listed cables with TPE (Thermoplastic Elastomer) jacket, defined according to the US/Canadian market requirements. Excellent flame resistance. Suitable for drag chain applications. The right choice for actuators (valves, slides, cylinders...) and control cabinets in combination with DIN, M16, M23 or heavy duty connectors.**



### Specifications

Application: Severe environment  
 Installation: Drag Chain  
 Halogen Free: No  
 Temp. rating (flexible installation):  
 -40°C/+105°C  
 Voltage rating: 300V  
 Bending radius (flex. install. at 20°C):  
 > 10xOD  
 Insulation material: PVC  
 Jacket material: TPE  
 Shielded: No

Approval: UL Listed PLTC  
 Marking: acc. to UL/CSA  
 Silicone, Pb,Cd,Hg & FCKW free: Yes  
 Flame resistance:  
 Excellent (FT4 & VW1/FT1 &  
 IEC60332-3A)  
 Key factor:  
 Designed in accordance with North  
 American market requirements.  
 Good resistance to oil. ECOLAB compatible  
 (for Food & Beverage environments).

Cross Section		No. of Circuits	Diameter in mm	Jacket Color	Packaging	Packaging Composition	Standard Order No	Sketch
mm <sup>2</sup>	AWG							
0,5	21	2	5,6	Black	S	3x100m	155240-0049	
					M	1x500m	155240-0050	
					L	1x1000m	155240-0051	
				Grey	S	3x100m	155240-0052	
					M	1x500m	155240-0053	
					L	1x1000m	155240-0054	
		3	6,0	Black	S	3x100m	155240-0055	
					M	1x500m	155240-0056	
					L	1x1000m	155240-0057	
				Grey	S	3x100m	155240-0058	
					M	1x500m	155240-0059	
					L	1x1000m	155240-0060	
				Orange	S	3x100m	155240-0061	
					M	1x500m	155240-0062	
					L	1x1000m	155240-0063	
		4	6,4	Black	S	3x100m	155240-0064	
					M	1x500m	155240-0065	
					L	1x1000m	155240-0066	
				Grey	S	3x100m	155240-0067	
					M	1x500m	155240-0068	
					L	1x1000m	155240-0069	
		5	6,9	Black	S	3x100m	155240-0070	
					M	1x500m	155240-0071	
					L	1x1000m	155240-0072	
Grey	S			3x100m	155240-0073			
	M			1x500m	155240-0074			
	L			1x1000m	155240-0075			
12	9,0	Black	S	1x200m	155240-0076			
			M	1x500m	155240-0077			
			L	1x1000m	155240-0078			
		Grey	S	1x200m	155240-0079			
			M	1x500m	155240-0080			
			L	1x1000m	155240-0081			

# Flamar Signal & Control

## 155240 Control Cables, TPE Jacket

Drag Chain Installation, Unshielded, -40°C/+105°C, 300V

**molex**



Cross Section		No. of Circuits	Diameter in mm	Jacket Color	Packaging	Packaging Composition	Standard Order No	Sketch
mm <sup>2</sup>	AWG							
0,75	19	2	6,5	Black	S	3x100m	155240-0082	
					M	1x500m	155240-0083	
					L	1x1000m	155240-0084	
				Grey	S	3x100m	155240-0085	
					M	1x500m	155240-0086	
					L	1x1000m	155240-0087	
		3	7,0	Black	S	3x100m	155240-0088	
					M	1x500m	155240-0089	
					L	1x1000m	155240-0090	
				Grey	S	3x100m	155240-0091	
					M	1x500m	155240-0092	
					L	1x1000m	155240-0093	
	4	7,7	Black	S	3x100m	155240-0094		
				M	1x500m	155240-0095		
				L	1x1000m	155240-0096		
			Grey	S	3x100m	155240-0097		
				M	1x500m	155240-0098		
				L	1x1000m	155240-0099		
	5	8,3	Black	S	1x200m	155240-0100		
				M	1x500m	155240-0101		
				L	1x1000m	155240-0102		
			Grey	S	1x200m	155240-0103		
				M	1x500m	155240-0104		
				L	1x1000m	155240-0105		
1,00	18	2	7,5	Black	S	3x100m	155240-0106	
					M	1x500m	155240-0107	
					L	1x1000m	155240-0108	
				Grey	S	3x100m	155240-0109	
					M	1x500m	155240-0110	
					L	1x1000m	155240-0111	
		3	7,9	Black	S	3x100m	155240-0112	
					M	1x500m	155240-0113	
					L	1x1000m	155240-0114	
				Grey	S	3x100m	155240-0115	
					M	1x500m	155240-0116	
					L	1x1000m	155240-0117	
	4	8,6	Black	S	1x200m	155240-0118		
				M	1x500m	155240-0119		
				L	1x1000m	155240-0120		
			Grey	S	1x200m	155240-0121		
				M	1x500m	155240-0122		
				L	1x1000m	155240-0123		
	5	9,3	Black	S	1x200m	155240-0124		
				M	1x500m	155240-0125		
				L	1x1000m	155240-0126		
			Grey	S	1x200m	155240-0127		
				M	1x500m	155240-0128		
				L	1x1000m	155240-0129		

# Flamar Signal & Control

## 155240 Control Cables, TPE Jacket

Drag Chain Installation, Unshielded, -40°C/+105°C, 300V

**molex**



Cross Section		No. of Circuits	Diameter in mm	Jacket Color	Packaging	Packaging Composition	Standard Order No	Sketch
mm <sup>2</sup>	AWG							
1,0	18	7	11,0	Black	S	1x100m	155240-0130	
					M	1x500m	155240-0131	
					L	1x1000m	155240-0132	
				Grey	S	1x100m	155240-0133	
					M	1x500m	155240-0134	
					L	1x1000m	155240-0135	
		11	13,0	Black	S	1x100m	155240-0136	
					M	1x500m	155240-0137	
					L	1x1000m	155240-0138	
				Grey	S	1x100m	155240-0139	
					M	1x500m	155240-0140	
					L	1x1000m	155240-0141	
		12	13,0	Black	S	1x100m	155240-0142	
					M	1x500m	155240-0143	
					L	1x1000m	155240-0144	
				Grey	S	1x100m	155240-0145	
					M	1x500m	155240-0146	
					L	1x1000m	155240-0147	
		17	15,0	Black	S	1x100m	155240-0148	
					M	1x250m	155240-0149	
L	1x500m				155240-0150			
Grey	S			1x100m	155240-0151			
	M			1x250m	155240-0152			
	L			1x500m	155240-0153			
25	18,0	Black	S	1x100m	155240-0154			
			M	1x250m	155240-0155			
			L	1x500m	155240-0156			
		Grey	S	1x100m	155240-0157			
			M	1x250m	155240-0158			
			L	1x500m	155240-0159			

# Flamar Signal & Control

## 155240 Control Cables, TPE Jacket

Drag Chain Installation, Unshielded, -40°C/+105°C, 300V

**molex**



Cross Section		No. of Circuits	Diameter in mm	Jacket Color	Packaging	Packaging Composition	Standard Order No	Sketch
mm <sup>2</sup>	AWG							
1,5	16	2	8,0	Black	S	1x200m	155240-0160	
					M	1x500m	155240-0161	
					L	1x1000m	155240-0162	
				Grey	S	1x200m	155240-0163	
					M	1x500m	155240-0164	
					L	1x1000m	155240-0165	
		3	8,5	Black	S	1x200m	155240-0166	
					M	1x500m	155240-0167	
					L	1x1000m	155240-0168	
				Grey	S	1x200m	155240-0169	
					M	1x500m	155240-0170	
					L	1x1000m	155240-0171	
		4	9,3	Black	S	1x200m	155240-0172	
					M	1x500m	155240-0173	
					L	1x1000m	155240-0174	
				Grey	S	1x200m	155240-0175	
					M	1x500m	155240-0176	
					L	1x1000m	155240-0177	
		4	9,3	Black	S	1x200m	155240-0178	
					M	1x500m	155240-0179	
					L	1x1000m	155240-0180	
				Grey	S	1x200m	155240-0181	
					M	1x500m	155240-0182	
					L	1x1000m	155240-0183	
5	10,0	Black	S	1x100m	155240-0184			
			M	1x500m	155240-0185			
			L	1x1000m	155240-0186			
		Grey	S	1x100m	155240-0187			
			M	1x500m	155240-0188			
			L	1x1000m	155240-0189			
7	11,8	Black	S	1x100m	155240-0190			
			M	1x500m	155240-0191			
			L	1x1000m	155240-0192			
		Grey	S	1x100m	155240-0193			
			M	1x500m	155240-0194			
			L	1x1000m	155240-0195			

# Flamar Signal & Control

## 155240 Control Cables, TPE Jacket

Drag Chain Installation, Unshielded, -40°C/+105°C, 300V

**molex**



Cross Section		No. of Circuits	Diameter in mm	Jacket Color	Packaging	Packaging Composition	Standard Order No	Sketch
mm <sup>2</sup>	AWG							
1,5	16	11	14,2	Black	S	1x100m	155240-0196	
					M	1x500m	155240-0197	
					L	1x1000m	155240-0198	
				Grey	S	1x100m	155240-0199	
					M	1x500m	155240-0200	
					L	1x1000m	155240-0201	
		12	14,2	Black	S	1x100m	155240-0202	
					M	1x500m	155240-0203	
					L	1x1000m	155240-0204	
				Grey	S	1x100m	155240-0205	
					M	1x500m	155240-0206	
					L	1x1000m	155240-0207	
		17	16,6	Black	S	1x100m	155240-0208	
					M	1x250m	155240-0209	
					L	1x500m	155240-0210	
				Grey	S	1x100m	155240-0211	
					M	1x250m	155240-0212	
					L	1x500m	155240-0213	
25	20,0	Black	S	1x350m	155240-0214			
		Grey	S	1x350m	155240-0217			
2,5	14	2	9,8	Black	S	1x200m	155240-0220	
					M	1x500m	155240-0221	
					L	1x1000m	155240-0222	
				Grey	S	1x200m	155240-0223	
					M	1x500m	155240-0224	
					L	1x1000m	155240-0225	
		3	10,5	Black	S	1x100m	155240-0226	
					M	1x500m	155240-0227	
					L	1x1000m	155240-0228	
				Grey	S	1x100m	155240-0229	
					M	1x500m	155240-0230	
					L	1x1000m	155240-0231	
		4	11,6	Black	S	1x100m	155240-0232	
					M	1x500m	155240-0233	
					L	1x1000m	155240-0234	
				Grey	S	1x100m	155240-0235	
					M	1x500m	155240-0236	
					L	1x1000m	155240-0237	
		5	12,6	Black	S	1x100m	155240-0238	
					M	1x500m	155240-0239	
					L	1x1000m	155240-0240	
				Grey	S	1x100m	155240-0241	
					M	1x500m	155240-0242	
					L	1x1000m	155240-0243	

# Flamar Signal & Control

## 155240 Control Cables, TPE Jacket

Drag Chain Installation, Unshielded, -40°C/+105°C, 300V


**molex**




Cross Section		No. of Circuits	Diameter in mm	Jacket Color	Packaging	Packaging Composition	Standard Order No	Sketch
mm <sup>2</sup>	AWG							
2,5	14	7	15,2	Black	S	1x100m	155240-0244	
					M	1x250m	155240-0245	
					L	1x500m	155240-0246	
				Grey	S	1x100m	155240-0247	
					M	1x250m	155240-0248	
					L	1x500m	155240-0249	
		11	18,4	Black	S	1x100m	155240-0250	
					M	1x250m	155240-0251	
					L	1x500m	155240-0252	
				Grey	S	1x100m	155240-0253	
					M	1x250m	155240-0254	
					L	1x500m	155240-0255	
		12	18,4	Black	S	1x100m	155240-0256	
					M	1x250m	155240-0257	
					L	1x500m	155240-0258	
				Grey	S	1x100m	155240-0259	
					M	1x250m	155240-0260	
					L	1x500m	155240-0261	
		17	21,4	Black	S	1x350m	155240-0262	
					S	1x350m	155240-0265	
25	25,6	Black	S	1x250m	155240-0268			
			S	1x250m	155240-0271			

### Related Products


**Field Attachable Connectors**




**121201, 121207** – Brad mPm DIN Valve Connectors, Form A, External Thread



**121202, 121208** – Brad mPm DIN Valve Connector, Form B - Industrial, External Thread




**121205, 121211** – Brad mPm DIN Valve Connector, Form C - Industrial, External Thread




**120071** – Brad Micro-Change (M12) Field Attachable Connectors

**Field Attachable Connectors**




**120085** – Brad Ultra-Lock (M12) Field Attachable Connectors



**93601** - GWconnect Heavy Duty Connectors

**Overmolded Connectors**



**120094** – Brad M23 Single-Ended Cordsets

# Flamar Signal & Control

## 155241 Sensor Cables, TPE Jacket

Drag Chain Installation, Shielded, -40°C/+105°C, 300V

**molex**

UL Listed cables with TPE (Thermoplastic Elastomer) jacket, defined according to the US/Canadian market requirements. Excellent flame resistance. Suitable for drag chain applications. Shielded cable for sensors (position, pressure, temperature, motion...) and optical switches in combination with M8 and M12 connectors.



### Specifications

Application: Severe environment  
 Installation: Drag Chain  
 Halogen Free: No  
 Temp. rating (flexible installation):  
 -40°C/+105°C  
 Voltage rating: 300V  
 Bending radius (flex. install. at 20°C):  
 > 10xOD  
 Insulation material: PVC  
 Jacket material: TPE  
 Shielded: Yes

Approval: UL Listed PLTC  
 Marking: acc. to UL/CSA  
 Silicone, Pb,Cd,Hg & FCKW free: Yes  
 Flame resistance:  
 Excellent (FT4 & VW1/FT1 &  
 IEC60332-3A)  
 Key factor:  
 Designed in accordance with North  
 American market requirements.  
 Good resistance to oil. ECOLAB compatible  
 (for Food & Beverage environments).

Cross section		No. of Circuits	Diameter in mm	Jacket Color	Packaging	Packaging Composition	Standard Order No	Sketch		
mm <sup>2</sup>	AWG									
0,34	22	3	5,7	Black	S	3x100m	155241-0001			
					M	1x500m	155241-0002			
					L	1x1000m	155241-0003			
				Grey	S	3x100m	155241-0004			
					M	1x500m	155241-0005			
					L	1x1000m	155241-0006			
				Yellow	S	3x100m	155241-0007			
					M	1x500m	155241-0008			
					L	1x1000m	155241-0009			
				Orange	S	3x100m	155241-0010			
					M	1x500m	155241-0011			
					L	1x1000m	155241-0012			
		4	6,0	4	6,0	Black	S	3x100m	155241-0013	
							M	1x500m	155241-0014	
							L	1x1000m	155241-0015	
						Grey	S	3x100m	155241-0016	
							M	1x500m	155241-0017	
							L	1x1000m	155241-0018	
						Yellow	S	3x100m	155241-0019	
							M	1x500m	155241-0020	
							L	1x1000m	155241-0021	
						Orange	S	3x100m	155241-0022	
							M	1x500m	155241-0023	
							L	1x1000m	155241-0024	
		5	6,4	5	6,4	Black	S	3x100m	155241-0025	
							M	1x500m	155241-0026	
							L	1x1000m	155241-0027	
						Grey	S	3x100m	155241-0028	
							M	1x500m	155241-0029	
							L	1x1000m	155241-0030	
						Yellow	S	3x100m	155241-0031	
							M	1x500m	155241-0032	
							L	1x1000m	155241-0033	
						Orange	S	3x100m	155241-0034	
							M	1x500m	155241-0035	
							L	1x1000m	155241-0036	

# Flamar Signal & Control

## 155241 Sensor Cables, TPE Jacket







Drag Chain Installation, Shielded, -40°C/+105°C, 300V

**molex**



Cross section		No. of Circuits	Diameter in mm	Jacket Color	Packaging	Packaging Composition	Standard Order No	Sketch
mm <sup>2</sup>	AWG							
0,34	22	5	6,4	Black	S	3x100m	155241-0037	
					M	1x500m	155241-0038	
					L	1x1000m	155241-0039	
				Grey	S	3x100m	155241-0040	
					M	1x500m	155241-0041	
					L	1x1000m	155241-0042	
				Yellow	S	3x100m	155241-0043	
					M	1x500m	155241-0044	
					L	1x1000m	155241-0045	
				Orange	S	3x100m	155241-0046	
					M	1x500m	155241-0047	
					L	1x1000m	155241-0048	

### Related Products

<p><b>Field Attachable Connectors</b></p>  <p><b>120091</b> – Brad Nano-Change (M8) Field Attachable Connectors</p>  <p><b>120071</b> – Brad Micro-Change (M12) Field Attachable Connectors</p>  <p><b>120085</b> – Brad Ultra-Lock (M12) Field Attachable Connectors</p>	<p><b>Overmolded Connectors</b></p>  <p><b>120027, 120028, 120086, 120087</b> – Brad Nano-Change (M8) Single-Ended and Double Ended Cordsets</p>  <p><b>120006</b> – Brad Micro-Change (M12) Single-Ended and Double Ended Cordsets</p> <p><b>120009</b> – Brad Micro-Change (M12) Cordsets with Knurled Hexnuts</p>  <p><b>120065, 120066</b> – Brad Micro-Push (M12) Single-Ended and Double Ended Cordsets</p>
--	---



## Servo Motor

Series	Environment	Installation	Halogen Free	Temperature Rating °C (flexible installation)		Voltage Rating V	Bending Radius (flex. install. at 20°C)
155311	Standard	Flexible	No	+5°C	+80°C	1000V power 600V feedback	> 15xOD
155321	Severe	Drag Chain	No	-25°C	+80°C	1000V power 600V feedback	> 10xOD
155331	Harsh	Drag Chain	Yes	-40°C	+80°C	1000V power 600V feedback	> 10xOD

## Typical Applications



Motors



Encoder / Resolver

## Jacket choice criteria

- PVC: The most cost-effective solution for flexible and static installation.
- WSOR: Weld-Slag and Oil-Resistant Cable, a single-cable solution designed to withstand the severe environments found in automotive and industrial factory floors. ECOLAB compatible (resistant to detergents, disinfectants and wash down water-jet used in Food & Beverage). Suitable for drag chain applications.
- PUR (Polyurethane): Ensures top mechanical performance, withstands harsh environments, abrasion resistant. Suitable for drag chain applications.



# Flamar Cables for Servo Motor Applications

Jacket Material	Shielded	Approval	Flame Resistance	Oil & Lubricants Resistance	Abrasion Resistance	Page No.
PVC	Yes	UL AWM 2570 / CSA	Good	Limited	Limited	56
WSOR	Yes	UL AWM 21939 / CSA power UL AWM 21215 / CSA feedback	Good	Good	Medium	58
PUR	Yes	UL AWM 21223 / CSA	Good	Excellent	Excellent	60

**Selecting the right cable for your application is very important to ensure a reliable, problem-free installation. Careful consideration of mechanical abrasion, fluid/chemical exposure, flexibility (C-track, torsion), temperature resistance and flame retardancy requirements is required to select the cable that will provide performance and reliability in service.**



# Flamar Servo Motor

## 155311 Power Cables, PVC Jacket

Flexible Installation, Shielded, +5°C/+80°C, 1000V

Cables with PVC jacket, suitable for flexible installation in standard environments. For servo motors power supply in combination with M23 power connector. Available with or without shielded pairs, in case brakes or thermal sensors (PTC) might be connected.



### Specifications

Application: Standard environment  
 Installation: Flexible  
 Halogen Free: No  
 Temp. rating (flexible installation):  
 +5°C/+80°C  
 Voltage rating: 1000V  
 Bending radius (flex. install. at 20°C):  
 > 15xOD  
 Insulation material: TPE  
 Jacket material: PVC  
 Shielded: Yes

Approval: UL AWM 2570 / CSA  
 Marking: acc. to UL/CSA  
 Silicone, Pb,Cd,Hg & FCKW free: Yes  
 Flame resistance:  
 Good (VW1/FT1 & IEC60332-1)  
 Key factor:  
 Cost-effective solution for less  
 demanding environments (limited  
 exposure to oil and lubricants)

Cross Section		No. of Circuits	Diameter in mm	In accordance with	Packaging	Packaging Composition	Standard Order No	Sketch	
mm <sup>2</sup>	AWG								
(4G1,5)	(4G AWG16)	4	9,0	Siemens 6FX5008	S	1x200m	155311-0001		
					M	1x500m	155311-0002		
					L	1x1000m	155311-0003		
(4G2,5)	(4G AWG14)	4	10,6		S	1x100m	155311-0004		
					M	1x500m	155311-0005		
					L	1x1000m	155311-0006		
(4G4,0)	(4G AWG12)	4	12,2		S	1x100m	155311-0007		
					M	1x500m	155311-0008		
					L	1x1000m	155311-0009		
(4G6,0)	(4G AWG10)	4	14,5		S	1x100m	155311-0010		
					M	1x500m	155311-0011		
					L	1x1000m	155311-0012		
(4G1,5 + 2x1,5)	(4G AWG16 + 2xAWG16)	6 (4+2)	11,1	Siemens 6FX5008	S	1x100m	155311-1001		
					M	1x500m	155311-1002		
					L	1x1000m	155311-1003		
					S	1x100m	155311-1004		
(4G2,5 + 2x1,5)	(4G AWG14 + 2xAWG16)	6 (4+2)	12,6		M	1x500m	155311-1005		
					L	1x1000m	155311-1006		
					S	1x100m	155311-1007		
					M	1x500m	155311-1008		
(4G4,0 + 2x1,5)	(4G AWG12 + 2xAWG16)	6 (4+2)	14,0		L	1x1000m	155311-1009		
					S	1x100m	155311-1010		
					M	1x250m	155311-1011		
					L	1x500m	155311-1012		
(4G1,5 + 2x(2x0,75))	(4G AWG16 + 2x(2xAWG19))	8 (4+2+2)	12,1	Bosch Rexroth INDRAMAT INK650	S	1x100m	155311-2001		
					M	1x500m	155311-2002		
					L	1x1000m	155311-2003		
(4G2,5 + 2x(2x1,0))	(4G AWG14 + 2x(2xAWG18))	8 (4+2+2)	14,1		S	1x100m	155311-2004		
					M	1x500m	155311-2005		
					L	1x1000m	155311-2006		
(4G4,0 + 2x(2x1,5))	(4G AWG12 + 2x(2xAWG16))	8 (4+2+2)	15,8		Bosch Rexroth INDRAMAT INK602	S	1x100m		155311-2007
					M	1x250m	155311-2008		
					L	1x500m	155311-2009		
(4G6,0 + 2x(2x1,5))	(4G AWG10 + 2x(2xAWG16))	8 (4+2+2)	17,9	Bosch Rexroth INDRAMAT INK603	S	1x100m	155311-2010		
				M	1x250m	155311-2011			
				L	1x500m	155311-2012			
(4G6,0 + 2x(2x1,5))	(4G AWG10 + 2x(2xAWG16))	8 (4+2+2)	17,9	Bosch Rexroth INDRAMAT INK604	S	1x100m	155311-2010		
				M	1x250m	155311-2011			
				L	1x500m	155311-2012			

# Flamar Servo Motor

## 155311 Feedback Cables, PVC Jacket

Flexible Installation, Shielded, +5°C/+80°C, 600V

**molex**

Cables with PVC jacket, suitable for flexible installation in standard environments. To connect encoders/ resolvers by means of a M23 signal connector.



### Specifications


Application: Standard environment  
 Installation: Flexible  
 Halogen Free: No  
 Temp. rating (flexible installation): +5°C/+80°C  
 Voltage rating: 600V  
 Bending radius (flex. install. at 20°C): > 15xOD  
 Insulation material: TPE  
 Jacket material: PVC  
 Shielded: Yes

Approval: UL AWM 2570 / CSA  
 Marking: acc. to UL/CSA  
 Silicone, Pb,Cd,Hg & FCKW free: Yes  
 Flame resistance: Good (VW1/FT1 & IEC60332-1)  
 Key factor: Cost-effective solution for less demanding environments (limited exposure to oil and lubricants)

Cross Section		No. of Circuits	Diameter in mm	In accordance with	Packaging	Packaging Composition	Standard Order No	Sketch
mm <sup>2</sup>	AWG							
(4x2x0,25 + 2x1,00)C	(4x2xAWG24 + 2xAWG18)C	10 (8+2)	8,8	Bosch Rexroth INDRAMAT INK 0209	S	1x200m	155311-9001	
					M	1x500m	155311-9002	
					L	1x1000m	155311-9003	
(3x(2x0,14)D + 2x(0,50)D)C	(3x(2xAWG26)D + 2x(AWG21)D)C	8 (6+2)	9,0	Heidenhain	S	1x200m	155311-9004	
					M	1x500m	155311-9005	
					L	1x1000m	155311-9006	
(4x2x0,38 + 4x0,50)C	(4x2xAWG22 + 4xAWG21)C	12 (8+4)	9,5	Siemens 6FX5008-1BD21	S	1x200m	155311-9007	
					M	1x500m	155311-9008	
					L	1x1000m	155311-9009	
(3x(2x0,14)D + 2x0,50 + 4x0,14 + 4x0,25)C	(3x(2xAWG26)D + 2xAWG21 + 4xAWG26 + 4xAWG24)C	16 (6+2+4+4)	10,0	Siemens 6FX5008-1BD51	S	1x100m	155311-9010	
					M	1x500m	155311-9011	
					L	1x1000m	155311-9012	

### Related Products

**Field Attachable Connectors**




**120230** – Brad M23 Signal Connectors

**120233** – Brad M23 Power Connectors


**120604** – Brad M40

**Overmolded Connectors**



**120480** – Brad M23 Power Cordsets

**120600** – Brad M40



**120490** – Brad M23 Signal Overmolded Cordsets

# Flamar Servo Motor

## 155321 Power Cables, WSOR Jacket

Drag Chain Installation, Shielded, -25°C/+80°C, 1000V

**molex**

Cables with Weld-Slag and Oil-Resistant "WSOR" jacket cover the broadest range of industrial applications, allowing the reduction of inventory costs. Suitable for drag chain applications. For servo motors power supply in combination with M23 power connector. Available with or without shielded pairs, in case brakes or thermal sensors (PTC) might be connected.



### Specifications

Application: Severe environment  
 Installation: Drag Chain  
 Halogen Free: No  
 Temp. rating (flexible installation):  
 -25°C/+80°C  
 Voltage rating: 1000V  
 Bending radius (flex. install. at 20°C):  
 > 10xOD  
 Insulation material: TPE  
 Jacket material: WSOR  
 Shielded: Yes

Approval: UL AWM 21939 / CSA  
 Marking: acc. to UL/CSA  
 Silicone, Pb,Cd,Hg & FCKW free: Yes  
 Flame resistance:  
 Good (VW1/FT1 & IEC60332-1)  
 Key factor:  
 Weld-Slag and Oil-Resistant. A single cable solution for automotive lines and industrial applications. ECOLAB compatible (for Food & Beverage environments).

Cross Section		No. of Circuits	Diameter in mm	In accordance with	Packaging	Packaging Composition	Standard Order No	Sketch
mm <sup>2</sup>	AWG							
(4G1,5)	(4G AWG16)	4	9,0	Siemens 6FX5008	S	1x200m	155321-0001	
					M	1x500m	155321-0002	
					L	1x1000m	155321-0003	
(4G2,5)	(4G AWG14)	4	10,6		S	1x100m	155321-0004	
					M	1x500m	155321-0005	
					L	1x1000m	155321-0006	
(4G4,0)	(4G AWG12)	4	12,2		S	1x100m	155321-0007	
					M	1x500m	155321-0008	
					L	1x1000m	155321-0009	
(4G6,0)	(4G AWG10)	4	14,5		S	1x100m	155321-0010	
					M	1x500m	155321-0011	
					L	1x1000m	155321-0012	
(4G1,5 + 2x1,5)	(4G AWG16 + 2xAWG16)	6 (4+2)	11,1	Siemens 6FX5008	S	1x100m	155321-1001	
					M	1x500m	155321-1002	
					L	1x1000m	155321-1003	
(4G2,5 + 2x1,5)	(4G AWG14 + 2xAWG16)	6 (4+2)	12,6		S	1x100m	155321-1004	
					M	1x500m	155321-1005	
					L	1x1000m	155321-1006	
(4G4 + 2x1,5)	(4G AWG12 + 2xAWG16)	6 (4+2)	14,0		S	1x100m	155321-1007	
					M	1x500m	155321-1008	
					L	1x1000m	155321-1009	
(4G6 + 2x1,5)	(4G AWG10 + 2xAWG16)	6 (4+2)	16,2		S	1x100m	155321-1010	
					M	1x250m	155321-1011	
					L	1x500m	155321-1012	
(4G1,5 + 2x(2x0,75))	(4G AWG16 + 2x(2xAWG19))	8 (4+2+2)	12,1	Bosch Rexroth INDRAMAT INK650	S	1x100m	155321-2001	
					M	1x500m	155321-2002	
					L	1x1000m	155321-2003	
(4G2,5 + 2x(2x1,0))	(4G AWG14 + 2x(2xAWG18))	8 (4+2+2)	14,1		S	1x100m	155321-2004	
					M	1x500m	155321-2005	
					L	1x1000m	155321-2006	
(4G4,0 + 2x(2x1,5))	(4G AWG12 + 2x(2xAWG16))	8 (4+2+2)	15,8		S	1x100m	155321-2007	
					M	1x250m	155321-2008	
					L	1x500m	155321-2009	
(4G6,0 + 2x(2x1,5))	(4G AWG10 + 2x(2xAWG16))	8 (4+2+2)	17,9	S	1x100m	155321-2010		
				M	1x250m	155321-2011		
				L	1x500m	155321-2012		

# Flamar Servo Motor

## 155321 Feedback Cables, WSOR Jacket

Drag Chain Installation, Shielded, -25°C/+80°C, 600V

**molex**

Cables with Weld-Slag and Oil-Resistant "WSOR" jacket cover the broadest range of industrial applications, allowing the reduction of inventory costs. Suitable for drag chain applications. To connect encoders/ resolvers by means of a M23 signal connector.



**ECOLAB**

### Specifications

Application: Severe environment  
 Installation: Drag Chain  
 Halogen Free: No  
 Temp. rating (flexible installation):  
 -25°C/+80°C  
 Voltage rating: 600V  
 Bending radius (flex. install. at 20°C):  
 > 12xOD  
 Insulation material: TPE  
 Jacket material: WSOR  
 Shielded: Yes

Approval: UL AWM 21215 / CSA  
 Marking: acc. to UL/CSA  
 Silicone, Pb,Cd,Hg & FCKW free: Yes  
 Flame resistance:  
 Good (VW1/FT1 & IEC60332-1)  
 Key factor:  
 Weld-Slag and Oil-Resistant. A single cable solution for automotive lines and industrial applications. ECOLAB compatible (for Food & Beverage environments).

Cross Section		No. of Circuits	Diameter in mm	In accordance with	Packaging	Packaging Composition	Standard Order No	Sketch
mm <sup>2</sup>	AWG							
(4x2x0,25 + 2x1,00)C	(4x2xAWG24 + 2xAWG18)C	10 (8+2)	8,8	Bosch Rexroth INDRAMAT INK 0209	S	1x200m	155321-9001	
					M	1x500m	155321-9002	
					L	1x1000m	155321-9003	
(3x(2x0,14)D + 2x(0,50)D)C	(3x(2xAWG26)D + 2x(AWG21)D)C	8 (6+2)	9,0	Heidenhain	S	1x200m	155321-9004	
					M	1x500m	155321-9005	
					L	1x1000m	155321-9006	
(4x2x0,38 + 4x0,50)C	(4x2xAWG22 + 4xAWG21)C	12 (8+4)	9,5	Siemens 6FX5008-1BD21	S	1x200m	155321-9007	
					M	1x500m	155321-9008	
					L	1x1000m	155321-9009	
(3x(2x0,14)D + 2x0,50 + 4x0,14 + 4x0,25)C	(3x(2xAWG26)D + 2xAWG21 + 4xAWG26 + 4xAWG24)C	16 (6+2+4+4)	10,0	Siemens 6FX5008-1BD51	S	1x100m	155321-9010	
					M	1x500m	155321-9011	
					L	1x1000m	155321-9012	

### Related Products

#### Field Attachable Connectors



**120230** – Brad M23 Signal Connectors

**120233** – Brad M23 Power Connectors

**120604** – Brad M40

#### Overmolded Connectors



**120480** – Brad M23 Power Cordsets  
**120600** – Brad M40



**120490** – Brad M23 Signal Overmolded Cordsets

# Flamar Servo Motor

## 155331 Power Cables, PUR Jacket

Drag Chain Installation, Shielded, -40°C/+80°C, 1000V

**molex**

Cables with Polyurethane (PUR, TPU) jacket ensure top mechanical performance, withstand harsh environments and resist to abrasion. Suitable for drag chain applications. For servo motors power supply in combination with M23 power connector. Available with or without shielded pairs, in case brakes or thermal sensors (PTC) might be connected.



### Specifications

Application: Harsh environment  
 Installation: Drag Chain  
 Halogen Free: Yes  
 Temp. rating (flexible installation):  
 -40°C/+80°C  
 Voltage rating: 1000V  
 Bending radius (flex. install. at 20°C):  
 > 10xOD  
 Insulation material: TPE  
 Jacket material: PUR  
 Shielded: Yes

Approval: UL AWM 21223 / CSA  
 Marking: acc. to UL/CSA  
 Silicone, Pb,Cd,Hg & FCKW free: Yes  
 Flame resistance:  
 Good (VW1/FT1 & IEC60332-1)  
 Key factor:  
 Excellent resistance to oil and abrasion. Ensures top mechanical performances.

Cross Section		No. of Circuits	Diameter in mm	In accordance with	Packaging	Packaging Composition	Standard Order No	Sketch
mm <sup>2</sup>	AWG							
(4G1,5)	(4G AWG16)	4	9,0	Siemens 6FX8008 Plus	S	1x200m	155331-0001	
					M	1x500m	155331-0002	
					L	1x1000m	155331-0003	
(4G2,5)	(4G AWG14)	4	10,6		S	1x100m	155331-0004	
					M	1x500m	155331-0005	
					L	1x1000m	155331-0006	
(4G4,0)	(4G AWG12)	4	12,2		S	1x100m	155331-0007	
					M	1x500m	155331-0008	
					L	1x1000m	155331-0009	
(4G6,0)	(4G AWG10)	4	14,5		S	1x100m	155331-0010	
					M	1x500m	155331-0011	
					L	1x1000m	155331-0012	
4G1,5 + (2x1,5)	(4G AWG16 + (2xAWG16))	6 (4+2)	11,1	Siemens 6FX8008 Plus	S	1x100m	155331-1001	
					M	1x500m	155331-1002	
					L	1x1000m	155331-1003	
(4G2,5 + (2x1,5))	(4G AWG14 + (2xAWG16))	6 (4+2)	12,6		S	1x100m	155331-1004	
					M	1x500m	155331-1005	
					L	1x1000m	155331-1006	
(4G4,0 + (2x1,5))	(4G AWG12 + (2xAWG16))	6 (4+2)	14,0		S	1x100m	155331-1007	
					M	1x500m	155331-1008	
					L	1x1000m	155331-1009	
(4G6,0 + (2x1,5))	(4G AWG10 + (2xAWG16))	6 (4+2)	16,2		S	1x100m	155331-1010	
					M	1x250m	155331-1011	
					L	1x500m	155331-1012	
(4G1,5 + 2x(2x0,75))	(4G AWG16 + 2x(2xAWG19))	8 (4+2+2)	12,1	Bosch Rexroth INDRAMAT INK650	S	1x100m	155331-2001	
					M	1x500m	155331-2002	
					L	1x1000m	155331-2003	
(4G2,5 + 2x(2x1,0))	(4G AWG14 + 2x(2xAWG18))	8 (4+2+2)	14,1	Bosch Rexroth INDRAMAT INK602	S	1x100m	155331-2004	
					M	1x500m	155331-2005	
					L	1x1000m	155331-2006	
(4G4 + 2x(2x1,5))	(4G AWG12 + 2x(2xAWG16))	8 (4+2+2)	15,8	Bosch Rexroth INDRAMAT INK603	S	1x100m	155331-2007	
					M	1x250m	155331-2008	
					L	1x500m	155331-2009	
(4G6 + 2x(2x1,5))	(4G AWG10 + 2x(2xAWG16))	8 (4+2+2)	17,9	Bosch Rexroth INDRAMAT INK604	S	1x100m	155331-2010	
					M	1x250m	155331-2011	
					L	1x500m	155331-2012	

# Flamar Servo Motor

## 155331 Feedback Cables, PUR Jacket

Drag Chain Installation, Shielded, -40°C/+80°C, 600V

**molex**

Cables with Polyurethane (PUR, TPU) jacket ensure top mechanical performance, withstand harsh environments and resist to abrasion. Suitable for drag chain applications. To connect encoders/ resolvers by means of a M23 signal connector.



### Specifications


Application: Harsh environment  
 Installation: Drag Chain  
 Halogen Free: Yes  
 Temp. rating (flexible installation):  
 -40°C/+80°C  
 Voltage rating: 600V  
 Bending radius (flex. install. at 20°C):  
 > 12xOD  
 Insulation material: TPE  
 Jacket material: PUR  
 Shielded: Yes

Approval: UL AWM 21223 / CSA  
 Marking: acc. to UL/CSA  
 Silicone, Pb,Cd,Hg & FCKW free: Yes  
 Flame resistance:  
 Good (VW1/FT1 & IEC60332-1)  
 Key factor:  
 Excellent resistance to oil and abrasion. Ensures top mechanical performances.


Cross Section		No. of Circuits	Diameter in mm	In accordance with	Packaging	Packaging Composition	Standard Order No	Sketch
mm <sup>2</sup>	AWG							
(4x2x0,25 + 2x1,00)C	(4x2xAWG24 + 2xAWG18)C	10 (8+2)	8,80	Bosch Rexroth INDRAMAT INK 0209	S	1x200m	155331-9001	
					M	1x500m	155331-9002	
					L	1x1000m	155331-9003	
(3x(2x0,14)D + 2x0,50)C	(3x(2xAWG26)D + 2x(AWG21)D)C	8 (6+2)	9,00	Heidenhain	S	1x200m	155331-9004	
					M	1x500m	155331-9005	
					L	1x1000m	155331-9006	
(4x2x0,38 + 4x0,50)C	(4x2xAWG22 + 4xAWG21)C	12 (8+4)	9,5	Siemens 6FX8008-1BD21	S	1x200m	155331-9007	
					M	1x500m	155331-9008	
					L	1x1000m	155331-9009	
(3x(2x0,14)D + 2x0,50 + 4x0,14 + 4x0,25)C	(3x(2xAWG26)D + 2xAWG21 + 4xAWG26 + 4xAWG24)C	16 (6+2+4+4)	10,0	Siemens 6FX8008-1BD51	S	1x100m	155331-9010	
					M	1x500m	155331-9011	
					L	1x1000m	155331-9012	

### Related Products

**Field Attachable Connectors**




**120230** – Brad M23 Signal Connectors




**120233** – Brad M23 Power Connectors  
**120604** – Brad M40

**Overmolded Connectors**



**120480** – Brad M23 Power Cordsets  
**120600** – Brad M40




**120490** – Brad M23 Signal Overmolded Cordsets



## Network

Series	Environment	Installation	Halogen Free	Temperature Rating °C (flexible installation)		Voltage Rating V	Bending Radius (flex. install. at 20°C)
155411	Standard	Flexible	No	+5°C	+60°C (CC-Link) +60°C (PROFIBUS) +70°C (PROFINET) +60°C (EtherNet/IP)	300V	>15xOD
155421	Severe	Drag Chain	No	-10°C	+60°C (CC-Link) +60°C (PROFIBUS) +70°C (PROFINET) +60°C (EtherNet/IP)	600V	> 15xOD
155431	Harsh	Drag Chain	Yes	-20°C	+60°C (CC-Link) +60°C (PROFIBUS) +70°C (PROFINET) +60°C (EtherNet/IP)	300V	> 15xOD

## Typical Applications



I/O Modules



Connections to PLC

## Jacket choice criteria

- PVC: The most cost-effective solution for flexible and static installation.
- WSOR: Weld-Slag and Oil-Resistant Cable, a single-cable solution designed to withstand the severe environments found in automotive and industrial factory floors. ECOLAB compatible (resistant to detergents, disinfectants and wash down water-jet used in Food & Beverage). Suitable for drag chain applications.
- PUR (Polyurethane): Ensures top mechanical performance, withstands harsh environments, abrasion resistant. Suitable for drag chain applications

# Flamar Cables for Network Applications



Jacket Material	Shielded	Approval	Flame Resistance	Oil & Lubricants Resistance	Abrasion Resistance	Page No.
PVC	Yes	UL AWM 2464 / CSA	Good	Limited	Limited	64
WSOR	Yes	UL AWM 21215 / CSA	Good	Good	Medium	68
PUR	Yes	UL AWM 20233 / CSA	Good	Excellent	Excellent	72

**Selecting the right cable for your application is very important to ensure a reliable, problem-free installation. Careful consideration of mechanical abrasion, fluid/chemical exposure, flexibility (C-track, torsion), temperature resistance and flame retardancy requirements is required to select the cable that will provide performance and reliability in service.**

CC-Link

PROFI<sup>®</sup>  
BUS

PROFI<sup>®</sup>  
NET

EtherNet/IP<sup>™</sup>



# Flamar Network Cables

## 155411 CC-Link, PVC Jacket

Flexible Installation, Shielded, +5°C/+60°C

**molex**

Cables with PVC jacket, suitable for flexible installation in standard environments. To connect field based devices (sensors, actuators, I/O modules, PLC) in combination with M12 and RJ45 connectors.



### Specifications

Application: Standard environment  
 Installation: Flexible  
 Halogen Free: No  
 Temp. rating (flexible installation):  
 +5°C / +60°C  
 Voltage rating: 300V  
 Bending radius (flex. install. at 20°C):  
 >15xOD  
 Insulation material: Foam PE  
 Jacket material: PVC

Shielded: Yes  
 Approval: UL AWM 2464 / CSA  
 Marking: acc. to UL/CSA  
 Silicone, Pb,Cd,Hg & FCKW free: Yes  
 Flame resistance:  
 Good (VW1/FT1 & IEC60332-1)  
 Key factor:  
 Cost-effective solution for less  
 demanding environments (limited  
 exposure to oil and lubricants)

### Network Cables - CC-Link

Cross Section		Diameter in mm	Jacket Color	Packaging	Packaging Composition	Standard Order No	Sketch
mm <sup>2</sup>	AWG						
3x0,5	3xAWG20	7,7	Red	S	3x100m	155411-2001	
				M	1x500m	155411-2002	
				L	1x1000m	155411-2003	

# Flamar Network Cables

## 155411 PROFIBUS, PVC Jacket

Flexible Installation, Shielded, +5°C/+60°C

**molex**

**Cables with PVC jacket, suitable for flexible installation in standard environments. To connect field based devices (sensors, actuators, I/O modules, PLC) in combination with M12 and RJ45 connectors.**



### Specifications

Application: Standard environment  
 Installation: Flexible  
 Halogen Free: No  
 Temp. rating (flexible installation):  
 +5°C / +60°C  
 Voltage rating: 300V  
 Bending radius (flex. install. at 20°C):  
 >15xOD  
 Insulation material: Foam PE  
 Jacket material: PVC

Shielded: Yes  
 Approval: UL AWM 2464 / CSA  
 Marking: acc. to UL/CSA  
 Silicone, Pb,Cd,Hg & FCKW free: Yes  
 Flame resistance:  
 Good (VW1/FT1 & IEC60332-1)  
 Key factor:  
 Cost-effective solution for less  
 demanding environments (limited  
 exposure to oil and lubricants)

### Network Cables - PROFIBUS "DP"

Cross Section		Diameter in mm	Jacket Color	Packaging	Packaging Composition	Standard Order No	Sketch
mm <sup>2</sup>	AWG						
2x0,34	2xAWG22	8,2	Violet	S	1x200m	155411-1004	
				M	1x500m	155411-1005	
				L	1x1000m	155411-1006	

# Flamar Network Cables

## 155411 Profinet, PVC Jacket

Flexible Installation, Shielded, +5°C/+70°C

**molex**

Cables with PVC jacket, suitable for flexible installation in standard environments. To connect field based devices (sensors, actuators, I/O modules, PLC) in combination with M12 and RJ45 connectors.




### Specifications

Application: Standard environment  
 Installation: Flexible  
 Halogen Free: No  
 Temp. rating (flexible installation):  
 +5°C / +70°C  
 Voltage rating: 300V  
 Bending radius (flex. install. at 20°C):  
 >15xOD  
 Insulation material: PE  
 Jacket material: PVC

Shielded: Yes  
 Approval: UL AWM 2464 / CSA  
 Marking: acc. to UL/CSA  
 Silicone, Pb,Cd,Hg & FCKW free: Yes  
 Flame resistance:  
 Good (VW1/FT1 & IEC60332-1)  
 Key factor:  
 Cost-effective solution for less  
 demanding environments (limited  
 exposure to oil and lubricants)

### Network Cables - PROFINET TYPE "C"

Cross Section		Diameter in mm	Jacket Color	Packaging	Packaging Composition	Standard Order No	Sketch
mm <sup>2</sup>	AWG						
2x2x0,34	2x2xAWG22	6,8	Green	S	3x100m	155411-5001	
				M	1x500m	155411-5002	
				L	1x1000m	155411-5003	

# Flamar Network Cables

## 155411 Ethernet, PVC Jacket

Flexible Installation, Shielded, +5°C/+60°C

**molex**

**Cables with PVC jacket, suitable for flexible installation in standard environments. To connect field based devices (sensors, actuators, I/O modules, PLC) in combination with M12 and RJ45 connectors.**



EtherNet/IP

### Specifications

Application: Standard environment  
 Installation: Flexible  
 Halogen Free: No  
 Temp. rating (flexible installation):  
 +5°C / +60°C  
 Voltage rating: 300V  
 Bending radius (flex. install. at 20°C):  
 >15xOD  
 Insulation material: PE  
 Jacket material: PVC

Shielded: Yes  
 Approval: UL AWM 2464 / CSA  
 Marking: acc. to UL/CSA  
 Silicone, Pb,Cd,Hg & FCKW free: Yes  
 Flame resistance:  
 Good (VW1/FT1 & IEC60332-1)  
 Key factor:  
 Cost-effective solution for less demanding environments (limited exposure to oil and lubricants)

### Network Cables - Ethernet Cat.5e

Cross Section		Diameter in mm	Jacket Color	Packaging	Packaging Composition	Standard Order No	Sketch
mm <sup>2</sup>	AWG						
2x2x0,14	2x2xAWG26	6,5	Teal	S	3x100m	155411-6001	
				M	1x500m	155411-6002	
				L	1x1000m	155411-6003	
4x2x0,14	4x2xAWG26	7,2		S	3x100m	155411-6004	
				M	1x500m	155411-6005	
				L	1x1000m	155411-6006	
2x2x0,25	2x2xAWG24	7,0		S	3x100m	155411-6007	
				M	1x500m	155411-6008	
				L	1x1000m	155411-6009	
4x2x0,25	4x2xAWG24	7,8	S	3x100m	155411-6010		
			M	1x500m	155411-6011		
			L	1x1000m	155411-6012		

# Flamar Network Cables

## 155421 CC-Link, WSOR Jacket

Drag Chain Installation, Shielded, -10°C/+60°C

**molex**

Cables with Weld-Slag and Oil-Resistant "WSOR" jacket cover the broadest range of industrial applications, allowing the reduction of inventory costs. Suitable for drag chain applications. To connect field based devices (sensors, actuators, I/O modules, PLC) in combination with M12 and RJ45 connectors.




### Specifications

Application: Severe environment  
 Installation: Drag Chain  
 Halogen Free: No  
 Temp. rating (flexible installation):  
 -10°C / +60°C  
 Voltage rating: 600V  
 Bending radius (flex. install. at 20°C):  
 > 15xOD  
 Insulation material: Foam PE  
 Jacket material: WSOR  
 Shielded: Yes

Approval: UL AWM 21215 / CSA  
 Marking: acc. to UL/CSA  
 Silicone, Pb,Cd,Hg & FCKW free: Yes  
 Flame resistance:  
 Good (VW1/FT1 & IEC60332-1)  
 Key factor:  
 Weld-Slag and Oil-Resistant. A single cable solution for automotive lines and industrial applications. ECOLAB compatible (for Food & Beverage environments).

### Network Cables - CC-Link

Cross Section		Diameter in mm	Jacket Color	Packaging	Packaging Composition	Standard Order No	Sketch
mm <sup>2</sup>	AWG						
3x0,5	3xAWG20	7,7	Red	S	3x100m	155421-2001	
				M	1x500m	155421-2002	
				L	1x1000m	155421-2003	

# Flamar Network Cables

## 155421 PROFIBUS, WSOR Jacket

Drag Chain Installation, Shielded, -10°C/+60°C

**molex**

Cables with Weld-Slag and Oil-Resistant "WSOR" jacket cover the broadest range of industrial applications, allowing the reduction of inventory costs. Suitable for drag chain applications. To connect field based devices (sensors, actuators, I/O modules, PLC) in combination with M12 and RJ45 connectors.



### Specifications

Application: Standard environment  
 Installation: Drag Chain  
 Halogen Free: No  
 Temp. rating (flexible installation):  
 -10°C / +60°C  
 Voltage rating: 600V  
 Bending radius (flex. install. at 20°C):  
 >15xOD  
 Insulation material: Foam PE  
 Jacket material: WSOR  
 Shielded: Yes

Approval: UL AWM 21215 / CSA  
 Marking: acc. to UL/CSA  
 Silicone, Pb,Cd,Hg & FCKW free: Yes  
 Flame resistance:  
 Good (VW1/FT1 & IEC60332-1)  
 Key factor:  
 Weld-Slag and Oil-Resistant. A single cable solution for automotive lines and industrial applications. ECOLAB compatible (for Food & Beverage environments).

### Network Cables - PROFIBUS "DP"

Cross Section		Diameter in mm	Jacket Color	Packaging	Packaging Composition	Standard Order No	Sketch
mm <sup>2</sup>	AWG						
2x0,34	2xAWG22	8,2	Violet	S	1x200m	155421-1004	
				M	1x500m	155421-1005	
				L	1x1000m	155421-1006	

# Flamar Network Cables

## 155421 Profinet, WSOR Jacket

Drag Chain Installation, Shielded, -10°C/+70°C

**molex**

Cables with Weld-Slag and Oil-Resistant "WSOR" jacket cover the broadest range of industrial applications, allowing the reduction of inventory costs. Suitable for drag chain applications. To connect field based devices (sensors, actuators, I/O modules, PLC) in combination with M12 and RJ45 connectors.



### Specifications

Application: Severe environment  
 Installation: Drag Chain  
 Halogen Free: No  
 Temp. rating (flexible installation):  
 -10°C / +70°C  
 Voltage rating: 600V  
 Bending radius (flex. install. at 20°C):  
 > 15xOD  
 Insulation material: PE  
 Jacket material: WSOR  
 Shielded: Yes

Approval: UL AWM 21215 / CSA  
 Marking: acc. to UL/CSA  
 Silicone, Pb,Cd,Hg & FCKW free: Yes  
 Flame resistance:  
 Good (VW1/FT1 & IEC60332-1)  
 Key factor:  
 Weld-Slag and Oil-Resistant. A single cable solution for automotive lines and industrial applications. ECOLAB compatible (for Food & Beverage environments).

### Network Cables - PROFINET TYPE "C"

Cross Section		Diameter in mm	Jacket Color	Packaging	Packaging Composition	Standard Order No	Sketch
mm <sup>2</sup>	AWG						
2x2x0,34	2x2xAWG22	6,8	Green	S	3x100m	155421-5001	
				M	1x500m	155421-5002	
				L	1x1000m	155421-5003	

# Flamar Network Cables

## 155421 Ethernet, WSOR Jacket

Drag Chain Installation, Shielded, -10°C/+60°C

**molex**

Cables with Weld-Slag and Oil-Resistant "WSOR" jacket cover the broadest range of industrial applications, allowing the reduction of inventory costs. Suitable for drag chain applications. To connect field based devices (sensors, actuators, I/O modules, PLC) in combination with M12 and RJ45 connectors.



### Specifications

Application: Severe environment  
 Installation: Drag Chain  
 Halogen Free: No  
 Temp. rating (flexible installation):  
 -10°C / +60°C  
 Voltage rating: 600V  
 Bending radius (flex. install. at 20°C):  
 > 15xOD  
 Insulation material: PE  
 Jacket material: WSOR  
 Shielded: Yes

Approval: UL AWM 21215 / CSA  
 Marking: acc. to UL/CSA  
 Silicone, Pb,Cd,Hg & FCKW free: Yes  
 Flame resistance:  
 Good (VW1/FT1 & IEC60332-1)  
 Key factor:  
 Weld-Slag and Oil-Resistant. A single cable solution for automotive lines and industrial applications. ECOLAB compatible (for Food & Beverage environments).

### Network Cables - Ethernet Cat.5e

Cross Section		Diameter in mm	Jacket Color	Packaging	Packaging Composition	Standard Order No	Sketch
mm <sup>2</sup>	AWG						
2x2x0,14	2x2xAWG26	6,5	Teal	S	3x100m	155421-6001	
				M	1x500m	155421-6002	
				L	1x1000m	155421-6003	
4x2x0,14	4x2xAWG26	7,2		S	3x100m	155421-6004	
				M	1x500m	155421-6005	
				L	1x1000m	155421-6006	
2x2x0,25	2x2xAWG24	7,0		S	3x100m	155421-6007	
				M	1x500m	155421-6008	
				L	1x1000m	155421-6009	
4x2x0,25	4x2xAWG24	7,8	S	3x100m	155421-6010		
			M	1x500m	155421-6011		
			L	1x1000m	155421-6012		


# Flamar Network Cables

## 155431 CC-Link, PUR Jacket

Drag Chain Installation, Shielded, -20°C/+60°C

**molex**

Cables with Polyurethane (PUR, TPU) jacket ensure top mechanical performance, withstand harsh environments and resist to abrasion. Suitable for drag chain applications. To connect field based devices (sensors, actuators, I/O modules, PLC) in combination with M12 and RJ45 connectors.



### Specifications

Application: Harsh environment  
 Installation: Drag Chain  
 Halogen Free: Yes  
 Temp. rating (flexible installation):  
 -20°C / +60°C  
 Voltage rating: 300V  
 Bending radius (flex. install. at 20°C):  
 > 15xOD  
 Insulation material: Foam PE  
 Jacket material: PUR

Shielded: Yes  
 Approval: UL AWM 20233 / CSA  
 Marking: acc. to UL/CSA  
 Silicone, Pb,Cd,Hg & FCKW free: Yes  
 Flame resistance:  
 Good (VW1/FT1 & IEC60332-1)  
 Key factor:  
 Excellent resistance to oil and abrasion. Ensures top mechanical performances.

### Network Cables - CC-Link

Cross Section		Diameter in mm	Jacket Color	Packaging	Packaging Composition	Standard Order No	Sketch
mm <sup>2</sup>	AWG						
3x0,5	3xAWG20	7,7	Red	S	3x100m	155431-2001	
				M	1x500m	155431-2002	
				L	1x1000m	155431-2003	

# Flamar Network Cables

## 155431 PROFIBUS, PUR Jacket

Drag Chain Installation, Shielded, -20°C/+60°C

**molex**

Cables with Polyurethane (PUR, TPU) jacket ensure top mechanical performance, withstand harsh environments and resist to abrasion. Suitable for drag chain applications. To connect field based devices (sensors, actuators, I/O modules, PLC) in combination with M12 and RJ45 connectors.



### Specifications

Application: Harsh environment  
 Installation: Drag Chain  
 Halogen Free: Yes  
 Temp. rating (flexible installation):  
 -20°C / +60°C  
 Voltage rating: 300V  
 Bending radius (flex. install. at 20°C):  
 >15xOD  
 Insulation material: Foam PE  
 Jacket material: PUR

Shielded: Yes  
 Approval: UL AWM 20233 / CSA  
 Marking: acc. to UL/CSA  
 Silicone, Pb,Cd,Hg & FCKW free: Yes  
 Flame resistance:  
 Good (VW1/FT1 & IEC60332-1)  
 Key factor:  
 Excellent resistance to oil and abrasion. Ensures top mechanical performances.

### Network Cables - PROFIBUS "DP"

Cross Section		Diameter in mm	Jacket Color	Packaging	Packaging Composition	Standard Order No	Sketch
mm <sup>2</sup>	AWG						
2x0,34	2xAWG22	8,2	Violet	S	1x200m	155431-1004	
				M	1x500m	155431-1005	
				L	1x1000m	155431-1006	

# Flamar Network Cables

## 155431 Profinet, PUR Jacket

Drag Chain Installation, Shielded, -20°C/+70°C

**molex**

Cables with Polyurethane (PUR, TPU) jacket ensure top mechanical performance, withstand harsh environments and resist to abrasion. Suitable for drag chain applications. To connect field based devices (sensors, actuators, I/O modules, PLC) in combination with M12 and RJ45 connectors.



### Specifications

Application: Harsh environment  
 Installation: Drag Chain  
 Halogen Free: Yes  
 Temp. rating (flexible installation):  
 -20°C / +70°C  
 Voltage rating: 300V  
 Bending radius (flex. install. at 20°C):  
 > 15xOD  
 Insulation material: PE  
 Jacket material: PUR

Shielded: Yes  
 Approval: UL AWM 20233 / CSA  
 Marking: acc. to UL/CSA  
 Silicone, Pb,Cd,Hg & FCKW free: Yes  
 Flame resistance:  
 Good (VW1/FT1 & IEC60332-1)  
 Key factor:  
 Excellent resistance to oil and abrasion. Ensures top mechanical performances.

### Network Cables - PROFIBUS TYPE "C"

Cross Section		Diameter in mm	Jacket Color	Packaging	Packaging Composition	Standard Order No	Sketch
mm <sup>2</sup>	AWG						
2x2x0,34	2x2xAWG22	6,8	Green	S	3x100m	155431-5001	
				M	1x500m	155431-5002	
				L	1x1000m	155431-5003	

### Related Products

#### Field Attachable Connectors



**130047** – Brad Micro-Change (M12) Ethernet Field Attachable Connectors

**120100** – Brad Micro-Change (M12) Field Attachable Connectors, PROFIBUS Shielded

**120071** – Brad Micro-Change (M12) Field Attachable Connectors



**130034** – Brad Mini-Change Field Attachable Connectors

#### Overmolded Connectors



**130050** - Brad RJ-Lnxx RJ-45 Connectors



**130048** – Brad Micro-Change (M12 D-coded) Double-Ended Cordsets

**120108** – Brad Micro-Change (M12 D-coded) Double-Ended Cordsets



**120341** – Brad Micro-Change (M12 X-coded) Cat6<sub>A</sub>



**120098** – Brad Micro-Change (M12 B-coded)

# Flamar Network Cables

## 155431 Ethernet, PUR Jacket

Drag Chain Installation, Shielded, -20°C/+60°C

**molex**

Cables with Polyurethane (PUR, TPU) jacket ensure top mechanical performance, withstand harsh environments and resist to abrasion. Suitable for drag chain applications. To connect field based devices (sensors, actuators, I/O modules, PLC) in combination with M12 and RJ45 connectors.



### Specifications

Application: Harsh environment  
 Installation: Drag Chain  
 Halogen Free: Yes  
 Temp. rating (flexible installation):  
 -20°C / +60°C  
 Voltage rating: 300V  
 Bending radius (flex. install. at 20°C):  
 > 15xOD  
 Insulation material: PE  
 Jacket material: PUR

Shielded: Yes  
 Approval: UL AWM 20233 / CSA  
 Marking: acc. to UL/CSA  
 Silicone, Pb,Cd,Hg & FCKW free: Yes  
 Flame resistance:  
 Good (VW1/FT1 & IEC60332-1)  
 Key factor:  
 Excellent resistance to oil and abrasion. Ensures top mechanical performances.

### Network Cables - Ethernet Cat.5e

Cross Section		Diameter in mm	Jacket Color	Packaging	Packaging Composition	Standard Order No	Sketch
mm <sup>2</sup>	AWG						
2x2x0,14	2x2xAWG26	6,5	Teal	S	3x100m	155431-6001	
				M	1x500m	155431-6002	
				L	1x1000m	155431-6003	
4x2x0,14	4x2xAWG26	7,2		S	3x100m	155431-6004	
				M	1x500m	155431-6005	
				L	1x1000m	155431-6006	
2x2x0,25	2x2xAWG24	7,0		S	3x100m	155431-6007	
				M	1x500m	155431-6008	
				L	1x1000m	155431-6009	
4x2x0,25	4x2xAWG24	7,8		S	3x100m	155431-6010	
				M	1x500m	155431-6011	
				L	1x1000m	155431-6012	

A photograph of an industrial environment, likely a factory or laboratory. In the foreground, a yellow safety barrier is visible. In the background, there are various pieces of machinery, including a large blue panel and several bundles of cables. A yellow caution sign is attached to a metal surface on the left. The text 'HYBRID CABLES > FOR CUSTOM SOLUTIONS' is overlaid in white, bold, uppercase letters on the image.

## **HYBRID CABLES > FOR CUSTOM SOLUTIONS**

**Flamar designs and manufactures custom made Hybrid Cables according to customer requirements for a broad range of applications.**



# Flamar Hybrid Cables



# Flamar Hybrid Cables

## 155500


**molex**

**Ideal solutions in applications with signal and power conductors together with coax and transmission elements to reduce installation space.**



### Specifications

Cross section: 12-26AWG  
Insulating Material: PE – PP – PEE  
Pair Tape: 9/12 – 40/36  
Pair shielding: Braid  
Covering Material: TPV – TPO  
Tape: 9/12 – 40/36  
Shield: Braid  
Jacketing Material: PVC – PUR – PE




# Flamar Hybrid Cables 155500

molex

**120355** M12 CHT, 6-Pole,  
4+2 and 4+4

## Cable construction:

Shielded, 2 twisted data pair  
separated from power pair



## M12 CHT 4+2 Male-to-Male

Molded Cable Assembly:

Shielded, 2 twisted-pair data cable for best Cat5e speed  
Ethernet performance



## M12 CHT 4+4 Male-to-Male

Molded Cable Assembly:

Shielded, 4 data lines for best Cat5e speed  
Ethernet performance

# Flamar Hybrid Cables 155500


**molex**

Flamar can design and manufacture custom solutions in order to accommodate in a unique cable coaxial elements, air tubes, multi-cores assemblies.

This allows significant space saving and reduces the number of connections needed.



Few examples of Hybrid cables:






Multicore cable  
with air tubes

Multicore cable  
with coaxial cores

Contact us at:  
[flamar.cables@molex.com](mailto:flamar.cables@molex.com)

For our Industrial Automation standard cables we offer three different packaging types.

## 3 Packaging sizes

Small	Medium	Large
<p>3x100m ÷ 3x200m*</p> <p>3 cardboard reels inside one box</p>	<p>250m ÷ 800m*</p> <p>1 plywood reel</p>	<p>500m ÷ 1500m*</p> <p>1 wooden drum</p>
		

\* Depending on cable diameter

# Useful documentation and resources available

## Molex Heavy Duty Connectors & Flamar Standard Cables For Industrial Automation

Size	Poles	Hoods & Inserts					Cable	Cable p/n per packaging size and jacket (1,5mm <sup>2</sup> - 16AWG)
		Straight	90°	Male Insert	Female Insert	Cable Gland		
<b>3A</b> "21x21"	4 + ground	*7803.6228.0 †93601-0682	*7803.6220.0 †93601-0668	*7204.6102.0 †93601-0133	*7204.6002.0 †93601-0129	*7000.6831.0 †93600-0024 metal		5 cores † <b>155220-0235</b> /6/7 <b>WSOR</b> † 155230-0235 /6/7 PUR
		*7803.6232.0 †93601-0692				*7000.7823.0 †93600-0349 plastic		
<b>6B</b> "44x27"	6 + ground	*7806.6553.0 †93601-0917	*7806.6551.0 †93601-0911	*7306.5961.0 †93601-0206	*7306.5861.0 †93601-0204	*7000.6831.0 †93600-0024 metal		7 cores † <b>155220-0241</b> /2/3 <b>WSOR</b> † 155230-0241 /2/3 PUR
						*7000.7823.0 †93600-0349 plastic		
<b>10B</b> "57x27"	10 + ground	*7810.6570.0 †93601-1746	*7810.6569.0 †93601-1741	*7310.5962.0 †93601-0230	*7310.5862.0 †93601-0228	*7000.6831.0 †93600-0024 metal		12 cores † <b>155220-0253</b> /4/5 <b>WSOR</b> † 155230-0253 /4/5 PUR
						*7000.7823.0 †93600-0349 plastic		
<b>16B</b> "77x27"	16 + ground	*7816.6572.0 †93601-2824	*7816.6571.0 †93601-2819	*7316.5963.0 †93601-0261	*7316.5863.0 †93601-0257	*7000.6832.0 †93600-0026 metal		17 cores † <b>155220-0259</b> /60/61 <b>WSOR</b> † 155230-0259 /60/61 PUR
						*7000.7824.0 †93600-0355 plastic		
<b>24B</b> "104x27"	24 + ground	*7824.6926.0 †93601-3857	*7824.6927.0 †93601-3862	*7324.5965.0 †93601-0295	*7324.5865.0 †93601-0291	*7000.6833.0 †93600-0028 metal		25 cores † <b>155220-0265</b> /6/7 <b>WSOR</b> † 155230-0265 /6/7 PUR
						*7000.7825.0 †93600-0361 plastic		

**Legend:**

WSOR: Weld-Slag and Oil-Resistant. PUR: Polyurethane (TPU).  
In **bold**: typical configuration. PVC (series 155210) and TPE (series 155240) jacket available as well.

**Ordering No. Legend:**

\*7000.6833.0: Engineering No.  
†93600-0028: Standard Ordering No.

**Flamar Cables Flyer**  
987651-4581

**Flamar Samples Card**

**Molex Heavy Duty Connectors Fast Check Fold Out**  
987651-1521

**Molex Heavy Duty Connectors Full Catalog**  
987651-1522

# Connector Series Index

Field Attachable Connectors	Pages												
93601 - GWconnect Heavy Duty Connectors	16	28	40	51									
120071 – Brad Micro-Change (M12)	10	16	19	22	28	31	34	40	43	45	51	53	74
120085 – Brad Ultra-Lock (M12)	10	16	19	22	28	31	34	40	43	45	51	53	
120091 – Brad Nano-Change (M8)	10	19	22	31	34	43	45	53					
120100 – Brad Micro-Change (M12) PROFIBUS Shielded	74												
120230 – Brad M23 Signal Connectors	17	29	41	57	59	61							
120233 – Brad M23 Power Connectors	17	29	41	57	59	61							
120604 – Brad M40	57	59	61										
121201, 121207 – Brad mPm DIN Valve Connectors, Form A, External Thread	16	28	40	51									
121202, 121208 – Brad mPm DIN Valve Connector, Form B - Industrial, External Thread	16	28	40	51									
121205, 121211 – Brad mPm DIN Valve Connector, Form C - Industrial, External Thread	16	28	40	51									
130034 – Brad Mini-Change	74												
130047 – Brad Micro-Change (M12) Ethernet	74												

Overmolded Connectors	Pages												
120006 – Brad Micro-Change (M12) Single-Ended Cordsets	10	19	22	31	34	43	45	53					
120009 – Brad Micro-Change (M12) Cordsets with Knurled Hexnuts	10	19	22	31	34	43	45	53					
120027, 120028, 120086, 120087 – Brad Nano-Change (M8) Single-Ended and Double Ended Cordsets	10	19	22	31	34	43	45	53					
120065, 120066 – Brad Micro-Push (M12) Single-Ended and Double Ended Cordsets	10	19	22	31	34	43	45	53					
120094 – Brad M23 Single-Ended Cordsets	16	17	28	29	40	41	51						
120098 – Brad Micro-Change (M12 B-coded)	74												
120108 – Brad Micro-Change (M12 D-coded) Double-Ended Cordsets	74												
120341 – Brad Micro-Change (M12 X-coded) Cat6A	74												
120355 M12 CHT, 6-Pole, 4+2 and 4+4	79												
120480 – Brad M23 Power Cordsets	57	59	61										
120490 – Brad M23 Signal Overmolded Cordsets	57	59	61										
120600 – Brad M40	57	59	61										
130048 – Brad Micro-Change (M12 D-coded) Double-Ended Cordsets	74												
130050 - Brad RJ-Lnxx RJ-45 Connectors	74												

Get more insights at: [www.molex.com/flamar](http://www.molex.com/flamar)

**molex**  
one company › a world of innovation

Molex is a registered trademark of Molex, LLC in the United States of America and may be registered in other countries. All other trademarks listed herein belong to their respective owners.

Order No. 987651-3992 Rev.2

Printed in Italy/3.5K/BD/LB/2017.03

©2017 Molex