

.050" 28 AWG STRANDED, MEDIUM FLEX LIFE, HALOGEN FREE PO



1. MATERIAL:
 - A) PRIMARY INSULATION: HALOGEN FREE POLYOLEFIN (PO).
 - B) CONDUCTORS: 28 AWG, 19 X 40 AWG (19 X , Ø 0.079), TINNED STRANDED COPPER.
2. REGULATORY INFORMATION:

ROHS COMPLIANT. SEE THE REGULATORY INFORMATION APPENDIX (RIA) IN THE "RoHS COMPLIANCE" SECTION OF WWW.3MCONNECTORS.COM FOR COMPLIANCE INFORMATION (RIA E1 & C1 APPLY)

UL FILE NO: E42769,
UL STYLE NO: 21682.
3. MARKINGS:

STANDARD: NONE
CANADIAN: SEE "PRINTING ILLUSTRATION" VIEW
PRIMARY CABLE: BLUE MARK ON EDGES
DESIGNATES WIRE NUMBER 1.
4. THE SURFACE DEFINED BY THE "ZIP" PROCESS IS NOT REQUIRED TO BE BLUE.
5. ENVIRONMENTAL:

TEMP RATING: -40°C TO 105°C
FLAMABILITY RATING: HORIZONTAL.
6. HALOGEN FREE IS DEFINED AS BOTH:
 - 1) NO HALOGEN COMPOUNDS THAT ARE INTENTIONALLY ADDED TO THE PRODUCT OR USED IN THE MANUFACTURING PROCESS FOR THE PRODUCT.
 - 2) ANY IMPURITIES PRESENT ARE LESS THAN 900 ppm BROMINE, LESS THAN 900 ppm CHLORINE AND/OR LESS THAN 1500 ppm TOTAL BROMINE AND CHLORINE. THE LATTER ARE THE LEVELS SET FORTH IN CERTAIN INDUSTRY STANDARDS FOR PRINTED CIRCUIT BOARDS, SUCH AS THE INTERNATIONAL ELECTROTECHNICAL COMMISSION (IEC) 61249-2-21 STANDARD. THIS INFORMATION REPRESENTS 3M/S KNOWLEDGE AND BELIEF WHICH MAY BE BASED IN WHOLE OR IN PART ON INFORMATION PROVIDED BY 3RD PARTY SUPPLIERS TO 3M.

NUMBER OF CONDUCTORS	3M PART NUMBER	DIMENSION 'A' ± AS NOTED	DIMENSION 'B' (SEE NOTE 2)
6	HF539/06	0.300"±0.010"	0.250"±0.007"
9	HF539/09	0.450"±0.010"	0.400"±0.007"
10	HF539/10	0.500"±0.010"	0.450"±0.007"
14	HF539/14	0.700"±0.010"	0.650"±0.007"
15	HF539/15	0.750"±0.010"	0.700"±0.007"
16	HF539/16	0.800"±0.015"	0.750"±0.011"
20	HF539/20	1.000"±0.015"	0.950"±0.011"
24	HF539/24	1.200"±0.015"	1.150"±0.011"
25	HF539/25	1.250"±0.015"	1.200"±0.011"
26	HF539/26	1.300"±0.015"	1.250"±0.011"
30	HF539/30	1.500"±0.020"	1.450"±0.015"
34	HF539/34	1.700"±0.020"	1.650"±0.015"
36	HF539/36	1.800"±0.020"	1.750"±0.015"
37	HF539/37	1.850"±0.020"	1.800"±0.015"
40	HF539/40	2.000"±0.020"	1.950"±0.015"
50	HF539/50	2.500"±0.020"	2.450"±0.015"
60	HF539/60	3.000"±0.020"	2.950"±0.015"
64	HF539/64	3.200"±0.020"	3.150"±0.015"

X HF539/XX XX
 BLANK = STANDARD
 C = CANADIAN
 NUMBER OF CONDUCTORS
 (SEE TABLE 1)
 BLANK = STANDARD
 SF = SPLICE FREE

VOLTAGE RATING	USA: 300V, CANADA: 150V, EU: 50V	
INSULATION RESISTANCE	PRIMARY CABLE $>1 \times 10^{10} \Omega/10 \text{ FT}$ [3 m]	
	UNBALANCED	BALANCED
CHARACTERISTIC IMPEDANCE	100 Ω	168 Ω
CAPACITANCE	15.0 pF/ft [49.2 pF/m]	8.4 pF/ft [27.7 pF/m]
INDUCTANCE	0.15 $\mu\text{H}/\text{ft}$ [0.49 $\mu\text{H}/\text{m}$]	0.24 $\mu\text{H}/\text{ft}$ [0.79 $\mu\text{H}/\text{m}$]
PROPAGATION DELAY	1.51 ns/ft [4.95 ns/m]	1.42 ns/ft [4.66 ns/m]
VELOCITY OF PROPAGATION	68%	72%

NOTE: UNBALANCED IS MEASURED BETWEEN GROUND-SIGNAL-GROUND CONDUCTORS.
BALANCED IS MEASURED WITHIN A PAIR.


3M™ ELECTRONIC SOLUTIONS DIVISION
INTERCONNECT SOLUTIONS
<http://www.3mconnectors.com>

3M IS A TRADEMARK OF 3M COMPANY.
FOR TECHNICAL, SALES OR ORDERING
INFORMATION CALL 800-225-5373

AWM 21682 105 °C 300V HOR  AWM 1A 105 ° 150V FT2 EU<50V

RADIUS	MINIMUM CYCLES
1/2"	0.4 MILLION
3/4"	5 MILLION
1 3/4"	10 MILLION

NOTE: REPRESENTS MINIMUM ROLLING FLEX CYCLES AT DATE OF PUBLICATION. ADDITIONAL TESTING IS ONGOING. CABLE CONSTRUCTION AND MATERIAL IS SIMILAR TO 3319 SERIES CABLE WHICH IS RATED TO 100 MILLION CYCLES AT 7/8" RADIUS. SEE TS-0732. CONTACT 3M FOR THE MOST UP-TO-DATE INFORMATION.

A 44734		DEC 06, 2012		JNC	RE
PRODUCTION RELEASE					
REV		ECO	ISSUE DATE AND DESCRIPTION	DRFT	CHKD
DPT CAST		GLIGLONE		DATE NOV 05, 2012	MFG DATE
CHKD		DATE		APPR R. EDWARDS	DATE NOV 05, 2012
DIVISION Interconnect Solutions		DIVISION CODE ISD		© 3M COPYRIGHT 2013	
DO NOT SCALE DRAWING		TOLERANCES EXCEPT AS NOTED		 St. Paul, MN 55144 This document and the information it contains are 3M property and may not be reproduced or further distributed without 3M permission, or used or disclosed other than for 3M authorized purposes. All rights reserved.	
 THIRD ANGLE PROJECTION		INCHES .00 .01 .05 .000 .010 .0000		TITLE MEDIUM FLEX LIFE FLAT CABLE, .050", 28 AWG, HF539	
INTERPRET PER ASME Y14.5 - 1994 MAX SURFACE ROUGHNESS ☒ FIN SURFACES ☐ MARKED ONLY		MILLIMETERS 0 .5 1.3 .00 .25 .000		CAGE NUMBER D 78-5100-2565-9	
ANGLE		SIZE D		DRAWING NO. 78-5100-2565-9	
MODEL		REV. DET. LISTS ☒ YES ☒ NO		SHT 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

3M:

[HF539/10](#) [HF539/14](#) [HF539/16](#) [HF539/20](#) [HF539/26](#) [HF539/30](#) [HF539/34](#) [HF539/34SF](#) [HF539/40](#) [HF539/50](#)
[HF539/64](#)