

High-Precision I²C 3D Linear Hall Effect Sensor for Rotary and Proximity Detection in Automotive Applications

The automotive-compliant* AH4930Q is Diodes Incorporated's (Diodes) first 3D linear Hall effect sensor. It has been qualified to AEC-Q100 Grade 1 with an extended temperature range of -40°C to +125°C.

The high-performance AH4930Q provides a compact solution for high-precision magnetic sensing. An integrated temperature sensor in this monolithic sensor IC provides accurate on-chip compensation. Its robust signal path and high-resolution ADC enables precise measurement of magnetic fields in all three axes, facilitating accurate decoding of motion and position information.

The AH4930Q integrates user-programmable configuration registers for optimized performance. Data is accessible via an I²C interface (up to 1Mbps), enabling seamless integration with host systems. The selectable power mode control unit allows for flexible operation, ranging from power-down (9nA) mode when the system is sleeping, to continuous (fast) mode (3.8mA) for constant measurement functionality in active, demanding applications.

Diodes also provides the AH4930 commercial-grade device for industrial applications. The AH4930Q and AH4930 are available in the industry-standard SOT26 package.

*Automotive-compliant - AEC qualified, manufactured in sites certified to IATF 16949 supporting PPAP documents.

The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries.

All other trademarks are the property of their respective owners.

© 2025 Copyright Diodes Incorporated. All Rights Reserved.



The DIODES Advantage

The AH4930Q 3D Hall sensor provides reliable and high-precision proximity detection in a wide range of automotive applications.


- **High-Accuracy 12-Bit Data Converter Hall Sensor Measurement**
Provides stable measurements with resolution down to 1 Gauss
- **1Mbps I²C Interface for Control and Measurements**
Provides seamless integration with host systems with increased flexibility
- **On-Chip 12-Bit Temperature Sensor**
Provides accurate junction temperature measurement across temperature measurement compensation
- **Three Operating Modes and Variable Update Rates with Power-Down Mode**
Enables an optimized speed/power performance solution with current consumption down to 9nA
- **Fast 10µs Start Up and 4µs Response Time**
Supports quick reaction to changes in magnetic field

Applications

Automotive contactless proximity/rotation detection in:

- Stalk gear shifters
- Shifter position sensors
- Flap positions
- Mirror positions
- Multimedia rotary/push-selectors
- Door handles & door locks
- Powered seat adjusters

Typical Application



Automotive-Compliant 3D Hall Sensor Portfolio

Part Number	Output Type	Operating Voltage	Ave. Supply	Typical Sensitivity	Output Resolution	Offset	Magnetic Linear Range	Temp. Sensor Resolution	ESD HBM/CDM	Ambient Temp. Range	Package
		V	µA	LSB/Gauss	Gauss/LSB	Gauss	Gauss	°C/LBM	kV	°C	
AH4930Q	I ² C	2.8 to 5.5	13	1	1	-2	±1300	1	2/1	-40 to +125	SOT26 (Type A1)

LSB: Last-Significant Bit in I²C data format

Ordering Information

Orderable Part Number	Compliance (Only Automotive Supports PPAP)	Package	Moisture Sensitivity	Packing	
				Quantity	Carrier
AH4930Q-W6-7	Automotive	SOT26 (Type A1)	MSL-1	3,000	7" Tape & Reel