



Product **APPLICATION** Guide

IEC60601-1-8 Medical Piezo Transducers



- **UL File # MDAF2.E480572**
- **cUL File # MDAF8.E480572**
- **The user needs to apply a square wave signal at the rated drive frequency (200 Hz).**
- **This results in a sound with a fundamental frequency < 1 kHz and at least 4 harmonics (1-4 kHz) that are within ± 15 dB of the fundamental frequency as required by Tables 3 & 4.**
- **It is up to the user to adjust the control signal to meet the required rise time and fall times listed in Tables 3 & 4.**

IEC60601-1-8 Piezo Transducer (No Circuitry)

Part Number	Typical Sound Level @ 10 cm	Freq (Hz)	Operating Voltage (Vp-p)	Current (mA)	Capacitance (pF)	Dia x Hgt (mm)	Housing Type
SBT200PC	90 dBa	200	1 - 30	1.5 - 10	70,000	44.5 x 14	2 PC Pins
SBT200FL	90 dBa	200	1 - 30	1.5 - 10	70,000	64.5 x 14	Flange

Call 317-612-1000 or Visit www.mallory-sonalert.com for More Details