

**THM MT30X 18/9 WS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Similar to illustration

The THM labels offer brilliant printing quality thanks to the thermal transfer technology. Different materials and the user-friendly printing system under Windows optimise every marking effort.

- High-quality polyester labels in various colours or inexpensive paper labels are available
- Labels are automatically positioned in the printer for perfectly centred prints on each label.

**General ordering data**

|                    |                                                       |
|--------------------|-------------------------------------------------------|
| Version            | THM, Device markers, 9 x 18 mm, white                 |
| Order No.          | <a href="#">1753251044</a>                            |
| Type               | THM MT30X 18/9 WS                                     |
| GTIN (EAN)         | 4032248008537                                         |
| Qty.               | 1 pc(s).                                              |
| compatible printer | <a href="#">2599430000</a> <a href="#">2599440000</a> |

## THM MT30X 18/9 WS

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 0.08 mm | Depth (inches)  | 0.003 inch |
| Height     | 9 mm    | Height (inches) | 0.354 inch |
| Width      | 18 mm   | Width (inches)  | 0.709 inch |
| Net weight | 350 g   |                 |            |

## Temperatures

|                             |              |
|-----------------------------|--------------|
| Operating temperature range | -40...150 °C |
|-----------------------------|--------------|

## General data

|                                              |                               |            |
|----------------------------------------------|-------------------------------|------------|
| Adhesive                                     | Acrylate adhesive             |            |
| Approval acc. to UL 969                      | Yes                           |            |
| Colour                                       | white                         |            |
| Halogen                                      | No                            |            |
| Material                                     | Polyester                     |            |
| Material colour according to resistance code | 9                             |            |
| Number of markers per combination            | 1 Label reel = Device markers |            |
| Number of markers per packaging unit         | Form of supply                | Label reel |
| Number per roll                              | 10,000                        |            |
| Operating temperature range                  | -40...150 °C                  |            |
| Operating temperature range, max.            | 150 °C                        |            |
| Operating temperature range, min.            | -40 °C                        |            |
| Printed characters                           | without                       |            |
| Printing method                              | Thermal transfer              |            |
| UL 94 flammability rating                    | V-0                           |            |
| Version                                      | Self-adhesive, halogen-free   |            |
| Width                                        | 18 mm                         |            |

## Device markers

|         |    |
|---------|----|
| Halogen | No |
|---------|----|

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001288    | ETIM 7.0    | EC001288    |
| ETIM 8.0    | EC001288    | ETIM 9.0    | EC001288    |
| ETIM 10.0   | EC001288    | ECLASS 9.0  | 27-40-06-29 |
| ECLASS 9.1  | 27-40-06-29 | ECLASS 10.0 | 27-40-06-29 |
| ECLASS 11.0 | 27-28-11-04 | ECLASS 12.0 | 27-28-11-04 |
| ECLASS 13.0 | 27-28-11-04 | ECLASS 14.0 | 27-28-11-04 |
| ECLASS 15.0 | 27-28-11-04 |             |             |

## Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### THM MT30X 18/9 WS

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Downloads

Engineering Data

[CAD data – STEP](#)

Catalogues

[Catalogues in PDF-format](#)

**THM MT30X 18/9 WS**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

