

TRAVEO™ T2G CYT3DL MCU series

Providing unparalleled excellence for automotive clusters and graphics

Infineon releases its second generation TRAVEO™ microcontroller in embedded flash 40 nm technology. It comes back with an increase in graphic performance, memory sizes and connectivity to address the new automotive trends and challenges. CYT3DL offers one of the most scalable safety and graphic microcontroller portfolios. In terms of performance, it offers single core Cortex® - M7 running up to 240 MHz, up to 2M Bytes embedded VRAM, graphics for up to 1280x480 display resolution on two packages (216-TQFP and 272-BGA). It is consuming below 457 mA in Active mode and 50 uA in DeepSleep mode with 32 KB RAM retention. Its mirrored embedded flash banks offer A/B swap capabilities.

Graphics subsystem supports 2D and 2.5D (perspective warping, 3D effects) graphics rendering up to 24-bit color resolution (RGB). CYT3DL provides one capture engine for video input processing for ITU 656 or parallel RGB/YUV or MIPI CSI-2 input and up to two video output interfaces supporting two displays from parallel RGB, FPD-link single.

Safety is the core know-how of Infineon, and all products provide safety mechanism (including MBIST, ECC Flash/RAM, CRC) to ensure a safety platform supporting ASIL-B ISO 26262. State-of-the-art security with Secure Boot support by a dedicated ARM® Cortex®-M0+ core and security hardware to accelerate cryptographic functions.

In terms of security, this product has an HSM compliant Evita full, ensuring the implementation of future proofed security measure. On top of this, it offers extensive connectivity with 4 CAN FD, 2 LINs, two SPIs and new high-speed communicating interfaces such as one 10/100MHz Ethernet and two CXPIs.

The TRAVEO™ CYT3DL offers single chip solution up to 1280x480 display with enhancing 2.5D graphics engine. On-The-Fly rendering mode and hardware decompression enables the most cost-efficient smart Cockpit without high-end 3D SoC or complicated software. And it features a dedicated best-in-class standby mode controller, with its own voltage domain to, not only support low power modes, but also to perform certain operations such as analog measurements, CAN and LIN communications, RTC and basic processing while the rest of microcontroller is in standby.



Key features

- ARM® Cortex®-M7 single CPU up to 240 MHz operation
- Up to 4 MB flash, 128 KB work flash, 384 KB SRAM
- 2.5D graphics engine for up to 1280x480 display, 2M VRAM, Vector drawing,
- Video-out: 2-ch (LVDS, RGB)/ Video-In: 1-ch (RGB, MIPI)
- 2x Mixer, 5x Sound Generator, 2x PCM-PWM, DAC
- Up to 1-ch 100M bit Ethernet, 4-ch CAN-FD, 12-ch SCB, 2-ch LIN, 2-ch CXPI and 2-ch SMIF
- Cortex®-M0+ for HSM security

Key benefits

- Single chip graphic solution up to 1280x480 display
- Optimized memory footprint for reduced BOM
- Best-in-class performance enabling ASIL-B designs
- A/B swap software update over the air support
- Best-in-class power consumption
- TRAVEO™ T2G graphic MCU portfolio for a wide range of applications and a high level of software re-use


Key applications

- Instrument cluster
- HUD
- Lighting system
- Cost effective cockpit solution



PRODUCT BRIEF

Block Diagram



Product table

Device Code	Ordering Code	Package	CM7 Cores	Code-flash (KB)	Work-flash (KB)	RAM (KB)	ADC Channels	SCB	CAN FD	LIN	CXPI	Ethernet Channels	SMIF	Audio DAC	MIPI	Temperature Grade	JTAG ID CODE
CYT3DLBBHS	CYT3DLBBHBQ1BZSGS	272-BGA	1	4160	128	384	48	12	4	2	2	1	2	1	1	105°C	0x1E848069
CYT3DLABHS	CYT3DLABHBQ1AESGS	216-TE-QFP	1	4160	128	384	48	12	4	2	2	1	2	1	1	105°C	0x1E850069

Published by
Infineon Technologies AG
Am Campeon 1-15, 85579 Neubiberg
Germany

© 2023 Infineon Technologies AG
All rights reserved.

Public

Date: 02/2024

Please note!
This Document is for information purposes only and any information given herein shall in no event be regarded as a warranty, guarantee or description of any functionality, conditions and/or quality of our products or any suitability for a particular purpose. With regard to the technical specifications of our products, we kindly ask you to refer to the relevant product data sheets provided by us. Our customers and their technical departments are required to evaluate the suitability of our products for the intended application.

We reserve the right to change this document and/or the information given herein at any time.

Additional information
For further information on technologies, our products, the application of our products, delivery terms and conditions and/or prices, please contact your nearest Infineon Technologies office (www.infineon.com).

Warnings
Due to technical requirements, our products may contain dangerous substances. For information on the types in question, please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by us in a written document signed by authorized representatives of Infineon Technologies, our products may not be used in any life-endangering applications, including but not limited to medical, nuclear, military, life-critical or any other applications where a failure of the product or any consequences of the use thereof can result in personal injury.



Scan QR code and explore offering
www.infineon.com