


Saddle Mount:
**Elegant
design meets
brute-force
performance.**

MADE FOR REAL®



Feature-rich cable mount for greater convenience, faster installs.

- Mount single or dual, separated routings with a single part.
- Screw mount allows flexibility of panel or frame attachment (with optional T-nut).
- Exclusive EZ Feed and CutZone features simplify insertion and safe removal of cable ties.



Double saddles firmly hold and separate wires (if wire separation is desired).



CutZone prevents nicking or cutting bundles.



Large center saddle to hold bigger bundles.

EZ Feed Cable Tie Slot for unobstructed tie insertion.



Screw mount allows flexibility of panel or frame attachment (with optional T-nut).

Bundling and Securing

Cable Tie Mounts

Screw Mounting Bases

Heat Stabilized Saddle Mounts

Designed specifically for holding heavier cable bundles, these mounting bases can be used in many industries from agriculture to truck manufacturing. They mount securely and can be used with a wide variety of heavy duty cable ties up to 8.3 mm width. Cables are held in place and aligned by troughs in the mount's arms. The EZ Feed cable tie slot eliminates common obstructions for faster completion. During rework, the CutZone prevents wire damage when cutting off cable ties.



Features and Benefits

- Saddle Mounts are designed to provide stability to wire bundles.
- These mounts can accommodate miniature, intermediate or standard cross-section cable ties.
- Built-in CutZone safety feature prevents damage to wires and cables.
- Unique EZ Feed slot maintains clear space to insert cable ties.
- Allows flexibility of frame size and mounting location with #10 (M5) screw into panel surface or with T-nut in frame.

MATERIAL	Polyamide 6.6 heat stabilized (PA66HS)
Flammability	UL 94 V-2



PART NO.	TYPE	Cable Tie Series	Mounting Screw Type	Length (L) in. (mm)	Width (W) in. (mm)	Height (H) in. (mm)	Color	Pkg. Qty.
151-04156	CTSM3CZS	T18 - T120	#10 (M5) Screw	1.1 (28.0)	0.7 (16.8)	0.5 (11.7)	Black	100
151-04488		T18 - T120	#10 (M5) Screw	1.1 (28.0)	0.7 (16.8)	0.5 (11.7)	Black	1000
151-04486		T18 - T120	#10 (M5) Screw	1.1 (28.0)	0.7 (16.8)	0.5 (11.7)	White	100
151-04487		T18 - T120	#10 (M5) Screw	1.1 (28.0)	0.7 (16.8)	0.5 (11.7)	White	1000

Dimensions are approximate and subject to technical changes. Use Part No. for ordering and Type for specification purposes.

HellermannTyton

HellermannTyton North American Corporate Headquarters

7930 N. Faulkner Rd, PO Box 245017
Milwaukee, WI 53224-9517
Phone: (414) 355-1130, (800) 537-1512
Fax: (414) 355-7341, (800) 848-9866
email: corp@htamericas.com
www.hellermann.tyton.com

IATF 16949, AS9100, ISO 9001 and ISO14001 certified

HellermannTyton Canada

Unit #4, 205 Industrial Parkway North
Aurora, Ontario L4G 4C4 Canada
Phone: (800) 661-2461
Fax: (800) 390-3904
email: sales@hellermanntyton.ca

HellermannTyton Mexico

Anillo Periferico Sur 7980 Edificio 6A
Parque Industrial Tecnologico II
Santa Maria Tequepexpan
Tlaquepaque, Jalisco, Mexico 45601
Phone: 011-52-33-3-133-9880
Fax: 011-52-33-3-133-9861
email: info-mx@hellermanntyton.com
ISO 9001 certified

Warranty Policy – HellermannTyton products are warranted to be free from defects in material and workmanship at the time sold by us; but our obligation under this warranty and that of the seller is limited to the replacement of the product, and neither we nor the seller are bound by any other warranty, expressed, implied or statutory. Under no circumstances are we or the seller liable for any loss, damage, expenses or consequential damages of any kind arising out of the use or inability to use these products. All are sold with the understanding that the user will test them in actual use and determine their adaptability for the intended uses.