

# M2-JODY-W2 module

## M.2 card with JODY-W2 Wi-Fi 5 and Bluetooth 5.0 module



### Module supporting IEEE 802.11ac and Bluetooth/Bluetooth Low Energy 5.0

- M.2 Type 2230 Key E form factor
- Dual-band Wi-Fi 2.4 GHz and 5 GHz, 802.11a/b/g/n/ac
- Dual-mode Bluetooth 5 (Bluetooth BDR/EDR/Low Energy)
- Simultaneous access point (AP), station (STA), or Wi-Fi Direct (P2P)
- Optimized for parallel operation of Wi-Fi and Bluetooth
- Compatible with NXP i.MX evaluation and development boards

22.0 x 30.0 x 4.2 mm



M2-JODY-W263

### Product description

The M2-JODY-W2 card combines the maximum performance of the JODY-W2 Wi-Fi 5 and Bluetooth 5.0 connectivity module with the flexibility and ease of use of a M.2 card. The card supports all features of the JODY-W2 series modules and is based on the NXP 88W8987 chipset. M2-JODY-W2 supports 1x1 single-antenna 802.11ac Wi-Fi operation, with data rates up to 433 Mbit/s. A second antenna is dedicated for Bluetooth operation.

M2-JODY-W2 is a host-based module that requires a host processor running a Linux or Android operating system. It connects to a host processor through SDIO (for Wi-Fi), or high-speed UART (for Bluetooth) interfaces. Support for other operating systems such as QNX will also be available. Radio type approvals are pending for the US, Europe, and Canada.

### Key features

- M.2 Type 2230 Key E form factor
- Wi-Fi 1x1 SISO IEEE 802.11ac data rates up to 433 Mbit/s (PHY, MCS9), beamforming
- Supports 802.11d/e/h (DFS)/i/k/r/u/v/w/ai
- Wi-Fi 20, 40, and 80 MHz channels
- Bluetooth BR/EDR and Bluetooth low energy v5.0 supporting 2 Mbit/s
- Chipset is compliant with AEC-Q100
- SDIO host interface
- PCM interface for Bluetooth audio
- Access point mode for up to 8 stations
- Hardware encryption engines: AES and TKIP
- Security: WPA, WAPI, WPA2, WPA3, WPS, and Easy Connect

Grade	Automotive
Professional	
Standard	•
Radio	
Chip inside	NXP 88W8987
Bluetooth qualification	v5.0
Bluetooth profiles	HCI
Bluetooth BR/EDR	•
Bluetooth Low Energy	•
Wi-Fi IEEE 802.11 standards	a/b/g/n/ac
Wi-Fi 2.4 / 5 [GHz]	2.4 and 5
Max output power at antenna pin [dBm]	18
Antenna type	2 U.FL connectors
OS support	
Android / Linux drivers (from u-blox)	•
Interfaces	
UART <sup>B</sup>	1
SDIO [version] <sup>W</sup>	v3
PCM (Bluetooth audio)	1
Features	
Micro Access Point [max connects]	8
AES hardware support	•
RF parameters in OTP memory	•
MAC addresses in OTP memory	•

B = For Bluetooth only  
W = For Wi-Fi only

DRCS = Dynamic Rapid Channel Switching

**Features**

Wi-Fi standards	IEEE 802.11a/b/g/n/ac IEEE 802.11d/e/h/i/k/r/u/v/w/ai
Wi-Fi channels	2.4 GHz: 1-13 5 GHz: 36-165
Bluetooth	v5.0 (Bluetooth Low Energy and Bluetooth with EDR) Class 1 and 2 transmission
Antenna connectors	U.FL 1: 2.4 GHz and 5 GHz Wi-Fi U.FL 2: Bluetooth
Output power	Wi-Fi IEEE 802.11b: 18 dBm Wi-Fi IEEE 802.11a/g/n/ac: 16.5 dBm Bluetooth BDR: 13 dBm (w/o LTE filter) Bluetooth EDR: 10 dBm (w/o LTE filter)
Security	Hardware encryption engine: AES-CCMP, AES-GCMP, TKIP WPA/WPA2/WPA3 128-bit AES hardware support

**Software features**

RF parameters	Available in on-board OTP memory
MAC addresses	Available in on-board OTP memory
Security	WEP WPA2 (CCMP, AES), WAPI WPA3 (OWE, SAE, CSNA, DPP)
Wi-Fi modes	Station (STA): Infrastructure and direct mode AP: Supports up to 8 stations Wi-Fi direct
Driver support	Linux drivers in source code

**Interfaces**

Wi-Fi	SDIO v3.0 (4-bit, 208 MHz)
Bluetooth	High-speed UART, 4-wire (default) SDIO v3.0 <sup>1</sup>
Bluetooth audio	High-speed UART, 4-wire, up to 4 Mbit/s PCM audio, 8, 16 KHz sampling
Other interfaces	GPIOs

<sup>1</sup> = Upon request; requires minor hardware modification

**Package**

Dimensions	22.0 x 30.0 x 4.2 mm
Mounting	M.2 Key-E connector 2199230-4 on host platform

**Environmental data, quality and reliability**

Operating temperature	TBD
Standard qualification	

**Electrical data**

Power supply	3.3 V (from M.2 card voltage pin) 1.8 V (generated by on-card DCDC)
I/O power supply	3.3 V or 1.8 V (default: 1.8 V)

**Certifications and approvals**

Type approvals	TBD
Bluetooth qualification	TBD

**Product variants**

M2-JODY-W263	Standard grade M.2 card module with two antenna connectors (one for 2.4 GHz and 5 GHz 802.11ac, and one for Bluetooth/Bluetooth Low Energy 5.0). NXP chipset 88W8987
--------------	--

**Further information**

For contact information, see [www.u-blox.com/contact-u-blox](http://www.u-blox.com/contact-u-blox).

For more product details and ordering information, see the product data sheet.

**Legal Notice:**

u-blox reserves all rights to this document and the information contained herein. Products, names, logos and designs described herein may in whole or in part be subject to intellectual property rights. Reproduction, use, modification or disclosure to third parties of this document or any part thereof without the express permission of u-blox is strictly prohibited.

The information contained herein is provided "as is". No warranty of any kind, either express or implied, is made in relation to the accuracy, reliability, fitness for a particular purpose or content of this document. This document may be revised by u-blox at any time. For most recent documents, please visit [www.u-blox.com](http://www.u-blox.com).

Copyright © 2021, u-blox AG