





CD-2001-XXX, CD-920-XXX



Using installation tooling shown on other side, insert connector in die and crimp between color bands or knurl markings, use these markings as a guide to evenly space crimps on barrel of connector. Begin crimping near the tongue end of the lug and continue crimping toward the wire end. REQUIRED NUMBER OF COMPRESSIONS SHOWN ON TOOL CHART IN ().



2
(CDI-920-XX)



(CD-920-XXXNEST)
1

Tool Chart for Compression Connectors Types LCMB and LCMC with Copper Cable

			Panduit Tool Part Number For Class 2 Wire		Panduit Tool Part Number For Class 5 & 6 Wire		
Panduit Part No.	Wire Size & Class	Wire Strip Length (mm)	Die Part Number Color & Die Index Number (Crimp Qty.)		Wire Size & Class	Die Part Number Color & Die Index Number (Crimp Qty.)	
LCMB10 LCMC10	10mm ² Class 2r	25.6	CD-2001-8 Red P21 (2)	CD-920-8 Red P21 (2)	CT-2001	CT-2931 CT-930, CT-930CH CT-2930 CT-940CH* CT-2940	CT-2931 CT-930, CT-930CH CT-2930 CT-940CH*, CT-2940*
LCMB16 LCMC16	16mm ² Class 2r	28.8	CD-2001-8 Red P21 (2)	CD-920-8 Red P21 (2)		HT131-C HT-131LN-C RHC131LN B131-C B131-CKV B131LN-C B131-UC	HT131-C HT-131LN-C RHC131LN B131-C B131-CKV B131LN-C B131-UC
LCMB25 LCMC25	25mm ² Class 2r	28.3	CD-2001-4 Gray P29 (2)	CD-920-4 Gray P29 (2)		CD-2001-8 Red P21 (2)	CD-920-8 Red P21 (2)
LCMB35 LCMC35	35mm ² Class 2r	34.4	CD-2001-4 Gray P29 (2)	CD-920-4 Gray P29 (2)	16mm ² Class 5f Class 6f	CD-2001-4 Gray P29 (2)	CD-920-4 Gray P29 (2)
LCMB50 LCMC50	50mm ² Class 2r	38.2	CD-2001-1 Green P37 (2)	CD-920-1 Green P37 (2)	25mm ² Class 5f Class 6f	CD-2001-2 Brown P33 (3)	CD-920-2 Brown P33 (3)
LCMB70 LCMC70	70mm ² Class 2r	39.6	CD-2001-2/0 Black P45 (3)	CD-920-2/0 Black P45 (3)	35mm ² Class 5f Class 6f	CD-2001-1 Green P37 (3)	CD-920-1 Green P37 (3)
LCMB95 LCMC95	95mm ² Class 2r	44.6	CD-2001-4/0 Purple P54 (3)	CD-920-4/0 Purple P54 (3)	50mm ² Class 5f Class 6f	CD-2001-2/0 Black P45 (3)	CD-920-2/0 Black P45 (3)
LCMB120 LCMC120	120mm ² Class 2r	41.3	CD-2001-250 Yellow P62 (3)	CD-920-250 Yellow P62 (3)	70mm ² Class 5f Class 6f	CD-2001-3/0 Orange P50 (3)	CD-920-3/0 Orange P50 (3)
LCMB150 LCMC150	150mm ² Class 2r	58.6	CD-2001-300 White P66 (3)	CD-920-300 White P66 (3)	95mm ² Class 5f Class 6f	CD-2001-3/0 Orange P50 (3)	CD-920-3/0 Orange P50 (3)
LCMB185 LCMC185	185mm ² Class 2r	57.9	CD-2001-400 Blue P76 (3)	CD-920-400 Blue P76 (3)	120mm ² Class 5f Class 6f	CD-2001-400 Blue P76 (3)	CD-920-400 Blue P76 (3)
LCMB240 LCMC240	240mm ² Class 2r	65.1	CD-2001-500 Brown P87 (3)	CD-920-500 Brown P87 (3)	150mm ² Class 5f Class 6f	CD-2001-400 Blue P76 (3)	CD-920-400 Blue P76 (3)
LCMB300 LCMC300	300mm ² Class 2r	70.0	CD-2001-600 Green P94 (3)	CD-920-600 Green P94 (3)	185mm ² Class 5f Class 6f	CD-2001-400 Blue P76 (3)	CD-920-400 Blue P76 (3)
LCMBX300 LCMCX300	---	74.6	CD-2001-750 CD-940-750** Black P106 (3)	CD-920-750 CD-940-750** Black P106 (3)	240mm ² Class 5f Class 6f	CD-2001-400 Blue P76 (3)	CD-920-400 Blue P76 (3)
LCMB400 LCMC400	400mm ² Class 2r	66.8	CD-2001-1000** White P125 (4)	CD-940-1000** White P125 (4)	300mm ² Class 5f Only	CD-2001-400 Blue P76 (3)	CD-920-400 Blue P76 (3)
LCMB500 LCMC500	500mm ² Class 2r	77.8	CD-2001-1000** White P125 (5)	CD-940-1000** White P125 (5)	CD-2001-400 Blue P76 (3)	CD-920-400 Blue P76 (3)	CD-920-400 Blue P76 (3)
LCMB630 LCMC630	630mm ² Class 2r	85.9	CD-2001-1000** White P125 (5)	CD-940-1000** White P125 (5)	CD-2001-400 Blue P76 (3)	CD-920-400 Blue P76 (3)	CD-920-400 Blue P76 (3)

*CD-920 dies can be used with CT-940CH and CT-2940 tools with CD-940-DA die adapter.

**CD-940 dies to be used exclusively with CT-940CH and CT-2940 tools.

Copper Class 2r, 5f and 6f stranded copper conductor per DIN VDE 0295, IEC 60228 and HDE 383.

† Parts are CE and tested per EN61238-1:2003/IEC 61238-1: 2003 Class B, with class 2r wire 4mm² - 240mm² for LCMB series and 4mm² - 630mm² for LCMC series.E-mail:
cs@panduit.comPhone:
800-777-3300For Instructions in Local Languages
and Technical Support:

techsupport@panduit.com



www.panduit.com