

Pressure Sensor Array





With 110 pressure sensing cells.

Application

- ✓ Pressure distribution applications such as body and foot pressure mapping system, balance training and rehabilitation, and inventory management.

Feature

- ✓ Provides multi-touch function with position (X-Y) and force (Z) detection.

Order Code	Outline Drawing
MMS1011-N-026-A01 	

SPECIFICATION

MODEL	MMS1011-N-026-A01
FORCE SENSITIVITY RANGE	20g~5000g(0.2N~49N)
FORCE REPEATABILITY (SINGLE PART)	±10%
FORCE REPEATABILITY (PART TO PART)	±20%
FORCE RESOLUTION	Continuous(Analog)
STAND-OFF RESISTANCE (UNLOADED)	>20M Ω
RESPONSE TIME	<1ms
OPERATING TEMPERATURE	-20°C to +70°C
LIFE CYCLE (WITHOUT FAILURE)	> 1 Million
IP RATING	IP65

Design and specifications presented here are for the standard parts only. Please kindly contact us for your special requests and ask for the current technical specifications before purchase and/or use.