


SERIES: PBO-3F | DESCRIPTION: AC-DC POWER SUPPLY
FEATURES

- compact size, industrial design
- available in straight and bent pin formats
- IEC/EN/UL 62368-1 certified
- wide operating temperature $-40^{\circ}\text{C} \sim 85^{\circ}\text{C}$ (with derating)
- wide input voltage range 85~305 Vac / 70~430 Vdc
- high efficiency, up to 80 %
- short-circuit and over current protection
- no-load power consumtion (<0.1W)
- open frame SIP design with bent pin option
- flexible implementations to power a wide array of applications
- MTBF >2,700,000 hours


MODEL

MODEL	output voltage (Vdc)	output current max (mA)	output power max (W)	ripple and noise ¹ max (mVp-p)	efficiency typ (%)
PBO-3F-3	3.3	600	1.98	150	67
PBO-3F-5	5	600	3.0	150	72
PBO-3F-9	9	333	3.0	150	76
PBO-3F-12	12	250	3.0	150	77
PBO-3F-15	15	200	3.0	150	78
PBO-3F-24	24	125	3.0	150	80

Notes: 1. Measured at nominal input with 20 MHz bandwidth oscilloscope.

PART NUMBER KEY


INPUT

parameter	conditions/description	min	typ	max	units
voltage	AC input DC input	85 70	100~277	305 430	Vac Vdc
frequency		47	50~60	63	Hz
current	at 115 Vac at 230 Vac			0.12 0.06	A A
inrush current	at 115 Vac at 230 Vac			13 23	A A
no load power consumption	at 230 Vac			0.1	0.15 W

OUTPUT

parameter	conditions/description	min	typ	max	units
capacitive load	3.3 Vdc output model 5 Vdc output model 9 & 12 Vdc output model 15 Vdc output model 24 Vdc output model			820 680 470 330 220	μF μF μF μF μF
initial set point accuracy	from 10~100% load 3.3 Vdc output model all other output models		±8 ±5		% %
line regulation	at rated load			±1.5	%
load regulation	from 10~100% load			±3	%
switching frequency				65	kHz

PROTECTIONS

parameter	conditions/description	min	typ	max	units
over current protection	auto recovery		110		%
short circuit protection	auto recovery				



SAFETY & COMPLIANCE

parameter	conditions/description	min	typ	max	units
isolation voltage	input to output for 5 seconds, 5mA max	3,600 5,000			Vac Vdc
safety approvals	certified to 62368-1: IEC, EN, UL				
conducted emissions	EN55032, CLASS B (see Fig. 2 for recommended circuit)				
radiated emissions	EN55032, CLASS B (see Fig. 2 for recommended circuit)				
EMC immunity	EN55035 (see Fig. 2 for recommended circuit)				
MTBF	as per MIL-HDBK-217F at 50°C ambient temperature		2,700,000		hours
RoHS	yes				

ENVIRONMENTAL

parameter	conditions/description	min	typ	max	units
operating temperature	see derating curves	-40		85	°C
storage temperature		-40		105	°C
operating humidity		-		95	%

DERATING CURVES




MECHANICAL

parameter	conditions/description	min	typ	max	units
dimensions	straight pin: 26.40 x 14.73 x 11.00 [1.039 x 0.578 x 0.433 inch] bent pin: 27.84 x 11.60 x 17.60 [1.096 x 0.457 x 0.693 inch]				mm mm
weight	straight pin bent pin		5.5 6.3		g g
cooling	natural convection				


MECHANICAL DRAWING

Straight pin

units: mm [inch]
pin section tolerance: $\pm 0.15[\pm 0.006]$
tolerance: $\pm 1.0[\pm 0.040]$



Bottom View



PIN CONNECTIONS	
PIN	Function
1	AC (L)
2	AC (N)
3	+V(CAP)
4	-V(CAP)
5	-Vo
6	+Vo


MECHANICAL DRAWING (CONTINUED)

Bent pin


units: mm [inch]
pin section tolerance: $\pm 0.15[\pm 0.006]$
tolerance: $\pm 1.0[\pm 0.040]$

PIN CONNECTIONS	
PIN	Function
1	AC (L)
2	AC (N)
3	+V(CAP)
4	-V(CAP)
5	-Vo
6	+Vo


Top View



Front View




Right View



APPLICATION DESIGN REFERENCE

Figure 1



EMC RECOMMENDED CIRCUIT

Figure 2




Table 1

Additional component selection guide						
	3.3	5	9	12	15	24
FUSE				300V/2A		
MOV				14D561K		
LF				UU9.8, 30mH min		
CX				0.1µF/310V		
CY0				1000pF/400V		
CY1, CY2				470pF/250V		
C1				10µF/450V		
C2	820µF/10V (solid-state capacitor)		470µF/25V (solid-state capacitor)		330µF/35V (solid-state capacitor)	
C3	470µF/10V		220µF/35V			
L1			2.2µH			
TVS	SMBJ7.0A	SMBJ7.0A	SMBJ12A	SMBJ20A	SMBJ20A	SMBJ30A

REVISION HISTORY

rev.	description	date
1.0	initial release	10/24/2025

The revision history provided is for informational purposes only and is believed to be accurate.



15575 SW Sequoia Pkwy #100
Portland, OR 97224
800.275.4899

Fax 503.612.2383
Belfuse.com
powersupport@belf.com

CUI offers a two (2) year limited warranty. Complete warranty information is listed on our website.

CUI reserves the right to make changes to the product at any time without notice. Information provided by CUI is believed to be accurate and reliable. However, no responsibility is assumed by CUI for its use, nor for any infringements of patents or other rights of third parties which may result from its use.

CUI products are not authorized or warranted for use as critical components in equipment that requires an extremely high level of reliability. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.