



Product Overview

The QPA8840 is a an ultra-linear, 22dB Gain, GaAs amplifier, intended for mid or output stage amplification in CATV infrastructure applications. The QPA8840 operates off a 12 Volt, 425 mA supply. The device features a push-pull cascode design which provides flat gain along with ultra-low distortion from 50MHz to 1.8GHz.



Functional Block Diagram



12-Pin 6x6 mm² Laminate Module

Key Features

- 50 MHz to 1800 MHz Operation
- 12 V Operation
- Gain: 22 dB Typical
- Noise Figure: 4.2 dB
- RoHS Compliant

Applications

- DOCSIS 4.0 Amplifiers
- DOCSIS 4.0 Optical Nodes
- Broadband Hybrid CATV Modules

Ordering Information

Part Number	Description
QPA8840EVB-01	Evaluation Board
QPA8840SB	Sample bag with 5 pieces
QPA8840SR	7" Reel with 100 pieces
QPA8840TR13	13" Reel with 2500 pieces

Absolute Maximum Ratings

Parameter	Rating
Supply Voltage (V_{DD})	+16V
Supply Current (I_{DD})	550 mA
Maximum Input Level	+70 dBmV
Operating Temperature Range	-40 to +100 °C
Storage Temperature Range	-65 to +150 °C
Maximum Junction Temperature	+150 °C


Exceeding any one or a combination of the Absolute Maximum Rating conditions may cause permanent damage to the device. Extended application of Absolute Maximum Rating conditions to the device may reduce device reliability.

Electrical Specifications at 12 V

Parameter	Condition ⁽¹⁾	Min	Typ	Max	Unit
Supply Voltage (V_{DD})			12		V
Supply Current (I_{DD})			425		mA
Frequency Range		50		1800	MHz
Gain			22		dB
Gain Slope			1		dB
Reverse Isolation			25		dB
Input Return Loss			20		dB
Output Return Loss			20		dB
MER	At +69dBmV Total Composite Output power. 108MHz to 1791MHz, 20dB tilt, 280 Ch. SC-QAM		42		dB
Noise Figure	Full Band		4.2		dB
OIP2L	Full Band, 15 dBm/tone output		84		dBm
OIP2U	Full Band, 15 dBm/tone output		75		dBm
OIP3	Full Band, 15 dBm/tone output		41		dBm
OP1dB			30		dBm
Thermal Resistance	Θ_{JC}		8		°C/W

Note: Typical performance at these conditions: Temp = +25 °C, V_{DD} = +12V, 75 Ω system, Full band unless otherwise noted



Evaluation Board Schematic 50 MHz – 1800 MHz



Evaluation Board Bill of Materials

Component	Value	Part #	Manufacturer	Component	Value	Part #	Manufacturer
R1	2.7k			C13, L7, L8, L4, L5, R11	0 Ohm		
R2, R8	1.2k			L6	1.3nH		
R7	20k			T1A, T1B	1:1	DXW21BN7511S#	Murata
R4	1.5k			T2	1:1	TRS1-182-75+	Mini-Circuits
R3	5.6k			J1, J2			
C2, C3	1000pF			J3, J4			
C7, C10, C11, C15, C24	0.01uF			R9, R10, R13, R14, R15, R12, C6, C12, C14, C16, C17, C18, C19, C22, C23, C25	DNP		
C1, C20, C21	0.5pF			U1		QPA8840	Qorvo
Cin	0.6pF						
C8, C9	0.7pF						
C4, C5	470pF						
L1	2.7nH						
L2, L3	470nH						

Evaluation Board Assembly Drawing








QPA8840 Evaluation Board





LAYER STACK LEGEND

Material	Layer	Thickness	Dielectric Material	Type	Comment
Surface Material	Top Overlay	0.0004in	SM-001	Legend	HIGH TEMPERATURE, NON-CONDUCTIVE, WHITE EPOXY BASED INK.
CF-004	Top Solder	0.0004in		Solder Mask	LPI (LIQUID PHOTO-IMAGEABLE), OR LDI (LASER DIRECT IMAGEABLE), GREEN.
CF-004	Top Layer	0.0014in		Signal	
Core		0.0200in	RO4003	Dielectric	
CF-004	Bottom Layer	0.0014in		Signal	
Finished board thickness: 0.0232					

Performance Data







Performance Data



Test Conditions:

1. Test conditions unless otherwise noted: $V_{dd} = +12V$, $Z_o = 75\Omega$
2. 108 – 1794 MHz, 280 Ch. SC-QAM, Tilt = 20dB


Performance Data



Test Conditions:


1. Test conditions unless otherwise noted: $V_{dd} = +12V$, $Z_o = 75\Omega$
2. OIP2: +15dBm/Tone, $\Delta f = 50MHz$, Full Band
3. OIP3: +15dBm/Tone, $\Delta f = 6MHz$, Full Band

Pin Configuration and Description



Pin Number	Label	Description
1	LIN	Linearizer Current Set
2	RFin+	RF Input +
3	SRC1	Source - (DC/RF gnd)
4	SRC2	Source + (DC/RF gnd)
5	RFin-	RF input -
6	Bias Adj	IDD adjust
7	Bias	Vdd connection for bias circuit
8	RFOUT-	RF output -
9	VG2	2nd stage gate bias adjust bin
10	N/A	No Connection
11	RFOUT+	RF output +
12	N/A	No Connection
Paddle	GND	DC/RF/Thermal Gnd (maximize vias in this area)

Package Outline




12-Pin 6x6 mm² Laminate Module

Notes:

1. Dimensions in millimeters

Package Marking



Pin 1 Indicator

Qorvo Logo - Use Q5D

Trace Code to be assigned by subcon

Handling Precautions

Parameter	Rating	Standard
ESD – Human Body Model (HBM)	500V	
ESD – Charged Device Model (CDM)	1000V	
MSL – Moisture Sensitivity Level	3	



Caution!
ESD-Sensitive Device

Solderability

Compatible with both lead-free (260 °C max. reflow temp.) and tin / lead (245 °C max. reflow temp.) soldering processes.
Solder profiles available upon request.

Contact plating: ENEPIG

RoHS Compliance

This part is compliant with 2011/65/EU RoHS directive (Restrictions on the Use of Certain Hazardous Substances in Electrical and Electronic Equipment) as amended by Directive 2015/863/EU.

This product also has the following attributes:

- PFOS Free
- Halogen Free (Chlorine, Bromine)
- Antimony Free
- TBBP-A (C₁₅H₁₂Br₄O₂) Free
- SVHC Free

Contact Information

For the latest specifications, additional product information, worldwide sales and distribution locations:

Tel: 1-844-890-8163

Web: www.qorvo.com

Email: customer.support@qorvo.com

Important Notice

The information contained herein is believed to be reliable; however, Qorvo makes no warranties regarding the information contained herein and assumes no responsibility or liability whatsoever for the use of the information contained herein. All information contained herein is subject to change without notice. Customers should obtain and verify the latest relevant information before placing orders for Qorvo products. The information contained herein or any use of such information does not grant, explicitly or implicitly, to any party any patent rights, licenses, or any other intellectual property rights, whether with regard to such information itself or anything described by such information. **THIS INFORMATION DOES NOT CONSTITUTE A WARRANTY WITH RESPECT TO THE PRODUCTS DESCRIBED HEREIN, AND QORVO HEREBY DISCLAIMS ANY AND ALL WARRANTIES WITH RESPECT TO SUCH PRODUCTS WHETHER EXPRESS OR IMPLIED BY LAW, COURSE OF DEALING, COURSE OF PERFORMANCE, USAGE OF TRADE OR OTHERWISE, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE.**

Without limiting the generality of the foregoing, Qorvo products are not warranted or authorized for use as critical components in medical, life-saving, or life-sustaining applications, or other applications where a failure would reasonably be expected to cause severe personal injury or death.

Copyright 2019 © Qorvo, Inc. | Qorvo is a registered trademark of Qorvo, Inc.