

**CABTITE SE 3-4 SML BK**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Similar to illustration**

Whether a large or small cable diameter – Cabtite always offers the right seal insert.

The conical shape of the sealing elements allows the previously positioned snap-in grid inlays to be pushed in easily from the inside to the outside. It reliably seals intermediate spaces and provides strain relief in accordance with DIN EN 62444. The seal inserts combined with the frames achieve an IP 66 degree of protection. As a result of its slotted design with wave cut, it is especially suitable for pre-assembled cables.

- The black seal inserts are designed for a particularly high operating temperature and offer fire safety class UL 94 HB
- The grey sealing elements comply with fire safety class UL 94 VO and are therefore suitable for the demands of the railway industry
- By using multiple inserts, two or more cables, as well as special cables, can be passed through a sealing element

**General ordering data**

Version	Sealing element, Cabtite (cable entry system), TPE, Deep black, Height: 20.3 mm, Width: 20.3 mm, Depth: 17.7 mm, -40 °C...120 °C, IP66
Order No.	<a href="#">2584730000</a>
Type	CABTITE SE 3-4 SML BK
GTIN (EAN)	4050118616279
Qty.	10 pc(s).

**CABTITE SE 3-4 SML BK**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergsstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data****Dimensions and weights**

Depth	17.7 mm
Height	20.3 mm
Width	20.3 mm
Net weight	6.3 g

Depth (inches)	0.697 inch
Height (inches)	0.799 inch
Width (inches)	0.799 inch

**Temperatures**

Operating temperature	-40 °C...120 °C
-----------------------	-----------------

**General information**

Halogen	No
Outer cable diameter, max.	4 mm
Protection degree	IP66
Silicone	No

Material	TPE
Outer cable diameter, min.	3 mm
Sealing element	1 small sealing element
UL 94 flammability rating	HB

**Classifications**

ETIM 6.0	EC000879
ETIM 8.0	EC000879
ETIM 10.0	EC000879
ECLASS 9.1	27-14-44-21
ECLASS 11.0	27-14-44-21
ECLASS 13.0	27-14-08-07
ECLASS 15.0	27-14-08-07

ETIM 7.0	EC000879
ETIM 9.0	EC000879
ECLASS 9.0	27-14-44-21
ECLASS 10.0	27-14-44-21
ECLASS 12.0	27-14-08-07
ECLASS 14.0	27-14-08-07

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**Approvals**

## Approvals



Approvals MAMID	<a href="https://mdcop.weidmueller.com/mediadelivery/rendition/900_319222/-T1z1mm-S800/">https://mdcop.weidmueller.com/mediadelivery/rendition/900_319222/-T1z1mm-S800/</a> <a href="https://mdcop.weidmueller.com/mediadelivery/rendition/900_319230/-T1z1mm-S800/">https://mdcop.weidmueller.com/mediadelivery/rendition/900_319230/-T1z1mm-S800/</a>
ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E223801

**Downloads**

Approval/Certificate/Document of Conformity	<a href="#">EU Declaration of Conformity - Cable entry system</a>
Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">Cabtite Installation Instructions</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>