

RIVET NUT HAND TOOLS

HAND TOOLS



DLHT



DRHT



RNHT

LHF TOOLS

STANDARD		
Thread Size	Mandrel	Anvil
6-32	LHFM 0632	LHFA 0632
8-32	LHFM 0832	LHFA 0832
10-24	LHFM 1024	LHFA 10
10-32	LHFM 1032	LHFA 10
1/4-20	LHFM 2520	LHFA 25
1/4-28	LHFM 2528	LHFA 25
M4	LHFM M4	LHFA M4
M5	LHFM M5	LHFA M5
M6	LHFM M6	LHFA M6
M8	LHFM M8	LHFA M8
M10	LHFM M10	LHFA M10

RIV-FLOAT®		
Thread Size	Mandrel	Anvil
6-32	LHFM 2528	LHFA 25
8-32	LHFM 2528	LHFA 25
10-32	LHFM 1032	LHFA 10RF
1/4-20	LHFM 2520	LHFA 25RF
M4	LHFM 2528	LHFA 25
M5	LHFM M5	LHFA M5RF
M6	LHFM M6	LHFA M6RF

RIV-FLOAT®-SHORT		
Thread Size	Mandrel	Anvil
8-32	LHFM 0832	LHFM 0832RFS
10-32	LHFM 1032	LHFM 1032RFS
M4	LHFM M4	LHFM M4RFS
M5	LHFM M5	LHFM M5RFS

LHF 202 (Imperial Tool) Includes: 8-32, 10-24, and 1/4-20 head sets

LHF 202M (Metric Tool) Includes: M4, M5, and M6 head sets

This hand tool was designed to install any rivet nut ranging in size from 6-32 to 1/4-28 (M4-M10), and is ideal for small production work and prototyping.

DLHT AND DRHT TOOLS (formerly M4 and M5 Hand Tool)

STANDARD			
Thread Size	Head Sets (Includes Anvil & Mandrel)	Anvil	Mandrel
6-32	MHS-0632	MA-0632	M-0632
8-32	MHS-0832	MA-0832	M-0832
10-24	MHS-1024	MA-1024	M-1024
10-32	MHS-1032	MA-1032	M-1032
1/4-20	MHS-2520	MA-2520	M-2520
1/4-28	MHS-2528	MA-2528	M-2528
5/16-18	MHS-3118	MA-3118	M-3118
3/8-16	MHS-3716	MA-3716	M-3716
1/2-13	MHS-5013	MA-5013	M-5013
M4	MHS-M4	MA-M4	M-M4
M5	MHS-M5	MA-M5	M-M5
M6	MHS-M6	MA-M6	M-M6
M8	MHS-M8	MA-M8	M-M8
M10	MHS-M10	MA-M10	M-M10
M12	MHS-M12	MA-M12	M-M12

RIV-FLOAT®			
Thread Size	Head Sets (Includes Anvil & Mandrel)	Anvil	Mandrel
8-32	MHS-0832RF	MA-2520/2528	M-2528
10-32	MHS-1032RF	MA-1032RF	M-1032
1/4-20	MHS-2520RF	MA-2520/2528RF	M-2520
M4	MHS-M4RF	MA-2520/2528	M-2528
M5	MHS-M5RF	MA-M5RF	M-M5
M6	MHS-M6RF	MA-M6RF	M-M6

RIV-FLOAT®-SHORT			
Thread Size	Head Sets (Includes Anvil & Mandrel)	Anvil	Mandrel
8-32	MHS-0832RF	MA-0832RFS	M-0832
10-24	MHS-1024RFS	MA-10RFS	M-1024
10-32	MHS-1032RF	MA-10RFS	M-1032
M4	MHS-M4RFS	MA-M4RFS	M-M4
M5	MHS-M5RFS	MA-M5RFS	M-M5

DLHT (Imperial Tool) Includes: 1/4-20, 5/16-18, 3/8-16, and 1/2-13 head sets.

DLHT (Metric Tool) Includes: M6, M8, M10, and M12 head sets

DRHT (Imperial Tool) Includes: 10-32, 1/4-20, 5/16-18, and 3/8-16 head sets.

DRHT (Metric Tool) Includes: M5, M6, M8, and M10 head sets

RNHT TOOL

STANDARD	
Part Number	Thread
RNHT-0632	6-32
RNHT-0832	8-32
RNHT-1024	10-24
RNHT-1032	10-32
RNHT-2520	1/4-20
RNHT-2528	1/4-28
RNHT-3118	5/16-18
RNHT-3124	5/16-24
RNHT-3716	3/8-16
RNHT-3724	3/8-24
RNHT-4320	7/16-20
RNHT-M3	M3
RNHT-M4	M4
RNHT-M5	M5
RNHT-M6	M6
RNHT-M8	M8
RNHT-M10	M10

RIV-FLOAT®	
Thread Size	Part Number
6-32	RNHT-2528RF
8-32	RNHT-2528RF
10-32	RNHT-1032RF
1/4-20	RNHT-2520RF
M4	RNHT-2528RF
M5	RNHT-M5RF
M6	RNHT-M6RF

RIV-FLOAT®-SHORT	
Thread Size	Part Number
M4	RNHT-M4RFS
M5	RNHT-M5RFS