

## S298 Coolant Level Switch - Capacitance Type with Voltage Output



The **S298** is an active device designed to give an alarm signal if liquid falls below, or rises above, a preset level. It can be specified with a delay to eliminate false alarms due to turbulence.

Containing a factory programmable microprocessor and an integral 3-pin Metripack 150 connector, this switch can be configured to provide most industry standard voltage outputs.

Its small footprint with limited intrusion into the tank means a reduced risk of damage and a wide range of customer specifiable options make it suitable for most applications.

The switch is designed to operate in both earthed metal and isolated plastic tanks. For high accuracy the S298 is ideally mounted horizontally at the point where an alarm or control signal is required. However, the switch can be mounted vertically – contact Rochester Sensors UK Limited with your application requirements.



### SPECIFICATION

#### Liquid types:

Water based liquids such as coolant or washer fluid.

#### Electrical rating

Supply voltage:  $5\pm0.25$  VDC.

Supply current: 5 mA + source output.

Alarm delay time: 0 to 25 s rising or falling (factory set).

Connection: 3 way Packard Metripack 150 connector.

Power up delay: 0 to 10 s (factory set).

Power up state: 'In Liquid' or 'Out of Liquid' (factory set).

Output type: Voltage.

Output pin: **Pin B.**

Output state in liquid\*:  $1.2\pm0.25$  VDC

Output state in air\*: 3.75 $\pm$ 0.25 VDC

Output current: 10 mA maximum.

Connections: See diagram below.

\*Outputs are factory selectable; opposite states and alternative values from 0.5-4.5 VDC are available on request.

#### Environmental Ratings

Ingress: IP67 (with mating connector fitted).

Max. pressure: 5.0 Bar (72 psi)

Temp. range: -40 °C to +125 °C (-40 °F to + 257 °F)

Weight: 70 g typical (dependent on thread size)

EMC: ISO13766:2006

#### Construction

**Body:** Brass or 316 stainless steel.



**Probe:** PTFE.

**Terminals:** Brass, Tin Plated.

**Seals:** EPDM & FVMQ.

**Connector:** PA66 30% Glass Filled Nylon.

**Thread sealant:** Vibra-Seal 516 (taper thread variants only).



#### Recommended Installation Tightening Torques:

1/4" NPTF	9 Nm	M14x1.5	10 Nm
3/8" NPTF	11 Nm	M18x1.5	15 Nm
1/2" NPTF	20 Nm		
1/2" BSPP	15 Nm		
1/2" BSPT	20 Nm		

#### Optional accessories

Packard Metri-Pack 150 series mating connector kit to suit harness wire cross sectional area of 0.8 to 1.0 mm<sup>2</sup> and sleeve Ø1.60 to 2.15 mm.

E. & O. E. © Rochester Sensors UK Limited.

Since the suitability of these products depends upon a wide range of factors not in our control, Rochester Sensors UK Limited expects and understands that you will conduct the testing and evaluation necessary to determine that these products are suitable for your application. Whilst every effort is made to ensure the above details are correct at the time of printing, Rochester Sensors UK Limited reserves the right to make material changes, and or technical changes without notification.

3.4 rev 4