

October 25th, 2021

SANYO DENKI AMERICA, INC
468 Amapola Avenue, Torrance, CA 90501

SANYO DENKI Launches 92 × 92 × 25 mm DC Fan with the Lowest Noise in the Industry

SANYO DENKI has developed and launched the 92 × 92 × 25 mm *San Ace 92 9RA* type DC Fan that features the lowest noise in the industry.⁽¹⁾

This fan is ideal for cooling medical equipment, measuring instruments, and other applications that require particularly quiet operation.

Features

1. Low Noise and Energy Saving

Compared to our current model,⁽²⁾ noise level has been more than halved⁽³⁾ and power consumption has been reduced by 44%.⁽⁴⁾

Moreover, the models with PWM control, which enables the control of fan speed, provide further optimized noise level and efficiency.

2. Long Life

This fan lasts 2 times longer than the current model,⁽²⁾ and is capable of continuous operation for 60,000 hours (approximately 7 years), improving the maintainability.

3. Rich Lineup

The product lineup is available in a wide variety in 12/24/48 voltage, cooling performance, noise level, and PWM control. This allows users to choose the most suitable one for their applications.

(1) Based on our own research as of July 20, 2021, conducted among axial DC fans of equivalent size and cooling performance on the market.

(2) Current model: 92 × 92 × 25 mm *San Ace 92 9A* type DC Fan (model: 9A0912G401).

(3) A 4 dB(A) decrease in noise level.

(4) For models 9RA0912P4G001 and 9RA0912G4001

Specifications

Dimensions: 92 × 92 × 25 mm, Mass: 130 g

The models listed below have pulse sensors with PWM control function.

Model no.	Rated voltage	Operating voltage range	Rated input	Rated speed	Max. airflow		Max. static pressure		Noise level
	[V]	[V]	[W]	[min ⁻¹]	[m ³ /min]	[CFM]	[Pa]	[inchH ₂ O]	[dB(A)]
9RA0912P4G001	12	10.8 to 13.2	2.64	4200	1.8	63.5	73.5	0.29	37
9RA0924P4G001	24	21.6 to 26.4	3.12	4200	1.8	63.5	73.5	0.29	37
9RA0948P4G001	48	43.2 to 52.8	3.36	4200	1.8	63.5	73.5	0.29	37

Expected life: 60000 hours (L10 life: 90% survival rate for continuous operation in free air at 60°C, rated voltage)

The models listed below have pulse sensors.

Models listed below can be made available with PWM control upon request. Please contact your sales representative.

Model no.	Rated voltage	Operating voltage range	Rated input	Rated speed	Max. airflow		Max. static pressure		Noise level
	[V]	[V]	[W]	[min ⁻¹]	[m ³ /min]	[CFM]	[Pa]	[inchH ₂ O]	[dB(A)]
9RA0912G4001	12	7 to 13.8	2.64	4200	1.8	63.5	73.5	0.29	37
9RA0912S4001			2.4	3850	1.65	58.3	61.7	0.25	35
9RA0912H4001			1.68	3400	1.46	51.6	48.1	0.19	31
9RA0912F4001			1.2	2850	1.22	43.1	33.8	0.14	27
9RA0912M4001			0.84	2450	1.05	37.1	25	0.1	23
9RA0924G4001	24	14 to 27.6	3.12	4200	1.8	63.5	73.5	0.29	37
9RA0924S4001			2.4	3850	1.65	58.3	61.7	0.25	35
9RA0924H4001			1.92	3400	1.46	51.6	48.1	0.19	31
9RA0924F4001			1.44	2850	1.22	43.1	33.8	0.14	27
9RA0924M4001			0.96	2450	1.05	37.1	25	0.1	23
9RA0948G4001	48	36 to 55.2	3.36	4200	1.8	63.5	73.5	0.29	37
9RA0948S4001			2.88	3850	1.65	58.3	61.7	0.25	35
9RA0948H4001			2.4	3400	1.46	51.6	48.1	0.19	31

Expected life: 60000 hours (L10 life: 90% survival rate for continuous operation in free air at 60°C, rated voltage)

Applications Medical equipment and measuring instruments

Release Date July 20, 2021

Price Open

Photo



Note: The information stated in this release is current as of July 20, 2021.

San Ace is a trademark of SANYO DENKI CO., LTD.

Kathleen Whitcher
 Distribution Sales Manager
 Cooling Systems Division
 SANYO DENKI AMERICA, INC
 TEL: (310) 783-5400
<https://www.sanyodenki.com/america>