


SPK0838HT4H-1

DIGITAL SISONIC™ MICROPHONE WITH MULTIPLE PERFORMANCE MODES

The SPK0838HT4H-1 is a miniature, high-performance, low power, top port silicon digital microphone with a single-bit PDM output. Using Syntiants' proven high performance SiSonic™ MEMS technology, the SPK0838HT4H-1 consists of an acoustic sensor, a low noise input buffer, and a sigma-delta modulator. These devices are suitable for applications such as cellphones, smart phones, laptop computers, sensors, digital still cameras, portable music recorders, and other portable electronic devices where excellent wideband audio performance and RF immunity are required. The high Signal-to-Noise Ratio (SNR) of the SPK0838HT4H-1 enhances the performance of far-field applications and many complex, multi-microphone algorithms. In addition, the SPK0838HT4H-1 offers multiple performance modes.



ABSOLUTE MAXIMUM RATINGS

Table 1: Absolute Maximum Ratings

Parameter	Absolute Maximum Rating	Units
Vdd to Ground	-0.3, +5.0	V
DATA, CLOCK, SELECT to Ground	-0.3, +5.0	V
Input Current	±5	mA
Short Circuit to/from DATA	Indefinite to Ground or Vdd	sec
Storage Temperature	-40 to +100	°C
Operating Temperature	-40 to +100	°C

Stresses exceeding these "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only. Functional operation at these or any other conditions beyond those indicated under "Acoustic & Electrical Specifications" is not implied. Exposure beyond those indicated under "Acoustic & Electrical Specifications" for extended periods may affect device reliability.



PRODUCT FEATURES

- Low Distortion of 2.2% at 115dB SPL
- Signal-to-Noise Ratio of 64dB(A)
- Flat Frequency Response 20 - 20kHz
- High Drive Capability
- Low Current Consumption of 230uA in Low-Power Mode
- RF Shielded
- PDM Output
- Supports Dual Multiplexed Channels
- Ultra-Stable Performance
- Standard SMD Reflow
- Omnidirectional
- Sensitivity Matching
- Standard 4x3x1 package size
- LGA Package

TYPICAL APPLICATIONS

- Portable Electronics
- Cellphones
- Laptop Computers
- Tablets
- Digital Still Cameras
- Portable Music Recorders

ACOUSTIC & ELECTRICAL SPECIFICATIONS¹

Table 2: General Microphone Specifications

Test Conditions: 23 \pm 2°C, 55 \pm 20% R.H., Vdd=1.8 V, Tedge \leq 3ns, unless otherwise indicated

Parameter	Symbol	Conditions	Min	Typ	Max	Units	
Supply Voltage	Vdd		1.6	1.8	3.6	V	
Low Frequency Rolloff	LFRO	-3dB relative to 1 kHz	-	35	-	Hz	
DC Offset		Fullscale = \pm 100	-	0	-	% FS	
Directivity			Omnidirectional				
Polarity		Increasing sound pressure	Increasing density of 1's				
Data Format			1/2 Cycle PDM				
Sensitivity Drop		Vdd(min) \leq Vdd \leq Vdd(max)	-	-	\pm 0.25	dB	
Clock Input Capacitance	Cin		-	5	-	pF	
Data Output Load	Cload		-	-	140	pF	
SELECT (high)			0.7xVdd	-	3.6	V	
SELECT (low)			-0.3	-	0.3xVdd	V	
Short Circuit Current	Isc	Grounded DATA pin	1	-	20	mA	
Fall-asleep Time ^{3,4}		Fclock < 250kHz	-	-	10	ms	
Wake-up Time ^{3,5}		Fclock \geq 350kHz	-	-	15	ms	
Startup Time ³		Powered Down \rightarrow Active, S within 1 dB of final value	-	-	50	ms	
Mode-Change Time ^{3,6}		Low Power Mode \leftrightarrow Normal Mode	-	-	10	ms	

SPK0838HT4H-1

Digital SiSonic™ Microphone With Multiple Performance Modes

Table 3: Normal Mode

Test Conditions: $23 \pm 2^\circ\text{C}$, $55 \pm 20\%$ R.H., $V_{dd}=1.8$ V, $F_{clock} = 2.4$ MHz (D.C. = 50%), $T_{edge} \leq 3$ ns, SELECT grounded, no load, unless otherwise indicated

Parameter	Symbol	Conditions	Min	Typ	Max	Units
Supply Current ²	I _{dd}	$F_{clock} = 2.4$ MHz	-	630	710	µA
Sensitivity	S	94 dB SPL @ 1 kHz	-27	-26	-25	dBFS
Signal to Noise Ratio	SNR	94 dB SPL @ 1 kHz, A-weighted, $F_{clock} = 2.4$ MHz	-	64	-	dB(A)
Total Harmonic Distortion	THD	94 dB SPL @ 1 kHz	-	0.1	-	%
		115 dB SPL @ 1 kHz	-	2.2	-	
		1% THD @ 1 kHz, S = typ	-	105	-	dB SPL
Acoustic Overload Point	AOP	10% THD @ 1 kHz, S = typ	-	120	-	dB SPL
Power Supply Rejection Ratio	PSRR	200 mVpp sinewave @ 1 kHz	-	70	-	dB V/FS
Power Supply Rejection	PSR+N	100 mVpp square wave @ 217 Hz, A-weighted @ 217 Hz, A-weighted, BW = 20 kHz	-	-90	-	dBFS(A)

Table 4: Low-Power Mode

Test Conditions: $23 \pm 2^\circ\text{C}$, $55 \pm 20\%$ R.H., $V_{dd}=1.8$ V, $F_{clock} = 768$ kHz (D.C. = 50%), $T_{edge} \leq 3$ ns, SELECT grounded, no load, unless otherwise indicated

Parameter	Symbol	Conditions	Min	Typ	Max	Units
Supply Current ²	I _{dd}		-	230	275	µA
Sensitivity	S	94 dB SPL @ 1 kHz	-27	-26	-25	dBFS
Signal to Noise Ratio	SNR	94 dB SPL @ 1 kHz, A-weighted (BW = 8 kHz)	-	64	-	dB(A)
Total Harmonic Distortion	THD	94 dB SPL @ 1 kHz	-	0.2	-	%
		1% THD @ 1 kHz, S = typ	-	105	-	
Acoustic Overload Point	AOP	10% THD @ 1 kHz, S = typ	-	120	-	dB SPL
Power Supply Rejection Ratio	PSRR	200 mVpp sinewave @ 1 kHz		75	-	dBV/FS
Power Supply Rejection	PSR+N	100 mVpp square wave @ 217 Hz, A-weighted @ 217 Hz, A-weighted, BW = 20 kHz	-	-91	-	dBFS(A)

Table 5: Sleep Mode

Test Conditions: $23 \pm 2^\circ\text{C}$, $55 \pm 20\%$ R.H., $V_{dd}=1.8$ V, $F_{clock} = 0$ Hz, SELECT grounded, no load, unless otherwise indicated

Parameter	Symbol	Conditions	Min	Typ	Max	Units
Sleep Current	I _{sleep}		-	26	-	µA

¹ Sensitivity and Supply Current are 100% tested.² I_{dd} varies with C_{load} according to: $\Delta I_{dd} = 0.5 * V_{dd} * \Delta C_{load} * F_{clock}$.

3 Valid microphones states are: Powered Down Mode (mic off), Sleep Mode (low current, DATA = high-Z, fast startup), Low-Power Mode (low clock speed) and Normal Mode.

4 Time from $F_{clock} < 250$ kHz to I_{sleep} specification is met when transitioning from Active Mode to Sleep Mode.5 Time from $F_{clock} \geq 350$ kHz to all applicable specifications are met when transitioning from Sleep Mode to Active Mode.

6 Audio is temporarily muted during the transition between any microphone state.

Table 6: Digital Interface

Test Conditions: $23 \pm 2^\circ\text{C}$, $55 \pm 20\%$ R.H., $V_{dd}=1.8$ V, $T_{edge} \leq 3$ ns, unless otherwise indicated

Parameter	Symbol	Conditions	Min	Typ	Max	Units
Logic Input High ⁷	Vih		$0.7xV_{dd}$	-	3.6	V
Logic Input Low ⁷	Vil		-0.3	-	$0.3xV_{dd}$	V
Logic Output High ⁷	Voh	$I_{OUT} = 2$ mA	$V_{dd}-0.45$	-	-	V
Logic Output Low ⁷	Vol	$I_{OUT} = 2$ mA	-	-	0.45	V
Low→High Threshold ⁸	VL-h		$0.55xV_{dd}$	-	$0.7xV_{dd}$	V
High→Low Threshold ⁸	Vh-l		$0.3xV_{dd}$	-	$0.45xV_{dd}$	V
Hysteresis Width ⁸	Vhyst		$0.10xV_{dd}$	-	$0.29xV_{dd}$	V
Clock Frequency ⁷	Fclock	Sleep Mode	0	-	250	kHz
		Low-Power Mode	350	-	800	
		Normal Mode	1.0	-	4.8	MHz
Clock Duty Cycle	D.C.		40	50	60	%
Delay Time to Data Line Driven ⁷	Tdd		18	-	-	ns
Delay Time to Valid Data ⁷	Tdv	Max Cload	-	-	110	ns
Delay Time to High Z ⁷	Tdz		3	-	16	ns
Hold Time ⁷	Thold	Thold, as observed by the input device, will be dependent on Cload	3	-	-	ns

⁷ See Figure 1: Timing Diagram.⁸ See Figure 2: Hysteresis Diagram.

SPK0838HT4H-1

Digital SiSonic™ Microphone With Multiple Performance Modes

Figure 1: Timing Diagram




Figure 2: Hysteresis Diagram




Figure 3: State Diagram




Figure 4: Typical Stereo Application Circuit





Figure 5: Typical Single-Microphone Application Circuit



NOTES:

All Ground pins must be connected to ground.
If necessary to improve RF performance, optional series components (resistors, ferrites, etc.) should be placed closest to the microphone pads.
Bypass capacitors should be placed near each Vdd pin for best performance.
Capacitors near the microphone should not contain Class 2 dielectrics due to their piezoelectric effect.

Table 7: SELECT Functionality

Microphone	SELECT	Asserts DATA on	Latch DATA on
Mic (High)	Vdd	CLK rising edge	CLK falling edge
Mic (Low)	Ground	CLK falling edge	CLK rising edge

PERFORMANCE CURVES

Test Conditions: $23 \pm 2^\circ\text{C}$, $55 \pm 20\%$ R.H., $\text{Vdd}=1.8$ V, $\text{Fclock} = 2.4$ MHz, SELECT grounded, no load, unless otherwise indicated

Figure 6: Typical Free Field Magnitude and Phase




Figure 8: Typical Phase and Group Delay




Figure 7: Typical THD vs SPL





Figure 9: Typical THD vs Frequency



SPK0838HT4H-1

Digital SiSonic™ Microphone With Multiple Performance Modes

Figure 10: Typical Free Field Ultrasonic Response




Figure 12: Noise Floor Power Spectral Density




Figure 11: Typical Idd vs Vdd








Figure 13: Typical PSRR




MECHANICAL SPECIFICATIONS




Item	Dimension	Tolerance
Length (L)	4.00	± 0.10
Width (W)	3.00	± 0.10
Height (H)	1.00	± 0.10
Acoustic Port (AP)	$\varnothing 0.25$	± 0.05

Pin #	Pin Name	Type	Description
1	DATA	Digital O	PDM Output
2	CLOCK	Digital I	Clock Input
3	SELECT	Non-Digital Input	Lo/Hi (L/R) Select. This pin is internally pulled low
4	Vdd	Power	Power Supply
5-8	GROUND	Power	Ground

Example Land Pattern




Example Solder Stencil Pattern




NOTES:

Pick Area only extends to 0.25 mm of any edge or hole unless otherwise specified.
Dimensions are in millimeters unless otherwise specified.
Tolerance is ± 0.15 mm unless otherwise specified.

In the acoustic path, the recommended Gasket Cavity Diameter is $D \geq 1.0$ mm and the recommended Case Hole Diameter is $1.0 \leq D \leq 1.5$ mm.
Further optimizations based on application should be performed.




PACKAGING & MARKING DETAIL



Model Number	Suffix	Reel Diameter	Quantity Per Reel
SPK0838HT4H-1	-7	13"	5700

Component	Surface Resistance (ohms)
Reel	10^5 - 10^9
Carrier Tape	10^5 - 10^9
Cover Tape	10^4 - 10^{10}



YWW: Year/Week date code
 Letter: "o", orientation mark (pin 1)
 Letter: "K"
 Alpha Character A:
 "S": Manufactured in China
 "M": Manufactured in Malaysia
 "I": Manufactured in Itasca
 Version Number Vx:
 Ex: Engineering version number x
 Px: Prototype version number x
 Mx: Mass production version number x
 12345678:
 Unique Job Identification Number for product traceability

NOTES:

Dimensions are in millimeters unless otherwise specified.


Vacuum pickup only in the pick area indicated in Mechanical Specifications.

Tape & reel per EIA-481.

Labels applied directly to reel and external package.

Shelf life: Twelve (12) months when devices are stored in the factory-supplied, unopened ESD moisture sensitive bag under the maximum environmental conditions of 30°C, 70% R.H.

RECOMMENDED REFLOW PROFILE



Profile Feature	Pb-Free
Average Ramp-up rate (T_{SMAX} to T_P)	3°C/second max.
Preheat	
• Temperature Min (T_{SMIN})	150°C
• Temperature Max (T_{SMAX})	200°C
• Time (T_{SMIN} to T_{SMAX}) (t_S)	60-180 seconds
Time maintained above:	
• Temperature (T_L)	217°C
• Time (t_L)	60-150 seconds
Peak Temperature (T_P)	260°C
Time within 5°C of actual Peak Temperature (t_P)	20-40 seconds
Ramp-down rate (T_P to T_{SMAX})	6°C/second max
Time 25°C to Peak Temperature	8 minutes max

NOTES:

Based on IPC/JEDEC J-STD-020 Revision C.

All temperatures refer to topside of the package, measured on the package body surface.

The actual reflow profile used should be optimized based on the reflow requirements of all components, board design, solder paste formulation and reflow equipment used. Details of recommended handling and manufacturing processes can be found in AN25 SMT Manufacturing Guidelines for SiSonic™ Microphones.

ADDITIONAL NOTES

- (A) MSL (moisture sensitivity level) Class 1.
- (B) Maximum of 3 reflow cycles is recommended.
- (C) In order to minimize device damage:
 - Do not board wash or clean after the reflow process.
 - Do not brush board with or without solvents after the reflow process.
 - Do not directly expose to ultrasonic processing, welding, or cleaning.
 - Do not insert any object in port hole of device at any time.
 - Do not apply over 30 psi of air pressure into the port hole.
 - Do not pull a vacuum over port hole of the microphone.
 - Do not apply a vacuum when repacking into sealed bags at a rate faster than 0.5 atm/sec.
 - Do not directly expose to vapor phase soldering.

MATERIALS STATEMENT

Meets the requirements of the European RoHS directive 2011/65/EC as amended.

Meets the requirements of the industry standard IEC 61249-2-21:2003 for halogenated substances and Syntiant Green Materials Standards Policy section on Halogen-Free.

Product is Beryllium Free according to limits specified on the Syntiant Hazardous Material List (HSL for Products).

Ozone depleting substances are not used in the product or the processes used to make the product, including compounds listed in Annex A, B, and C of the "Montreal Protocol on Substances That Deplete the Ozone Layer".

RELIABILITY SPECIFICATIONS

Test	Description
Thermal Shock	100 cycles of air-air thermal shock from -40°C to +125°C with 15 minute soaks (IEC 68-2-4)
High Temperature Storage	+105°C environment for 1,000 hours (IEC 68-2-2 Test Ba)
Low Temperature Storage	-40°C environment for 1,000 hours (IEC 68-2-1 Test Aa)
High Temperature Bias	+105°C environment while under bias for 1,000 hours (IEC 68-2-2 Test Ba)
Low Temperature Bias	-40°C environment while under bias for 1,000 hours (IEC 68-2-1 Test Aa)
Temperature/Humidity Bias	+85°C/85% R.H. environment while under bias for 1,000 hours (JESD22-A101A-B)
Vibration	12 minutes in each X, Y, Z axis from 20 to 2,000 Hz with peak acceleration of 20 G (MIL 883E, Method 2007.2,A)
ESD-LID/GND	3 discharges at $\pm 8\text{kV}$ direct contact to lid when unit is grounded (IEC 61000-4-2)
ESD-MM	3 discharges at $\pm 200\text{V}$ direct contact to IO pins (MIL 883E, Method 3015.7)
Reflow	5 reflow cycles with peak temperature of +260°C
Mechanical Shock	3 pulses of 10,000 G in each of the X, Y, and Z directions (IEC 68-2-27 Test Ea)

NOTES:

Microphones meet all acoustic and electrical specifications before and after reliability testing, except sensitivity which can deviate up to 3dB.

After 3 reflow cycles, the sensitivity of the microphones shall not deviate more than 1 dB from its initial value.

Temperature Storage testing is covered by Temperature Bias testing as $T_a = T_j$ for Syntiant Microphones.

SPECIFICATION REVISIONS

Revision	Specification Changes	Date
A	MP Release ECR #18-2222	3/19/18
B	Update 2d drawing ECR#18-2534	7/19/18
C	Update 2d drawing for Correct pin definiton ECR#18-2601	8/13/18
C-1	Updated template	12/2/24

Information contained herein is subject to change without notice. It may be used by a party at their own discretion and risk. We do not guarantee any results or assume any liability in connection with its use. This publication is not to be taken as a license to operate under any existing patents.