

Product data sheet

Specifications



Controller, Modicon M171/M172/ M173, flush mounted, 22 IO, 2 RS485, solid state relay

TM173OFM22S

Main

Range of product	Modicon M171/M172/M173
Product or component type	Programmable controllers
Product specific application	HVAC and pumping solution
Variant	Programmable
Total inputs/outputs	22
Discrete input number	6
Discrete output number	3 relay outputs SPST with same common 2 solid state, isolated SPST with independent common
Discrete output current	5 A relay SPST 0.5 A solid state, isolated
Analogue input number	6 configurable by pair 1 configurable
Analogue output number	1 voltage/current 0...10 V or 4...20 mA 3 voltage 0...10 V or PWM (10Hz...2 kHz)

Complementary

Number of port	1 USB type C - screw terminal block 2 RS485 1 display port - screw terminal block Modbus serial link) 1 communication module port - TTL connector
Input/output number	6 digital input 5 digital output 7 analog input 4 analog output
Discrete input logic	Sink or source (positive/negative)
Contacts usage	Volt-free contacts
Discrete input voltage	24 V AC/DC
Discrete input current	2.5 mA
Input impedance	20 kOhm
Analogue input type	NTC 103AT-2 Beta 3435 temperature probe - 50...100 °C 0.1 °C 10 kOhm Pt 1000 temperature probe - 50...400 °C 0.1 °C 2 kOhm voltage 0...10 V 0.001 V > 10 kOhm voltage 0...5 V 0.001 V 110 kOhm current 4...20 mA 13 bits 100 Ohm direct input > 10 kOhm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Measurement accuracy	NTC NK103 Beta 3977 - 40...+110 °C +/- 1 °C NTC NK103 Beta 3977 110...137 °C +/- 1.9 °C NTC 103AT-2 Beta 3435 - 50...110 °C +/- 1 °C PTC - 55...155 °C +/- 1.1 °C Pt 1000 - 100...50 °C +/- 5 °C Pt 1000 - 50...100 °C +/- 1 °C Pt 1000 100...400 °C +/- 5 °C 0...20 mA 0...4 mA +/- 2 % of full scale +/- 1 digit 0...20 mA 4...20 mA +/- 1 % of full scale +/- 1 digit 4...20 mA +/- 1 % of full scale +/- 1 digit 0...10 V +/- 1 % of full scale +/- 1 digit 0...5 V +/- 1 % of full scale +/- 1 digit HOhm 0...1500 hOhm +/- 8.5 hOhm DaOhm 0...300 daOhm +/- 2.5 daOhm
Sensor power supply	5 V DC 50 mA supplied by the controller 24 V DC 125 mA supplied by the controller
[Us] rated supply voltage	24 V +/- 10 % AC 20...38 V DC
Power consumption in W	10 W 24 V AC/DC
Realtime clock	Built-in clock, clock drift <= 30 s/month at -4...149 °F (-20...65 °C)
Display type	LED
Memory type	1 MB flash 380 kB RAM
Overvoltage category	II
Local signalling	USB pendrive download status 1 LED green)
Mounting support	Panel mounting with accessory DIN rail
Width	3.2 in (80.5 mm)
Height	1.4 in (34.5 mm)
Depth	3.3 in (82.7 mm)
Product weight	0.2282 lb(US) (0.1035 kg)

Environment

Directives	2014/30/EU - electromagnetic compatibility 2014/35/EU - low voltage directive
Standards	CAN/CSA-E60730-1 CSA E60730-2-9 EN 60068-2-27 EN 60068-2-6 Fc EN 60730-1 EN 60730-2-9 UL 60730-1 UL 60730-2-9 IEC 61000-4-2 IEC 61000-4-3 IEC 61000-4-4 IEC 61000-4-5 IEC 61000-4-6 IEC 61000-4-11 UL94 (material V0)
Product certifications	EAC (pending) CE cURus CSA RCM (pending)
Ambient air temperature for operation	-4...149 °F (-20...65 °C) UL 60730-1 EN 60730-1 EN 60730-2-9
Ambient air temperature for storage	-22...158 °F (-30...70 °C)

Relative humidity	5...95 % non-condensing
IP degree of protection	IP65 conforming to EN/IEC 60730
pollution degree	2
Operating altitude	0...2000 m

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.76 in (7.000 cm)
Package 1 Width	3.62 in (9.200 cm)
Package 1 Length	5.20 in (13.200 cm)
Package 1 Weight	6.737 oz (191.000 g)
Unit Type of Package 2	S02
Number of Units in Package 2	15
Package 2 Height	5.91 in (15.000 cm)
Package 2 Width	11.81 in (30.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	6.956 lb(US) (3.155 kg)

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

 Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	255
Environmental Disclosure	Product Environmental Profile

Use Better


 Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	4549fe6c-7ae3-49e1-a5a8-d6c3d1ca3e52
REACH Regulation	REACH Declaration

Use Again

 Repack and remanufacture	
Circularity Profile	End of Life Information
Take-back	No


Dimensions Drawings

Dimensions



Mounting and Clearance

Mounting




- (1) Insert the device
- (2) Secure it with the special brackets provided
- (3) Front panel only (tested in accordance with EN 60529 with a steel sheet 2 mm (0.08 in.) thick $\pm 10\%$)

Connections and Schema


Wiring

Power supply




- (1) Type T fuse 1.25 A
(2) Power Supply

Digital input



Digital output




- DO1, DO5: SSR 0.5 A 240 Vac
DO2, DO3, DO4: relay SPST 3 A 250 Vac

Analog inputs





- (1) Max. current : 50 mA.
(2) Max. current : 125 mA.

Analog Output



RS 485 port



(1) Signal Reference

Image of product / Alternate images

Alternative

