

**IE-S1DS2VE0050T01T01-E****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



SPElink®



Single pair Ethernet is a technology that only requires one pair of wires to transmit data and power. The resulting benefits will make SPE the preferred network at the field level and beyond.

**Advantages of Single Pair Ethernet**

- Consistent: Single Pair Ethernet enables uniform Ethernet-based communication from the sensor to the cloud
- Future-proof: key technology for Industry 4.0 and IIoT
- Flexible: ranges of up to 1000 m and transmission properties of up to 1 Gbps enable use across applications
- Innovative: lighter, less space required, and reduced installation effort

**General ordering data**

Version	Patch cable, SPE plug (IEC 63171-2) - IP20 socket contact straight, SPE plug (IEC 63171-2) - IP20 socket contact straight, T1-B, PVC, 5 m
Order No.	<a href="#">2725850050</a>
Type	IE-S1DS2VE0050T01T01-E
GTIN (EAN)	4050118825336
Qty.	1 pc(s).

**IE-S1DS2VE0050T01T01-E****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Length	5 m	Length (inches)	196.85 inch
Net weight	176 g		

**Temperatures**

Operating temperature	-40 °C...80 °C
-----------------------	----------------

**Electrical properties**

Dielectric strength, contact / contact	1000 V DC	Dielectric strength, contact / shield	2250 V DC
Insulation strength	≥ 500 MΩ	PoE / PoE+	PoDL acc. to IEEE 802.3bu / cg

**Standards**

Connector standard	IEC 63171-2
--------------------	-------------

**Cable structure**

Colour coding	white / blue	Complete shielding	Shielding braid made from copper wiring
Cross-section	2*AWG 22	Insulation	PE
Insulation diameter 2	1.65 mm	Material sheath	PVC
Number of wires	2	Overlap of shielding braid	80 %
Sheath diameter, max.	5.3 mm	Sheath diameter, min.	4.9 mm
Sheathing colour	black	Shielding	STP
Strands	7		

**Electrical properties of cable**

Capacity at 800 Hz	1.6 nF/km	Category	T1-B
Characteristic impedance	100 ± 15 Ω at 20 MHz	Coupling attenuation 1 to 600 MHz	Type I
Insulation strength	≥ 500 MΩ	Rated current	3.5 A
Rated voltage (DC)	60 V	Resistance differential	2 %
Test voltage: wire-wire-shield	1 kV DC, 1 min	Transmission rate	10/100 MBit/s, 1000 MBit/s

**Mechanical and material properties of cable**

Bending radius	20 mm	Colour	black
Halogen	Yes	Resistance to oils	IRM 902/903 oil resistance test at (70°Cx4h)
Resistance to spread of flame	FT1	UV-resistant	Complies with UL 1581 Sec. 1200

**Plug**

Plug left	SPE, IP20, female contact, straight, plug, Plastic, IEC 63171-2, shielded	Plug right	SPE, IP20, female contact, straight, plug, Plastic, IEC 63171-2, shielded
-----------	---	------------	---

**Plug, left**

Plug left	SPE, IP20, female contact, straight, plug, Plastic, IEC 63171-2, shielded
-----------	---

Creation date June 16, 2025 5:54:53 PM CEST

Catalogue status 07.06.2025 / We reserve the right to make technical changes.

**IE-S1DS2VE0050T01T01-E****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Plug, right**

Plug right	SPE, IP20, female contact, straight, plug, Plastic, IEC 63171-2, shielded
------------	---

**Classifications**

ETIM 6.0	EC002599	ETIM 7.0	EC002599
ETIM 8.0	EC002599	ETIM 9.0	EC002599
ETIM 10.0	EC002599	ECLASS 9.0	27-06-03-08
ECLASS 9.1	27-06-03-08	ECLASS 10.0	27-06-03-08
ECLASS 11.0	27-06-03-08	ECLASS 12.0	27-06-03-08
ECLASS 13.0	27-06-03-08	ECLASS 14.0	27-06-03-08
ECLASS 15.0	27-06-03-08		

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**Approvals**

Approvals



Approvals MAMID	<a href="https://mdcop.weidmueller.com/mediadelivery/rendition/900_319222/-T1z1mm-S800/">https://mdcop.weidmueller.com/mediadelivery/rendition/900_319222/-T1z1mm-S800/</a> <a href="https://mdcop.weidmueller.com/mediadelivery/rendition/900_319228/-T1z1mm-S800/">https://mdcop.weidmueller.com/mediadelivery/rendition/900_319228/-T1z1mm-S800/</a> <a href="https://mdcop.weidmueller.com/mediadelivery/rendition/900_319260/-T1z1mm-S800/">https://mdcop.weidmueller.com/mediadelivery/rendition/900_319260/-T1z1mm-S800/</a>
-----------------	---

ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E316369

**Downloads**

Engineering Data	<a href="#">CAD data – STEP</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**Data sheet**


**IE-S1DS2VE0050T01T01-E**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

**Detailed drawing**



**Dimensional drawing**

