

Bundling and Securing

Cable Ties


Heavy-Duty Cable Ties

T250 Series

These cable ties offer a high minimum tensile strength and have a buckle feature which allows the end of the cable tie to be tucked away if necessary. The buckle also snaps into HellermannTyton lashing tie mounts (LTM.) T-Series Cable Ties feature inside serrations to provide a positive hold on wire and cable bundles. The head design guarantees high tensile strength and a low insertion force. The bent tail design allows quick and simple installations by hand. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.

Features and Benefits

- Engineered and manufactured for maximum performance and quality.
- Made from 100% high-quality plastic to ensure efficient recycling.
- Inside serration for a strong grip onto bundles.
- Easy application either manually or with a tensioning tool.
- Bent tail allows for simpler insertion.



PART NO.	TYPE	Min. Tensile Strength lbs. (N)	Length (L) in. (mm)	Max. Bundle Diameter in. (mm)	Width (W) in. (mm)	Material	Color	Pkg. Qty.
T250S0X2*	T250S	250.0 (1,115.0)	9.1 (230.0)	2.0 (50.0)	0.5 (12.4)	PA66	Black	25
T250S9X2*		250.0 (1,115.0)	9.1 (230.0)	2.0 (50.0)	0.5 (12.4)	PA66	Natural	25
T250R0X2*	T250R	250.0 (1,115.0)	20.3 (515.0)	4.9 (124.5)	0.5 (12.4)	PA66	Black	25
T250R9X2*		250.0 (1,115.0)	20.3 (515.0)	4.9 (124.5)	0.5 (12.4)	PA66	Natural	25
T250M0X2*	T250M	250.0 (1,115.0)	22.3 (565.3)	5.9 (150.0)	0.5 (12.4)	PA66	Black	25
T250M9X2*		250.0 (1,115.0)	22.3 (565.3)	5.9 (150.0)	0.5 (12.4)	PA66	Natural	25
T250I0X2*	T250I	250.0 (1,115.0)	28.7 (730.0)	8.0 (203.0)	0.5 (12.4)	PA66	Black	25
T250I9X2*		250.0 (1,115.0)	28.7 (730.0)	8.0 (203.0)	0.5 (12.4)	PA66	Natural	25
T250L0X2*	T250L	250.0 (1,115.0)	34.7 (880.0)	10.0 (254.0)	0.5 (12.4)	PA66	Black	25
T250L9X2*		250.0 (1,115.0)	34.7 (880.0)	10.0 (254.0)	0.5 (12.4)	PA66	Natural	25
T250XL0X2*	T250XL	250.0 (1,115.0)	40.6 (1,030.0)	12.0 (305.0)	0.5 (12.4)	PA66	Black	25
T250XL9X2*		250.0 (1,115.0)	40.6 (1,030.0)	12.0 (305.0)	0.5 (12.4)	PA66	Natural	25

Dimensions are approximate and subject to technical changes. Use Part No. for ordering and Type for specification purposes.

Installation tools: EVO9, EVO9HT, MK9P. *This product meets UL standards. Please see appendix for specific file numbers.



Please note! Not all products listed on this page may have this approval. Please check our website for latest approvals.