

CABTITE EP 24/20 GY**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Cabtite - Cable Entry Plates**

Insert cables and wires without plugs into control cabinets, enclosures or machines in the smallest of spaces, easily and in a space-saving manner.

With the Cabtite cable entry plates, you can do this even in harsh environments, whether protective hoses, pneumatic/hydraulic hoses or fiber optic cables - you can install your cables quickly, easily and in a space-saving manner. The installation is done through only one rectangular wall cut-out and is therefore up to 40% faster in the installation time (compared to standard cable glands).

The IP66 screw version of cable entry plates are tested according to DIN EN 60529 and made of UL94 V-0 certified TPE material with hard plastic core, suitable for the temperature range from -40°C to +90°C.

Cabtite cable entry plates are an economical alternative to conventional cable glands.

General ordering data

Version	Cable entry plate, Cabtite (cable entry system), TPE, grey, Height: 58 mm, Width: 149.6 mm, Depth: 20.2 mm, -40 °C...90 °C, IP66
Order No.	2779360000
Type	CABTITE EP 24/20 GY
GTIN (EAN)	4064675048930
Qty.	10 pc(s).

CABTITE EP 24/20 GY**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	20.2 mm	Depth (inches)	0.795 inch
Height	58 mm	Height (inches)	2.283 inch
Width	149.6 mm	Width (inches)	5.89 inch
Net weight	108.1 g		

Temperatures

Operating temperature	-40 °C...90 °C
-----------------------	----------------

General information

Material	TPE	Protection class (UL)	Type 1, Type 12, Type 4X
Protection degree	IP66	Silicone	No
Tightening torque	3.5 Nm	UL 94 flammability rating	V-0

Number of connectable cables

Type of mounting	4 screws		
Number of connectable cables	20		
Cable entries	Number	12	
	Cable diameter, min.	3.2 mm	
	Cable diameter, max.	6.3 mm	
	Cable type	Round cable	
	Number	8	
	Cable diameter, min.	5.5 mm	
	Cable diameter, max.	10.5 mm	
	Cable type	Round cable	

Classifications

ETIM 6.0	EC002624	ETIM 7.0	EC002624
ETIM 8.0	EC002624	ETIM 9.0	EC002624
ETIM 10.0	EC002624	ECLASS 9.0	27-18-28-15
ECLASS 9.1	27-18-92-65	ECLASS 10.0	27-18-28-15
ECLASS 11.0	27-18-28-15	ECLASS 12.0	27-18-28-15
ECLASS 13.0	27-18-28-15	ECLASS 14.0	27-18-28-15
ECLASS 15.0	27-18-28-15		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Approvals

Approvals



Approvals MAMID	https://mdcop.weidmueller.com/mediadelivery/rendition/900_319222/-T1z1mm-S800/ https://mdcop.weidmueller.com/mediadelivery/rendition/900_319230/-T1z1mm-S800/
ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E223801

Creation date June 12, 2025 12:52:27 PM CEST

Catalogue status 07.06.2025 / We reserve the right to make technical changes.

CABTITE EP 24/20 GY

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

Approval/Certificate/Document of Conformity

[EU Declaration of Conformity - Cabtite EP - DoC DE PS2483](#)

Engineering Data

[CAD data – STEP](#)

User Documentation

[INSTR CABTITE EP DE/EN](#)

Catalogues

[Catalogues in PDF-format](#)

CABTITE EP 24/20 GY

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

