

Underwater Multi-Conductor Cables

Our polyurethane jacketed underwater cables are engineered to perform reliably in harsh marine environments. Designed with a flexible, premium-grade polymer insulation with low moisture absorption characteristics and clean-stripping elastomer water block, our Xtreme cables are pressure-resistant and built to withstand demanding underwater conditions. Optional shielding is available with 100% aluminum/mylar coverage or a braided tin copper shield with a minimum of 85% coverage. Optional synthetic fiber (Kevlar, Vectran) or steel (GIPS, SS) strength layers upon request.


KEY FEATURES

Rugged multiconductor cables are designed for:

- Continuous underwater use in freshwater or seawater

Winchester's Xtreme grade polyurethane jacket:

- Improves abrasion and cut through resistance
- 7km depth rated pressure resistant waterblocked core
- Provides a solid cable for various marine applications



WINCONN P/N	NO.# COND.	NOMINAL O.D.		JKT. WALL NOM.	MIN BEND RADIUS	NOMINAL WEIGHT (Air) (Sea)	
		inch	mm	inch	inch	lb/1000 ft.	lb/1000 ft.
24AWG							
FM091003-2402	2	0.215	5.5	0.060	2.50	21	5
FM091003-2403	3	0.230	5.8	0.065	2.50	24	6
FM091003-2404	4	0.245	6.2	0.065	2.50	28	7
FM091003-2406	6	0.275	7.0	0.068	3.00	36	10
FM091003-2408	8	0.315	8.0	0.068	3.50	48	13
FM091003-2412	12	0.325	8.3	0.068	3.50	55	18
FM091003-2419	19	0.375	9.5	0.072	4.00	75	26
FM091003-2424	24	0.420	10.7	0.072	4.50	97	35
22AWG		inch	mm	inch	inch	lb/1000 ft.	lb/1000 ft.
FM091003-2202	2	0.240	6.1	0.065	2.50	27	7
FM091003-2203	3	0.260	6.6	0.070	3.00	32	8
FM091003-2204	4	0.275	7.0	0.070	3.00	36	10
FM091003-2206	6	0.305	7.7	0.070	3.50	48	15
FM091003-2208	8	0.365	9.3	0.072	4.00	67	20
FM091003-2212	12	0.380	9.7	0.075	4.00	77	26
FM091003-2219	19	0.435	11.0	0.080	4.50	104	37
FM091003-2224	24	0.480	12.2	0.080	5.00	131	50
20AWG		inch	mm	inch	inch	lb/1000 ft.	lb/1000 ft.
FM091003-2002	2	0.290	7.4	0.070	3.00	37	8
FM091003-2003	3	0.300	7.6	0.070	3.00	42	11
FM091003-2004	4	0.330	8.4	0.075	3.50	52	14
FM091003-2006	6	0.370	9.4	0.075	4.00	68	21
FM091003-2007	7	0.370	9.4	0.075	4.00	72	24
FM091003-2010	10	0.440	11.2	0.075	4.50	99	31
FM091003-2012	12	0.465	11.8	0.080	5.00	114	38
FM091003-2019	19	0.525	13.3	0.080	5.50	151	55

XTREME CABLE

WINCONN P/N	NO.# COND.	NOMINAL O.D.		JKT. WALL NOM.	MIN BEND RADIUS	NOMINAL WEIGHT (Air) (Sea)	
		inch	mm	inch	inch	lb/1000 ft.	lb/1000 ft.
18AWG							
FM091003-1802	2	0.310	7.9	0.070	3.50	44	11
FM091003-1803	3	0.320	8.1	0.070	3.50	51	16
FM091003-1804	4	0.355	9.0	0.075	4.00	65	21
FM091003-1806	6	0.400	10.2	0.075	4.00	86	30
FM091003-1808	7	0.485	12.3	0.075	5.00	117	35
FM091003-1812	12	0.510	13.0	0.082	5.50	148	57
FM091003-1819	19	0.585	14.9	0.085	6.00	204	84
FM091003-1824	24	0.665	16.9	0.085	7.00	263	109
16AWG		inch	mm	inch	inch	lb/1000 ft.	lb/1000 ft.
FM091003-1602	2	0.320	8.1	0.070	3.50	49	13
FM091003-1603	3	0.345	8.8	0.075	3.50	61	19
FM091003-1604	4	0.370	9.4	0.075	4.00	73	26
FM091003-1606	6	0.420	10.7	0.075	4.50	99	37
FM091003-1608	8	0.525	13.3	0.080	5.50	137	41
FM091003-1612	12	0.530	13.5	0.080	5.50	169	71
FM091003-1619	19	0.610	15.5	0.082	6.50	235	105
FM091003-1624	24	0.695	17.7	0.082	7.00	305	136
14AWG		inch	mm	inch	inch	lb/1000 ft.	lb/1000 ft.
FM091003-1402	2	0.355	9.0	0.072	4.00	63	19
FM091003-1403	3	0.375	9.5	0.075	4.00	79	30
FM091003-1404	4	0.415	10.5	0.080	4.50	100	40
FM091003-1406	6	0.485	12.3	0.085	5.00	141	59
FM091003-1408	8	0.585	14.9	0.085	6.00	184	64
FM091003-1412	12	0.600	15.2	0.085	6.00	240	114
12AWG		inch	mm	inch	inch	lb/1000 ft.	lb/1000 ft.
FM091003-1202	2	0.415	10.5	0.075	4.50	88	28
FM091003-1203	3	0.455	11.6	0.085	5.00	118	46
FM091003-1204	4	0.490	12.4	0.085	5.00	146	62
FM091003-1206	6	0.565	14.4	0.085	6.00	205	94
FM091003-1208	8	0.675	17.1	0.090	7.00	259	100
FM091003-1212	12	0.725	18.4	0.090	7.50	361	178
10AWG		inch	mm	inch	inch	lb/1000 ft.	lb/1000 ft.
FM091003-1002	2	0.485	12.3	0.080	5.50	134	52
FM091003-1003	3	0.525	13.2	0.085	5.50	172	77
FM091003-1004	4	0.560	14.2	0.085	6.00	216	104
FM091003-1006	6	0.655	16.6	0.085	7.00	301	152
FM091003-1008	8	0.830	21.1	0.090	9.00	415	174
FM091003-1010	10	0.830	21.1	0.090	9.00	488	248
8AWG		inch	mm	inch	inch	lb/1000 ft.	lb/1000 ft.
FM091003-0802	2	0.670	17.0	0.085	7.00	219	62
FM091003-0803	3	0.710	18.0	0.085	7.50	294	117
FM091003-0804	4	0.785	19.9	0.090	8.00	377	162
6AWG		inch	mm	inch	inch	lb/1000 ft.	lb/1000 ft.
FM091003-0602	2	0.770	19.6	0.090	8.00	304	97
FM091003-0603	3	0.815	20.7	0.090	8.50	413	180
FM091003-0604	4	0.905	23.0	0.095	9.50	535	249
4AWG		inch	mm	inch	inch	lb/1000 ft.	lb/1000 ft.
FM091003-0402	2	0.900	22.9	0.090	9.00	445	161
FM091003-0403	3	0.965	24.5	0.095	10.00	622	297
FM091003-0404	4	1.055	26.8	0.095	11.00	797	408

Dayville
349 Lake Road
Dayville, CT 06241

San Marcos
1810 Diamond St.
San Marcos, CA 92078

Empalme, Mexico
Edificio 54 Parque Industrial Bella Vista
Carretera Internacional KM.1969
Empalme, Sonora México, 85340

 **Winchester**
Interconnect.
www.winconn.com