

VICTORIA

Round lens arrays for industrial lighting. Optimized for 2835 and compatible with up to 5630 size mid-power LED packages.

The VICTORIA-family has been designed for industrial scale lighting. VICTORIA is a Ø300 mm 160 lens array with a space in the middle large enough to house a smart light and other sensors, as well as a built-in-driver. VICTORIA-MINI is a Ø180 mm 80 lens array and supports an optional installation clip to maintain lens performance even in high temperatures. Variants are available with up to IP67 ingress protection. Optimized for 2835 and compatible with up to 5630 size mid-power LED packages.


VICTORIA-MINI

Ø180 mm 80 lens array



PRODUCTS:


C17975_VICTORIA-MINI-W



Dimensions: 180.0 mm x 180.0 mm
Height: 10.75 mm

~60° wide beam.


C17974_VICTORIA-MINI-WWW



Dimensions: 180.0 mm x 180.0 mm
Height: 10.75 mm

~90° wide beam.

CS17977_VICTORIA-MINI-W




Dimensions: 180.0 mm x 180.0 mm
Height: 10.75 mm

~60° wide beam. Ingress protected version.

PRODUCTS:

CS18056_VICTORIA-MINI-WWW-PC




Dimensions: 180.0 mm x 180.0 mm

Height: 10.75 mm

~90° wide beam. Ingress protected
version made from PC.

CS18055_VICTORIA-MINI-W-PC




Dimensions: 180.0 mm x 180.0 mm

Height: 10.75 mm

~60° wide beam. Ingress protected
version made from PC.

CS17978_VICTORIA-MINI-WWW



Dimensions: 180.0 mm x 180.0 mm

Height: 10.75 mm

~90° wide beam. Ingress protected
version.

GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDiL Oy
Joensuunkatu 13
FI-24240 SALO
Finland

LEDiL Inc.
228 West Page Street
Suite D
Sycamore IL 60178
USA

Local sales and technical support
[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)

Shipping locations
Salo, Finland
Hong Kong, China

Distribution Partners
[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)