

H0,34/7**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.comFor conductors from 0.25 to 6,0 mm² (AWG 24 - 10)

tin-plated copper

dimensional tolerances to DIN 46228 part 1

- supplied loose in polybag

General ordering data

Version	Wire-end ferrule, Standard, 7 mm, 7 mm, No
Order No.	2919630000
Type	H0,34/7
GTIN (EAN)	4099986576759
Qty.	1,000 pc(s).

H0,34/7**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Height	7 mm	Height (inches)	0.276 inch
Diameter	1.8 mm	Net weight	0.02 g

Technical data

Version	Standard
---------	----------

Wire-end ferrules

Collar diameter (D2)	1.8 mm	Conductor cross-section	0.34 mm ²
Contact surface diameter (D1)	0.85 mm	Contact surface length (L2)	7 mm
L1 in mm	7 mm	Stripping length	7 mm
Wire connection cross section AWG, max.	AWG 22		

Classifications

ETIM 6.0	EC000005	ETIM 7.0	EC000005
ETIM 8.0	EC000005	ETIM 9.0	EC000005
ETIM 10.0	EC000005	ECLASS 9.0	27-40-02-01
ECLASS 9.1	27-40-02-01	ECLASS 10.0	27-40-02-01
ECLASS 11.0	27-40-02-01	ECLASS 12.0	27-40-02-01
ECLASS 13.0	27-40-02-01	ECLASS 14.0	27-40-02-01
ECLASS 15.0	27-40-02-01		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E499744

Downloads

Catalogues	Catalogues in PDF-format
------------	--

H0,34/7

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

