

Xtreme-Light® & Xtreme-Light-Flex®

Xtreme-Light® fiber designed for rugged applications, with a unique high modulus coating for better survivability in harsh environments. Xtreme-Light cable designs are compression resistant, hydrostatic tested to 15kpsi, subsea depths to 10km. Xtreme-Light cables are available as sub-cables in composite electro-optical cables on other Winchester ROV tethers and Xtreme-Marine E0.



SIMPLEX DESIGNS

Flexible fiber tether with high modulus coated fiber, synthetic strength member and Xtreme grade polyurethane jacket.

MULTI-FIBER DESIGNS

Compact designs with semi-rigid center strength core, waterblocked interstice and Xtreme grade polyurethane jacket.

OPTIONAL ORDERING

- Increased Strength
- Neutral Buoyant
- Insensitive Fibers
- Optional Colors

FIBER PROPERTIES

Fiber Type	Single Mode	Multimode	Multimode
Diameters	9.3/125/245/900um	62.5/125/245/900um	50/125/245/900um
IEC/ISO 11801 TIA/EIA	OS2	OM1	OM4
Attenuation db/km	492AAA @ 1310/ .40 @ 1550/ .30	494AAA @ 850db/ 3.5 @ 1300db/ 1.0	494AAA @ 850db/ 3.0 @ 1300db/ 1.0
Proof Test	200 kpsi	200 kpsi	200 kpsi
Temp Range	-60c to 150c	-60c to 150c	-60c to 150c
900um Fiber	-60c to 120c short term	-60c to 120c short term	-60c to 120c short term
Extreme PU Jacketed	-60c to 90c long term	-60c to 90c long term	-60c to 90c long term

XTREME CABLES

PART NUMBERS

<i>Part Number</i>	<i>Type/ Power</i>	<i>Break Strength</i>		<i>Finished Diameter</i>		<i>Min Bend Radius</i>		<i>Weight Air</i>	
Xtreme-Light Simplex		LBS.	KG	Inch	mm	Inch	mm	LB/1000 ft	KG/KM
FM011402SM12	Single Mode	300	136	0.092	2.3	2.0	50	3.5	5.2
FM011402SM13	Single Mode	300	136	0.118	3.0	2.0	50	5.7	8.5
FM011402MM12	MM 62.5/125	300	136	0.092	2.3	2.0	50	3.5	5.2
FM011402MM13	MM 62.5/125	300	136	0.118	3.0	2.0	50	5.7	8.5
Xtreme-Light Simplex Neutral Buoyant		LBS.	KG	Inch	mm	Inch	mm	LB/1000 ft	KG/KM
FM011402SMNBT	Single Mode	300	136	0.144	3.7	2.0	50	7.3	10.9
FM011402MMNBT	MM 62.5/125	300	136	0.144	3.7	2.0	50	7.3	10.9
FM011402SMNBF*	Single Mode	300	136	0.100	2.5	2.0	50	3.5	5.2
FM011402MMNBF*	MM 62.5/125	300	136	0.100	2.5	2.0	50	3.5	5.2
Xtreme-Light Multifiber		LBS.	KG	Inch	mm	Inch	mm	LB/1000 ft	KG/KM
FM011402SM33	3 ea.	200	90	0.180	4.6	3.0	76	14	21
FM011402SM34	4 ea.	200	90	0.180	4.6	3.0	76	14	21
FM011402SM36	6 ea.	200	90	0.180	4.6	3.0	76	15	22
FM011402MM33	3 ea.	200	90	0.180	4.6	3.0	76	14	21
FM011402MM34	4 ea.	200	90	0.180	4.6	3.0	76	14	21
FM011402MM36	6 ea.	200	90	0.180	4.6	3.0	76	15	22
Xtreme-Light-Flex Simplex		LBS.	KG	Inch	mm	Inch	mm	LB/1000 ft	KG/KM
FM011402SM14	Single Mode	300	136	0.092	2.3	2.0	50	3.5	5.2
FM011402MM14	MM 50/125	300	136	0.092	2.3	0.80	20	3.5	5.2

Dayville
349 Lake Road
Dayville, CT 06241

San Marcos
1810 Diamond St.
San Marcos, CA 92078

Empalme, Mexico
Edificio 54 Parque Industrial Bella Vista
Carretera Internacional KM.1969
Empalme, Sonora México, 85340