

ZED-F20P

u-blox F20 triple-band high precision GNSS module




High precision GNSS receiver for air and ground robotics

- Triple-band GNSS module with RTK and PPP-RTK support
- Optimal performance for compact, high-volume applications
- Native support for u-blox PointPerfect Flex and Live
- Industrial standard ZED form factor
- u-blox end-to-end hardened security



17.0 x 22.0 x 2.4 mm



ZED-F20P

Product description

The ZED-F20P module delivers robust high-precision GNSS performance for fast-scaling robotics applications on the ground and in the air. With support for triple-band GNSS (L1/L2/L5) and advanced positioning techniques, including RTK and PPP-RTK, it enables centimeter-level accuracy with fast convergence and highest reliability — ideal for autonomous systems operating in dynamic, real-world conditions.

Optimized for the needs of robotic lawn mowers, unmanned autonomous vehicles (UAVs), and other industrial automation platforms, ZED-F20P balances high performance with power efficiency in a compact, integration-friendly design. It concurrently receives signals from GPS, Galileo, BeiDou, QZSS, and NavIC across three frequency bands, ensuring resilient positioning even in GNSS-challenged environments.

ZED-F20P supports RTCM and SPARTN correction formats, enabling flexibility across local and cloud-based correction sources, including Virtual Reference Stations (VRS) and continental-wide SSR services. Its fast update rate, minimal cycle slips, and low-noise measurements make it ideal for precise control loops and smooth path execution.

Designed to accelerate time-to-market for innovative robotic platforms, ZED-F20P includes key security features, including OSNMA-based message authentication, providing both accuracy and integrity in safety-critical systems.

ZED-F20P is your GNSS foundation for the next generation of scalable robotic applications.

	ZED-F20P
Grade	
Automotive	
Professional	•
Standard	
GNSS	
GPS / SBAS	•
QZSS	•
Galileo	•
BeiDou	•
NavIC	•
Band support	L1/L2/L5
Compatible u-blox services	
AssistNow™	•
PointPerfect Flex	•
PointPerfect Live	•
Interfaces	
UART	2
SPI	1
DDC (I2C compliant)	1
Features	
Programmable (flash)	•
Carrier phase output	•
Additional SAW	•
RTC crystal	•
Oscillator	T
RTK rover	•
RTK base station	•
Timepulse	1
Power supply	
2.7 V – 3.6 V	•

T = TCXO



Features

Receiver type	672-channel u-blox F20 engine GPS L1C/A, L2C, L5 GAL E1B/C, E5a BDS B1I, B1C, B2a QZSS L1C/A, L1C/B*, L2C, L5 NavIC L1*, L5 SBAS L1C/A	
Nav. update rate	RTK	up to 25 Hz
Position accuracy ¹	Standalone SBAS RTK PPP-RTK	1.2 m 0.6 m 0.6 cm + 1 ppm < 6 cm
Convergence time ¹	RTK PPP-RTK	< 7 sec < 40 sec
Acquisition	Cold starts Aided starts Reacquisition	25 s 2 s 2 s
Sensitivity	Tracking & Nav. Cold starts Hot starts Reacquisition	-167 dBm -148 dBm -158 dBm -160 dBm
Assistance	AssistNow Online OMA SUPL & 3GPP compliant	
Oscillator	TCXO	
RTC crystal	Built-in	
Anti-jamming	CW detection	
Anti-spoofing	Advanced anti-spoofing algorithms and OSNMA	
Memory	Flash	
Moving base*	For attitude sensing and heading applications	
Supported antennas	Active	

¹ Depends on atmospheric conditions, baseline length, GNSS antenna, multipath conditions, satellite visibility, and geometry

* Feature in development

Interfaces

Serial interfaces	2 UART 1 SPI 1 DDC (I2C compliant)
Digital I/O	Configurable timepulse EXTINT input for wakeup RTK fix status GEOFENCE status
Timepulse	Configurable: 0.25 Hz to 10 MHz
Protocols	NMEA 4.11, UBX binary, RTCM v. 3.4, SPARTN v. 2.0.2

Package

54-pin LGA (land grid array), 17 x 22 x 2.4 mm
--

Environmental data, quality, and reliability

Operating temp.	-40 °C to +85 °C
Storage temp.	-40 °C to +85 °C
Vibration	MIL-STD-810G (Category 24, 7.7g RMS)
Environmental grade	RoHS compliant (2015/863/EU)
Green (halogen-free)	
EU Radio Equipment Directive	compliant 2014/53/EU
Environmental grade	Qualified according to u-blox qualification policy, based on a subset of AEC-Q104
Quality management	Manufactured and fully tested in ISO/TS 16949 certified production sites

Electrical data

Supply voltage	2.7 V to 3.6 V
Power consumption	55 mA at 3.0 V
Backup supply	1.65 V to 3.6 V

Compatible u-blox location services

Location services	AssistNow A-GNSS service PointPerfect Flex GNSS correction service PointPerfect Live GNSS correction service
-------------------	--

Support products

u-blox support products provide reference design, and allow efficient integration and evaluation of u-blox positioning technology.

EVK-X20P-00	Evaluation kit with ZED-X20P configurable as ZED-F20P
u-center 2	Highly intuitive software for GNSS performance evaluation
ANN-MB2	All-band high precision antenna

Product variants

ZED-F20P-00B	Triple-band high precision GNSS module
--------------	--

Further information

For contact information, see www.u-blox.com/contact-u-blox.

For more product details and ordering information, see the product data sheet.

Legal Notice:

u-blox or third parties may hold intellectual property rights in the products, names, logos and designs included in this document. Copying, reproduction, or modification of this document or any part thereof is only permitted with the express written permission of u-blox. Disclosure to third parties is permitted for clearly public documents only.

The information contained herein is provided "as is". No warranty of any kind, either express or implied, is made in relation to the accuracy, reliability, fitness for a particular purpose, or content of this document. This document may be revised by u-blox at any time. For most recent documents, please visit www.u-blox.com.