


Automotive Thick Film Chip Resistors (CQ Series)



Features:

- AEC-Q200 Compliant
- Suitable for reflow and wave soldering
- Stable electrical capability, High reliability
- Anti Sulfuration
- Available in KIT packaging 1% E24





Application:

- Entertainment System
- Outdoor Electronic app
- Comfort & Safety Controls
- Lighting
- Batteries & Chargers
- Telecom
- Consumer Electronics
- General purpose

Automotive Thick Film Chip Resistors (CQ Series)



Derating Curve



Operating Temperature Range -55~+155°C

Type	Power (70°C)	Max Working Voltage	Max Overload Voltage	Dielectric With standing Voltage	Resistance Value of Jumper	Rated Current of Jumper	Max. Current of Jumper
CQ01	1/20W	25V	50V	/	<50mΩ	0.5A	1A
CQ02	1/16W	50V	100V	100V	<50mΩ	1A	2A
CQ03	1/10W	75V	150V	300V	<50mΩ	1A	2A
CQ05	1/8W	150V	300V	500V	<50mΩ	2A	5A
CQ06	1/4W	200V	400V	500V	<50mΩ	2A	10A
CQ07	1/2W	200V	500V	500V	<50mΩ	2A	10A
CQ10	3/4W	200V	500V	500V	<50mΩ	2A	10A
CQ12	1W	200V	500V	500V	<50mΩ	2A	10A

Characteristic

Test Item	Standard	Test Item	Standard
Temperature Coefficient	CQ01: $1\Omega \leq R \leq 10\Omega \pm 400\text{ppm/}^{\circ}\text{C}$ $>10\Omega: \pm 200\text{ppm/}^{\circ}\text{C}$ CQ02-CQ12: $1\Omega \leq R \leq 10\Omega: \pm 200\text{ppm/}^{\circ}\text{C}$ $>10\Omega: \pm 100\text{ppm/}^{\circ}\text{C}$	Resistance to Soldering Heat	$\pm(1.0\%+0.05\Omega)$ Max
Short Time Overload	$\pm 1\%: \pm(1.0\%+0.1\Omega)$ Max $\pm 5\%: \pm(2.0\%+0.1\Omega)$ Max	Temperature Cycling	$\pm 1\%: \pm(0.5\%+0.1\Omega)$ Max $\pm 5\%: \pm(1.0\%+0.1\Omega)$ Max
Terminal Bending	$\pm(1.0\%+0.05\Omega)$ Max	Biased Humidity	$\pm 1\%: \pm(1.0\%+0.1\Omega)$ Max $\pm 5\%: \pm(3.0\%+0.1\Omega)$ Max
Solderability	Min. 95%coverage	Load Life	$\pm 1\%: \pm(1.0\%+0.1\Omega)$ Max $\pm 5\%: \pm(3.0\%+0.1\Omega)$ Max
Dielectric Withstanding Voltage	No evidence of flashover, mechanical damage, arcing or insulation breakdown	Moisture Resistance	$\pm 1\%: \pm(0.5\%+0.1\Omega)$ Max $\pm 5\%: \pm(3.0\%+0.1\Omega)$ Max

Note: $0.1\Omega \sim 0.97\Omega : \pm 800\text{PPM/}^{\circ}\text{C}$ can be supply on a case to case basis.

Load Life test condition: 35% rated power at 125°C, 1000H.

Anti-sulfurized performance: H₂S 3~5ppm, 50°C ±2°C, 91%~93%RH, 1000H; Excellent stability



**IATF 16949
ISO 14001**

This document is a general reference only
Any inquiry/technical support pls. send
email to your contact sales.

Legal Disclaimer



The information provided in the catalog/data sheet /single pages/short form is for the purpose of describing product specifications only, and ROYALOHM and its affiliates (hereinafter collectively referred to as "ROYALOHM") hereby disclaim any liability for any errors, inaccuracies or incompleteness contained in any product-related information (including but not limited to product specifications, datasheets, pictures, graphics). ROYALOHM reserves the right to modify this content without prior notice. Thank you for your understanding.

ROYALOHM makes no representation, warranty, and guarantee as to the fitness of its products for any particular purpose or the continuing production of any ROYALOHM products.

To the maximum extent permitted by law, ROYALOHM disclaims

- I. any and all liability arising out of the application or use of any ROYALOHM product,
- II. any and all liability, including without limitation special, consequential or incidental damages, and
- III. any and all implied warranties, including warranties of fitness for a particular purpose, non-infringement and merchantability.

ROYALOHM products are not intended for use in medical, life-saving, or life-sustaining equipment, nor are they intended for any other purpose where product failure or mismanagement could endanger life or cause harm to or death to the human body.

Customers use or sell ROYALOHM products for the above purposes at their own risk. If need products for such purposes, please be sure to consult with our company to obtain relevant information about the applicable products.

Regardless of the application of ROYALOHM products, it is recommended to carry out safety tests while using measures such as protective circuits and redundant circuits to protect the safety of equipment.



IATF 16949
ISO 14001

This document is a general reference only
Any inquiry/technical support pls. send
email to your contact sales.