

ISSUE 16; January 2025

Description

- Standard 7.0 x 5.0mm crystal oscillator in a ceramic package with a seam sealed metal lid, hermetically sealed.
Stock parts are available.
Fast Make capability: CFPP-73 series programmable oscillators are the nearest equivalent fast make model.



Frequency Parameters

- Frequency: 500.0kHz to 160.0MHz
- Frequency Stability: $\pm 50.00\text{ppm}$ to $\pm 100.00\text{ppm}$
- Ageing: $\pm 5\text{ppm}$ per year

Electrical Parameters

- Supply Voltage: $3.3\text{V} \pm 10\%$
- Note: parameters are referenced to 15pF load

Operating Temperature Ranges

- 20 to 70°C
- 40 to 85°C

Output Details

- Output Compatibility: CMOS
- Drive Capability: 15pF typ, 30pF max
- Start up time: 10ms max, 0.9ms typ to 90% of final amplitude (under ideal conditions @25°C).

Output Control

- Standby Operation:
Logic '1' (>70% VS) to pad 1 enables oscillator output
Logic '0' (<30% VS) to pad 1 disables oscillator output; the oscillator output goes to the high impedance state
No connection to pad 1 enables oscillator output
Standby Current: 10µA max, 0.9µA typ @25°C.

Environmental Parameters

- Shock: Half Sine shock pulse with peak acceleration 500g; Pulse duration: 0.3ms
- Vibration: MIL-STD-202 Method 204. 5g for 20 minutes, 12 cycles in each of the 3 orientations, 10 - 2000 Hz. As per Table 11 of AEC-Q200.
- Storage Temperature Range: -55 to 125°C

Manufacturing Details


- RoHS Terminations: NiAu
- RoHS Reflow: 260°C 10s max

Ordering Information


- Frequency*
Model
Output
Frequency Stability*
Operating Temperature Range*
Supply Voltage
(*minimum required)
- Example:
10.0MHz CFPS-73
CMOS $\pm 50\text{ppm}$ -20 to 70C 3.3V



Outline (mm)



Recommended Solder Pad Layout



Sales Office Contact Details:

UK: +44 (0)1460 270200

Email: info@iqdfrequencyproducts.com

Web: www.iqdfrequencyproducts.com


Compliance

- RoHS Status (2015/863/EU) Compliant
- REACH Status Compliant
- MSL Rating (JDEC-STD-033): Not Applicable


Packaging Details

- Tape & reel in accordance with EIA-481
Quantities below the standard reel size to be supplied on cut tape.
Standard Pack Quantity: 1,000

Test Circuit



Waveform



Electrical Specification - maximum limiting values @ 15pF and 3.3V ±10%

Frequency Min	Frequency Max	Temperature Range	Stability (Min)	Current Draw	Rise and Fall Time	Duty Cycle
		°C	ppm	mA	ns	%
500.0kHz	16.999999MHz	-20 to 70	±50.0	7	10	40/60
		-40 to 85	±50.0	7	10	40/60
17.0MHz	49.999999MHz	-20 to 70	±50.0	38	10	40/60
		-40 to 85	±50.0	38	10	40/60
50.0MHz	79.999999MHz	-20 to 70	±50.0	38	8	40/60
		-40 to 85	±50.0	38	8	40/60
80.0MHz	80.999999MHz	-20 to 70	±50.0	38	5	40/60
		-40 to 85	±50.0	38	5	40/60
81.0MHz	160.0MHz	-20 to 70	±50.0	65	5	40/60
		-40 to 85	±50.0	65	5	40/60

This document was correct at the time of printing; please contact your local sales office for the latest version.

[Click to view latest version on our website.](#)

Sales Office Contact Details:

UK: +44 (0)1460 270200

Email: info@iqdfrequencyproducts.com

Web: www.iqdfrequencyproducts.com