

# How the ES2P PDU Stacks Up Against the Competition

**A practical, reliable workhorse. Built for how operations run today.**

The ES2P PDU delivers pure essentials in rack power distribution, bringing intelligent visibility, gigabit connectivity, simplified maintenance, and built-in security to modern data center and enterprise IT applications. Here's how it compares with the competition.



| Feature                                      | Panduit Ranking | Panduit ES2P                                  | Competitor 1     | Competitor 2           | Competitor 3                          | Competitor 4           |
|----------------------------------------------|-----------------|-----------------------------------------------|------------------|------------------------|---------------------------------------|------------------------|
| <b>Network Connectivity</b>                  | Best            | 10/100/1000 - Single Gigabit Ethernet, Serial | 10/100 MBPS      | 10/100 MBPS            | 10/100 MBPS                           | 10/100 MBPS            |
| <b>Controller Interface Display</b>          |                 | Color LCD                                     | Dot Matrix       | Segment LCD            | Segment LCD                           | Dot Matrix             |
| <b>Colored Display</b>                       |                 | ✓                                             | –                | 2 Digit Display        | 4 Digit Display                       | –                      |
| <b>Security</b>                              |                 | SNMPv3, TLS, encrypted protocols              | SNMP             | SNMPv3                 | SNMPv3                                | SNMPv3                 |
| <b>API</b>                                   |                 | ✓                                             | –                | –                      | –                                     | –                      |
| <b>Daisy Chain (Max)</b>                     |                 | 16                                            | 4                | 4                      | 4                                     | 4                      |
| <b>Mixed Daisy Chaining</b>                  | Equal           | –                                             | –                | –                      | –                                     | –                      |
| <b>Secure Zero Touch Provisioning (sZTP)</b> |                 | –                                             | –                | –                      | –                                     | –                      |
| <b>Hot-Swappable Controller</b>              |                 | ✓                                             | –                | –                      | ✓                                     | ✓                      |
| <b>Environmental Monitoring</b>              |                 | ✓                                             | ✓                | ✓                      | ✓                                     | ✓                      |
| <b>Rack Access Control</b>                   |                 | Yes with SRC01                                | Yes with NetBotz | –                      | –                                     | –                      |
| <b>Outlet Type</b>                           |                 | C13 / C19 / NEMA 5-20R                        | C13 / C19        | C13 / C19 / NEMA 5-15R | C13 / C19 / NEMA 5-20R                | C13 / C19 / NEMA 5-20R |
| <b>Outlet Switching</b>                      |                 | –                                             | –                | –                      | –                                     | –                      |
| <b>Outlet Metering</b>                       |                 | ✓                                             | ✓                | ✓                      | ✓                                     | ✓                      |
| <b>Metering Accuracy</b>                     |                 | ± 2%                                          | ± 3%             | ± 2%                   | ± 1%                                  | ± 1%                   |
| <b>Vertical Toolless Mounting</b>            |                 | ✓                                             | ✓                | ✓                      | ✓                                     | ✓                      |
| <b>Operating Temperature (Max)</b>           |                 | 55°C                                          | 60°C             | 40°C                   | 60°C                                  | 45°C                   |
| <b>TAA Compliant (North America)</b>         |                 | ✓                                             | ✓                | ✓                      | ✓                                     | ✓                      |
| <b>Warranty</b>                              |                 | 3 Standard + 2 Year Extended Warranty         | 2 Year Standard  | 2 Year Standard        | 3 Standard + 2 Year Extended Warranty | 5 Year Standard        |

► For more information, visit [panduit.com/pdu](https://panduit.com/pdu)