

TSZ SERIES

High-precision, zero-drift op amp



Precision and low power consumption for high-accuracy sensor interfaces

The **TSZ series** of operational amplifiers offer low power consumption and zero-drift in compact packages. These amplifiers implement a chopper-stabilized architecture that minimizes offset voltages and drift, making them ideal for high-accuracy sensor interfaces. Despite their miniature size, these ultra-precise amplifiers offer high-impedance inputs with a common-mode range of 100 mV beyond the rails and rail-to-rail output that ranges within 50 mV of the rails. They are qualified for automotive applications at 125°C, 150°C, and 175°C maximum temperatures.

KEY FEATURE & BENEFITS


- Offset: (TSZ12 series)
 - $\pm 1 \mu\text{V}$ typ.
 - $\pm 8 \mu\text{V}$ max.
- Offset drift: (TSZ12 series)
 - $10 \text{ nV/}^\circ\text{C}$ typ.
 - $30 \text{ nV/}^\circ\text{C}$ max.
- 400 kHz GBW (TSZ12 series)
- 1.6 MHz GBW (TSZ15 series)
- 3 MHz GBW (TSZ18 series)
- Operating range: 1.8 to 5.5 V
- Temperature range:
-40 to 125°C (optionally up to 175°C)
- Rail-to-rail input and output
- ESD: 4 kV HBM
- AEC-Q100 qualified

KEY APPLICATIONS

- Portable instrumentation
- Battery-powered devices
- Sensor interfaces
- Medical instrumentation
- Electronic scales
- Temperature measurement
- Automotive current measurement
- Gearbox, brake, and exhaust systems
- Engine controller unit (ECU)



High-precision operational amplifiers



TSZ family portfolio

Part number	Automotive	Package	I _{cc} (μA) typ.	SR (V/μs) typ.	N° channels	Temperature
Gain bandwidth product 400 kHz						
TSZ121	•	SC70-5	31	0.19	1	-40 to 125°C
TSZ122	•	S08 MiniS08 DFN8			2	
TSZ124	•	QFN16 TSSOP14			4	
Gain bandwidth product 1.6 MHz						
TSZ151	•	SC70-5 SOT23-5	210	0.8	1	-40 to 125°C
TSZ152	•	S08 MiniS08 DFN8			2	
Gain bandwidth product 3 MHz						
TSZ181	•	DFN6 SOT23-5	800	4.7	1	-40 to 125°C
TSZ181H	•	S08				-40 to 150°C
TSZ181H1	•	SOT23-5				-40 to 175°C
TSZ182	•	S08 MiniS08 DFN8			2	-40 to 125°C
TSZ182H	•	S08				-40 to 150°C
TSZ182H1	•	SOT23-5				-40 to 175°C



X-NUCLEO-IKA01A1
Multifunctional expansion board based on operational amplifiers (TSZ124, TSU104, TSV734) for STM32 Nucleo



P-NUCLEO-IKA02A1
STM32 Nucleo pack: electrochemical toxic gas sensor expansion board with CO sensor



STEVAL-CCA022V1
Evaluation board for SOT23 and SC70



Scan this QR code to get access to documentation and applications notes



© STMicroelectronics - April 2025 - Printed in the United Kingdom - All rights reserved
ST and the ST logo are registered and/or unregistered trademarks of STMicroelectronics International NV or its affiliates in the EU and/or elsewhere. In particular, ST and the ST logo are Registered in the US Patent and Trademark Office.

For additional information about ST trademarks, please refer to www.st.com/trademarks.

All other product or service names are the property of their respective owners.

