



Automotive 2-in-1 Package, High Current, Dual Inductor, Linear Saturation Series for Reduced Signal Distortion



FEATURES

- 7.80 mm x 7.26 mm x 7.39 mm size
- Two inductors in one package saves board space and assembly time
- Improved linear magnetization of core material reduces formation of total harmonic distortion (THD)
- Inductors can be connected in series, parallel, or operated independently
- Magnetically shielded composite construction minimizes flux leakage compared to gapped ferrite inductors
- Optimized design realizes high quality sound and low signal distortion
- Low coupling for minimal cross-talk between inductors
- Handles high transient current spikes without saturation
- Ultra-low buzz noise, due to composite construction
- AEC-Q200 qualified
- **Patent pending**
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912




RoHS
COMPLIANT
HALOGEN
FREE
GREEN
(5-2008)

LINKS TO ADDITIONAL RESOURCES


[Product Page](#)

[3D Models](#)

APPLICATIONS

- Class D audio amplifiers
- Multi-phase converters

PART NUMBER	L ₀ INDUCTANCE ± 20 % AT 100 kHz, 0.25 V, 0 A (μ H)	DCR TYP. 25 °C (m Ω)	DCR MAX. 25 °C (m Ω)	HEAT RATING CURRENT DC TYP. (A) ⁽¹⁾	SATURATION CURRENT DC TYP. (A)		SRF TYP. (MHz)
					20 % DROP ⁽²⁾	30 % DROP ⁽³⁾	
IHLD2525GGER3R3MA1	3.3	25	28.5	6.5	14.0	17.7	31
IHLD2525GGER4R7MA1	4.7	37	39.6	5.5	10.0	13.0	25
IHLD2525GGER5R6MA1	5.6	47	50.3	5.0	9.2	11.8	24.5
IHLD2525GGER100MA1	10	86	90.9	3.7	7.5	9.5	20.4
IHLD2525GGER150MA1	15	117	125	3.0	6.4	7.5	14.4



Notes

- All test data is referenced to 25 °C ambient
- Test condition: 100 kHz, 0.25 V
- Electrical data is specified for a single coil; placing coils in series will double the DCR and inductance; placing coils in parallel will cut the DCR and inductance in half
- Operating temperature range -55 °C to +125 °C
- The part temperature (ambient + temp. rise) should not exceed the maximum rating under worst case operating conditions. Circuit design, component placement, PCB trace size and thickness, airflow and other cooling provisions all affect the part temperature. Part temperature should be verified in the end application
- Rated operating voltage (across inductor) = 50 V

⁽¹⁾ DC current (A) that will cause an approximate ΔT of 40 °C

⁽²⁾ DC current (A) that will cause L₀ to drop approximately 20 %

⁽³⁾ DC current (A) that will cause L₀ to drop approximately 30 %

DIMENSIONS in inches [millimeters]

SCHEMATICS

DESCRIPTION






IHLD2525GG-A1	4.7 μ H	ER	e3
MODEL	INDUCTANCE VALUE	PACKAGE CODE	JEDEC® LEAD (Pb)-FREE STANDARD






GLOBAL PART NUMBER

I	H	L	D	2	5	2	5	G	G	E	R	4	R	7	M	A	1
PRODUCT FAMILY								PACKAGE CODE		INDUCTANCE VALUE				TOLERANCE	SERIES		

ER = tape and reel 4R7 = 4.7 μ H

M = 20 %

PERFORMANCE GRAPHS


PERFORMANCE GRAPHS: INDUCTANCE AND Q VS. FREQUENCY


Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.