


Commercial, High Current, Radial, Through-Hole Inductor, High Temperature (155 °C)



LINKS TO ADDITIONAL RESOURCES


[Product Page](#)

MECHANICAL SPECIFICATIONS

- Terminations: solder dipped pure tin
- Weight: 182 g

FEATURES

- High temperature rating, up to 155 °C
- 38.1 mm x 38.1 mm x 21.89 mm size
- Improved core material for 20 % reduction in core loss from previous IHXL-5A models
- Metal alloy construction for excellent magnetic shielding and high thermal conductivity to minimize hot spots
- Flat surface for mounting heat sink or active cooling cold plate
- Handles high transient current spikes without saturation
- Custom solutions available for termination style (swaged, 90° bend, SMD, etc.), inductance, current, temperature, and voltage rating
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912



RoHS
COMPLIANT
HALOGEN
FREE
GREEN
(5-2008)

APPLICATIONS

- High current battery charging
- Brushless DC motor (BLDC)
- DC-Link filter
- Differential mode choke
- Boost power factor correction choke
- Solar power / wind power applications

STANDARD ELECTRICAL SPECIFICATIONS

PART NUMBER	L ₀ INDUCTANCE ± 20 % AT 100 kHz, 0.25 V, 0 A (μH)	DCR 25 °C (mΩ)		HEAT RATING CURRENT DC TYP. ⁽¹⁾ (A)		SATURATION CURRENT DC TYP. ⁽²⁾ (A)		SRF TYP. (MHz)
		TYP.	MAX.	40 °C RISE	80 °C RISE	20 % DROP	30 % DROP	
IHXL1500VZEBR68M31	0.68	0.12	0.13	180	280	235	335	37.8
IHXL1500VZEBR82M31	0.82	0.17	0.18	159	248	230	330	27.9
IHXL1500VZEB1R5M31	1.5	0.25	0.26	146	220	138	193	17.2
IHXL1500VZEB2R2M31	2.2	0.32	0.34	133	210	104	150	15.0
IHXL1500VZEB3R3M31	3.3	0.40	0.42	111	170	87	124	12.4
IHXL1500VZEB5R6M31	5.6	0.61	0.64	88	130	67	96	9.7
IHXL1500VZEB6R8M31	6.8	0.79	0.83	60	95	64	94	8.7
IHXL1500VZEB100M31	10	1.10	1.16	55	88	49	72	7.6

Notes

- All test data is referenced to 25 °C ambient
 - Operating temperature range -55 °C to +155 °C
 - The part temperature (ambient + temp. rise) should not exceed 155 °C under worst case operating conditions. Circuit design, component placement, PCB trace size and thickness, airflow and other cooling provisions all affect the part temperature. Part temperature should be verified in the end application
 - Rated operating voltage, across inductor = 100 V
- ⁽¹⁾ DC current (A) that will cause an approximate ΔT of +40 °C and +80 °C, respectively
- ⁽²⁾ DC current (A) that will cause L₀ to drop approximately 20 % and 30 %, respectively

**DESCRIPTION**

IHXL1500VZ-31	0.68 μH	$\pm 20\%$	BULK / TRAY PACKAGING	e3
MODEL	INDUCTANCE VALUE	INDUCTANCE TOLERANCE	PACKAGE CODE	JEDEC® LEAD (Pb)-FREE STANDARD

GLOBAL PART NUMBER

I	H	X	L	1	5	0	0	V	Z	E	B	R	6	8	M	3	1
PRODUCT FAMILY				SIZE				PACKAGE CODE		INDUCTANCE VALUE		INDUCTANCE TOLERANCE		SERIES			
								EB = tray pack 50 pcs/box		R68 = 0.68 μ H		M = $\pm 20\%$					

DIMENSIONS in inches [millimeters]

Figure A















Figure B



VALUE	X - LEAD WIDTH	Y - LEAD THICKNESS	FIGURE
0.68	0.298 [7.34]	0.162 [4.11]	A
0.82	0.253 [6.43]	0.102 [2.59]	A
1.5	0.253 [6.43]	0.102 [2.59]	A
2.2	0.253 [6.43]	0.102 [2.59]	A
3.3	0.253 [6.43]	0.102 [2.59]	A
5.6	0.253 [6.43]	0.087 [2.21]	B
6.8	0.253 [6.43]	0.071 [1.80]	B
10	0.253 [6.43]	0.059 [1.50]	B











PERFORMANCE GRAPHS: INDUCTANCE VS. CURRENT













PERFORMANCE GRAPHS: INDUCTANCE AND Q VS. FREQUENCY





PERFORMANCE GRAPHS: IMPEDANCE VS. FREQUENCY





Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.