


# POWER SOLUTIONS FOR PRECISION TECHNOLOGY SIGNAL CHAINS

## PRECISION LOW POWER Single Channel Voltage, Current and Biosignal Measurement Noise Optimized

Rev. 0 | Apr. 2022



©2022 Analog Devices, Inc. All rights reserved.  
Trademarks and registered trademarks are the  
property of their respective owners.

This document is interactive. You can click on any underlined text to navigate through the document.

For the resources:

|          |                           |
|----------|---------------------------|
| APPENDIX | <u>Parts Guide</u>        |
|          | <u>Power Requirements</u> |

Left-click the Parts Guide and Power Requirements to go through the list of power devices and other references.

The Power Components are listed on the Appendix, and you may click on the part to go through its product page online.

| PART #          | DESCRIPTION                                                                 |
|-----------------|-----------------------------------------------------------------------------|
| <u>LT3471</u>   | Dual 1.3A, 1.2MHz Boost/Inverter in 3mm × 3mm DFN                           |
| <u>LT8604</u>   | High Efficiency 42V/120mA Synchronous Buck                                  |
| <u>LT8570-1</u> | Boost/SEPIC/Inverting DC/DC Converter with 65V Switch, Soft-Start and Sync. |

For the individual pages:

Left-click the specific signal chain to go through its respective block diagram or power tree.

|                  |                  |
|------------------|------------------|
| Non-isolated     | <b>POWER RE</b>  |
| <u>1-Channel</u> |                  |
|                  |                  |
|                  |                  |
|                  |                  |
|                  | <b>PARAMETER</b> |
|                  |                  |
|                  | Supply Voltage   |
|                  | Supply Current   |
|                  | PSRR             |

APPENDIX

[Parts Guide](#)


[USER GUIDE](#)

[Power Requirements](#)

Voltage, Current & Biosignal Measurement

Noise Optimized – Single Channel

| Non-isolated  | Isolated  |
|---------------|-----------|
| 1.5V Supply   | 5V Supply |
| 3.7V Supply   |           |
| > 5.5V Supply |           |



## APPENDIX

## Parts Guide


## USER GUIDE

## Power Requirements

## Voltage, Current & Biosignal Measurement

## Noise Optimized – Single Channel


| Non-isolated            | Isolated         |
|-------------------------|------------------|
| <u>1.5V Supply</u>      | <u>5V Supply</u> |
| <u>3.7V Supply</u>      |                  |
| <u>&gt; 5.5V Supply</u> |                  |



### APPENDIX

[Parts Guide](#)
[USER GUIDE](#)
[Power Requirements](#)
[Voltage, Current & Biosignal Measurement](#)
[Noise Optimized – Single Channel](#)

| Non-isolated                     | Isolated                  |
|----------------------------------|---------------------------|
| <a href="#">1.5V Supply</a>      | <a href="#">5V Supply</a> |
| <a href="#">3.7V Supply</a>      |                           |
| <a href="#">&gt; 5.5V Supply</a> |                           |



**APPENDIX**

[Parts Guide](#)

[USER GUIDE](#)

[Power Requirements](#)

Voltage, Current & Biosignal Measurement

Noise Optimized – Single Channel


Non-isolated      Isolated

1.5V Supply

3.7V Supply

> 5.5V Supply

5V Supply



Precision Low Power

Voltage, Current & Biosignal Measurement

Noise Optimized – Single Channel

| Non-isolated  | Isolated  |
|---------------|-----------|
| 1.5V Supply   | 5V Supply |
| 3.7V Supply   |           |
| > 5.5V Supply |           |

| PART #                 | DESCRIPTION                                                                                                             |
|------------------------|-------------------------------------------------------------------------------------------------------------------------|
| <b><u>MAX77642</u></b> | Ultra Configurable PMIC Featuring 93% Peak Efficiency Single-Inductor, 3-Output Buck-Boost, 1-LDO for Long Battery Life |
| <b><u>MAX17220</u></b> | 400mV to 5.5V Input, nanoPower Synchronous Boost Converter with True Shutdown                                           |
| <b><u>MAX17530</u></b> | 4V to 42V, 25mA, Ultra-Small, High-Efficiency, Synchronous Step-Down DC-DC Converter with 22µA No-Load Supply Current   |
| <b><u>ADP150</u></b>   | Ultralow Noise, 150 mA CMOS Linear Regulator                                                                            |
| <b><u>ADuM5028</u></b> | Low Emission Isolated DC to DC Converter                                                                                |

Voltage, Current & Biosignal Measurement

Noise Optimized – Single Channel

| Non-isolated  | Isolated  |
|---------------|-----------|
| 1.5V Supply   | 5V Supply |
| 3.7V Supply   |           |
| > 5.5V Supply |           |

POWER REQUIREMENTS

| PARAMETER      | STAGES | Amplifier       |                 | ADC             |                 | Reference   | Isolation        |                  |
|----------------|--------|-----------------|-----------------|-----------------|-----------------|-------------|------------------|------------------|
|                | Part # | AD8237          |                 | AD4001          |                 | ADR3425     | ADuM1441         |                  |
|                | Pin    | +V <sub>S</sub> | -V <sub>S</sub> | V <sub>DD</sub> | V <sub>IO</sub> | IN          | V <sub>DD1</sub> | V <sub>DD2</sub> |
| Supply Voltage | V      | 3.3             | -               | 1.8             | 1.8 (or 3.3)    | 3.3         | 3.3              | 3.3              |
| Supply Current | mA     | 0.15            | -               | 5.3             | 0.555           | 0.1         | 0.9              | 0.9              |
| PSRR           | dB     | 73 (100Hz)      |                 | 55 (750kHz)     |                 | 54 (100kHz) | -                |                  |

- Note 1:** The supply currents indicated are the maximum quiescent current of the supply rails. For overall full load or short circuit current specifications, refer to the datasheets of the signal chain components.
- Note 2:** The supply voltages indicated are the values for typical applications.
- Note 3:** Consult the corresponding datasheets for details on power dissipation if needed.
- Note 4:** The actual supply current requirement shall be multiplied depending on the number of channels on the signal chain.