





High Power SiC MOSFET Transistor

AMR027V065H2



Applications:

- Solar Inverters
- Uninterrupted power supplies
- Switch mode power supplies
- Motor drives

Features:

- High blocking voltage with low on-resistance
- High switching speed with low capacitance
- Very low switching losses
- Excellent avalanche ruggedness
- Very fast and robust intrinsic body diode with low reverse recovery
- 0V turn-off V_{gs} for gate driving ease
- RoHS compliant

Absolute Maximum Ratings ($T_{amb}=25^{\circ}\text{C}$, unless specified otherwise)

Symbol	Parameter	Value	Unit
V_{DS}	DC Reverse Voltage	650	V
V_{GSmax}	Gate-source voltage, max. transient voltage	-11/+25	
V_{GSmax}	Gate-source voltage, max. static voltage	-10/+22	
V_{GSop}	Gate-source voltage (Recommended operation values)	-5/+18	
I_D	Continuous drain current ($V_{GS} = 18\text{V}$)	102	A
	Continuous drain current ($V_{GS} = 18\text{V}$), $T_C = 100^{\circ}\text{C}$	72	
$I_{D(pulse)}$	Pulsed drain current (Pulse width limited by T_{jmax})	256	A
P_{tot}	Power dissipation	368	W
T_j	Operating junction temperature	-55 to 175	$^{\circ}\text{C}$
T_{stg}	Storage temperature	-55 to 175	$^{\circ}\text{C}$

Thermal and Mechanical Characteristics

Symbol	Parameter	Min	Typ	Max	Unit
$R_{\theta JC}$	Junction-to-case thermal Resistance	-	0.35	-	$^{\circ}\text{C/W}$
$R_{\theta JA}$	Junction-to-ambient thermal Resistance	-	-	40	$^{\circ}\text{C/W}$

Static Electrical Characteristics ($T_A = 25^\circ\text{C}$, unless specified otherwise)

Symbol	Parameter	Test Conditions	Min	Typ	Max	Unit
BV_{DSS}	Drain-Source Breakdown Voltage	$V_{GS} = 0V, I_D = 100\mu A$	650	-	-	V
$V_{GS(th)}$	Gate-Source Threshold Voltage	$V_{DS} = V_{GS}, I_D = 8mA^a$	1.8	3.1	4.2	
		$V_{DS} = V_{GS}, I_D = 8mA, T_j = 175^\circ\text{C}^a$	-	2.1	-	
I_{DSS}	Drain-Source Leakage current	$V_{DS} = 650V, V_{GS} = 0V$	-	1	50	μA
I_{GSS}	Gate-Source leakage current	$-11V < V_{GS} < 25V$	-	1	100	nA
$R_{DS(on)}$	Drain-Source ON Resistance	$V_{GS} = 15V, I_D = 30A$	-	34	-	m Ω
		$V_{GS} = 18V, I_D = 30A$	-	27	35	
		$V_{GS} = 18V, I_D = 30A, T_j = 175^\circ\text{C}$	-	32	-	
g_{fs}	Transconductance	$V_{DS} = 20V, I_D = 30A$	-	20	-	S
		$V_{DS} = 20V, I_D = 30A, T_j = 175^\circ\text{C}$	-	21	-	
$R_{g(int)}$	Internal gate resistance	$f = 1MHz, V_{AC} = 25mV$	-	3.6	-	Ω

^a Pre-condition V_{th} , as per JEDEC standard JEP183A, (Revision of JEP183 January 2021)

Dynamic Characteristics ($T_A = 25^\circ\text{C}$, unless specified otherwise)

Symbol	Parameter	Test conditions	Min	Typ	Max	Unit
C_{iss}	Input Capacitance	$V_{GS} = 0V, V_{DS} = 600V, f = 100kHz, V_{AC} = 25mV$	-	1946	-	pF
C_{oss}	Output Capacitance		-	161	-	
C_{rss}	Reverse Transfer Capacitance		-	8	-	
E_{oss}	C_{oss} stored energy		-	33	-	μJ
Q_{gs}	Gate-Source Gate Charge	$V_{DD} = 400V, V_{GS} = -5/+18V, I_D = 30A, I_{GS} = 1mA$	-	30	-	nC
Q_{gd}	Gate-Drain Gate Charge		-	16	-	
Q_g	Total Gate Charge		-	80	-	

Switching Characteristics ($T_A = 25^\circ\text{C}$, unless specified otherwise)

Symbol	Parameter	Test conditions	Min	Typ	Max	Unit
$T_{d(on)}$	Turn-on delay time	$V_{DD} = 400\text{V}$, $V_{GS} = -5/+18\text{V}^b$, $I_D = 30\text{A}$, $R_{G(ext)} = 2.4\Omega$, $L = 110\mu\text{H}$	-	14	-	ns
T_r	Rise time		-	16	-	
$T_{d(off)}$	Turn-off delay time		-	30	-	
T_f	Fall time		-	6	-	
E_{on}	Turn On Switching Energy		-	95	-	μJ
E_{off}	Turn Off Switching Energy		-	17	-	
$T_{d(on)}$	Turn-on delay time	$V_{DD} = 400\text{V}$, $V_{GS} = -5/+18\text{V}^b$, $I_D = 30\text{A}$, $R_{G(ext)} = 2.4\Omega$, $L = 110\mu\text{H}$, $T_j = 175^\circ\text{C}$	-	12	-	ns
T_r	Rise time		-	17	-	
$T_{d(off)}$	Turn-off delay time		-	36	-	
T_f	Fall time		-	7	-	
E_{on}	Turn On Switching Energy		-	100	-	μJ
E_{off}	Turn Off Switching Energy		-	24	-	

^b This SiC MOSFET can switch with driver pulses 0V to 18V with optimized PCB layouts and gate drive circuits.

Body Diode Characteristics ($T_A = 25^\circ\text{C}$, unless specified otherwise)

Symbol	Parameter	Test conditions	Min	Typ	Max	Unit
V_{SD}	Body Diode Forward Voltage	$V_{GS} = -5\text{V}$, $I_{SD} = 30\text{A}$	-	3.8	-	V
		$V_{GS} = -5\text{V}$, $I_{SD} = 30\text{A}$, $T_j = 175^\circ\text{C}$	-	3.4	-	
I_S	Continuous diode forward current	$V_{GS} = -5\text{V}$, $T_C = 25^\circ\text{C}$	-	-	76	A
$I_{S, pulse}$	Diode Pulse Current	$V_{GS} = -5\text{V}$, pulse width t_p limited by T_{jmax}	-	-	190	A
t_{rr}	Reverse recovery time	$V_{GS} = -5\text{V}$, $I_{SD} = 30\text{A}$, $V_R = 400\text{V}$, $di/dt = 1.07\text{kA}/\mu\text{s}$	-	17	-	ns
Q_{rr}	Reverse recovery charge		-	0.19	-	μC
I_{rrm}	Peak reverse recovery current		-	19	-	A
t_{rr}	Reverse recovery time	$V_{GS} = -5\text{V}$, $I_{SD} = 30\text{A}$, $V_R = 400\text{V}$, $T_j = 175^\circ\text{C}$, $dif/dt = 1.11\text{kA}/\mu\text{s}$	-	23	-	ns
Q_{rr}	Reverse recovery charge		-	0.33	-	μC
I_{rrm}	Peak reverse recovery current		-	25	-	A

Electrical Characteristic Diagrams





Figure 1. Output characteristics at $T_j = -55^\circ\text{C}$ Figure 2. Output characteristics at $T_j = 25^\circ\text{C}$ Figure 3. Output characteristics at $T_j = 175^\circ\text{C}$ 

Figure 4. Normalized on-resistance vs. temperature




Figure 5. On-resistance vs. drain current for various temperatures




Figure 6. On-resistance vs. temperature for various gate voltages




Figure 7. Transfer characteristic for various junction temperatures




Figure 8. Body diode characteristic at $T_J = -55^\circ C$




Figure 9. Body diode characteristic at $T_j = 25^\circ\text{C}$ Figure 10. Body diode characteristic at $T_j = 175^\circ\text{C}$ 

Figure 11. Threshold voltage vs. temperature




Figure 12. Gate charge characteristics




Figure 13. 3rd quadrant characteristic at $T_j = -55^\circ\text{C}$




Figure 14. 3rd quadrant characteristic at $T_j = 25^\circ\text{C}$




Figure 15. 3rd quadrant characteristic at $T_j = 175^\circ\text{C}$




Figure 16. Output capacitor stored energy




Figure 17. Capacitance vs. drain-source voltage (0 - 200V)




Figure 18. Capacitance vs. drain-source voltage (0 - 600V)




Figure 19. Continuous drain current derating vs. temperature




Figure 20. Maximum power dissipation derating vs. temperature



Figure 21. Switching Times vs. $R_{G(ext)}$ 

Figure 22. Clamped inductive Switching energy vs. drain current





Figure 23. Clamped inductive Switching energy vs. temperature

Figure 24. Clamped inductive Switching energy vs. $R_{G(ext)}$




Figure 25. Reverse recovery charge vs. di/dt Figure 26. Reverse recovery current vs. di/dt 

Figure 27. Transient thermal impedance




Figure 28. Safe Operating Area (SOA)




Figure 29. Switching times definition




Figure 30. Clamped inductive switching waveform test circuit





Figure 31. Reverse Bias Safe Operating Area


Package Information:

Dimension unit: [mm]			
Symbol	Min	Nom	Max
A	4.80	5.00	5.20
A1	2.21	2.41	2.61
A2	1.85	2.00	2.15
b	1.11	1.21	1.36
b1	1.11	1.37	1.57
b2	2.24	2.40	2.60
b3	2.11	2.21	2.36
c	0.51	0.60	0.75
D	20.70	20.90	21.30
D1	15.92	16.22	16.52
D2	1.00	1.20	1.35
E	15.50	15.80	16.10
E1	13.00	13.30	13.60
E2	4.80	5.00	5.20
E3	2.30	2.50	2.70
e	2.54 BSC		
e1	5.08 BSC		

Dimension unit: [mm]			
Symbol	Min	Nom	Max
L	19.62	19.92	20.22
L1	-	-	4.30
øP	3.40	3.60	3.80
øP1	-	-	7.30
Q	5.40	5.80	6.20
S	6.20 BSC		

Recommended Solder Pad Layout

Note: All dimensions are in mm



Ordering Information

Part number	AMR027V065H2
Package	TO-247-4L
Unit quantity	300 EA
Packing type	Tube

IMPORTANT NOTICE AND DISCLAIMER

The information provided in this document is for reference purposes only and is subject to change without notice. The manufacturer makes no representation or warranty, express or implied, regarding the accuracy, completeness, or reliability of the information contained herein. Please contact your local salesperson for information related to warranties. Any datasheet marked as “preliminary” is subject to change and product samples provided with a preliminary datasheet are not intended for reliability testing, may differ from those provided in mass production, and are subject to change or even discontinuation. APC-E makes reasonable commercial efforts to make all datasheets accurate in all material aspects.

All parameters, including but not limited to electrical characteristics, are provided for informational purposes and do not constitute a guarantee of performance under all operating conditions. Typical values are not tested and are not guaranteed.

Products are not authorized for use and must not be used as critical components in life-support devices or systems, safety-critical applications, or any application in which failure of the product could result in personal injury, death, or severe property or environmental damage.

The user is solely responsible for: the selection, qualification, and validation of the product for the intended application; compliance with all applicable laws, regulations, and safety requirements; implementation of adequate design and operating safeguards. Due to technical requirements, components described in this datasheet may contain dangerous substances.

No license, express, implied or by estoppel to any intellectual property rights is granted under this document.

EXCEPT AS EXPRESSLY SET FORTH IN APC-E/LUMINUS’ TERMS AND CONDITIONS OF SALE, THE PRODUCT IS PROVIDED “AS IS” AND “WITH ALL FAULTS.” LUMINUS DISCLAIMS ALL WARRANTIES, EXPRESS IMPLIED, OR BY ESTOPPEL INCLUDING BUT NOT LIMITED TO MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT. LUMINUS DOES NOT WARRANT THAT THE DEVICE WILL OPERATE ERROR FREE OR IN COMBINATIONS SELECTED BY THE USER.

IN NO EVENT SHALL LUMINUS BE LIABLE FOR ANY INDIRECT, INCIDENTAL, SPECIAL, CONSEQUENTIAL, OR PUNITIVE DAMAGES, INCLUDING WITHOUT LIMITATION LOST PROFITS, LOSS OF DATA, OR BUSINESS INTERRUPTION, ARISING OUT OF OR RELATED TO THE USE OF THE PRODUCT OR THIS DOCUMENT, EVEN IF ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.