


QFN-28 to DIP-28 SMT Adapter (0.65 mm pitch, 6 x 6 mm body)


REF.	DIMENSIONS					
	mm			inches		
	MIN.	TYP.	MAX.	MIN.	TYP.	MAX.
A		5.30				
A2		5.30				
B		0.75				
C		0.35				
D		0.30				
E		0.65				
F					0.600	
G					0.100	
H					0.025	

Top View (SMT Footprint)




(Representative drawing only - not to scale)

Bottom View (DIP Pins)



(Representative drawing only - not to scale)

Side View (DIP Pins)



(Representative drawing only - not to scale)