

LISA2-WWW-PIN

~80° wide beam optimized for 3535 size LED packages. 6.6 mm high variant with location pin installation.



SPECIFICATION:


Dimensions	Ø 9.9
Height	6.7 mm
Fastening	glue, pin
ROHS compliant	yes ⓘ

MATERIALS:

Component	Type	Material	Colour	Finish	Length (mm)
LISA2-HLD-PIN-OSL	Holder	PC	black		
LISA2-WWW	Single lens	PMMA	clear		

ORDERING INFORMATION:

Component	Qty in box	MOQ	MPQ	Box weight (kg)
FP11957_LISA2-WWW-PIN	2000	100	1.4	
» Box size:				




See also our general installation guide: www.ledil.com/installation_guide

OPTICAL RESULTS (MEASURED):

OSRAM

Opto Semiconductors

LED OSLON Square EC
FWHM / FWTM 80.0° / 118.0°
Efficiency 72 %
Peak intensity 0.5 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:





Light distribution files

OSRAM

Opto Semiconductors

LED OSLON SSL 150
FWHM / FWTM 91.0° / 132.0°
Efficiency 68 %
Peak intensity 0.4 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:




Light distribution files

OPTICAL RESULTS (SIMULATED):




LED CSP 2323 (BXCP)
 FWHM / FWTM 67.0° / 116.0°
 Efficiency 85 %
 Peak intensity 0.7 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files




LED XE-G
 FWHM / FWTM 86.0° / 140.0°
 Efficiency 83 %
 Peak intensity 0.5 cd/lm
 LEDs/each optic 1
 Light colour/type Green
 Required components:



Light distribution files



LED XE-G
 FWHM / FWTM 89.0° / 138.0°
 Efficiency 83 %
 Peak intensity 0.5 cd/lm
 LEDs/each optic 1
 Light colour/type Red
 Required components:




Light distribution files

OPTICAL RESULTS (SIMULATED):




LED XE-G
 FWHM / FWTM 87.0° / 139.0°
 Efficiency 83 %
 Peak intensity 0.5 cd/lm
 LEDs/each optic 1
 Light colour/type Blue
 Required components:



Light distribution files




LED XE-G
 FWHM / FWTM 88.0° / 141.0°
 Efficiency 82 %
 Peak intensity 0.5 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files



LED LUXEON Rubix
 FWHM / FWTM 71.0° / 138.0°
 Efficiency 84 %
 Peak intensity 0.5 cd/lm
 LEDs/each optic 1
 Light colour/type Red
 Required components:




Light distribution files

OPTICAL RESULTS (SIMULATED):




LED LUXEON Rubix
 FWHM / FWTM 89.0° / 140.0°
 Efficiency 84 %
 Peak intensity 0.5 cd/lm
 LEDs/each optic 1
 Light colour/type Blue
 Required components:



Light distribution files




LED LUXEON Rubix
 FWHM / FWTM 80.0° / 138.0°
 Efficiency 84 %
 Peak intensity 0.5 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files



LED LUXEON Rubix
 FWHM / FWTM 92.0° / 140.0°
 Efficiency 84 %
 Peak intensity 0.5 cd/lm
 LEDs/each optic 1
 Light colour/type Green
 Required components:




Light distribution files

OPTICAL RESULTS (SIMULATED):

OSRAM

Opto Semiconductors

LED OSCONIQ P 3030
FWHM / FWTM 82.0° / 130.0°
Efficiency 86 %
Peak intensity 0.5 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:




Light distribution files

OSRAM

Opto Semiconductors

LED OSLON Signal
FWHM / FWTM 71.0 + 68.0° / 128.0°
Efficiency 87 %
Peak intensity 0.6 cd/lm
LEDs/each optic 1
Light colour/type Yellow
Required components:




Light distribution files

OSRAM


Opto Semiconductors

LED OSLON Signal
FWHM / FWTM 88.0° / 132.0°
Efficiency 87 %
Peak intensity 0.5 cd/lm
LEDs/each optic 1
Light colour/type Green
Required components:



Light distribution files

OPTICAL RESULTS (SIMULATED):



GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDiL Oy
Joensuunkatu 7
FI-24100 SALO
Finland

LEDiL Inc.
228 West Page Street
Suite D
Sycamore IL 60178
USA

Ledil Optics Technology (Shenzhen) Co., Ltd.
405 , Block B
Casic Motor Building
Shenzhen 518057
P.R.CHINA

Local sales and technical support
[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)

Shipping locations
Poznan, Poland
Hong Kong, China

Distribution Partners
[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)