


NTC Thermistors, Miniature Immersion, Liquid Cooled Automotive Systems



LINKS TO ADDITIONAL RESOURCES



3D Models



Design Tools



Calculators

QUICK REFERENCE DATA		
PARAMETER	VALUE	UNIT
Resistance value at 25 °C	10K	Ω
Tolerance on R_{25} -value	± 2	%
$B_{25/85}$ -value	3984	K
Tolerance on $B_{25/85}$ -value	± 0.5	%
Operating temperature range at zero power ⁽¹⁾	-40 to +125 Peak: 150	°C
Storage temperature range	-55 to +125	°C
Response time $t_{63.2\%}$ of ΔT (air 25 °C to 85 °C)	1.5	s
Dissipation factor δ (for information only)		mW/K
In still air	2.8	
In still water	5.6	
Maximum power dissipation at 25 °C $P_{max,25}$	100	mW
Min. dielectric withstanding voltage between terminals and capsule (10 s)	500	V _{AC}
Insulation resistance at 500 V _{DC}	> 100M	Ω
Thermal gradient	< 0.02	K/K
Weight	2	g

DESIGN-IN SUPPORT

- Other resistance curves and tolerances are available on request
- Consult Vishay for other lead length or connector options
- The part can be provided with bare copper conductors for optimal electrical welding extension cable connection
- The sensor is provided without O-ring
- 3D solid models: www.vishay.com/doc?29247
- NTC curve computation: www.vishay.com/thermistors/ntc-rt-calculator/

FEATURES

- Fast time response to temperature change in automotive fluid immersion applications
- Reduced thermal gradient, due to the use of small tip dimensions and thin insulated wire
- Sensor for permanent contact with water or other liquids
- AEC-Q200 qualified
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912


RoHS
COMPLIANT

APPLICATIONS

Immersion sensor used for temperature measurement, sensing and control in liquid cooled systems:

- Inverters
- On board chargers (OBC)
- Battery management systems (BMS)
- DC/DC converters
- EV charging plugs
- EV charging inlets
- Solar heating systems
- Heat pumps
- Energy storage systems (ESS)

DESCRIPTION

Miniature insulated chip NTC thermistor mounted in a SS316 housing and a 60 V_{AC} rated, 3000 V_{AC} tested, FLR2X type, PEX insulated AWG#22 lead wire connection. The conductors are tin plated.


Optional lead (Pb)-free conductors are available.

MOUNTING

- The sensor can be mounted by means of a sealing O-ring and screw or holder
- The end wire can be soldered, or crimped to a connector
- Optional connector for wire to wire or wire to board connections
- The epoxy lead-wire side can not be in permanent contact with liquids, or water

PACKAGING

Available in plastic bags of 500 pieces.

DIMENSIONS in millimeters (FOLLOW ISO2768-M FOR TOLERANCES NOT INDICATED)



L ₁	L ₃	L ₆	Ø D ₁	Ø D ₂	Ø D ₅	Ø D ₆
Refer to the ordering table	23 ± 1	3.4 ± 0.2	6.8 ± 0.1	3.9 ± 0.1	1.27 + 0.13 / - 0.07	0.8 ± 0.1

Notes

1. Vishay thermistor chip NTC, epoxy insulated
2. PEX insulated cables, 600 V rated, 3000 V tested, 0.35 mm² / AWG#22 multi-stranded tin plated copper
3. Stainless steel (SS316) housing with lead (Pb)-free brass

ELECTRICAL DATA AND ORDERING INFORMATION

R ₂₅ (Ω)	R ₂₅ -TOL. (%)	B _{25/85} (K)	B _{25/85} -TOL. (± %)	L ₁	DESCRIPTION	SAP MATERIAL AND ORDERING NUMBER
10 000	± 2	3984	0.5	300 mm ± 5	NTC Immersion 10K 3984K 300 mm 0.35 mm ² AWG#22	NTCAIMM66H103G301A

MOUNTING


**AEC-Q200 STRESS QUALIFICATIONS FOR THERMISTORS NTC**

STRESS	NO.	REFERENCE	ADDITIONAL REQUIREMENTS
High temperature exposure (storage)	3	MIL-STD-202 Method 108	- Unpowered - Tested at 150 °C 1000 h $\Delta R_{25}/R_{25} \leq \pm 5 \% \text{ after test}$
Temperature cycling	4	JESD22-A104	- Unpowered 1000 cycles - Lower temperature of the chamber: -55 °C - Upper temperature of the chamber: maximum specified operating temperature and shall not exceed 125 °C - Dwell time: 15 minutes - Transition time: 1 minute maximum $\Delta R_{25}/R_{25} \leq \pm 5 \% \text{ after test}$
Humidity bias	7	MIL-STD-202 Method 103	1000 h 85 °C / 85 % RH 5 V_{DC}, R_S = 1 kΩ $\Delta R_{25}/R_{25} \leq \pm 5 \% \text{ after test}$
High temperature operating life	8	MIL-STD-202 Method 108	1000 h 5 V_{DC}, R_S = 1 kΩ - Temperature of the chamber: maximum specified operating temperature up to 150 °C $\Delta R_{25}/R_{25} \leq \pm 5 \% \text{ after test}$
External visual	9	MIL-STD-883 Method 2009	- Inspect device construction, marking and workmanship - Pre and post electrical test not required
Physical dimensions	10	JESD22-B100	- Verify physical dimensions to the applicable component specification - Pre and post electrical test not required
Terminal strength (pull test)	11	MIL-STD-202 Method 211	- Test THT component lead integrity only - Test condition A (pull test): 2.27 kg $\Delta R_{25}/R_{25} \leq \pm 5 \% \text{ after test}$
Resistance to solvents	12	MIL-STD-202 Method 215	All parts OK, no visible damage after test
Mechanical shock	13	MIL-STD-202 Method 213	- Figure 1 of Method 213 - THT: condition C $\Delta R_{25}/R_{25} \leq \pm 5 \% \text{ after test}$
Vibration	14	MIL-STD-202 Method 204	5 g's for 20 minutes 12 cycles each of 3 orientations - Test from 10 Hz to 2000 Hz $\Delta R_{25}/R_{25} \leq \pm 5 \% \text{ after test}$
Resistance to soldering heat	15	MIL-STD-202 Method 210	Non-soldered type mounting / attach are not applicable
ESD	17	AEC-Q200-002	25 kV air discharge 2 pulses 1+ / 1- $\Delta R_{25}/R_{25} \leq \pm 5 \% \text{ after test}$
Solderability	18	J-STD-002	n/a
Electrical characterization	19	User specification	All parts are within specification limits
Flammability	20	UL 94 or IEC 60695-11-5 fixed	UL 94 V-0 or UL 94 V-1; within specification of the flammability norm
Board flex (SMD)	21	AEC-Q200-005	n/a
Terminal strength (SMD)	22	AEC-Q200-006	n/a



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.