

G2-LAURA-O-P

~40° x 13° oval beam. Assembly with thinner white holder, installation tape and location pins.

SPECIFICATION:

Dimensions	21.6 x 21.6
Height	13.1 mm
Fastening	tape, pin
ROHS compliant	yes ⓘ




MATERIALS:

Component	Type	Material	Colour	Finish	Length (mm)
LAURA-LT-PIN-XP-HLD-WHT » Box size: 480 x 280 x 300 mm	Holder	PC	white		
LAURA-O » Box size: 480 x 280 x 300 mm	Single lens	PMMA	clear		
ROSE-TAPE	Tape	Acryl tape	grey		

ORDERING INFORMATION:

Component	Type	Qty in box	MOQ	MPQ	Box weight (kg)
C10278_ROSE-TAPE	Tape	1440	360	180	6.0
C11363_LAURA-O	Single lens	1440	360	180	6.0
C13265_LAURA-LT-PIN-XP-HLD-WHT	Holder	1440	360	180	6.0





See also our general installation guide: www.ledil.com/installation_guide

OPTICAL RESULTS (MEASURED):





LED XB-D
 FWHM / FWTM 41.0 + 13.0° / 57.0 + 26.0°
 Efficiency 86 %
 Peak intensity 4.8 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files



LED XB-H
 FWHM / FWTM 41.0 + 13.0° / 58.0 + 26.0°
 Efficiency 87 %
 Peak intensity 4.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files





LED XP-E
 FWHM / FWTM 40.0 + 13.0° / 55.0 + 24.0°
 Efficiency 91 %
 Peak intensity 4.8 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:

Light distribution files

OPTICAL RESULTS (MEASURED):





LED XP-E2
 FWHM / FWTM 41.0 + 11.0° / 55.0 + 22.0°
 Efficiency 88 %
 Peak intensity 5.8 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files





LED XP-G2
 FWHM / FWTM 41.0 + 14.0° / 58.0 + 27.0°
 Efficiency 87 %
 Peak intensity 4.8 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files



LED XP-G3
 FWHM / FWTM 39.0 + 13.0° / 58.0 + 29.0°
 Efficiency 93 %
 Peak intensity 4.3 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:





Light distribution files

OPTICAL RESULTS (MEASURED):





LED XP-L HD
 FWHM / FWTM 38.0 + 16.0° / 60.0 + 34.0°
 Efficiency 89 %
 Peak intensity 3.8 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files





LED XP-L2
 FWHM / FWTM 38.0 + 17.0° / 64.0 + 38.0°
 Efficiency 84 %
 Peak intensity 3.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files



LED XT-E
 FWHM / FWTM 40.0 + 14.0° / 59.0 + 29.0°
 Efficiency 87 %
 Peak intensity 4.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:





Light distribution files

OPTICAL RESULTS (MEASURED):




LED LUXEON 3030 2D (Round LES)
 FWHM / FWTM 40.0 + 13.0° / 58.0 + 26.0°
 Efficiency 88 %
 Peak intensity 4.7 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files





LED LUXEON T
 FWHM / FWTM 40.0 + 15.0° / 60.0 + 28.0°
 Efficiency 90 %
 Peak intensity 4.7 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files



LED LUXEON TX
 FWHM / FWTM 41.0 + 14.0° / 59.0 + 27.0°
 Efficiency 87 %
 Peak intensity 4.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

OPTICAL RESULTS (MEASURED):





LED LUXEON V2
 FWHM / FWTM 39.0 + 13.0° / 58.0 + 29.0°
 Efficiency 93 %
 Peak intensity 4.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files





LED NCSxx19A
 FWHM / FWTM 41.0 + 13.0° / 58.0 + 27.0°
 Efficiency 87 %
 Peak intensity 4.7 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files



LED NCSxx19B
 FWHM / FWTM 40.0 + 12.0° / 56.0 + 24.0°
 Efficiency 87 %
 Peak intensity 4.9 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:





Light distribution files

OPTICAL RESULTS (MEASURED):





LED NVSW219D
 FWHM / FWTM 38.0 + 14.0° / 59.0 + 29.0°
 Efficiency 94 %
 Peak intensity 4.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files



LED NVSxx19A
 FWHM / FWTM 40.0 + 15.0° / 60.0 + 30.0°
 Efficiency 87 %
 Peak intensity 4.3 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files



LED NVSxx19B/NVSxx19C
 FWHM / FWTM 37.0 + 12.0° / 62.0 + 28.0°
 Efficiency 89 %
 Peak intensity 5.3 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

OPTICAL RESULTS (MEASURED):

OSRAM
Opto Semiconductors



LED OSLON Square CSSRM2/CSSRM3
FWHM / FWTM 39.0 + 12.0° / 57.0 + 25.0°
Efficiency 94 %
Peak intensity 4.9 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files

OSRAM
Opto Semiconductors



LED OSLON Square EC
FWHM / FWTM 40.0 + 13.0° / 58.0 + 27.0°
Efficiency 87 %
Peak intensity 4.8 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files

SAMSUNG

LED LH351D
FWHM / FWTM 37.0 + 17.0° / 63.0 + 34.0°
Efficiency 92 %
Peak intensity 3.6 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:





Light distribution files

OPTICAL RESULTS (MEASURED):




LED Z5M1/Z5M2
 FWHM / FWTM 40.0 + 12.0° / 57.0 + 26.0°
 Efficiency 86 %
 Peak intensity 4.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files



LED Z5M3
 FWHM / FWTM 39.0 + 15.0° / 60.0 + 32.0°
 Efficiency 94 %
 Peak intensity 4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

OPTICAL RESULTS (SIMULATED):




LED CSP 2323 (BXCP)
 FWHM / FWTM 62.0 + 12.0° / 84.0 + 25.0°
 Efficiency 89 %
 Peak intensity 2.8 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files




LED CSP 2424 (BXCP)
 FWHM / FWTM 62.0 + 12.0° / 84.0 + 24.0°
 Efficiency 90 %
 Peak intensity 2.8 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files



LED XD16
 FWHM / FWTM 62.0 + 11.0° / 82.0 + 23.0°
 Efficiency 88 %
 Peak intensity 3 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

OPTICAL RESULTS (SIMULATED):




LED XP-G4
 FWHM / FWTM 62.0 + 12.0° / 84.0 + 26.0°
 Efficiency 89 %
 Peak intensity 2.9 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files




LED XQ-E HD
 FWHM / FWTM 66.0 + 9.0° / 89.0 + 18.0°
 Efficiency 94 %
 Peak intensity 4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files



LED LUXEON 3535L
 FWHM / FWTM 62.0 + 10.0° / 84.0 + 23.0°
 Efficiency 91 %
 Peak intensity 3.2 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

OPTICAL RESULTS (SIMULATED):




LED	LUXEON HL2X
FWHM / FWTM	58.0 + 14.0° / 83.0 + 30.0°
Efficiency	89 %
Peak intensity	2.6 cd/lm
LEDs/each optic	1
Light colour/type	White
Required components:	



Light distribution files




LED	LUXEON HL2X-E
FWHM / FWTM	60.0 + 14.0° / 84.0 + 32.0°
Efficiency	89 %
Peak intensity	2.6 cd/lm
LEDs/each optic	1
Light colour/type	White
Required components:	



Light distribution files



LED	LUXEON HL2X-V
FWHM / FWTM	60.0 + 14.0° / 84.0 + 30.0°
Efficiency	90 %
Peak intensity	2.8 cd/lm
LEDs/each optic	1
Light colour/type	White
Required components:	




Light distribution files

OPTICAL RESULTS (SIMULATED):




LED LUXEON HL2Z
 FWHM / FWTM 62.0 + 12.0° / 84.0 + 24.0°
 Efficiency 90 %
 Peak intensity 2.9 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files




LED SST-20 Gen1
 FWHM / FWTM 64.0 + 10.0° / 84.0 + 22.0°
 Efficiency 90 %
 Peak intensity 3 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files



LED SST-20 Gen2
 FWHM / FWTM 62.0 + 12.0° / 84.0 + 24.0°
 Efficiency 90 %
 Peak intensity 3 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

OPTICAL RESULTS (SIMULATED):




LED SST-20F-W
 FWHM / FWTM 62.0 + 12.0° / 84.0 + 28.0°
 Efficiency 90 %
 Peak intensity 2.7 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files




LED NCSxE17A
 FWHM / FWTM 62.0 + 10.0° / 82.0 + 20.0°
 Efficiency 90 %
 Peak intensity 3.3 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files



LED NVSW219C-V2
 FWHM / FWTM 60.0 + 10.0° / 82.0 + 20.0°
 Efficiency 90 %
 Peak intensity 3.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

OPTICAL RESULTS (SIMULATED):




LED NVSW219F-V2
 FWHM / FWTM 60.0 + 14.0° / 84.0 + 30.0°
 Efficiency 88 %
 Peak intensity 2.7 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files




LED NVSW219GF
 FWHM / FWTM 62.0 + 10.0° / 82.0 + 21.0°
 Efficiency 92 %
 Peak intensity 3.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files



LED NVSxE21A
 FWHM / FWTM 62.0 + 12.0° / 84.0 + 24.0°
 Efficiency 90 %
 Peak intensity 2.8 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

OPTICAL RESULTS (SIMULATED):




LED NVSxx19B/NVSxx19C
 FWHM / FWTM 58.0 + 12.0° / 84.0 + 28.0°
 Efficiency 89 %
 Peak intensity 2.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files




LED OSCONIQ C 2424 Gen1
 FWHM / FWTM 61.0 + 12.0° / 82.0 + 24.0°
 Efficiency 90 %
 Peak intensity 3 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files



LED OSCONIQ P 3030
 FWHM / FWTM 66.0 + 10.0° / 85.0 + 19.0°
 Efficiency 91 %
 Peak intensity 3.7 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

OPTICAL RESULTS (SIMULATED):

OSRAM
Opto Semiconductors


LED OSLON Black
FWHM / FWTM 62.0 + 10.0° / 83.0 + 20.0°
Efficiency %
Peak intensity 3.2 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files

OSRAM
Opto Semiconductors


LED OSLON Black Flat (LUW HWQP)
FWHM / FWTM 62.0 + 8.0° / 82.0 + 16.0°
Efficiency 91 %
Peak intensity 4.1 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files

OSRAM
Opto Semiconductors

LED OSLON Signal
FWHM / FWTM 62.0 + 8.0° / 82.0 + 18.0°
Efficiency 90 %
Peak intensity 3.9 cd/lm
LEDs/each optic 1
Light colour/type Red
Required components:





Light distribution files

OPTICAL RESULTS (SIMULATED):

OSRAM
Opto Semiconductors


LED OSLON Square Flat
FWHM / FWTM 61.0 + 10.0° / 82.0 + 23.0°
Efficiency 89 %
Peak intensity 3.1 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files

OSRAM
Opto Semiconductors


LED OSLON SSL 150
FWHM / FWTM 62.0 + 10.0° / 83.0 + 20.0°
Efficiency 91 %
Peak intensity 3.5 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files

OSRAM
Opto Semiconductors

LED OSLON SSL 80
FWHM / FWTM 62.0 + 10.0° / 84.0 + 24.0°
Efficiency 90 %
Peak intensity 3.2 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:





Light distribution files

OPTICAL RESULTS (SIMULATED):

OSRAM
Opto Semiconductors

LED SFH 4715AS
FWHM / FWTM $66.0 \pm 10.0^\circ / 85.0 \pm 23.0^\circ$
Efficiency 90 %
LEDs/each optic 1
Light colour/type IR
Required components:



Light distribution files


OSRAM
Opto Semiconductors

LED SFH 4770S
FWHM / FWTM $63.0 \pm 11.0^\circ / 83.0 \pm 27.0^\circ$
Efficiency 88 %
LEDs/each optic 1
Light colour/type White
Required components:

Light distribution files

SEKUL
SEOUL SEMICONDUCTOR

LED Z5M4
FWHM / FWTM $62.0 \pm 14.0^\circ / 84.0 \pm 30.0^\circ$
Efficiency 90 %
Peak intensity 2.5 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:




Light distribution files

OPTICAL RESULTS (SIMULATED):




LED Z8Y22
 FWHM / FWTM 62.0 + 14.0° / 84.0 + 32.0°
 Efficiency 87 %
 Peak intensity 2.3 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files



LED Z8Y22P
 FWHM / FWTM 60.0 + 12.0° / 84.0 + 30.0°
 Efficiency 93 %
 Peak intensity 2.7 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files

GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDiL Oy

Joensuunkatu 7
FI-24100 SALO
Finland

LEDiL Inc.

228 West Page Street
Suite D
Sycamore IL 60178
USA

Ledil Optics Technology (Shenzhen) Co., Ltd.

405 , Block B
Casic Motor Building
Shenzhen 518057
P.R.CHINA

Local sales and technical support

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)

Shipping locations

Poznan, Poland
Hong Kong, China

Distribution Partners

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)