


## | FORK TRUCK MAST HEIGHT

**Background**

Hoisting loads with a fork truck might seem like a pretty simple task, but there are a lot of ways it can go wrong. Skilled operators make it look easy, but they are constantly balancing load weight and height above the floor, with speed and turn radius while moving. They also need to be expert at positioning the forks properly when it is often hard to get a clear sightline to the pallet. It turns out that it takes quite a bit of experience to do the job well and efficiently.



*A Draw Wire Encoder can help take some of the risk out of fork truck operation*

**Solution**

Sensata-BEI Sensors can help the Fork Truck operator work more efficiently. By using a Draw Wire Encoder to monitor the fork height, the operator gains several advantages. Speed of operation is limited by the load weight and height. With Draw Wire feedback, operating speed can be safely optimized over a wide range while reducing the risk of a tip-over. In addition, it is common to have level changes throughout a warehouse and maintaining the forks at the right height for each section avoids crashes with objects at ceiling height during transitions. Avoiding tip-overs and potential crashes are just two of the immediate benefits to using a Draw Wire Encoder for Fork Truck mast height.






## RECOMMENDED PRODUCTS

| Reference on Diagram | Product  | Type              | Features                   | Features                        | Brand       |
|----------------------|--|-------------------|----------------------------|---------------------------------|-------------|
| 1                    |  CD120          | Draw-Wire Encoder | Up to 10' of Measurement   | • Length (Distance) Measurement | BEI Sensors |
| 2                    |  CD150 (Analog) | Draw-Wire         | Up to 19.7' of measurement | • Analog length Measurement     | BEI Sensors |
| 3                    |  CDS12 (Analog) | Draw-Wire         | Up to 49.2' of measurement | • Analog length Measurement     | BEI Sensors |



## FORK TRUCK WITH DRAW WIRE TO INDICATE MAST HEIGHT



Page 2

Sensata Technologies, Inc. ("Sensata") data sheets are solely intended to assist designers ("Buyers") who are developing systems that incorporate Sensata products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products. Sensata data sheets have been created using standard laboratory conditions and engineering practices. Sensata has not conducted any testing other than that specifically described in the published documentation for a particular data sheet. Sensata may make corrections, enhancements, improvements and other changes to its data sheets or components without notice. Buyers are authorized to use Sensata data sheets with the Sensata component(s) identified in each particular data sheet. **HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER SENSATA INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN.** SENSATA DATA SHEETS ARE PROVIDED "AS IS". SENSATA MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE DATA SHEETS OR USE OF THE DATA SHEETS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. SENSATA DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO SENSATA DATA SHEETS OR USE THEREOF.

All products are sold subject to Sensata's terms and conditions of sale supplied at [www.sensata.com](http://www.sensata.com) SENSATA ASSUMES NO LIABILITY FOR APPLICATIONS ASSISTANCE OR THE DESIGN OF BUYERS' PRODUCTS. BUYER ACKNOWLEDGES AND AGREES THAT IT IS SOLELY RESPONSIBLE FOR COMPLIANCE WITH ALL LEGAL, REGULATORY AND SAFETY-RELATED REQUIREMENTS CONCERNING ITS PRODUCTS, AND ANY USE OF SENSATA COMPONENTS IN ITS APPLICATIONS, NOTWITHSTANDING ANY APPLICATIONS-RELATED INFORMATION OR SUPPORT THAT MAY BE PROVIDED BY SENSATA.

Mailing Address: Sensata Technologies, Inc., 529 Pleasant Street, Attleboro, MA 02703, USA.

## CONTACT US

### Americas

+1 (800) 350 2727 – Option 1  
[sales.beisensors@sensata.com](mailto:sales.beisensors@sensata.com)

### Europe, Middle East & Africa

+33 (3) 88 20 8080  
[position-info.eu@sensata.com](mailto:position-info.eu@sensata.com)

### Asia Pacific

[sales.isasia@list.sensata.com](mailto:sales.isasia@list.sensata.com)  
 China +86 (21) 2306 1500  
 Japan +81 (45) 277 7117  
 Korea +82 (31) 601 2004  
 India +91 (80) 67920890  
 Rest of Asia +886 (2) 27602006 ext 2808