

CHIP CONVEYOR MOTOR CONTROL IN MACHINE TOOLS

Background

A chip conveyor system is very common on CNC machine tools; it can be part of the machine or it can be offered as an accessory. The main function of a chip conveyor system is to remove the cutting excess material, which can be metal or plastic, from the machine tool. A chip conveyor is commonly driven using a small to medium size three-phase motor, and the conveyor control system is generally mounted next to the motor in the conveyor. Reliability is a prime concern on these systems, since repair downtime could be very costly, so this should be considered when designing the control system for a chip conveyor. It also needs to have capacity for reversing, in case chips get stuck.

In addition to having standard start/stop and reversing control, using a Motor Starter can add other features that help reduce current surges and extend the life of the motor and the conveyor mechanical parts

Solution

Control of start/stop and forward/reverse of the conveyor motor can be achieved using electromechanical contactors, but this has several disadvantages: it requires 2 contactors plus an interlock system, and there is also a reliability issue since the life expectancy of an EMR solution is much lower (typically lower than 100K cycles)

Solid State Relays and Contactors are a great solution for this application, being more compact than the equivalent EMR solution and having higher reliability. For a simple control system, a basic reversing contactor like a **Solicon DRC**, can be used to provide start/stop and forward/reverse control.

For a more complete control solution a Hybrid Motor Starter, such as the **DRMS**, would be an excellent option. This device combines EMR and solid state switching technology on an integrated solution in a slimmer 22.5mm package. In addition to having standard start/stop and reversing control, using a Motor Starter we can add other features such as overload detection (there is no need to add an external overload relay) and soft start/stop function, which can help to reduce current surges and extend the life of the motor and the conveyor mechanical parts.






RECOMMENDED PRODUCTS

Reference on Diagram	Product	Features	Function	Brand
1	 DRC Series	• Solid state contactor • Reversing of 3-phase motors up to 5HP (3.7kW) • Available with auxiliary contacts • Built-in overvoltage protection	Conveyor Start/Stop with Fwd/Rev	Crydom
2	 DRMS Series	• Hybrid relay technology • Reversing of 3-phase motors up to 4kW • Soft start/stop capability • Overload protection	Conveyor Start/Stop with Fwd/Rev and Overload Protection	Crydom



DIAGRAM



Page 2

Sensata Technologies, Inc. ("Sensata") data sheets are solely intended to assist designers ("Buyers") who are developing systems that incorporate Sensata products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products. Sensata data sheets have been created using standard laboratory conditions and engineering practices. Sensata has not conducted any testing other than that specifically described in the published documentation for a particular data sheet. Sensata may make corrections, enhancements, improvements and other changes to its data sheets or components without notice.

Buyers are authorized to use Sensata data sheets with the Sensata component(s) identified in each particular data sheet. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER SENSATA INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN. SENSATA DATA SHEETS ARE PROVIDED "AS IS". SENSATA MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE DATA SHEETS OR USE OF THE DATA SHEETS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. SENSATA DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO SENSATA DATA SHEETS OR USE THEREOF.

All products are sold subject to Sensata's terms and conditions of sale supplied at www.sensata.com. SENSATA ASSUMES NO LIABILITY FOR APPLICATIONS ASSISTANCE OR THE DESIGN OF BUYERS' PRODUCTS. BUYER ACKNOWLEDGES AND AGREES THAT IT IS SOLELY RESPONSIBLE FOR COMPLIANCE WITH ALL LEGAL, REGULATORY AND SAFETY-RELATED REQUIREMENTS CONCERNING ITS PRODUCTS, AND ANY USE OF SENSATA COMPONENTS IN ITS APPLICATIONS, NOTWITHSTANDING ANY APPLICATIONS-RELATED INFORMATION OR SUPPORT THAT MAY BE PROVIDED BY SENSATA.

Mailing Address: Sensata Technologies, Inc., 529 Pleasant Street, Attleboro, MA 02703, USA.

CONTACT US

Americas

+1 (877) 502 5500 – Option 2
sales.crydom@sensata.com

Europe, Middle East & Africa

+44 (1202) 416170
ssr-info.eu@sensata.com

Asia Pacific

sales.isasia@list.sensata.com
China +86 (21) 2306 1500
Japan +81 (45) 277 7117
Korea +82 (31) 601 2004
India +91 (80) 67920890
Rest of Asia +886 (2) 27602006
ext 2808