

ADELIA-75-M

~24° medium beam

SPECIFICATION:

Dimensions	Ø 74.7
Height	42.8 mm
Fastening	snaps
ROHS compliant	yes 




MATERIALS:

Component	Type	Material	Colour	Finish	Coating
ADELIA-75-M	Reflector	Aluminium	metal	gloss	Anodized

ORDERING INFORMATION:

Component	Qty in box	MOQ	MPQ	Box weight (kg)
C18428_ADELIA-75-M	840	70	70	14.1
» Box size: 400 x 300 x 300 mm				




See also our general installation guide: www.ledil.com/installation_guide

OPTICAL RESULTS (SIMULATED):



LED V18 Gen 8-9
 FWHM / FWTM 26.0° / 60.0°
 Efficiency 79 %
 Peak intensity 2.7 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 C18432_ADELIA-ADAPTER-C


Bender Wirth: 639b Hekla XL



Light distribution files




LED V6 Gen 8-9
 FWHM / FWTM 17.0° / 32.0°
 Efficiency 93 %
 Peak intensity 6.7 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15253_HEKLA-SOCKET-A
 C18432_ADELIA-ADAPTER-C



Light distribution files

CITIZEN

LED CLU03x
 FWHM / FWTM 24.0° / 54.0°
 Efficiency 86 %
 Peak intensity 3.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17438_HEKLA-G2-I
 C18432_ADELIA-ADAPTER-C




Light distribution files

OPTICAL RESULTS (SIMULATED):

CITIZEN

LED CLU03x
 FWHM / FWTM 22.0° / 54.0°
 Efficiency 86 %
 Peak intensity 3.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 C18431_ADELIA-ADAPTER-B


BJB: 47.360.1010



Light distribution files

CREE LEDs


LED CXA/B 15xx
 FWHM / FWTM 18.0° / 34.0°
 Efficiency 87 %
 Peak intensity 5.5 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17436_HEKLA-G2-D
 C18432_ADELIA-ADAPTER-C



Light distribution files

CREE LEDs

LED CXA/B 1830
 FWHM / FWTM 22.0° / 52.0°
 Efficiency 85 %
 Peak intensity 3.8 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 C18432_ADELIA-ADAPTER-C




Bender Wirth: 637b Hekla

Light distribution files

OPTICAL RESULTS (SIMULATED):

SAMSUNG


LED LC003D / LC006D / LC009D / LC013D
 FWHM / FWTM 20.0° / 37.0°
 Efficiency 90 %
 Peak intensity 5.2 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17435_HEKLA-G2-C
 C18432_ADELIA-ADAPTER-C



Light distribution files

SAMSUNG


LED LC003D / LC006D / LC009D / LC013D
 FWHM / FWTM 18.0° / 36.0°
 Efficiency 87 %
 Peak intensity 5.3 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17435_HEKLA-G2-C
 C18432_ADELIA-ADAPTER-C



Light distribution files

SAMSUNG

LED LC016D / LC019D / LC026D / LC033D
 FWHM / FWTM 24.0° / 56.0°
 Efficiency 85 %
 Peak intensity 3.3 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17438_HEKLA-G2-I
 C18432_ADELIA-ADAPTER-C




Light distribution files

OPTICAL RESULTS (SIMULATED):

SAMSUNG

LED LC016D / LC019D / LC026D / LC033D
FWHM / FWTM 24.0° / 56.0°
Efficiency 88 %
Peak intensity 3.5 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:
F17438_HEKLA-G2-I
C18432_ADELIA-ADAPTER-C



Light distribution files

GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

Due to use of high power COB's with this product, special attention to proper thermal design is highly recommended. LEDiL has no liability for direct, indirect or consecutive damages arising from the LEDiL products being used outside of the recommended temperature range.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDiL Oy
Joensuunkatu 7
FI-24100 SALO
Finland

LEDiL Inc.
228 West Page Street
Suite D
Sycamore IL 60178
USA

**Ledil Optics Technology
(Shenzhen) Co., Ltd.**
405 , Block B
Casic Motor Building
Shenzhen 518057
P.R.CHINA

**Local sales and technical
support**
www.ledil.com/
where_to_buy

Shipping locations
Poznan, Poland
Hong Kong, China

Distribution Partners
www.ledil.com/
where_to_buy