

## SOLAR PHOTOVOLTAIC TRACKING SYSTEM

### Background

Large solar panel installation is becoming more economical as a viable alternative to coal, oil or gas-fired power plants. To make the most of the panels, it is cost effective to install them on a structure that can follow the sun from east to west (azimuth) and from north to south (elevation) as the sun moves across the sky. By tracking the sun's path across the sky the solar panels can produce 10% to 25% more energy per day than a similar system that has no tracking capability.

*"As the panels themselves are large and subject to hot, dusty conditions they typically need a geared motor for precise movement, which in turn requires a MT absolute encoder for tracking"*

### Solution

Since the sun's movement across the sky is predictable from day-to-day and from season to season, by providing a motor/feedback system for each axis of each solar panel, it is straightforward to program the correct movement of the panel depending on the season. As the panels themselves are large and subject to hot, dusty conditions they typically need a geared motor for precise movement, which in turn requires a multi-turn absolute encoders. In addition, should there be a power outage during tracking, it is important that the encoder can maintain information about its current position, so that when power is restored, it can move directly to the correct position without having to follow a homing sequence.






## RECOMMENDED PRODUCTS

Reference on Diagram	Product	Type	Features	Part Number	Function	Brand
1		MHK5 Hollow Shaft Encoder	Ethernet IP or ProfiNet interface	MHM5/MHK5 Family	Rotary Multiturn Encoder	BEI Sensors



## DIAGRAM



Page 2

Sensata Technologies, Inc. ("Sensata") data sheets are solely intended to assist designers ("Buyers") who are developing systems that incorporate Sensata products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products. Sensata data sheets have been created using standard laboratory conditions and engineering practices. Sensata has not conducted any testing other than that specifically described in the published documentation for a particular data sheet. Sensata may make corrections, enhancements, improvements and other changes to its data sheets or components without notice.

Buyers are authorized to use Sensata data sheets with the Sensata component(s) identified in each particular data sheet. **HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER SENSATA INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN. SENSATA DATA SHEETS ARE PROVIDED "AS IS". SENSATA MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE DATA SHEETS OR USE OF THE DATA SHEETS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. SENSATA DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO SENSATA DATA SHEETS OR USE THEREOF.**

All products are sold subject to Sensata's terms and conditions of sale supplied at [www.sensata.com](http://www.sensata.com) SENSATA ASSUMES NO LIABILITY FOR APPLICATIONS ASSISTANCE OR THE DESIGN OF BUYERS' PRODUCTS. BUYER ACKNOWLEDGES AND AGREES THAT IT IS SOLELY RESPONSIBLE FOR COMPLIANCE WITH ALL LEGAL, REGULATORY AND SAFETY-RELATED REQUIREMENTS CONCERNING ITS PRODUCTS, AND ANY USE OF SENSATA COMPONENTS IN ITS APPLICATIONS, NOTWITHSTANDING ANY APPLICATIONS-RELATED INFORMATION OR SUPPORT THAT MAY BE PROVIDED BY SENSATA.

Mailing Address: Sensata Technologies, Inc., 529 Pleasant Street, Attleboro, MA 02703, USA.

## CONTACT US

### Americas

+1 (800) 350 2727 – Option 1

[sales.beisensors@sensata.com](mailto:sales.beisensors@sensata.com)

### Europe, Middle East & Africa

+33 (3) 88 20 8080

[position-info.eu@sensata.com](mailto:position-info.eu@sensata.com)

### Asia Pacific

[sales.isasia@list.sensata.com](mailto:sales.isasia@list.sensata.com)

China +86 (21) 2303 1500

Japan +81 (45) 277 7117

Korea +82 (31) 601 2004

India +91 (80) 67920890

Rest of Asia +86 (2) 27602006 ext 2808