

MEDICAL APPLICATION

OXYGEN CONCENTRATORS

What is an Oxygen Concentrator?

It is a medical device that is used to deliver oxygen to those who require it due to low levels of oxygen in their blood.

Concentrators are powered by batteries or conventional electrical wall outlets.

A concentrator is made up of a compressor, sieve bed filter and circuit boards.


In comparison with an oxygen tank that has a set amount of oxygen a concentrator filters in air, compresses it and delivers air continuously. The air supply should never run out like an Oxygen tank would as long as electrical power is provided.

How does it work?

An oxygen concentrator is similar to how a window air conditioning unit works. It takes in air, modifies it and delivers it in a new form. An oxygen concentrator takes in air and purifies it for use by people requiring medical oxygen.

The 5 steps in Oxygen Concentration:

1. The concentrator takes in air from its surroundings
2. It then compresses the air, while the cooling mechanism prevents overheating of the concentrator
3. The concentrator removes nitrogen from the air by way of a filter and sieve beds



A concentrator is made up of a compressor, sieve bed filter and circuit boards.

4. The concentrator uses an electronic interface to adjust delivery settings

5. The delivery of the purified oxygen is by use of a nasal cannula or mask

Where are pressure sensors used on an Oxygen Concentrator?

Not all concentrators are the same but the common areas where pressure sensors are being used are as follows and as shown in the below diagram.

1. Measurement of Oxygen tank pressure about 2,000 psi (136 bar)
2. Flow of oxygen being delivered to patient approximately .58 psi (16" of H₂O)
3. Measurement of concentrated oxygen in surge tank typically 30 psi (2 bar)






RECOMMENDED PRODUCTS

Reference on Diagram	Product Series	Type	Features	Function	Brand	
1		P1K*	PCB Mount	<ul style="list-style-type: none"> • 5V input • Ratiometric output • 0-2" to 0-10" H₂O range 	Differential Low Pressure Sensor	Kavlico
2		P1J*	PCB Mount	<ul style="list-style-type: none"> • 2.7-5.5V input • Digital output (I²C or SPI) • 0-2" to 0-10" H₂O range • Low power (<2.5mA) 	Differential Low Pressure Sensor	Kavlico

*For breathing pressure sensor (typically 0-2" to 0-10") see standard P1J and P1K options. For tank pressure sensor (typically >15psi) contact Sensata or higher pressure options



DIAGRAM



Sensata Technologies, Inc. ("Sensata") data sheets are solely intended to assist designers ("Buyers") who are developing systems that incorporate Sensata products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products. Sensata data sheets have been created using standard laboratory conditions and engineering practices. Sensata has not conducted any testing other than that specifically described in the published documentation for a particular data sheet. Sensata may make corrections, enhancements, improvements and other changes to its data sheets or components without notice.

Buyers are authorized to use Sensata data sheets with the Sensata component(s) identified in each particular data sheet. **HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER SENATA INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN. SENATA DATA SHEETS ARE PROVIDED "AS IS". SENATA MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE DATA SHEETS OR USE OF THE DATA SHEETS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. SENATA DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO SENATA DATA SHEETS OR USE THEREOF.**

All products are sold subject to Sensata's terms and conditions of sale supplied at www.sensata.com SENATA ASSUMES NO LIABILITY FOR APPLICATIONS ASSISTANCE OR THE DESIGN OF BUYERS' PRODUCTS. BUYER ACKNOWLEDGES AND AGREES THAT IT IS SOLELY RESPONSIBLE FOR COMPLIANCE WITH ALL LEGAL, REGULATORY AND SAFETY-RELATED REQUIREMENTS CONCERNING ITS PRODUCTS, AND ANY USE OF SENATA COMPONENTS IN ITS APPLICATIONS, NOTWITHSTANDING ANY APPLICATIONS-RELATED INFORMATION OR SUPPORT THAT MAY BE PROVIDED BY SENATA.

Mailing Address: Sensata Technologies, Inc., 529 Pleasant Street, Attleboro, MA 02703, USA.

CONTACT US

Americas

+1 (800) 350 2727
sensors@sensata.com
switches@sensata.com

Europe, Middle East & Africa

+359 (2) 809 1826
pressure-info.eu@sensata.com

Asia Pacific

sales.issasia@list.sensata.com
 China +86 (21) 2306 1500
 Japan +81 (45) 277 7117
 Korea +82-10-9218-1179
 India +91 (80) 67920890
 Rest of Asia +886 (2) 27602006
 ext 2808