

- Compact metal case with screw terminal block
- Universal input 90-264 VAC
- I/O reinforced isolation 3000 VAC
- Active power factor correction >0.9
- Internal EN 55032 class B filter
- High efficiency up to 89%
- Operating temperature range -30°C to 70+°C
- Short circuit, overvoltage and overload protection
- IEC/EN/UL 62368-1 safety approvals
- 3-year product warranty



The TXN 200 is a cost efficient, metal enclosed AC/DC power supplies series and is designed for industrial applications. With a low-profile metal case and screw terminal block connection, they are easy to install in any equipment. Active PFC (>0.9), internal EMC filter, high IO-isolation and wide temperature range qualify them for numerous industrial applications. All models within the TXN 200 series have universal input (90-264 VAC) and comply with the latest industrial standard IEC/EN/UL 62368-1, European EMC standards and the Low Voltage Directive (LVD).

Models				
Order Code	Output Power max.	Output Voltage nom. (adjustable)	Output Current max.	Efficiency typ.
TXN 200-112	200 W	12 VDC (10.0 - 13.2 VDC)	16'600 mA	87 %
TXN 200-115		15 VDC (13.5 - 15.5 VDC)	13'300 mA	87 %
TXN 200-124		24 VDC (20.0 - 26.4 VDC)	8'300 mA	88 %
TXN 200-148		48 VDC (41.0 - 56.0 VDC)	4'200 mA	89 %

Options	
on demand (backorder with MOQ non stocking item)	- Optional model with 36 VDC and 5'500 mA

Input Specifications

Input Voltage	- AC Range	Operational Range: 90 - 264 VAC (Full Range) Rated Range: 100 - 240 VAC (Full Range)
	- DC Range	Operational Range: 140 - 340 VDC (Designed for, no certification) Polarity: +DC: L / -DC: N
Input Frequency		Operational Range: 47 - 63 Hz Certified: 50/60 Hz
Power Consumption	- No load & Vin = 230 VAC	6 W max.
	- No load & Vin = 115 VAC	6 W max.
Input Current	- Full load & Vin = 230 VAC	1.3 A max.
	- Full load & Vin = 115 VAC	3 A max.
Input Inrush Current	- At 230 VAC	60 A max.
	- At 115 VAC	30 A max.
Power Factor	- At 230 VAC	0.9 min. (Active Power Factor Correction)
	- At 115 VAC	0.95 min. (Active Power Factor Correction)
Input Protection		T 6.3 A / 250 VAC (Internal Fuse in L)
Recommended Input Fuse		(The need of an external fuse has to be assessed in the final application.)

Output Specifications

Output Voltage Adjustment		12 VDC model: 10.0 - 13.2 VDC 15 VDC model: 13.5 - 15.5 VDC 24 VDC model: 20.0 - 26.4 VDC 36 VDC model: 32.4 - 39.6 VDC 48 VDC model: 41.0 - 56.0 VDC (By trim potentiometer) Output power must not exceed rated power!
Voltage Set Accuracy		±1% max.
Regulation	- Input Variation (Vmin - Vmax)	0.5% max.
	- Load Variation (10 - 90%)	1% max.
Ripple and Noise (20 MHz Bandwidth)	12 VDC model:	150 mVp-p max. (w/ 0.1 µF 47 µF)
	15 VDC model:	150 mVp-p max. (w/ 0.1 µF 47 µF)
	24 VDC model:	150 mVp-p max. (w/ 0.1 µF 47 µF)
	36 VDC model:	240 mVp-p max. (w/ 0.1 µF 47 µF)
	48 VDC model:	240 mVp-p max. (w/ 0.1 µF 47 µF)
Minimum Load		Not required
Temperature Coefficient		±0.03 %/K max.
Hold-up Time	- At 230 VAC	8 ms min.
	- At 115 VAC	8 ms min.
Start-up Time	- At 230 VAC	1.5 s max.
	- At 115 VAC	1.5 s max.
Short Circuit Protection		Continuous, Automatic recovery
Output Current Limitation		110 - 160% of Iout max.
Overvoltage Protection		110 - 140% of Vout nom.

Safety Specifications

Standards	- IT / Multimedia Equipment	EN 62368-1 IEC 62368-1 UL 62368-1
	- Certification Documents	www.tracopower.com/overview/txn200
Protection Class		Class I (Prepared): Connection to PE
Pollution Degree		PD 2
Over Voltage Category		OVC II

All specifications valid at nominal voltage, resistive full load and +25°C after warm-up time, unless otherwise stated.

EMC Specifications

EMI (Emissions)	- Conducted Emissions	EN 55032 class B (internal filter)
	- Radiated Emissions	EN 55032 class B (internal filter)
	- Harmonic Current Emissions	EN 61000-3-2, class A
	- Voltage Fluctuations & Flicker	EN 61000-3-3
EMS (Immunity)		EN 55035 (Multimedia)
	- Electrostatic Discharge	Air: EN 61000-4-2, ± 8 kV, perf. criteria B
		Contact: EN 61000-4-2, ± 6 kV, perf. criteria B
		EN 61000-4-3, 10 V/m, perf. criteria A
		EN 61000-4-4, ± 2 kV, perf. criteria A
	- RF Electromagnetic Field	L to L: EN 61000-4-5, ± 1 kV, perf. criteria B
		L to PE: EN 61000-4-5, ± 2 kV, perf. criteria B
		EN 61000-4-6, 10 Vrms, perf. criteria B
		Continuous: EN 61000-4-8, 30 A/m, perf. criteria A
	- EFT (Burst) / Surge	230 VAC / 50 Hz: EN 61000-4-11
		30%, 25 periods, perf. criteria C
		>95%, 0.5 periods, perf. criteria B
		>95%, 250 periods, perf. criteria C
	- Conducted RF Disturbances	
	- PF Magnetic Field	
	- Voltage Dips & Interruptions	
EMC / Environmental	- Certification Documents	www.tracopower.com/overview/txn200

General Specifications

Relative Humidity		95% max. (non condensing)
Temperature Ranges	- Operating Temperature	-30°C to +70°C
	- Storage Temperature	-40°C to +80°C
Power Derating	- High Temperature	2 %/K above 50°C
	- Low Input Voltage	1 %/V below 110 VAC
	See application note: www.tracopower.com/overview/txn200	
Over Temperature Protection Switch Off	- Protection Mode	Automatic recovery
	- Measurement Point	Internal IC temperature
Cooling System		Natural convection (20 LFM)
Remote Control	- Voltage Controlled Remote (passive = on)	Off: 4 to 10 VDC
		Refers to '+Remote' and '-Remote' Pin
	- Remote Pin Input Current	On: < 0.6 VDC or open circuit or short circuit 0.5 to 2.5 mA
Altitude During Operation		5'000 m max.
Regulator Topology		Forward Converter
Switching Frequency		75 kHz typ. (PWM)
Insulation System		Reinforced Insulation
Isolation Test Voltage	- Input to Output, 60 s	3'000 VAC
	- Input to Case or PE, 60 s	1'500 VAC
	- Output to Case or PE, 60 s	500 VAC
Isolation Resistance	- Input to Output, 500 VDC	10 MΩ min.
Leakage Current (at 240 VAC / 60 Hz)	- Earth Leakage Current	3.5 mA max.
Reliability	- Calculated MTBF	225'800 h (MIL-HDBK-217F, ground benign)
Washing Process		Not allowed
Environment	- Vibration	2 g, 3 axis, 60 min, 10-500 Hz, 10 min/cycle
	- Mechanical Shock	20 g, 3 axis, 3 shocks
Housing Material		Aluminum (Chassis)
Housing Type		Metal Case
Mounting Type		Chassis Mount
Connection Type		Screw Terminal
Weight		800 g
Status Indicator		Indicated by green LED
Sense Function		0.2% max. of Vout nom.

All specifications valid at nominal voltage, resistive full load and +25°C after warm-up time, unless otherwise stated.

Environmental Compliance - REACH Declaration

- RoHS Declaration

- SCIP Reference Number

www.tracopower.com/info/reach-declaration.pdf

REACH SVHC list compliant

REACH Annex XVII compliant

www.tracopower.com/info/rohs-declaration.pdf

Exemptions: 7a, 7c-I

(RoHS exemptions refer to the component concentration only, not to the overall concentration in the product (O5A rule).)


10d38219-6664-4b19-bdba-f0841289695e

Supporting Documents

Overview Link (for additional Documents)

www.tracopower.com/overview/txn200

Outline Dimensions




Dimensions in mm

Terminal screw tightening torque: Max. 1.2 Nm

Mounting screw tightening torque: Max. 0.8 Nm

Mounting screw penetration depth: Max. 4 mm



Pin connectors

Input/Output		AUX	
Pin	Function	Pin	Function
1	AC (L)	1	+Remote
2	AC (N)	2	-Remote
3	PE	3	+Sense
4	-Vout	4	-Sense
5			
6	+Vout		
7			
8			
9			

Input/Output:

Wire dimension range: 22 - 12 AWG
0.324 - 3.31 mm²

AUX:

mating connector: YL028-106-004, 2mm pitch