



AMD UltraScale+™ FPGAs Product Selection Guide

AMD Spartan™ UltraScale+™ FPGAs – Resources & Packaging

	Device Name		SU10P	SU25P	SU35P	SU45P	SU60P	SU65P	SU100P	SU150P	SU200P
Logic	System Logic Cells (K)		11	22	36	53	66	66	101	138	219
	CLB Flip-Flops (K)		10	20	33	48	60	60	92	126	200
	CLB LUTs (K)		5	10	16	24	30	30	46	63	100
Memory	Max. Distributed RAM (Mb)		0.07	0.14	0.23	0.53	0.66	0.57	0.88	1.25	1.99
	Total Block RAM (Mb)		1.7	1.7	1.7	2.5	3.4	3.8	5.1	5.9	6.8
	36K Block RAM		48	48	48	72	96	108	144	168	192
	Total UltraRAM (Mb)		0	0	0	0	0	0	0	4.5	18.0
	288K UltraRAM		0	0	0	0	0	0	0	16	64
	Integrated Memory Controller		0	0	0	0	0	2	2	2	2
Clocking	Clock Mgmt Tiles (CMTs)		2	2	2	3	3	5	5	6	6
Integrated IP	DSP Slices		24	36	48	96	144	144	144	384	384
	PCIE4CE		0	0	0	1x Gen4x4	1x Gen4x4	1x Gen4x4	1x Gen4x4	1x Gen4x8 or 2x Gen4x4	1x Gen4x8 or 2x Gen4x4
I/O	Max. Single-Ended HDIO		252	252	252	210	210	294	294	336	336
	Max. Single-Ended HPIO		52	52	52	52	52	52	52	104	104
	Max. Single-Ended XP5IO		0	0	0	0	0	132	132	132	132
	GTH Transceivers (16.3 Gb/s) ¹		0	0	0	4	4	4	4	8	8
Security	Platform Management Controller		✓	✓	✓	✓	✓	✓	✓	✓	✓
Speed Grades	Extended		-1, -2								
	Industrial		-1, -2, -1L								
Package	Dimensions (mm)	Ball Pitch (mm)	HDIO, HPIO, XP5IO, GTH								
CMVA361	10x10	0.5	168, 52, 0, 0	168, 52, 0, 0	168, 52, 0, 0						
CMVA529	12x12	0.5	252, 52, 0, 0	252, 52, 0, 0	252, 52, 0, 0						
CMVB529	12x12	0.5						100, 52, 132, 4	100, 52, 132, 4		
CMVE529	12x12	0.5				188, 52, 0, 4	188, 52, 0, 4				
SBVC529	19x19	0.8						120, 52, 132, 0	120, 52, 132, 0		
SBVD529	19x19	0.8				210, 52, 0, 4	210, 52, 0, 4				
SBVB625	21x21	0.8	252, 52, 0, 0	252, 52, 0, 0	252, 52, 0, 0	188, 52, 0, 0	188, 52, 0, 0				
SBVF784	23x23	0.8						224, 52, 132, 4	224, 52, 132, 4	224, 52, 132, 4	224, 52, 132, 4
SBVG784	23x23	0.8						126, 52, 132, 4	126, 52, 132, 4	126, 104, 132, 8	126, 104, 132, 8
SBVF900 ⁽²⁾	25x25	0.8								78, 104, 132, 8	78, 104, 132, 8
SBVA1024	27x27	0.8						294, 52, 132, 4	294, 52, 132, 4	294, 104, 132, 8	294, 104, 132, 8
NBVA1089	31x31	0.92								336, 104, 132, 8	336, 104, 132, 8

1. GTH data rates are package dependent:
- Maximum 12.5 Gb/s in CMVB529
- Maximum 16.3 Gb/s in SBVF784, SBVG784, SBVA1024, and NBVA1089

2. Footprint compatible with 2KU30P, 2KU40P, and 2KU50P.

Important: Verify all data in this document with the device data sheets.

AMD Artix™ UltraScale+™ FPGAs – Resources & Packaging

Device Name			AU7P	AU10P	AU15P	AU20P	AU25P
System Logic Cells (K)			82	96	170	238	308
CLB Flip-Flops (K)			75	88	156	218	282
CLB LUTs (K)			37	44	78	109	141
Dist. RAM (Mb)			1.1	1.0	2.5	3.2	4.7
Total Block RAM (Mb)			3.8	3.5	5.1	7.0	10.5
36K Block RAM Blocks			108	100	144	200	300
UltraRAM (Mb)			–	–	–	–	–
Clock Management Tiles (CMTs)			2	3	3	4	4
DSP Slices			216	400	576	900	1,200
PCI Express®			1x Gen3x4	1x Gen4x8 ⁽¹⁾	1x Gen4x8 ⁽¹⁾	1x Gen3x8	1x Gen3x8
AMS - System Monitor			1	1	1	1	1
Max. Single-Ended HD I/Os			144	72	72	72	96
Max. Single-Ended HP I/Os			104	156	156	156	208
GTH Transceivers ⁽²⁾			4	12	12	–	–
GTY Transceivers ⁽²⁾			–	–	–	12	12
Extended			-1 -2				
Industrial			-1 -2 -1L				
Package	Dim. (mm)	Ball Pitch (mm)	HDIO, HPIO, GTH, GTY				
FCVA289	9x9	0.5	72, 58, 4, 0				
UBVA368	11.5x9.5	0.5		24, 104, 8, 0	24, 104, 8, 0		
SBVB484	19x19	0.8		48, 156, 12, 0	48, 156, 12, 0		
SBVC484	19x19	0.8	144, 104, 4, 0				
SFVB784	23x23	0.8				72, 156, 0, 12	96, 208, 0, 12
FFVB676	27x27	1.0		72, 156, 12, 0	72, 156, 12, 0	72, 156, 0, 12	72, 208, 0, 12

1. PCIe Gen4 is available in AU10P and AU15P in the FFVB676 package. AU10P and AU15P in other packages support Gen3x8.

2. GTH and GTY data rates are package dependent:

- Maximum 12.5 Gb/s in FCVA289, UBVA368, SBVB484, SBVC484, SFVB784
- Maximum 16.3 Gb/s in FFVB676.

Important: Verify all data in this document with the device data sheets.

AMD Kintex™ UltraScale+™ FPGAs – Resources

	Device Name	KU3P	KU5P	KU9P	KU11P	KU13P	KU15P	KU19P
Logic	System Logic Cells (K)	356	475	600	653	747	1,143	1,843
	CLB Flip-Flops (K)	325	434	548	597	683	1,045	1,685
	CLB LUTs (K)	163	217	274	299	341	523	842
Memory	Max. Distributed RAM (Mb)	4.7	6.1	8.8	9.1	11.3	9.8	11.6
	Total Block RAM (Mb)	12.7	16.9	32.1	21.1	26.2	34.6	60.8
	UltraRAM (Mb)	13.5	18.0	0	22.5	31.5	36.0	81.0
Clocking	Clock Mgmt Tiles (CMTs)	4	4	4	8	4	11	9
Integrated IP	DSP Slices	1,368	1,824	2,520	2,928	3,528	1,968	1,080
	PCIe4 (PCIe® Gen3 x16)	1	1	0	4	0	5	0
	PCIe4C (PCIe® Gen3 x16 / Gen4 x8)	0	0	0	0	0	0	3
	150G Interlaken	0	0	0	1	0	4	0
	100G Ethernet w/ KR4 RS-FEC	0	1	0	2	0	4	1
I/O	Max. Single-Ended HD I/Os	96	96	96	96	96	96	72
	Max. Single-Ended HP I/Os	208	208	208	416	208	572	468
	GTH 16.3 Gb/s Transceivers	0	0	28	32	28	44	0
	GTY 32.75 Gb/s Transceivers	16	16	0	20	0	32	32
Speed Grades	Extended ⁽¹⁾	-1 -2 -2L -3	-1 -2 -2L -3	-1 -2 -2L -3	-1 -2 -2L -3	-1 -2 -2L -3	-1 -2 -2L -3	-1 -2 -2L -3
	Industrial	-1 -1L -2	-1 -1L -2	-1 -1L -2	-1 -1L -2	-1 -1L -2	-1 -1L -2	-1 -1L -2

1. -2LE (Tj = 0°C to 110°C). For more details, see the Ordering Information section in DS890, UltraScale Architecture and Product Overview.

Important: Verify all data in this document with the device data sheets.

AMD Kintex™ UltraScale+™ FPGAs – Packaging

Footprint compatible with 20 nm UltraScale Devices with same footprint identifier	Device Name		KU3P	KU5P	KU9P	KU11P	KU13P	KU15P	KU19P
	Package ^(1, 2)	Dimensions (mm)	HD I/O, HP I/O, GTH 16.3 Gb/s, GTY 32.75 Gb/s						
	SFVB784 ⁽³⁾	23x23 ⁽⁴⁾	96, 208, 0, 16	96, 208, 0, 16					
	FFVA676 ⁽³⁾	27x27	48, 208, 0, 16	48, 208, 0, 16					
	FFVB676	27x27	72, 208, 0, 16	72, 208, 0, 16					
	FFVD900 ⁽³⁾	31x31	96, 208, 0, 16	96, 208, 0, 16		96, 312, 16, 0			
	FFVE900	31x31			96, 208, 28, 0		96, 208, 28, 0		
	FFVA1156 ⁽³⁾	35x35				48, 416, 20, 8		48, 468, 20, 8	
	FFVE1517	40x40				96, 416, 32, 20		96, 416, 32, 24	
	FFVA1760	42.5x42.5						96, 416, 44, 32	
	FFVE1760	42.5x42.5						96, 572, 32, 24	
	FFVJ1760	42.5x42.5							72, 468, 0, 32
	FFVB2104	47.5x47.5							72, 468, 0, 32

1. Maximum achievable performance is device and package dependent; consult the associated data sheet for details.
2. For full part number details, see the Ordering Information section in DS890, *UltraScale Architecture and Product Overview*.
3. GTY transceiver line rates are package limited: B784 to 12.5 Gb/s; A676, D900, and A1156 to 16.3 Gb/s. Refer to data sheet for details.
4. The B784 package is only offered in 0.8 mm ball pitch. All other packages are 1.0 mm ball pitch.

AMD Kintex™ UltraScale+™ Gen 2 FPGAs Resources & Packaging

	Device Name		2KU030P	2KU040P	2KU050P
Logic	System Logic Cells (K)		328	410	491
	CLB Flip-Flops (K)		300	374	449
	CLB LUTs (K)		150	187	225
Memory	Max. Distributed RAM (Mb)		4.1	5.1	6.2
	Total Block RAM (Mb)		11.8	14.8	17.7
	36K Block RAM		336	420	504
	Total UltraRAM (Mb)		18.0	22.5	27.0
	288K UltraRAM		64	80	96
	Integrated Memory Controller		4	6	6
Clocking	Clock Mgmt Tiles (CMTs)		4	6	6
Integrated IP	DSP Slices		1,248	1,560	1,872
	PCIE4CE (up to Gen4 x8)		2	2	3
	100G Ethernet w/RS-FEC		2	2	2
I/O	Max. Single-Ended HDIO		78	78	120
	Max. Single-Ended HPiO		0	0	0
	Max. Single-Ended XP5iO		264	396	396
	GTy Transceivers (32.75 Gb/s)		16	16	24
Security	Platform Management Controller		✓	✓	✓
Speed Grades	Extended		-1, -2, -3, -2L		
	Industrial		-1, -2, -1L		
Package	Dimensions (mm)	Ball Pitch (mm)	HDIO, HPiO, XP5iO, GTy		
SFVF900 ⁽¹⁾	25x25	0.8	78, 0, 198, 12	78, 0, 198, 12	78, 0, 198, 12
SSVA1440	31x31	0.8	78, 0, 264, 16	78, 0, 396, 16	120, 0, 396, 24

1. Footprint compatible with SU150P and SU200P.

AMD Virtex™ UltraScale+™ FPGAs – Resources

Important: Verify all data in this document with the device data sheets.

Device Name	Foundation							58G PAM4		
	VU3P	VU5P	VU7P	VU9P	VU11P	VU13P	VU19P	VU23P	VU27P	VU29P
System Logic Cells (K)	862	1,314	1,724	2,586	2,835	3,780	8,938	2,252	2,835	3,780
CLB Flip-Flops (K)	788	1,201	1,576	2,364	2,592	3,456	8,172	2,059	2,592	3,456
CLB LUTs (K)	394	601	788	1,182	1,296	1,728	4,086	1,030	1,296	1,728
Max. Dist. RAM (Mb)	12.0	18.3	24.1	36.1	36.2	48.3	58.4	14.2	36.2	48.3
Total Block RAM (Mb)	25.3	36.0	50.6	75.9	70.9	94.5	75.9	74.3	70.9	94.5
UltraRAM (Mb)	90.0	132.2	180.0	270.0	270.0	360.0	90.0	99.0	270.0	360.0
DSP Slices	2,280	3,474	4,560	6,840	9,216	12,288	3,840	1,320	9,216	12,288
Peak INT8 DSP (TOP/s)	7.1	10.8	14.2	21.3	28.7	38.3	10.4	4.1	28.7	38.3
PCIe® Gen3 x16	2	4	4	6	3	4	0	0	1	1
PCIe Gen3 x16/Gen4 x8 ⁽¹⁾	–	–	–	–	–	–	8	4	–	–
150G Interlaken	3	4	6	9	6	8	0	0	8	8
100G Ethernet w/ KR4 RS-FEC	3	4	6	9	9	12	0	2	15	15
Max. Single-Ended HP I/Os	520	832	832	832	624	832	1,976	572	676	676
Max. Single-Ended HD I/Os	0	0	0	0	0	0	96	72	0	0
GTY 32.75 Gb/s Transceivers	40	80	80	120	96	128	80	34	32	32
GTM 58 Gb/s PAM4 Transceivers	–	–	–	–	–	–	–	4	48	48
100G / 50G KP4 FEC	–	–	–	–	–	–	–	2 / 4	24 / 48	24 / 48
Extended ⁽²⁾	-1 -2 -2L -3	-1 -2 -2L -3	-1 -2 -2L -3	-1 -2 -2L -3	-1 -2 -2L -3	-1 -2 -2L -3	-1 -2	-1 -2 -2L -3	-1 -2 -2L -3	-1 -2 -2L -3
Industrial	-1 -2	-1 -2	-1 -2	-1 -2	-1 -2	-1 -2	–	-1, -2	-1 -2	-1 -2

1. This block operates in compatibility mode for 16.0 GT/s (Gen4) operation. See PG213, *UltraScale+ Devices Integrated Block for PCI Express v1.2 Product Guide*.

2. -2LE (Tj = 0°C to 110°C). See Ordering Information in DS890, *UltraScale Architecture and Product Overview*.

AMD Virtex™ UltraScale+™ FPGAs – Packaging

Important: Verify all data in this document with the device data sheets.

		Foundation							58G PAM4		
Device		VU3P	VU5P	VU7P	VU9P	VU11P	VU13P	VU19P	VU23P	VU27P	VU29P
Footprint ^(1,2,3)	Dim. (mm)	HPIO, GTY							HPIO, HDIO, GTY	HPIO, HDIO, GTY, GTM	
Footprint compatible with 20nm UltraScale Devices with same footprint identifier	A1365 ⁽²⁾	35x35							364, 0, 34 ⁽⁶⁾ , 4		
	C1517	40x40	520, 40								
	J1760	42.5x42.5							572, 72, 34, 4		
	F1924 ⁽⁴⁾	45x45				624, 64					
	A2104	47.5x47.5	832, 52	832, 52	832, 52						
		52.5x52.5 ⁽⁵⁾				832, 52					
	B2104	47.5x47.5	702, 76	702, 76	702, 76	572, 76					
		52.5x52.5 ⁽⁵⁾				702, 76					
	C2104	47.5x47.5	416, 80	416, 80	416, 104	416, 96					
		52.5x52.5 ⁽⁵⁾				416, 104					
	D2104	47.5x47.5			676, 76	572, 76					
		52.5x52.5 ⁽⁵⁾				676, 76			676, 0, 16, 30	676, 0, 16, 30	
	H2104	47.5x47.5									
	A2577	52.5x52.5			448, 120	448, 96	448, 128			448, 0, 32, 48	448, 0, 32, 48
	A3824	65x65						1976, 96, 48			
	B3824	65x65						1664, 96, 80			

1. For full part number details, see DS890, *UltraScale Architecture and Product Overview*.
2. All packages are 1.0 mm ball pitch, with the exception of A1365, which is 0.92 mm.
3. Consult UG583, *UltraScale Architecture PCB Design User Guide* for specific migration details.
4. The GTY transceiver line rate in the F1924 footprint is package limited to 16.3 Gb/s. Refer to data sheet for details.
5. These 52.5x52.5 mm packages have the same PCB ball footprint as the 47.5x47.5 mm packages and are footprint compatible.
6. GTYs in quads 224-230 and 232 are limited to 16 Gb/s.

AMD Virtex™ UltraScale+™ HBM FPGAs – Resources & Packaging

		HBM (4GB)	HBM (8GB)			HBM (16GB)		
Device Name		VU31P	VU33P	VU35P	VU37P	VU45P	VU47P	VU57P
System Logic Cells (K)		962	962	1,907	2,852	1,907	2,852	2,852
CLB Flip-Flops (K)		879	879	1,743	2,607	1,743	2,607	2,607
CLB LUTs (K)		440	440	872	1,304	872	1,304	1,304
Max. Dist. RAM (Mb)		12.5	12.5	24.6	36.7	24.6	36.7	36.7
Total Block RAM (Mb)		23.6	23.6	47.3	70.9	47.3	70.9	70.9
UltraRAM (Mb)		90.0	90.0	180.0	270.0	180.0	270.0	270.0
HBM DRAM (GB)		4	8	8	8	16	16	16
HBM AXI Interfaces		16	32	32	32	32	32	32
Clock Mgmt Tiles (CMTs)		4	4	8	12	8	12	12
DSP Slices		2,880	2,880	5,952	9,024	5,952	9,024	9,024
Peak INT8 DSP (TOP/s)		8.9	8.9	18.6	28.1	18.6	28.1	28.1
PCIe® Gen3 x16		0	0	1	2	1	2	0
PCIe Gen3 x16/Gen4 x8 ⁽¹⁾		4	4	4	4	4	4	4
150G Interlaken		0	0	2	4	2	4	4
100G Ethernet w/ KR4 RS-FEC		2	2	5	8	5	8	10
Max. Single-Ended HPIOs		208	208	416	624	416	624	624
GTY 32.75 Gb/s Transceivers		32	32	64	96	64	96	32
GTM 58 Gb/s PAM4 Transceivers		–	–	–	–	–	–	32
100G / 50G KP4 FEC		–	–	–	–	–	–	16/32
Extended ⁽²⁾		-1 -2 -2L -3	-1 -2 -2L -3	-1 -2 -2L -3	-1 -2 -2L -3	-1 -2 -2L -3	-1 -2 -2L -3	-1 -2 -2L -3
Industrial		–	–	–	–	–	–	–
Footprint ^(3, 4, 5, 6)	Dim. (mm)	HPIO, GTY						HPIO, GTY, GTM
H1924	45x45	208, 32						
H2104	47.5x47.5		208, 32	416, 64		416, 64		
H2892	55x55			416, 64	624, 96	416, 64	624, 96	
K2892	55x55							624, 32, 32

1. This block operates in compatibility mode for 16.0GT/s (Gen4) operation. See PG213, *UltraScale+ Devices Integrated Block for PCI Express v1.2 Product Guide*.

2. -2LE (Tj = 0°C to 110°C). See Ordering Information in DS890, *UltraScale Architecture and Product Overview*.

3. For full part number details, see DS890, *UltraScale Architecture and Product Overview*.

4. All packages are 1.0 mm ball pitch.

5. Consult UG583, *UltraScale Architecture PCB Design User Guide* for specific migration details.

6. Footprint compatible with 20nm UltraScale Devices with same footprint identifier.

Important: Verify all data in this document with the device data sheets.



together we advance_

9

AMD UltraScale™ Architecture Migration Table

Legend


■ Device

— Migration Path

Footprint	Artix™ UltraScale+				Kintex™ UltraScale™							Kintex UltraScale+					Virtex™ UltraScale						Virtex UltraScale+								
	AU10P	AU15P	AU20P	AU25P	KU025	KU035	KU040	KU060	KU085	KU095	KU115	KU3P	KU5P	KU11P	KU15P	KU19P	VU065	VU080	VU095	VU125	VU160	VU190	VU3P	VU5P	VU7P	VU9P	VU11P	VU13P	VU27P	VU29P	
B784			■	■								■	■																		
A676						■	■					■	■																		
B676	■	■	■	■								■	■																		
A1156					■	■	■	■		■				■	■																
C1517										■							■	■	■				■								
D1517											■							■	■	■	■										
B1760									■	■	■							■	■	■	■										
F1924									■		■																■				
A2104											■							■	■	■	■			■	■	■		■			
B2104										■	■					■		■	■	■	■	■		■	■	■	■	■	■		
C2104																			■	■	■	■		■	■	■	■	■			
A2577																						■				■	■	■	■	■	■

Footprint	Spartan™ UltraScale+							Kintex UltraScale+ Gen 2				
	SU10P	SU25P	SU35P	SU45P	SU60P	SU65P	SU100P	SU150P	SU200P	2KU030P	2KU040P	2KU050P
F900								■	■	■	■	■

AMD UltraScale+™ Device Ordering Information



E = Extended (Tj = 0°C to +110°C⁽³⁾)
I = Industrial (Tj = -40°C to +100°C)

- Notes:
- 1. In the AU7P device, the FCVA289 package is a chipscale package with 0.5 mm ball pitch and molded lid.
 - 2. This character is only present in AMD Kintex™ UltraScale+™ Gen 2 FPGAs.
 - 3. For more details on 110°C operation, see the Ordering Information section in DS890, *UltraScale Architecture and Product Overview*



Disclaimer and Attribution

DISCLAIMER: The information contained herein is for informational purposes only and is subject to change without notice. While every precaution has been taken in the preparation of this document, it may contain technical inaccuracies, omissions and typographical errors, and AMD is under no obligation to update or otherwise correct this information. Advanced Micro Devices, Inc. makes no representations or warranties with respect to the accuracy or completeness of the contents of this document, and assumes no liability of any kind, including the implied warranties of noninfringement, merchantability or fitness for particular purposes, with respect to the operation or use of AMD hardware, software or other products described herein. No license, including implied or arising by estoppel, to any intellectual property rights is granted by this document. Terms and limitations applicable to the purchase or use of AMD products are as set forth in a signed agreement between the parties or in AMD's Standard Terms and Conditions of Sale. GD-18u.

© Copyright 2015–2026 Advanced Micro Devices, Inc. AMD, the AMD Arrow logo, Artix, Kintex, Spartan, Virtex, UltraScale, UltraScale+, and combinations thereof are trademarks of Advanced Micro Devices, Inc. AMBA, AMBA Designer, Arm, ARM1176JZ-S, CoreSight, Cortex, PrimeCell, Mali, and MPCore are trademarks of Arm Limited in the EU and other countries. PCI, PCIe, and PCI Express are trademarks of PCI-SIG and used under license. Other product names used in this publication are for identification purposes only and may be trademarks of their respective companies. All other trademarks are the property of their respective owners.