

Datasheet

LL01OS-EES2030L06

Available Distribution



20°x30°

Dimensions

Part Number	Diameter	Height
LL01OS-EES2030L06	Ø16	9.3


*All dimensions are in millimeters.

LED



CREE
J2835

Packaging Details (SPQ)



Recommend Applications



Landscape



Architectural



Waterproof

General Information



PMMA
70°C
-40°C



400nm~900nm
> 90%




- Lens Material PMMA
- Lens Color Transparent
- Operating Temperature -40°C~+70°C
- Light Transmission Rate 400nm~900nm > 90%
- ☑ If necessary, Clean lenses with mild soap, water and soft cloth.
- ⚠ Never use any commercial cleaning solvents on lenses, like alcohol.
- 🧤 Please handle or install lenses with wearing gloves, skin oils may damage lens or its optical characteristic.

Mechanical Specification

*All dimensions are in millimeters.

Lens Dimension



LL010S-EES2030L06




Assembly Instruction

Part No LL010S-EES2030L06

Fixing Method



Photometric Distribution



Details by LED

Part No	Accessories	LED Package Size	LED
LL010S-EES2030L06	-	2835	 CREE J2835

LED	Part No	FWHM	cd / lm	IES
 CREE J2835	LL010S-EES2030L06	20°×36°	2.3	↓

Product Nomenclature

Ledlink Led Type Lens Angle
LL 01 OS- EES 2030 L06
Lens Dot Number Serial Number Type of Material

Ledlink Optics, Inc

Taiwan HQ

15F, No.655, Bannan Rd., Chung-Ho Dist.,
New Taipei City, Taiwan 235

Ledlink Optics (Dongguan) Co., Ltd

Dongguan Factory

No.6, Gaoxin Road, Tiankeng, Hengli Town, Dongguan City,
Guangdong Province, China 523478

Ledlink Optics (Yangzhou) Co., Ltd

Yangzhou Factory

No.180, LinJiang Rd., YangZhou City, Jiangsu Province, China 225009

www.ledlink-optics.com

service@ledlink-optics.com

