

A

B

C

D




E

1

2

3

4



Aufschrift


© 1205.0101

10 (61)/250 ~



Herstelljahr/-woche: JJWW in Anlehnung an DIN EN 60062  
auf Verpackung: 760385004

Umschalter 2 - polig  
fuer Gerate der Kl.II geeignet



|                                         |   |                               |                    |                        |               |              |       |                                             |              |  |               |                 |                                 |                |
|-----------------------------------------|---|-------------------------------|--------------------|------------------------|---------------|--------------|-------|---------------------------------------------|--------------|--|---------------|-----------------|---------------------------------|----------------|
| -                                       |   | -                             |                    |                        |               | -            |       |                                             | 1205.0101-xx |  |               |                 |                                 |                |
| Figure                                  |   | Type                          |                    |                        |               | Customer No. |       |                                             | Art.No.-PI   |  |               |                 |                                 |                |
| General tolerances                      |   |                               |                    |                        |               |              |       |                                             | Sheet<br>01  |  |               | Ident.<br><br>K | Document number<br><br>12050101 | Index<br><br>k |
| All dimensions<br>are in<br>millimetres |   | Shape and<br>location<br><br> | Angle<br><br>± 2 ° | Edge tolerance<br><br> |               | Length       | Radii |                                             |              |  |               |                 |                                 |                |
|                                         |   |                               |                    |                        | 0-6           | ± 0.3        | ±     |                                             |              |  |               |                 |                                 |                |
|                                         |   |                               |                    |                        | >6-15         | ±            | ±     |                                             |              |  |               |                 |                                 |                |
|                                         |   |                               |                    |                        | >15-30        | ±            | ±     |                                             |              |  |               |                 |                                 |                |
|                                         |   |                               |                    |                        | >30-70        | ±            | ±     |                                             |              |  |               |                 |                                 |                |
|                                         |   |                               |                    |                        | >70-120       | ±            |       |                                             |              |  |               |                 |                                 |                |
| >120                                    | ± |                               |                    |                        |               |              |       |                                             |              |  |               |                 |                                 |                |
|                                         |   |                               |                    |                        | Format<br>DIN | Projection   | Scale | appliance switch                            |              |  |               |                 |                                 |                |
|                                         |   |                               |                    |                        | A4            |              | 1:1   |                                             |              |  |               |                 |                                 |                |
| k                                       |   | 124781                        |                    | 2019-05-24             |               | LAUFERU      |       | System<br>NX V11.0                          |              |  | <br>MARQUARDT |                 |                                 |                |
| j                                       |   | 70275                         |                    | 2010-09-08             |               | KMI          |       |                                             |              |  |               |                 |                                 |                |
| i                                       |   | 27874                         |                    | 2001-08-01             |               | WJ           |       |                                             |              |  |               |                 |                                 |                |
| h                                       |   | 31463                         |                    | 2001-03-28             |               | HIN          |       |                                             |              |  |               |                 |                                 |                |
| Index                                   |   | MEC-No.                       |                    | Date (YYYY-MM-DD)      |               | Edited by    |       | Replacement of<br><br>Zg.gl.Nr.v.01.07.1976 |              |  |               |                 |                                 |                |