





A	1	2	3	4
	recommended cut-out for snap-in fixing (edge opposite to snap-in direction)	wall thickness	length of cut-out	width of cut-out
		0.75 to 1.25	19.2 -0.1	6.8+0.1
		1.25 to 2	19.4 -0.1	6.8+0.1
		2 to 3	19.8 -0.1	6.8+0.1
B				
C				
D	Marking Ⓜ 1901. 4(1)/250~5E4 6(2)/250~ T80/55   Code of manufacture: place/year/week			
E				

-		-									1901.1104-XX				
Figure		Type						Customer Part No.			Art.No.-PI				
Shape and location 		Angle $\pm 2^\circ$ Edge tolerance 		Length			Radii			Sheet 01			Ident. K	Document number 19011104	Index e
				0-6	± 0.2		$\pm$		± 0.2	Format DIN A4	Projection 	Scale 1:1			
				>6-15	± 0.4		$\pm$		$\pm$						
				>15-30	± 0.4		$\pm$		$\pm$						
					$\pm$		$\pm$		$\pm$						
					$\pm$		$\pm$		$\pm$						
					$\pm$		$\pm$		$\pm$						
					$\pm$		$\pm$		$\pm$						
					$\pm$		$\pm$		$\pm$						
						All dimensions are in millimetres									Appliance Switch
e	141238	2022-11-17		MOHITEN											
d	102884	2016-08-02		HHE		System NX V1899									
c	43248	2005-05-12		hhe		Replacement of									
b	25497	1997-11-10		SIG		Zg.gl.Nr.v.07.06.1994									
Index	MEC-No.	Date (YYYY-MM-DD)		Edited by					 MARQUARDT						