

# BGA Heat Sink (High Aspect Ratio Ext.) Standard Pin Fin



ATS Part#: **ATS041041013-PF027**  
Description: 40.60 x 40.60 x 13.30 mm BGA Heat Sink (High Aspect Ratio Ext.) Standard Pin Fin



Heat Sink Type: Standard Pin Fin  
Heat Sink Attachment: N/A  
Equivalent Part Number: N/A

\*Image above is for illustration purpose only.

## Features & Benefits

- Excellent balance of low cost and high performance in an aluminum heat sink.
- Designed for semiconductor devices with omni-directional airflow requirements.
- 11 x 11 pin array
- Available with a variety of thermal adhesive tape options. Contact [sales@qats.com](mailto:sales@qats.com) for product configurations.

## Thermal Performance

AIR VELOCITY		@200 LFM 1.0 M/S	@300 LFM 1.5 M/S	@400 LFM 2.0 M/S	@500 LFM 2.5 M/S	@600 LFM 3.0 M/S	@700 LFM 3.5 M/S	@800 LFM 4.0 M/S
THERMAL RESISTANCE	Unducted Flow	3.3 °C/W	N/A °C/W					
	Ducted Flow	0	N/A	N/A	N/A	N/A	N/A	N/A

## Product Detail

Schematic Image	Dimension A	Dimension B	Dimension C	Dimension D	TIM	Finish
	40.60 mm	40.60 mm	13.30 mm	N/A mm	NO TIM	Black Anodized
<b>Notes:</b>						
<ul style="list-style-type: none"><li>Dimension A and B refer to component size.</li><li>Dimension C is the heat sink height from the bottom of the base to the top of the fin field.</li><li>Thermal performance data are provided for reference only. Actual performance may vary by application.</li><li>ATS reserves the right to update or change its products without notice to improve the design or performance.</li><li>ATS certifies that this heat sink assembly is RoHS-6 and REACH compliant.</li><li>Contact ATS to learn about custom options available.</li></ul>						

\*Image above is for illustration purpose only.

For more information, to find a distributor or to place an order, please contact us at  
781-769-2800 (North America), [sales@qats.com](mailto:sales@qats.com) or [www.qats.com](http://www.qats.com).

© 2013 Advanced Thermal Solutions, Inc. | 89-27 Access Road | Norwood MA | 02062 | USA