


COH-1706

Features

- High thermal conductivity
- Softness relieves mechanical stress
- Good handling makes easy apply to heating elements
- Wide operating temperature range

Characteristic item	COH-1706	COH-1016LVC
Thermal conductivity (W/m·K)	Our tests Hot Wire Method	3.8 1.7
Hardness (Asker C)	27	60
Appearance	Gray	White
Tensile strength (MPa)	0.24	0.21
Volume resistivity (Ω·cm)	4.8×10^{12}	6.1×10^{13}
Dielectric breakdown strength (kV/mm)	18.6	18.8
Elongation (%)	75	205
Compression set (%)	84	15
Flame retardance (UL94)	V-0 (Equivalent)	V-0 (Equivalent)
Temperature range (°C)	-40~150	-40~150



Applications

- LED, Backlight module
- Engine control unit for hybrid vehicle
- Battery for electric vehicle
- CPU



Notes

● To the best of our knowledge, the information and statements on this brochure are believed to be true and reliable; however, the PRODUCTS described herein are sold WITHOUT ANY GUARANTEE OR WARRANTY INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR PARTICULAR PURPOSES since the application and conditions of each use vary and change, and are beyond the control of manufacturer and seller(s). The customers and users of the PRODUCTS shall assume the responsibility for determining the suitability of the PRODUCTS based on their tests and for whatever risks and liability associated with the use of the PRODUCTS. NEITHER MANUFACTURER NOR SELLER(S) SHALL BE LIABLE EITHER IN TORT OR CONTRACT OR ANY OTHER CAUSE FOR ANY KIND OF LOSS OF PROFITS OR DAMAGE, INCIDENTAL, DIRECT, OR CONSEQUENTIAL, ARISING OUT OF OR IN CONNECTION WITH THE USE OF OR THE INABILITY TO USE THE PRODUCTS.

- It is highly recommended that users would not use the products shown in the brochure in medical applications, particularly for implantation use.
- The users shall be aware of the fact that silicone oil could bleed from silicone-gel. It is therefore that any user should be responsible for conducting reliability test in advance before delivering the products in the market.
- The silicone-gel contains low molecular siloxane, which could be volatile.

* The copyright of this brochure belongs to Taica Corporation. It is prohibited to copy and to use the contents of this brochure without our prior consent.



<http://www.taica.co.jp/english/>

Head Office / Takanawa Sengakuji-ekimae Bldg.3F, 2-18-10 Takanawa, Minato-ku, Tokyo 108-0074 JAPAN

Tel +81-3-6367-6624 Fax +81-3-6367-6620

Taica, **αGEL** and the visual image of falling eggs are trademarks of Taica Corporation, registered in Japan and / or other countries.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Taica:

[COH-1706LVC t0.5](#) [COH-1706LVC t1.0](#) [COH-1706LVC t2.0](#) [COH-1706LVC t3.0](#) [COH-1706LVC \(1NT\) t0.5](#) [COH-1706LVC \(1NT\) t1.0](#) [COH-1706LVC \(1NT\) t2.0](#) [COH-1706LVC \(1NT\) t3.0](#) [COH-1706 \(1NT\) t3.0](#) [COH-1706 t0.5](#) [COH-1706 t3.0](#) [COH-1706 \(1NT\) t2.0](#) [COH-1706 t1.0](#) [COH-1706 \(1NT\) t1.0](#) [COH-1706 t2.0](#) [COH-1706 \(1NT\) t0.5](#)